
STREIT The FASTEST Way to Terminate MC into a Bo



NEW RACO[®] STRE






LISTED Outlet Box E195978

Rolled steel edges eliminate the need for plastic bushings, except for AC Cable

Find your local Sales Agent here to request samples and pricing.



RACO is proud to introduce STAB-IT[®], a new line of boxes with **built-in cable connectors** for flexible armored cable. <u>The patent pending connec</u>tors are designed to lock the cable in place quickly and easily to increase production on every job.

Application

• For any job where flexible armored cable is being used (see selection chart below)

Product Features

- Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
- Accepts cable sizes from 14/2 up to 10/3 for most cable types
- 3 TIMES FASTER than traditional connectors
- Available in 4" sq. 2-1/8" deep boxes with 1 or 2 STAB-IT $^{\mbox{\tiny (B)}}$ connectors
- Available in 2-1/2" deep switch boxes for new work, old work, and stud mounting
- 4" Square Boxes available with built-in cable management clip to offer first means of support
- UL listed for use without a plastic bushing (except for AC Cable)
- Each STAB-IT[®] connector accommodates two cables
- 4" Square Boxes available with "H" or "M" brackets for stud mounting
- Pre-installed 8" solid #12 pigtail for faster installation
- Suitable for use without a bonding jumper in circuits up to 600 volts
- Patented design allows cable to easily be removed, and allows connector to be reused
- UL listed
- Patent Pending
- Designed in USA

CABLE TYPES AND RANGES FOR STAB-IT® CLAMP

CABLE TYPE	CABLE RANGE				
AC STEEL & ALUMINUM	14-2, 14-3, 14-4, 12-2, 12-3, 12-4, 10-2, 10-3				
HCF AC STEEL	14-2, 14-3, 14-4, 12-2, 12-3, 10-2, 10-3				
HCF AC ALUMINUM	12-2, 12-3, 12-4, 10-2, 10-3				
MC STEEL & ALUMINUM	14-2, 14-3, 14-4, 12-2, 12-3, 12-4, 10-2, 10-3				
MCI-A STEEL & ALUMINUM	14-2, 14-3, 14-4, 12-2, 12-3, 12-4, 10-2, 10-3				
HCF MCI-A STEEL	12-2, 12-3, 10-2				
HCF MCI-A ALUMINUM	14-2, 14-3, 14-4, 12-2, 12-3, 12-4, 10-2, 10-3				
3/8 TRADE SIZE FLEX. RWFMC CONDUIT STEEL & ALUMINUM Anti Short Bushings Required					

CABLE RANGE .400" DIA. MIN. TO .605" DIA. MAX.

Cable Armor must comply with NEC 250.96

To remove cable unscrew clamp from the box then pull clamp off cable.


To install more cables use any of the RACO® REDI-LOC® connectors.



R Y



Ideal for PREFAB Applications



Gangable



-11



NEW! BUILT-IN FIRST MEANS OF SUPPORT

232SCM











523S



244SCM



244MS

244MSCM



248S



248HS



248MS

232SCM





5



NEW!

a **NEW!** NEW! 623S

624S

CAT.	DESCRIPTION	CU. IN.	CTN.	CTN. DIMS.	KNOCKOUTS		UPC-A
NO.		CAP.	QTY.	CIN. DIMS.	SIDES	BOTTOM	
232\$	4" Sq., 2-1/8" Dp., (1) STAB-IT® Connector, w/Pigtail	30.3	25	18.75L x 7.375W x 8.625H	(6) 1/2", (3) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169500705
232MS	4" Sq., 2-1/8" Dp., (1) STAB-IT Connector, M Bracket, w/Pigtail	30.3	25	20.875L x 8.5W x 8.75H	(6) 1/2", (3) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169500736
232SCM	4" Sq., 2-1/8" Dp., (1) STAB-IT Connector, w/Pigtail and Cable Management Clip	30.3	25	18.75L x 7.375W x 8.625H	(6) 1/2", (3) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169892329
232MSCM	4" Sq., 2-1/8" Dp., (1) STAB-IT Connector, M Brkt, w/Pigtail and Cable Management Clip	30.3	25	20.875L x 8.5W x 8.75H	(6) 1/2", (3) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169922323
244S	4" Sq., 2-1/8" Dp., (2) STAB-IT Connectors on top, w/Pigtail	30.3	25	18.75L x 7.375W x 8.5H	(6) 1/2", (3) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169982440
	4" Sq., 2-1/8" Dp., (2) STAB-IT Connectors on top, w/Pigtail and (2) Cable Management Clips	30.3	25	18.75L x 7.375W x 8.5H	(6) 1/2", (3) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169962442
244MS	4" Sq., 2-1/8" Dp., (2) STAB-IT Connectors on top, M Bracket, w/Pigtail	30.3	25	20.875L x 8W x 8.5H	(6) 1/2", (3) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169992449
3.3.2	4" Sq., 2-1/8" Dp., (2) STAB-IT Connectors on top, M Bracket, w/Pigtail and (2) Cable Management Clips	30.3	25	20.875L x 8W x 8.5H	(6) 1/2", (3) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169972441
248S	4" Sq., 2-1/8" Dp., (2) STAB-IT Connectors, w/Pigtail	30.3	25	19L x 7.75W x 8.75H	(4) 1/2", (2) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169500712
248HS	4" Sq., 2-1/8" Dp., (2) STAB-IT Connectors, H Bracket, w/Pigtail	30.3	25	20.875L x 8.5W x 8.75H	(4) 1/2", (2) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169501122
248MS	4" Sq., 2-1/8" Dp., (2) STAB-IT Connectors, M Bracket, w/Pigtail	30.3	25	20.875L x 8.5W x 8.75H	(4) 1/2", (2) 1/2"-3/4" TKO	(1) 1/2", (1) 1/2"-3/4" TKO	050169500798
518S	3" x 2" x 2-1/2" Dp., Old Work Switch Box (1) STAB-IT Connector, w/Pigtail	12.5	25	12.875L x 8.75W x 5.375H	—	(1) 1/2"	050169500781
523S	3" x 2" x 2-1/2" Dp., Old Wk Switch Bx (1) STAB-IT Cnctr, w/Old Wk Clips, w/Pigtail	12.5	25	11.25L x 8.5W x 8.25H	—	(1) 1/2"	050169500514
524S	3" x 2" x 2-1/2" Dp., Old Wk Switch Bx (1) STAB-IT Cnctr, w/TS Bracket, w/Pigtail	12.5	50	20.0L x 13.5W x 7.25H	—	(1) 1/2"	050169500729
618S 竝	3" x 2" x 3-1/2" Dp., Old Work Switch Box (1) STAB-IT Connector, w/Pigtail	18.0	25	11.125L x 10W x 8.375H	—	(1) 1/2"	050169966181
623S 🗯	$3"$ x $2"$ x $3\mathchar`$ Jp., Old Wk Switch Bx (1) STAB-IT Cnctr, w/Old Wk Clips, w/Pigtail	18.0	25	13.125L x 10W x 8.375H	—	(1) 1/2"	050169966235
624S 竝	3" x 2" x 3-1/2" Dp., Old Wk Switch Bx (1) STAB-IT Cnctr, w/TS Bracket, w/Pigtail	18.0	25	16.125L x 11.25W x 7.625H	—	(1) 1/2"	050169966242

1 STAB-IT[®] connector can accommodate up to 2 cables. 2 STAB-IT[®] connectors can accommodate up to 4 cables

Patent Pending

Traditional vs. STAB-IT[®]



Reduce SKU's With STAB-IT

Manage Fewer Inventory SKU's



STABIT

Traditional Traditional Method 1 Method 2

Increase Productivity With STAB-IT

Cut Down on Installation Time by More Than Half!



Scan to see the time test between traditional methods & STAB-IT

Reduce Work Site Waste With STAB-IT

Fewer SKU's On Site Means Less Trash to Dispose Of

