

**MP300 Submittal Packages**

| Voltage     | HP Range                |                         |                         |                         |                         |
|-------------|-------------------------|-------------------------|-------------------------|-------------------------|-------------------------|
| 200         | 15-60                   | 75-125                  | 150                     | 200-250                 |                         |
| <b>File</b> | <a href="#">DP300S1</a> | <a href="#">DP300S2</a> | <a href="#">DP300S3</a> | <a href="#">DP300S4</a> | ---                     |
| 208         | 15-75                   | 100-150                 | ---                     | 200-250                 | ---                     |
| <b>File</b> | <a href="#">DP300S1</a> | <a href="#">DP300S2</a> | ---                     | <a href="#">DP300S4</a> | ---                     |
| 220-240     | 15-75                   | 100-150                 | 200                     | 250                     | 300                     |
| <b>File</b> | <a href="#">DP300S1</a> | <a href="#">DP300S2</a> | <a href="#">DP300S3</a> | <a href="#">DP300S4</a> | <a href="#">DP300S5</a> |
| 380-415     | 15-125                  | 150-250                 | 300                     | 350-400                 | ---                     |
| <b>File</b> | <a href="#">DP300S1</a> | <a href="#">DP300S2</a> | <a href="#">DP300S3</a> | <a href="#">DP300S4</a> | ---                     |
| 440-480     | 15-150                  | 200-300                 | 350-400                 | 500                     | 600                     |
| <b>File</b> | <a href="#">DP300S1</a> | <a href="#">DP300S2</a> | <a href="#">DP300S3</a> | <a href="#">DP300S4</a> | <a href="#">DP300S5</a> |