

MP420 Submittal Packages

Voltage	HP Range				
200	15-60	75-125	150	200-250	300
File	DP420S1	DP420S2	DP420S3	DP420S4	DP420S5
208	15-75	100-150	- - -	200-250	300
File	DP420S1	DP420S2	- - -	DP420S4	DP420S5
220-240	15-75	100-150	200	250-300	300
File	DP420S1	DP420S2	DP420S3	DP420S4	DP420S5
380-415	15-125	150-250	300	400	500-600
File	DP420S1	DP420S2	DP420S3	DP420S4	DP420S5
440-480	15-150	200-300	350-400	500	600-700
File	DP420S1	DP420S2	DP420S3	DP420S4	DP420S5