

MP420 with ATS Submittal Packages

Voltage	HP Range				
200	15-60	75-125	150	200-250	300
File	DP420TS1	DP420TS2	DP420TS3	DP420TS4	DP420TS5
208	15-75	100-150	- - -	200-250	300
File	DP420TS1	DP420TS2	- - -	DP420TS4	DP420TS5
220-240	15-75	100-150	200	250	300
File	DP420TS1	DP420TS2	DP420TS3	DP420TS4	DP420TS5
380-415	15-125	150-250	300	350-400	500-600
File	DP420TS1	DP420TS2	DP420TS3	DP420TS4	DP420TS5
440-480	15-150	200-300	350-400	500	600-700
File	DP420TS1	DP420TS2	DP420TS3	DP420TS4	DP420TS5