

MP435 Submittal Packages

Voltage	HP Range				
200	15-60	75	100-150	200-250	300
File	DP435S1	DP435S2	DP435S3	DP435S4	DP435S5
208	15-75	100	125-150	200-250	300
File	DP435S1	DP435S2	DP435S3	DP435S4	DP435S5
220-240	15-75	100	125-200	250	300
File	DP435S1	DP435S2	DP435S3	DP435S4	DP435S5
380-415	15-125	150	200-300	350-400	450-600
File	DP435S1	DP435S2	DP435S3	DP435S4	DP435S5
440-480	15-150	200	250-400	500	600-700
File	DP435S1	DP435S2	DP435S3	DP435S4	DP435S5