

MP435 with ATS Submittal Packages

Voltage	HP Range				
200	15-20	25-60	75-100	125-150	200-250
File	DP435TS1	DP435TS2	DP435TS3	DP435TS4	DP435TS5
208	15-20	25-75	100	125-150	200-250
File	DP435TS1	DP435TS2	DP435TS3	DP435TS4	DP435TS5
220-240	15-25	30-75	100-125	150-200	250
File	DP435TS1	DP435TS2	DP435TS3	DP435TS4	DP435TS5
380-415	15-40	50-125	150-200	250-300	350
File	DP435TS1	DP435TS2	DP435TS3	DP435TS4	DP435TS5
440-480	15-50	60-150	200-250	300-400	500
File	DP435TS1	DP435TS2	DP435TS3	DP435TS4	DP435TS5