

MP700 Submittal Packages

Voltage	HP Range				
200	15-60	75-100	125	150	200-250
File	DP700S1	DP700S2	DP700S3	DP700S4	DP700S5
208	15-75	100	125-150	---	200-250
File	DP700S1	DP700S2	DP700S3	---	DP700S4
220-240	15-75	100-125	150	200	250
File	DP700S1	DP700S2	DP700S3	DP700S4	DP700S5
380-415	15-125	150-200	250	300	350
File	DP700S1	DP700S2	DP700S3	DP700S4	DP700S5
440-480	15-150	200-250	300	350-400	500
File	DP700S1	DP700S2	DP700S3	DP700S4	DP700S5