

**MPT420TS w/ATS Submittal Packages**

Voltage	HP Range					
200	5-60	N/A	75-125	150	200-250	300
	<a href="#">DT420TS1</a>	-	<a href="#">DT420TS3</a>	<a href="#">DT420TS4</a>	<a href="#">DT420TS5</a>	<a href="#">DT420TS6</a>
208	5-60	75	100-150	N/A	200-250	300
	<a href="#">DT420TS1</a>	<a href="#">DT420TS2</a>	<a href="#">DT420TS3</a>	-	<a href="#">DT420TS5</a>	<a href="#">DT420TS6</a>
220-240	5-60	75	100-150	200	250	300
	<a href="#">DT420TS1</a>	<a href="#">DT420TS2</a>	<a href="#">DT420TS3</a>	<a href="#">DT420TS4</a>	<a href="#">DT420TS5</a>	<a href="#">DT420TS6</a>
380-415	5-100	125	150-250	300	350-400	500
	<a href="#">DT420TS1</a>	<a href="#">DT420TS2</a>	<a href="#">DT420TS3</a>	<a href="#">DT420TS4</a>	<a href="#">DT420TS5</a>	<a href="#">DT420TS6</a>
440-480	5-150	N/A	200-300	350-400	500	600-700
	<a href="#">DT420TS1</a>	-	<a href="#">DT420TS3</a>	<a href="#">DT420TS4</a>	<a href="#">DT420TS5</a>	<a href="#">DT420TS6</a>