



RLA – Recessed LED Architectural*

RLA provides a luminaire that is price competitive and provides an architectural design without forfeit.



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

RLA					G		U	
MODEL	SIZE	COLOR TEMP	LUMEN OUTPUT	CEILING TYPE	DRIVER	VOLTAGE	OPTIONS	
RLA Recessed LED Architectural Luminaire	22 2' x 2' 24 2' x 4'	35 3500K 40 4000K	LW Low Watt ML Medium Lumen HL High Lumen VL Very High Lumen	G Grid ¹	E Fixed Output ED 0-10V Dimming ED1 0-10V 1% Dimming	U 120V-277V	C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex ELL14 Emergency Battery Pack Installed, 1400 Lumen ²	

¹ For drywall, order G with Flange Kit Accessory.

² For compatibility with Dual-Lite LiteGear[®] inverters in lieu of installed Battery Pack, contact Hubbell Lighting Representative.