



3L-W-D*

The MOD™ 3L LED Wall Direct (3L-W-D) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.



Click RDC/QS Guide for full details.



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

3L	-	W	-		-		-		-			
SERIES		MOUNTING		FIXTURE DISTRIBUTION		ROW LENGTH		MAX LENGTH IN ROW		DIRECT OPTICAL DISTRIBUTION		FINISH/COLOR²
3L MOD		W Wall		D Direct AD Asymmetric Direct		—' Enter in foot increments		02 2', 609mm 03 3', 914mm 04 4', 1219mm 05 5', 1524mm 06 6', 1829mm 08 8', 2438mm		SOF Soft Diffuse Lens, Lambertian REG Regressed Diffuse Lens BWO Blade Baffle with Overlay ASYM Asymmetric Diffuse Lens ^{3,4} DRP Drop Lens		C1 Matte White (Default) C2 Textured Matte White C3 Light Silver C4 Machined Aluminum C5 Carbon Black C6 Textured Camera Black

	-		-		-	1C	-		
COLOR TEMPERATURE		DIRECT OUTPUT/FT ⁶		DRIVER		CIRCUITING		VOLTAGE	
27K	2700K ¹	D030	300 (min)	D01	1% Dimming, 0-10V	1C	1 Circuit	UNV	Universal Voltage (120V-277V)
30K	3000K		to	D00	1% Dim-to-Off, 0-10V			347	347 Volt ^{1,7}
35K	3500K	D125	1250 (max)	D05	SpectraSync 5% Dimming, 0-10V ⁹				
40K	4000K			DS1	1% Dimming w/ Soft Start, 0-10V				
50K	5000K ¹			DS0	1% Dim-to-Off w/ Soft Start, 0-10V				
27K9	2700K, 90 CRI ¹			LEC	Hi-lume 1% Ecosystem LED Driver				
30K9	3000K, 90 CRI			DALI	DALI ¹				
35K9	3500K, 90 CRI			DALIP	Powered by DALI (2.0) ¹				
40K9	4000K, 90 CRI			NDM	Non-Dimming				
50K9	5000K, 90 CRI ¹								
2230TD	2200K-3000K SpectraSync™ Dim-to-Warm ⁵								
2750T	2700K-5000K SpectraSync™ Tunable White ⁵								
2765T	2700K-6500K SpectraSync™ Tunable White ⁵								

OPTIONAL

	-		-	
NIGHTLIGHT		EMERGENCY		THRU-WIRING
NL Nightlight Circuit Required. Enter quantity. 2NL = 2 nightlight circuits/row		EF 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. ⁸		W1 No Thru Wire W2 Provide Normal and Emergency/ Nightlight Thru Wiring ¹⁰ W3 Provide Normal Thru Wiring Only

Notes:

- Additional lead time may be applicable. Contact factory.
- Visit www.litecontrol.com/finishes for details.
- Not Available with Patterns.
- Must be ordered with AD.
- Must be ordered with D05 Driver option; excludes 2' lengths and patterns.
- Specifiable in 50 lumen increments. Reference the Performance Data Table for full performance offering and exceptions.
- Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers
- EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others.
- Must be ordered with 2230TD, 2750T or 2765T Option
- Only applicable when specified with Emergency/Nightlight.
- Contact Factory for pattern configurations. Approval drawings required.