



**4L-P-D\***

The MOD™ 4L LED Pendant Direct (4L-P-D) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.

Click RDC/QS Guide  
for full details.



## 10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

**4L** - **P** -  -  -  -  -

SERIES	MOUNTING	FIXTURE DISTRIBUTION	ROW LENGTH	MAX LENGTH IN ROW	DIRECT OPTICAL DISTRIBUTION	FINISH/COLOR <sup>2</sup>
4L MOD	P Pendant	D Direct AD Asymmetric Direct	—' Enter in foot increments	02 2', 609mm 03 3', 914mm 04 4', 1219mm 05 5', 1524mm 06 6', 1829mm 08 8', 2438mm	SOF Soft Diffuse Lens, Lambertian REG Regressed Diffuse Lens <sup>3</sup> BWO Blade Baffle with Overlay <sup>3</sup> ASYM Asymmetric Diffuse Lens <sup>3,4</sup> BAT Batwing Lens DRP Drop Lens <sup>1,3</sup>	C1 Matte White (Default) C2 Textured Matte White C3 Light Silver C4 Machined Aluminum C5 Carbon Black C6 Textured Camera Black

-  -  - **1C** -  -  -

COLOR TEMPERATURE	DIRECT OUTPUT/FT <sup>6</sup>	DRIVER	CIRCUITING	VOLTAGE	SUSPENSION KIT <sup>8</sup>
27K 2700K <sup>1</sup>	D030 300 (min) <sup>7</sup>	D01 1% Dimming, 0-10V	1C 1 Circuit	UNV Universal Voltage (120V-277V)	FA1 Suspension Kit, 51"
30K 3000K	to	D00 1% Dim-to-Off, 0-10V			FA2 Suspension Kit, 87"
35K 3500K	D125 1250 (max)	D05 SpectraSync 5% Dimming, 0-10V <sup>10</sup>		347 347 Volt <sup>1,7</sup>	FA3 Suspension Kit, 219"
40K 4000K		DS1 1% Dimming w/ Soft Start, 0-10V			FA4 Suspension Kit, 363"
50K 5000K <sup>1</sup>		DS0 1% Dim-to-Off w/ Soft Start, 0-10V			
27K9 2700K, 90 CRI <sup>1</sup>		LEC Hi-lume 1% Ecosystem LED Driver			
30K9 3000K, 90 CRI		DALI DALI <sup>1</sup>			
35K9 3500K, 90 CRI		DALIP Powered by DALI (2.0) <sup>1</sup>			
40K9 4000K, 90 CRI		NDM Non-Dimming			
50K9 5000K, 90 CRI <sup>1</sup>					
2230TD 2200K-3000K SpectraSync™ Dim-to-Warm <sup>5</sup>					
2750T 2700K-5000K SpectraSync™ Tunable White <sup>5</sup>					
2765T 2700K-6500K SpectraSync™ Tunable White <sup>5</sup>					

## OPTIONAL

\_\_\_\_\_ - \_\_\_\_\_ - \_\_\_\_\_ - \_\_\_\_\_

NIGHTLIGHT	EMERGENCY	THRU-WIRING	T-BAR CLIPS <sup>12</sup>
<b>NL</b> Nightlight Circuit Required. Enter quantity. 2NL = 2 nightlight circuits/row	<b>EF</b> 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. <sup>9</sup>	<b>W1</b> No Thru Wire <b>W2</b> Provide Normal and Emergency/ Nightlight Thru Wiring <sup>11</sup> <b>W3</b> Provide Normal Thru Wiring Only	<b>CB1</b> T-bar clip - 15/16" <b>CB2</b> T-bar clip - 9/16" <b>CB3</b> T-bar clip - 9/16" SS

Notes:

- |   |  |    |   |
|---|--|----|---|
| 1 | Additional lead time may be applicable. Contact factory.   | 8  | Add suffix /V to replace all 2" non-feed canopy covers with 5" canopy covers. FA1/V = 51" suspension kit w/ 5" canopies; canopies and feed cord are supplied in white regardless of fixture color unless otherwise specified. |
| 2 | Visit <a href="http://www.litecontrol.com/finishes">www.litecontrol.com/finishes</a> for details.                      | 9  | EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others.   |
| 3 | Not Available with Patterns.   | 10 | Must be ordered with 2230TD, 2750T or 2765T Option  |
| 4 | Must be ordered with AD.   | 11 | Only applicable when specified with Emergency/Nightlight.   |
| 5 | Must be ordered with D05 Driver option; excludes 2' lengths and patterns.  | 12 | Includes Luminaire Canopy Box.  |
| 6 | Specifiable in 50 lumen increments. Reference the Performance Data Table for full performance offering and exceptions. |    |   |
| 7 | Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers                     |    |   |