

4L-R-D*

The MOD™ 4L LED Recessed Direct (4L-R-D) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.



Click RDC/QS Guide for full details.



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

4L						
SERIES	CEILING TYPE ¹	FIXTURE DISTRIBUTION	ROW LENGTH	ROW LENGTH ADDER	MAX LENGTH IN ROW	DIRECT OPTICAL DISTRIBUTION
4L MOD	DW Drywall PT Drywall with plaster trim (trimless finish) LG 15/16 Grid NG 9/16 Grid SS 9/16 Screw Slot	D Direct AD Asymmetric Direct	' Enter in foot increments	.3 Row length +3" .6 Row length +6" .9 Row length +9" Measured in inches	02 2', 609mm 03 3', 914mm 04 4', 1219mm 05 5', 1524mm 06 6', 1829mm 08 8', 2438mm	SOF Soft Diffuse Lens, Lambertian REG Regressed Diffuse Lens ⁴ BWO Blade Baffle with Overlay ⁴ ASYM Asymmetric Diffuse Lens ^{4,5} BAT Batwing Lens DRP Drop Lens ^{2,4}

				1C	
FINISH/COLOR ³	COLOR TEMPERATURE	DIRECT OUTPUT/FT ⁷	DRIVER	CIRCUITING	VOLTAGE
C1 Matte White (Default)	27K 2700K ²	D030 300 (min) ⁸	D01 1% Dimming, 0-10V	1C 1 Circuit	UNV Universal Voltage (120V-277V)
C2 Textured Matte White	30K 3000K	to	D00 1% Dim-to-Off, 0-10V		347 347 Volt ^{2,9}
C3 Light Silver	35K 3500K	D125 1250 (max)	D05 SpectraSync 5% Dimming, 0-10V ¹¹		
C4 Machined Aluminum	40K 4000K		DS1 1% Dimming w/ Soft Start, 0-10V		
C5 Carbon Black	50K 5000K ²		DS0 1% Dim-to-Off w/ Soft Start, 0-10V		
C6 Textured Camera Black	27K9 2700K, 90 CRI ²		LEC Hi-lume 1% Ecosystem LED Driver		
	30K9 3000K, 90 CRI		DALI DALI ²		
	35K9 3500K, 90 CRI		DALIP Powered by DALI (2.0) ²		
	40K9 4000K, 90 CRI		NDM Non-Dimming		
	50K9 5000K, 90 CRI ²				
	2230TD 2200K-3000K SpectraSync™ Dim-to-Warm ⁶				
	2750T 2700K-5000K SpectraSync™ Tunable White ⁶				
	2765T 2700K-6500K SpectraSync™ Tunable White ⁶				

OPTIONAL

NIGHTLIGHT	EMERGENCY	THRU-WIRING	CHICAGO ENVIRONMENTAL AIR MODIFICATION
NL Nightlight Circuit Required. Enter quantity. 2NL = 2 nightlight circuits/row	EF 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. ¹⁰	W1 No Thru Wire W2 Provide Normal and Emergency/ Nightlight Thru Wiring ¹² W3 Provide Normal Thru Wiring Only	CCEA Chicago Environmental Air Modification

Notes:

- Ceiling type can not be retrofitted in the field.
- Additional lead time may be applicable. Contact factory.
- Visit www.litecontrol.com/finishes for details.
- Not Available with Patterns.
- Must be ordered with IAD.
- Must be ordered with D05 Driver option; excludes 2' lengths and patterns.
- Specifiable in 50 lumen increments. Reference the Performance Data Table for full performance offering and exceptions.
- Not available in 2'
- Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers
- EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others.
- Must be ordered with 2230TD, 2750T or 2765T Option
- Only applicable when specified with Emergency/Nightlight.