



AW - Wraparounds

- Low Profile
- Lens Hinges From Either Side
- White Steel Housing
- 2, 3 and 4 Lamp Available



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

			32		U	
MODEL	SIZE	LAMP TYPE			VOLTAGE	OPTIONS
AWN 8 ⁵ / ₁₆ " Wide	4 4'	32 4', T8 ¹			U 120V-277V	EL Emergency Battery Pack
AWW 14 ⁵ / ₈ " Wide	8 8' (AWN only)					
NO. OF LAMPS IN CROSS SECTION		BALLAST				
2 Two		E Electronic Instant Start (Std.)				
3 Three (AWW only)		3E 3-Lamp Electronic T8, Instant Start				
4 Four (AWW only)		4E 4-Lamp Electronic T8, Instant Start				
		24E (1) 2-Lamp and (1) 4-Lamp Electronic T8, Instant Start				

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.