



## AW – Commercial Wrap

Low Profile Fluorescent Wrap



**10-Day Quick Ship Ordering Guide**

**Order Limit Per Fixture Selection: 100**

<input type="text"/>	<input type="text"/>	-	<input type="text"/>	<input type="text" value="32"/>	-	<input type="text"/>	<input type="text" value="U"/>	-	<input type="text"/>
MODEL	SIZE		NO. OF LAMPS IN CROSS SECTION	LAMP TYPE		BALLAST	VOLTAGE		OPTIONS
<b>AWN</b> 8 $\frac{5}{16}$ " Wide	<b>4</b> 4'		<b>2</b> Two	<b>32</b> 4', T8 <sup>1</sup>		<b>E</b> Electronic Instant Start (Std.)	<b>U</b> 120V-277V		<b>EL</b> Emergency Battery Pack
<b>AWW</b> 14 $\frac{1}{8}$ " Wide	<b>8</b> 8' (AWN only)		<b>3</b> Three (AWW only)			<b>3E</b> 3-Lamp Electronic T8, Instant Start			
			<b>4</b> Four (AWW only)			<b>4E</b> 4-Lamp Electronic T8, Instant Start			
						<b>24E</b> (1) 2-Lamp and (1) 4-Lamp Electronic T8, Instant Start			

<sup>1</sup> Capable of operating 32, 30, 28 or 25 Watt T8 only.