



CS - Striplights



10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 100

CS						U	EL	
MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	LAMP TYPE	BALLAST	VOLTAGE	OPTIONS		
CS Straight-Sided Utility Channel	2 2' 4 4' 8 8'	1 One 2 Two	17 2', T8: 17 Watt 32 4', T8 ¹	E Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start	U 120V-277V 347 347V	EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8		
							ACCESSORIES (ORDER SEPARATELY)	
							CSRA4	4' Asymmetric Reflector
							CSRU4	4' Symmetric Reflector 5% Uplight

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.