



CV-Curv



10-Day Quick Ship Ordering Guide

Order Limit 1000' Linear Feet (See Alera Express Brochure for Limitations and Details.)

CV								U		MW	
MODEL		HOUSING TYPE			ADJUSTABLE CABLE LENGTH (CM)		VOLTAGE		FINISH		OPTIONS
CV Cûrv		PERF Perforated (1T8 not recommended on suspended unit)			48 48" 96 96"		U 120V-277V		MW Matte White		DC Dust Cover (T8 and T5 with standard distribution only)
		S Solid									SCE Sculpted End Cap (5 5/16" each)
ROW LENGTH		LAMP TYPE & PROFILE			MOUNTING METHOD		BALLAST				
4 4' Single		1T5 1 T5 Lamp			CM Adjustable Aircraft Cable Mount		E Electronic, Instant Start (Std. for T8)				
8 8' Single		2T5 2 T5 Lamps			WM Wall Mount		EP Electronic, Programmed Start (Std. for T5 & T5HO, optional for T8)				
— Indicate row length over 8' in 4' increments		3T5 3 T5 Lamps (N/A WM)					ELW Electronic T8, 0.77BF, Low Watt, Instant Start				
		1T5HO 1 T5HO Lamp					EPLW Electronic T8, 0.77BF, Low Watt, Programmed Start				
		2T5HO 2 T5HO Lamps					ED_ADVMK10 Electronic Dimming, Must Specify Voltage, Advance, Mark10 Powerline, 2T8 only				
		3T5HO 3 T5HO Lamps (N/A WM)					EDUADVMK7 Universal Voltage, Electronic Dimming, Advance Mark7(0-10v) 2T8 only				
		1T8 1 T8 Lamp (Solid only)									
		2T8 2 T8 Lamps									
		3T8 3 T8 Lamps (N/A WM)									
		4T8 4 T8 Lamps (N/A WM)									
Note: Rows over 8' will be configured by Alera. Example: 16' will be (2) 8'. Alternate configurations: contact factory.											
General Note: Not all options are available in every possible configuration.											
Specifications apply. Please see Alera Express Program Rules page.											
¹ Specify voltage.											
² EMC/NLC is installed in right-hand side of 8' unit. Consists of 1 lamp ballast and one power drop. EMC/NLC is not available for dimming on Alera Express.											
³ See Alera Express Program Rules page for emergency battery pack information.											

General Note: Not all options are available in every possible configuration.

Specifications apply. Please see Alera Express Program Rules page.

¹ Specify voltage.

² EMC/NLC is installed in right-hand side of 8' unit. Consists of 1 lamp ballast and one power drop. EMC/NLC is not available for dimming on Alera Express.

³ See Alera Express Program Rules page for emergency battery pack information.