



## Dynamo Series

- NEMA4X Industrial High Lumen LED Emergency Light
- Fully Adjustable LED Lamphead
- Includes Universal Mounting Plate
- Wet Location or NEMA4X Application

Part Number	Catalog Number	UPC Code	Description	CA 03	GA 27	IL 06	PA 10	TX 04	Wt. each	Ctn. Qty
93048720	DYN6	782520867416	6 Watt Capacity, 3 Watt Heads, Wet Location (10° to 50°C)	●	●				8.00 lbs.	4
93048722	DYN6I	782520867423	6 Watt Capacity, 3 Watt Heads, Self-diag., Wet Location (10° to 50°C)	●	●				8.00 lbs.	4
93048721	DYN6I-4X	782520867447	6 Watt Capacity, 3 Watt Heads, Self-diag., NEMA4X (10° to 50°C)	●	●				8.00 lbs.	4
93048723	DYN12	782520867478	12 Watt Capacity, 3 Watt Heads, Wet Location (10° to 50°C)	●	●				10.00 lbs.	4
93048725	DYN12-4X	782520867485	12 Watt Capacity, 3 Watt Heads, NEMA4X (10° to 50°C)	●	●				10.00 lbs.	4
93048727	DYN12I	782520867492	12 Watt Capacity, 3 Watt Heads, Self-diag., Wet Location (10° to 50°C)	●	●				10.00 lbs.	4
93048724	DYN12-06L	782520867539	12 Watt Capacity, 6 Watt Heads, Wet Location (10°-50°C)	●	●				10.00 lbs.	4
93048728	DYN12I-06L	782520867546	12 Watt Capacity, 6 Watt Heads, Self-diag., Wet Location (10° to 50°C)	●	●				10.00 lbs.	4
93048726	DYN12-4X-06L	782520867553	12 Watt Capacity, 6 Watt Heads, Self-diag., NEMA4X (10° to 50°C)	●	●				10.00 lbs.	4
93048729	DYN12I-4X-HTR-06L	782520867560	12 Watt Capacity, 6 Watt Heads, Self-diag., NEMA4X, with Heater (-30° to 50°C)	●	●				10.00 lbs.	4
<b>Matching Remote Heads</b>										
93059702	DYNRS-4X	782520867584	3 Watt Single Head Remote, -30° to 50°C	●	●				2.40 lbs	4
93059703	DYNRD-4X	782520867591	3 Watt Double Head Remote, -30° to 50°C	●	●				3.10 lbs.	4