



EVHC Series

- High Output
- 120/277 VAC

- Damp Listed
- Wall or Ceiling Mounting

Part Number	Catalog Number	UPC Code	Description	CA 03	GA 27	IL 06	PA 10	TX 04	Wt. each	Ctn. Qty
93050453	EVHC6	782520866839	326 Lumen Lamphead, White Finish	•	•	•			3.00 lbs.	6
93050454	EVHC6I	782520866846	326 Lumen Lamphead, Spectron® Self-Diag., White Finish	•	•	•		•	3.00 lbs.	6
93050457	EVHC12	782520866877	326 Lumen Lamphead, Remote Capacity, White Finish	•	•				3.22 lbs.	6
93050458	EVHC12I	782520866884	326 Lumen Lamphead, Remote Capacity, Spectron®, White Finish	•	•				3.22 lbs.	6
93050459	EVHC12-06L	782520866891	546 Lumen Lamphead, White Finish	•	•				3.22 lbs.	6
93050460	EVHC12I-06L	782520866907	546 Lumen Lamphead, Spectron® Self-Diag., White Finish	•	•			•	3.22 lbs.	6
93050456	EVHC6-B	782520866860	326 Lumen Lamphead, Black Finish	•	•				3.00 lbs.	6
93050690	EVHCR2	782520867249	326 lumen lamp-head remote head, white finish	•	•	•			2.50 lbs.	6
93059794	EVHC6-BC	782520867379	326 lumen lamp-head, white finish, battery compartment	•	•	•			3.00 lbs.	6
93059795	EVHC6I-BC	782520867386	326 lumen lamp-head, Spectron, white finish, battery compartment	•	•	•			3.00 lbs.	6
93059796	EVHC12-BC	782520867393	326 lumen lamp-head, remote capacity, white finish, battery comp.	•	•				3.50 lbs.	6
93059797	EVHC12I-BC	782520867409	326 lumen lamp-head, Spectron Self Diag., white finish, battery comp.	•	•				3.50 lbs.	6