



ASL LED Area/Site*



10-Day Quick-Ship Ordering Guide

Order Limit Per Luminaire Selection: 15 (Contact factory for larger quantities)

ASL - [] - [] - [] - [] - [] - [] - [] - []									
SERIES	MOUNTING	NUMBER OF LEDS	DRIVE CURRENT	CCT	DISTRIBUTION	VOLTAGE	FINISH	OPTION	
ASL Area/Site	A Arm	8L 8 LEDs	210 2100mA 070 700mA	4K 4000K	3 Type III 4 Type IV	U Universal 120-277V	DB Bronze	7PR Twist lock PC receptacle SCP Programmable motion control, factory default is 10% light output SCP-40F Programmable dimming control (see spec sheet for complete ordering information)	
	MAF Mast Arm	16L 12 LEDs		5K 5000K			BL Black		
		24L 24 LEDs					PS Platinum		

*Please refer to the DLC website for specific product qualifications at www.designlights.org