



ASL LED Area/Site*

Part Number	Catalog Number	UPC Code	Description	CA 03	TX 04	IL 06	PA 10	GA 27	Wt. each
ASL16L3	ASL-16L-3	785988031603	Medium size 11,000 lumen LED, Dark Bronze, Type III, 4000K, 120-277 Volt	●	●	●	●	●	18.0
ASL16L4	ASL-16L-4	785988031627	Medium size 11,000 lumen LED, Dark Bronze, Type IV, 4000K, 120-277 Volt	●	●	●	●	●	18.0
ASL24L3	ASL-24L-3	785988031610	Large size 16,000 lumen LED, Dark Bronze, Type III, 4000K, 120-277 Volt	●	●	●	●	●	20.0
ASL24L4	ASL-24L-4	785988031634	Large size 16,000 lumen LED , Dark Bronze, Type IV, 4000K, 120-277 Volt	●	●	●	●	●	20.0
ASL24L3HO	ASL-24L-3-HO	785988032785	Large size 21,000 lumen LED, Dark Bronze, Type III, 4000K, High Output, 120-277 Volt	●		●	●	●	20.0
ASL24L4HO	ASL-24L-4-HO	785988032792	Large size 21,000 lumen LED, Dark Bronze, Type IV, 4000K, High Output, 120-277 Volt	●		●	●	●	20.0
ASL24L3HOSCPW	ASL-A-24L4K-070-3-U-DB-SCP-40F	785988033454	Large size 21,000 lumen LED, Dark Bronze, High Output, occupancy & PC control, 120-277 Volt	●					20.0
ASL24L3SCPW	ASL-A-24L4K-210-3-U-DB-SCP-40F	785988033461	Large size 21,000 lumen LED, Dark Bronze, occupancy & PC control, 120-277 Volt	●					20.0
ASL16L3SCPW	ASL-A-16L4K-210-3-U-DB-SCP-40F	785988033478	Medium size 11,000 lumen LED, Dark Bronze, Type III, 4000K, occupancy & PC control, 120-277 Volt	●					18.0
ASLMAF	ASL-MAF	785988031641	Mast arm kit and bird shield for mounting on 2 3/8" OD arms	●	●	●	●	●	4.0
CL1SRPA3ACCDDB	CL1S-RPA3-ACC-DB	-	Round Pole Adapter for ASL and CL1S luminaires (3.25"-3.75" diameter poles)	●	●	●	●	●	0.5
CL1SRPA4ACCDDB	CL1S-RPA4-ACC-DB	-	Round Pole Adapter for ASL and CL1S luminaires (3.875"-6" diameter poles)	●	●	●	●	●	0.5
WBAREADB	WB-AREA-DB	-	Wall Bracket for Area Lights with #2 arm bolt pattern (ASL, Cimarron, M-Pulsive, Raven, ARA3)	●	●	●	●	●	3.5