



LCAT - LED Contemporary Architectural Troffer

- Aesthetically Pleasing
- Reduce Maintenance
- 2'x2', 2'x4'
- DesignLights Consortium**



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 250

LCAT		-		-	G		-	U	-		
MODEL			COLOR TEMP		CEILING TYPE		DRIVER		VOLTAGE		OPTIONS
LCAT LED Contemporary Architectural Troffer			35 3500K 40 4000K		G Grid Lay-in ¹		E Fixed Output ED 0-10V Dimming ED1 0-10V 1% Dimming		U 120V-277V		ELL14 Emergency Battery Pack Installed, 1400 Lumen ² C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex
	SIZE				LUMEN OUTPUT						
	22 2' x 2'				LW Low Watt ML Medium Lumen HL High Lumen VL Very High Lumen						
	24 2' x 4'										

¹ For drywall, order G with Flange Kit Accessory.

² For compatibility with Dual-Lite LiteGear[®] inverters in lieu of installed Battery Pack, contact Hubbell Lighting Representative.

*DLC[®] (DesignLights Consortium) Qualified, with some Premium Qualified configurations. Please refer to the DLC website for specific product qualifications at www.designlights.org.