

LCVR-L- LED Curv Radial Lens



10-Day Quick Ship Ordering Guide

Order Limit 1000' Linear Feet (See Alera Express Brochure for Limitations and Details.)

LCVR	L					CM			U	MW	
MODEL	ROW LENGTH	LUMEN PACKAGE	SUSPENSION LENGTH	VOLTAGE	FINISH	OPTIONS	SHIELDING	MOUNTING METHOD	DISTRIBUTION	DRIVER	
LCVR Curv Radial Lens LED	4 4' Single 8 8' Single — Indicate row length over 8' in 4' increments Note: Rows over 8' will be configured by Alera. Example: 16' will be (2) 8'. Alternate configurations: contact factory.	VW Very Low Watt LW Low Watt ML Medium Lumen HL High Lumen VL Very High Lumen	48 48" 96 96" Other lengths available on request	U 120V-277V	MW Matte White (Std.)	AB A/B Circuitry ELL10 Emergency Battery Pack ² EMC One Emergency Circuit ¹ NLC One Night Light Circuit ¹ GTD Generator Transfer Device ^{1,2} GLR Fast Blow Fuse TBAR TBAR Clips DC Dust Cover SLC Sloped Ceiling Coupler UB Upper/Lower separate circuits ³ SCE Sculpted End Cap BN Bull Nose End Cap	L Opal Lens	CM Adjustable Cable	20 80% Up / 20% Down 40 60% Up / 40% Down 60 40% Up / 60% Down 80 20% Up / 80% Down 100 0% Up / 100% Down	E Fixed Output ED 0-10V Dimming	
		LED COLOR									
		30 3000K 35 3500K 40 4000K									

Specifications apply. Please see Alera Express Program Rules page.

¹ Additional feed drop per EMC, NLC or GTD. (For through wiring, contact factory.)

² For additional, specify quantity before nomenclature (Example: 2ELL10).

³ Not available with all configurations. Some limitations apply. Contact factory for details.