



## LHA - Industrial Fluorescent High Bay

- Economical and Serviceable
- Compact, Open body, 2" Height
- Rotary Locking Lampholders
- Quick and Easy Mounting



### 5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

<b>LHA</b>	<b>4</b>						
<b>SIZE</b> 4 4'	<b>NO. OF LAMPS</b> 4 Four 6 Six	<b>REFLECTOR</b> N Narrow Distribution W Wide Distribution	<b>UPLIGHT</b> ST Solid Top U Uplight	<b>VOLTAGE</b> U 120V-277V 347 347V	<b>OPTIONS</b>		
<b>MODEL</b> LHA Industrial Fluorescent High Bay	<b>LAMP TYPE</b> 32 4', T8 <sup>1</sup> 54 4', T5HO: 54 or 51 Watt	<b>BALLAST</b> <u>LHA4-454</u> 4EP (1) 4-Lamp Electronic T5HO, Programmed Start <u>LHA4-654</u> 24EP (1) 2-Lamp and (1) 4-Lamp Electronic T5HO, Programmed Start		<b>LAMPS INSTALLED</b> <u>T5HO</u> F554841 54 Watt, 85 CRI, 4100K F554850 54 Watt, 85 CRI, 5000K			
<p><b>EL141</b> Emergency Battery Pack, T8, 1400 Lumens  <b>EL5H</b> Emergency Battery Pack, T5, 1250 Lumens  <b>F3C5</b> 3-Conductor Cord  <b>F4C5</b> 4-Conductor Cord</p>							

<sup>1</sup> Capable of operating 32, 30, 28 or 25 Watt T8 only.