

LP7- Plank 7" LED



10-Day Quick Ship Ordering Guide

Order Limit 1000' Linear Feet (See Alera Express Brochure for Limitations and Details.)

LP7	OA					CM			U	MW	
MODEL LP7 Plank 7" LED	ROW LENGTH 4 4' Single 8 8' Single — Indicate row length over 8' in 4' increments Note: Rows over 8' will be configured by Alera. Example: 16' will be (2) 8'. Alternate configurations: contact factory.	LUMEN PACKAGE VW Very Low Watt LW Low Watt ML Medium Lumen HL High Lumen VL Very High Lumen	LED COLOR 30 3000K 35 3500K 40 4000K	SUSPENSION LENGTH 48 48" 96 96" Other lengths available on request	MOUNTING METHOD CM Adjustable Aircraft Cable Mount (Std.)	VOLTAGE U 120V-277V	FINISH MW Matte White (Std.)	DRIVER E Fixed Output ED 0-10V Dimming	OPTIONS AB A/B Circuitry ELL10 Emergency Battery Pack ³ EMC One Emergency Circuit ¹ GTD Generator Transfer Device ^{1,3} NLC One Night Light Circuit ¹ GLR Fast Blow Fuse TBAR TBAR Clips DC Dust Cover SLC Sloped Ceiling Coupler UB Upper Lower Separate Circuits	DISTRIBUTION 20 80% Up / 20% Down 40 60% Up / 40% Down ² 60 40% Up / 60% Down ² 80 20% Up / 80% Down ² 100 0% Up / 100% Down	SHIELDING OA Acrylic Lens

Specifications apply. Please see Alera Express Program Rules page.

¹ Additional feed drop per EMC, NLC or GTD. (For through wiring, contact factory.)

² Optional down light reflector provides approximate patterns. Distribution pattern results may vary.

³ For additional, specify quantity before nomenclature (Example: 2ELL10).