



LTRE - Transition® Enclosed LED High Efficiency Architectural Lens

- Designed for flexibility
- Full distribution
- Enclosed lens resists intrusion of contaminants
- DesignLights Consortium**



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

LTRE	-		-	G	-	RFA	-		-	U	-	
MODEL		COLOR TEMP		CEILING TYPE		SHIELDING		VOLTAGE		OPTIONS		
LTRE Transition® Enclosed LED High Efficiency Architectural Lensed		35 3500K 40 4000K		G Grid Lay-in ¹		RFA Ribbed Frosted Acrylic		U 120V-277V		C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex ELL14 Emergency Battery Pack, 1400 Lumen ²		
		SIZE		LUMEN OUTPUT		DRIVER						
		22 2' x 2' 24 2' x 4'		LW Low Watt (2x4 only) ML Medium Lumen HL High Lumen (2x2 only) VL Very High Lumen (2x2 only)		E Fixed Output ED 0-10V Dimming						

¹ For drywall, order G with Flange Kit Accessory.

² For compatibility with Dual-Lite LiteGear® inverters in lieu of installed Battery Pack, contact Hubbell Lighting Representative.

*DLC® (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org.