



## 5-Day Quick-Ship Ordering Guide

Order Limit Per Luminaire Selection: 20 Pieces or Less

D2LED		2D9LED	9L	30K	8	MD25		
J-TUBE ASSEMBLY	VOLTAGE	LIGHT ENGINE	OUTPUT	LED COLOR	CRI	BEAM ANGLE	REFLECTOR FINISH	REFLECTOR COLORS
<b>D2LED</b> J-Tube Assembly with Standard 0-10V 10% Dimming	<i>Standard 120V</i> <b>277 277V</b>	<b>2D9LED</b> 2" Open Reflector/ Light Engine Assembly	<b>9L</b> 900 Lumens <b>12L</b> 1200 Lumens <b>15L</b> 1500 Lumens	<b>30K</b> 3000 Kelvin <b>35K</b> 3500 Kelvin	<b>8</b> Nominal 80+ CRI	<b>WFL45</b> Spun Aluminum reflector with a 45° wide flood distribution <b>MD25</b> Spun Aluminum reflector with a 25° medium distribution <b>FL35</b> Spun Aluminum reflector with a 35° flood distribution <b>WW</b> Wall Wash	<i>Standard Specular</i>	<i>Standard Clear Alzak</i>

\*Reflector finishes other than clear specular are not QS items.



## 10-Day Quick-Ship Ordering Guide

Order Limit Per Luminaire Selection: 50 Pieces or Less

D2LED		2D9LED	9L	30K	8	MD25			WT
J-TUBE ASSEMBLY	VOLTAGE	LIGHT ENGINE	OUTPUT	LED COLOR	CRI	BEAM ANGLE	REFLECTOR FINISH	REFLECTOR COLORS	REFLECTOR OPTIONS
<b>D2LED</b> J-Tube Assembly with Standard 0-10V 10% Dimming	<i>Standard 120V</i> <b>277 277V</b>	<b>2D9LED</b> 2" Open Reflector/ Light Engine Assembly	<b>9L</b> 900 Lumens <b>12L</b> 1200 Lumens <b>15L</b> 1500 Lumens	<b>30K</b> 3000 Kelvin <b>35K</b> 3500 Kelvin	<b>8</b> Nominal 80+ CRI	<b>WFL45</b> Spun Aluminum reflector with a 45° wide flood distribution <b>MD25</b> Spun Aluminum reflector with a 25° medium distribution <b>FL35</b> Spun Aluminum reflector with a 35° flood distribution <b>WW</b> Wall Wash	<i>Standard Specular</i>	<i>Standard Clear Alzak</i>	<b>WT</b> White trim

\*Reflector finishes other than clear specular are not OS items.