



5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 20 Pieces or Less



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50 Pieces or Less

LC6SL	DM1	EM	6LCSL	14L	35K	8	WH	EM
HOUSING	DRIVER OPTION	HOUSING OPTION	TRIM APERTURE	OUTPUT	KELVIN	CRI	REF. FINISH/ COLOR OPTION	REF. OPTIONS
LC6SL Standard lumen 0-10V 10% dimming 120V-277V LC6ML Medium lumen 0-10V 10% dimming 120V-277V	<i>Standard 0-10V 10% Dimming</i> DM1 0-10V 1% Dimming	EM Integral Battery Pack EMR Remote Battery Pack	6LCSL Standard Lumen Clear Alzak Reflector 6LCML Medium Lumen Clear Alzak Reflector	10L Nominal 1000 delivered Lumens 14L Nominal 1400 delivered Lumens 18L Nominal 1800 delivered Lumens 24L¹ Nominal 2400 delivered Lumens 30L¹ Nominal 3000 delivered Lumens	27K 2700 Kelvin 30K 3000 Kelvin 35K 3500 Kelvin 40K 4000 Kelvin	8 Nominal 80+ CRI	WH Painted white reflector and trim	WT Painted white flange WW Wall Wash EM Integral Battery with pre-punched reflector

¹ 24L and 30L is only available with LC6ML housing and 6LCML trim.