



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50 Pieces or Less

ORDERING INFORMATION

EXAMPLE: LCC6LEDP18L35K8WFL45 BL

LCC6LED	P	18L	35K	8			WFL45			BL			
HOUSING		LED COLOR TEMP		CRI		OPTIONS		BEAM		REFLECTOR FINISH		CYLINDER COLOR	
LCC6LED	6" LED Cylinder	27K 2700 Kelvin	30K 3000 Kelvin	35K 3500 Kelvin	40K 4000 Kelvin	50K 5000 Kelvin	8 80+ CRI	Blank Standard 0-10V dimming to 10%	WFL45 Nominal 45 Degree Cutoff	Blank Clear Alzak, Semi-Dif-fuse	BA Brushed Aluminum	BZ Bronze	BL Matte Black
MOUNTING		OUTPUT		VOLTAGE		NOTES				REFLECTOR COLOR		WH Matte White	Z Zet
				Blank 120V-277V									
				120V 120 Volt (for 2DM)									
P Pendant		10L 1000 Delivered Lumens	14L 1400 Delivered Lumens	18L 1800 Delivered Lumens						BC Painted Black Cone	WC Painted White Cone		
S Surface													
CM ^{1,2} Cord Mount													
W Wall Mount													

NOTES

¹ Cord length 6 feet, clear sleeve

² Plastic bushings are grey on white, brushed aluminum and zet cylinder; black on black and bronze