



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50 Pieces or Less

LF8SL	DM1	EMR	8LFSL	20L	35K	8	WW	WT
HOUSING	DRIVER OPTIONS	HOUSING OPTIONS	TRIM APERTURE	OUTPUT	KELVIN	CRI	REFLECTOR OPTIONS	TRIM OPTIONS
LF8SL Standard Lumen 0-10V 10% dimming 120V-277V	<i>Standard 0-10V 10% Dimming</i> DM1 0-10V 1% dimming, 120-277V	EM Emergency Battery Pack with integral test switch and indicator light EMR Emergency Battery Pack with remote test switch and indicator light	8LFSL Standard Lumen Semi-Diffuse Clear Alzak 8LFML Medium Lumen Semi-Diffuse Clear Alzak	11L 1100 Lumen Module 15L 1500 Lumen Module 20L 2000 Lumen Module 30L¹ 3000 Lumen Module	30K 3000 Kelvin 35K 3500 Kelvin 40K 4000 Kelvin	8 80+ CRI 9 90+ CRI	WW Wall Wash EM Integral Battery with pre-punched reflector	WT Painted White Flange only

¹ 30L is only available with LF8ML housing and 8LFML trim.