



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50 Pieces or Less

RLC6SL	DM1		6LCSL	14L	35K	8	WH	EM
HOUSING	DRIVER OPTIONS	HOUSING OPTIONS	TRIM APERTURE	OUTPUT	KELVIN	CRI	REF. FINISH/ COLOR OPTION	REF. OPTIONS
RLC6SL Standard Lumen 0-10V Dimming to 10% 120V-277V	<i>Standard 0-10V 10% Dimming</i>	SD Small Diameter	6LCSL Standard Lumen Clear Alzak Reflector	10L Nominal 1000 delivered Lumens	27K 2700 Kelvin	8 Nominal 80+ CRI	WH Painted white reflector and trim	WT Painted white flange
RLC6ML Medium Lumen 0-10V Dimming to 10% 120V-277V	DM1 0-10V 1% Dimming		6LCML Medium Lumen Clear Alzak Reflector	14L Nominal 1400 delivered Lumens	30K 3000 Kelvin			
				18L Nominal 1800 delivered Lumens	35K 3500 Kelvin			
				24L¹ Nominal 2400 delivered Lumens	40K 4000 Kelvin			
				30L¹ Nominal 3000 delivered Lumens				

¹ 24L and 30L is only available with RLC6ML housing and 6LCML trim.