



STE - Stratus Recessed Direct/Indirect

- Stratus® E-Series Fluorescent
- T8, T5, T5HO, 40TT, 50TT

- Plastic Ends Caps Seal Light
- Aesthetically Delivers Uniform Illumination



5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

STE			G	MPO			
MODEL	NO. OF LAMPS IN CROSS SECTION		CEILING TYPE		BALLAST		OPTIONS
STE Stratus Recessed Indirect	2 Two 3 Three		G Grid Lay-in		E Electronic T8, Instant Start EP Electronic T5, T5HO, or T8, Programmed Start ETT Electronic Twin Tube, Instant Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8 or T5, Programmed Start		EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 F830 30K 78+CRI 17 or 32W T8 Lamps Installed F835 35K 78+CRI 17 or 32W T8 Lamps Installed F841 41K 78+CRI 17 or 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HOLamps Installed F5835 35K 85CRI T5 or T5HOLamps Installed F5841 41K 85CRI T5 or T5HOLamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed C388 3-Wire Flex C488 4-Wire Flex
SIZE	LAMP TYPE		SHIELDING		VOLTAGE		
22 2' x 2' 24 2' x 4'	17 2', T8: 17 Watt 24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 32 4', T8 ¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2-Lamp only)		MPO Metal Perf w/Overlay		U 120V-277V 347 347V (T5 and T8 only)		

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.