



**Hubbell USA**

47 East Industrial Park Drive  
Manchester, NH 03109  
[www.hubbell.com/burndy](http://www.hubbell.com/burndy)  
1-800-346-4175 | 1-603-647-5000

**Hubbell Canada**

870 Brock Road South  
Pickering, Ontario, Canada  
L1W 1Z8  
[www.hubbell.ca](http://www.hubbell.ca)  
[serviceexcellence@hubbell.ca](mailto:serviceexcellence@hubbell.ca)  
1-800-465-7051

**Hubbell Mexico**

011-52-722-265-4400

**Tool Repair Center**

1-800-426-8720

**Technical Service**

603-647-5019 | 1-800-451-4956

# BURNDY® TOOLS

## PATRIOT® PAT221 BATTERY CRIMPER SERIES



A Hubbell brand

©2025 Burndy, LLC. All rights reserved.

Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners.





BURNDY® PATRIOT® PAT221 SERIES

FEATURES & BENEFITS



Crimp #22 - #1 AWG,  
the largest range in its class!



- Scissor action, angled head design
- One-second crimp time with auto retract and calibration
- Interchangeable dies and wheels
- Connector hold feature for easy wire insertion
- Red LED to indicate an incomplete crimp
- LED worklight
- Safety trigger lock – **Burndy Exclusive!**
- Emergency release
- Industry standard battery

Try the PATRIOT® PAT221 for convenience, ergonomics, speed, safety, and improved user experience.



TRUST THE BURNDY ENGINEERED SYSTEM

MODELS, SPECIFICATIONS & CAPACITIES

MODELS*	
PAT221A02A2	Tool, (2) Dies, (2) Wheels, 2Ah, 120V AC
PAT221B02A2	Tool, No Dies, 2Ah, 120V AC
PAT221C02A2	Tool, (2) Dies, 2Ah, 120V AC
PAT221D02A2	Tool, (2) Wheels, 2Ah, 120V AC
PAT221B0000	Bare Tool Only

SPECIFICATIONS	
Tool Weight	2.6 lbs (without battery)
Size	10.60" x 4.20" x 2.80"
Die Style	Interchangeable with permanent grooves
Operating Voltage	18 V-DC Lithium-ion
Recharge Time	<25 minutes (2.0Ah)
Battery	Accepts 2.0Ah-6.0Ah Makita Batteries
Warranty	3 year limited warranty
	3 years on batteries and charger
*Kit Contents	Includes (2) 2.0Ah batteries, charger, case and respective dies noted



WHEEL/NEST AND DIE SETS	COPPER CRIMPING CAPACITIES	CONNECTOR CATALOG TYPES
81WHL221 Wheel/Nest Set	#8 - #1 AWG	YA, YAV, YS, YSV
122WHL221 Wheel/Nest Set	#12 - #2 AWG	T, YAD, YA, YAV, YAZ, YAZV, YS, YSV
2210B221 Die Set	#22 - #10 AWG Bare	T, YAD, T-F, YAD-H, YAV, YAV-H, YAV-H-F, YAV-R, YAV-T-F, YAV-Z, YSV, YSV-H
2210NV221 Die Set	#22 - #10 AWG Nylon and Vinyl	TP, BA, TP-F, BA-EF, TP-Z, BA-EZ, TP-LF, BA-EL, SP, BS, TN, YAES, TN-F, YAES-F, SNM*, YSES*, YAE-N, YAE-N-F, YAE-Z, YSE-HN, YSE-H, YAEV (*Excludes #10 Size)