

BURNDY® PATRIOT® PAT750 SERIES

FEATURES & BENEFITS

Also available with T3 Technology! See T3 Tech Series Brochure for details.



MODELS, SPECIFICATIONS & CAPACITIES

MODELS	
PAT750LI	Tool, 3Ah, 120V AC
PAT750L5	Tool, 5Ah, 120V AC
PAT750LCB	Tool, No Charger/Batteries

SPECIFICATIONS	
Output Force	12 Tons
Tool Weight	14.25 lbs (without battery)
Size	15.75" x 13.5" x 3.5"
Die Style	U Style
Operating Voltage	18 V-DC Lithium-ion
Recharge Time	30 minutes (3.0Ah)
	45 minutes (5.0Ah)
Warranty	5 year limited warranty
	Lifetime warranty on INFINITY DRIVE®
	3 years on batteries and charger



CRIMPING CAPACITIES	TERMINALS & SPLICES	TENSION SLEEVES	TAPS	AERIAL CABLE	HYGROUND®
Copper	#8 AWG - 750 kcmil	#8 Solid - 500 kcmil	#14 Solid - 500 kcmil	#6 AWG - 500 kcmil	#8 AWG - 500 kcmil
Aluminum	#8 AWG - 750 kcmil	#8 Solid - 587.2 kcmil	#8 AWG - 500 kcmil		
ACSR	#4 - 556.5 kcmil	#4 - 556.5 kcmil			
Ground Rod					1/2" - 1" Diameter



TRUST THE BURNDY® ENGINEERED SYSTEM



Hubbell USA
47 East Industrial Park Drive
Manchester, NH 03109
www.hubbell.com/burndy
1-800-346-4175 | 1-603-647-5000

Hubbell Canada
870 Brock Road South
Pickering, Ontario, Canada
L1W 1Z8
www.hubbell.ca
serviceexcellence@hubbell.ca
1-800-465-7051

Hubbell Mexico
011-52-722-265-4400

Tool Repair Center
1-800-426-8720

Technical Service
603-647-5019 | 1-800-451-4956

BURNDY® TOOLS

PATRIOT® PAT750
12-TON C-HEAD
SERIES



©2024 Burndy, LLC. All rights reserved.

Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners.

