



DUSK TO DAWN

PRODUCT SELECTION GUIDE

Features →

		tradeSELECT [®]			tradeSELECT [®]		
		 PATROLMAN			 SLING SGD		
FEATURES	Easy to Install	Yes			Yes		
	Mounting Options	2 3/8"-1 5/8", Pipe & Wall Mount			2 3/8"-1 5/8", Pipe & Wall Mount		
	Features	++			++		
	Maintenance	Low, Aiming			Low, Aiming		
PERFORMANCE	Lumens	4320			5700-8000		
	Watts	39W			40, 60W		
	Efficacy (maximum LPW)	108			142-143		
	Distribution	Symmetric Type V			Type V		
	CCT	5000K			4000K		
	CRI	70			70		
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	Yes	Yes	Yes	Yes
	Product Life	60,000hrs.			60,000hrs.		
	HID Equivalence	150W			100-250W		
Energy Savings (Based on HID Equivalence)	78%			78%			
Voltage	120-277V			120-277V			
CONTROLS	Basic occupancy	Yes			Yes		
	Occupancy and Daylight Harvesting	Yes			Yes		