

HUBBELL
Wiring Device-Kellems

PRODUCT OVERVIEW

inREACH[®] Motorized Cord Reels



inREACH® Motorized Cord Reels

Transforming the power delivery experience

Hubbell's inREACH motorized cord reels provide a safer and more accessible cable management solution than ever before. With the press of a switch, users can easily access power cords from above.

Applications

- Big box retail stores
- Laboratories
- Manufacturing facilities
- Convention centers
- Classrooms
- Aircraft hangars
- Stages
- Distribution and fulfillment centers
- Arenas



Features



Durable

- Light-weight, corrosion resistant aluminum housing
- Impact-resistant thermoplastic cover



Safe

- Automatic stops prevent personnel injury and equipment damage



Feature-Rich

- Power indicating LED
- Backup retraction button
- Shock absorber ball stop



Reliable

- Over-sized motor ensures a long product life
- Rated for 6,000 cycles per UL 355 standards



Installation Efficient

- Easy access to wire control switch
- Labor-saving mounting accessories



Configurable

- Cord lengths and gauges
- Factory installed wiring devices
- White or black reel housing





Control Switch Accessories

Description	Catalog Number
Low voltage, decorator push-button switch, single pole, momentary contact, 100mA 30V DC, two button, white	DSM30W2
Low voltage, specification grade, toggle switch, momentary, single pole double throw, 5A 24V DC, white	HBL1557WLV
Industrial grade, toggle switch, momentary single pole, double throw center off, 15A 120/277V AC	HBL1556LW
Locking key for HBL1556LW	HBL1209
Industrial grade, toggle switch, momentary single pole, double throw center off, 15A 120/277V AC	HBL1556W

Mounting Accessories

inREACH® Mounting Bracket

Mounting brackets enable quick and efficient installation of cord reels. Made of durable, corrosion-resistant cast aluminum.

Description	Catalog Number
Mounting bracket	HBLIMB
Mounting bracket with junction box mount	HBLIMBJ

inREACH Plenum Rated Enclosure

Steel enclosures to securely mount cord reels in drop ceilings while isolating them from the plenum space. Listed to UL2416, and compliant with plenum requirements per the NEC.

Description	Catalog Number
Plenum rated enclosure	HBLIPRBOX



Before After

Motorized cord reels



Description	Amps	Volts AC	Cable Length Feet (m)	Cable Type	Weight lbs (kg)	Catalog Number
White motorized reel without end effectors	20	125	25 (7.6)	12/3 SJO	32 (14.5)	HBLM25123
Black motorized reel without end effectors	20	125	25 (7.6)	12/3 SJO	32 (14.5)	HBLM25123BLK
White motorized reel with white cable and no end effectors	20	125	25 (7.6)	12/3 SJO	32 (14.5)	HBLMWC25123
White motorized reel with (1) 20A Insulgrip plug	20	125	25 (7.6)	12/3 SJO	33 (15.0)	HBLM25123C20
White motorized reel with (2) 20A tamper resistant duplex receptacles	20	125	25 (7.6)	12/3 SJO	34 (15.4)	HBLM25123R220M1
White motorized reel with (1) 20A tamper resistant duplex receptacle	20	125	25 (7.6)	12/3 SJO	34 (15.4)	HBLM25123GF20M1
White motorized reel with GFCI module and (2) 20A duplex receptacles	20	125	25 (7.6)	12/3 SJO	34 (15.4)	HBLM25123GF220M1
White reel with a white cord and (2) 20A duplex receptacles	20	125	25 (7.6)	12/3 SJO	34 (15.4)	HBLMWC25123R220M2
Black motorized reel with (2) tamper resistant duplex receptacles	20	125	25 (7.6)	12/3 SJO	34 (15.4)	HBLM25123BLKR220M1
White motorized reel without end effectors	20	125/250	25 (7.6)	12/4 SJO	33 (15.0)	HBLM25124
White motorized reel with (1) L14 20A Twist lock plug and (1) female L14 plug	20	125/250	25 (7.6)	12/4 SJO	34 (15.4)	HBLM25124C
White motorized reel with (1) L14 20A Twist lock plug and (2) 20A duplex receptacles	20	125/250	25 (7.6)	12/4 SJO	34 (15.4)	HBLM25124SC
White motorized reel without end effectors	20	125	45 (13.7)	12/3 SJO	35 (15.9)	HBLM45123
Black motorized reel without end effectors	20	125	45 (13.7)	12/3 SJO	35 (15.9)	HBLM45123BLK
White motorized reel with white cable and no end effectors	20	125	45 (13.7)	12/3 SJO	35 (15.9)	HBLMWC45123
White motorized reel with (1) 20A Insulgrip plug	20	125	45 (13.7)	12/3 SJO	36 (16.3)	HBLM45123C20
White motorized reel with (2) 20A Duplex Receptacles	20	125	45 (13.7)	12/3 SJO	37 (16.8)	HBLM45123R220M1
White motorized reel with (1) 20A tamper resistant duplex receptacle	20	125	45 (13.7)	12/3 SJO	37 (16.8)	HBLM45123GF20M1
White motorized reel with GFCI module and (2) 20A Duplex Receptacles	20	125	45 (13.7)	12/3 SJO	37 (16.8)	HBLM45123GF220M1
White reel with a white cord and (2) 20A duplex receptacles	20	125	45 (13.7)	12/3 SJO	37 (16.8)	HBLMWC45123R220M2
Black motorized reel with (2) tamper resistant duplex receptacles	20	125	45 (13.7)	12/3 SJO	37 (16.8)	HBLM45123BLKR220M1
White motorized reel without end effectors	20	125/250	45 (13.7)	12/4 SJO	37 (16.8)	HBLM45124
White motorized reel with (1) L14 20A Twist lock plug and (1) female L14 plug	20	125/250	45 (13.7)	12/4 SJO	37 (16.8)	HBLM45124C
White motorized reel with (1) L14 20A Twist lock plug and (2) 20A duplex receptacles	20	125/250	45 (13.7)	12/4 SJO	36 (16.3)	HBLM45124SC
White motorized reel without end effectors	20	125V	75 (22.9)	12/3 SJO	40 (18.1)	HBLM75123
White motorized reel without end effectors	20	125/250	75 (22.9)	12/4 SJO	43 (19.5)	HBLM75124
White motorized reel with (1) L14 20A Twist lock plug and (1) female L14 plug	20	125/250	75 (22.9)	12/4 SJO	37 (16.8)	HBLM75124C
White motorized reel with (1) L14 20A Twist lock plug and (2) 20A duplex receptacles	20	125/250	75 (22.9)	12/4 SJO	37 (16.8)	HBLM75124SC
White motorized reel without end effectors	30	125	25 (7.6)	10/3 SJO	35 (15.9)	HBLM25103
White motorized reel without end effectors	30	125/250	25 (7.6)	10/4 SJO	37 (16.8)	HBLM25104
White motorized reel with (1) L14 20A Twist lock plug and (1) female L14 plug	30	125/250	25 (7.6)	10/4 SJO	34 (15.4)	HBLM25104C
White motorized reel with (1) L14 20A Twist lock plug and (2) 20A duplex receptacles	30	125/250	25 (7.6)	10/4 SJO	36 (16.3)	HBLM25104SC
White motorized reel without end effectors	30	125	45 (13.7)	10/3 SJO	40 (18.1)	HBLM45103
White motorized reel without end effectors	30	125/250	45 (13.7)	10/4 SJO	45 (20.4)	HBLM45104
White motorized reel with (1) L14 20A Twist lock plug and (1) female L14 plug	30	125/250	45 (13.7)	10/4 SJO	36 (16.3)	HBLM45104C
White motorized reel with (1) L14 20A Twist lock plug and (2) 20A duplex receptacles	30	125/250	45 (13.7)	10/4 SJO	36 (16.3)	HBLM45104SC
White motorized reel without end effectors	30	125	60 (18.3)	10/3 SJO	44 (22.0)	HBLM60103

HUBBELL

Wiring Device-Kellems

Count on Hubbell Wiring Device-Kellems for the most reliable and innovative wiring device product line in North America

GET IN TOUCH:

✉ custserv@hubbell.com

☎ (800) 288-6000

🖱 www.hubbell.com/wiringdevice-kellem

📍 **Hubbell Wiring Device-Kellems**
40 Waterview Drive
Shelton, CT 06484

