


# FLOODLIGHTS

## PRODUCT SELECTION GUIDE

Features 

		tradeSELECT <sup>®</sup>			tradeSELECT <sup>®</sup>			tradeSELECT <sup>®</sup>			tradeSELECT <sup>®</sup>		
													
		Colt Mini			Marshal			Colt LBUL			ALF 6/12		
FEATURES	Easy to Install	Yes			Yes			Yes			Yes		
	Mounting Options	½" 14 NPS			Junction box			½" 14 NPS			½" 14 NPS		
	Features	+			+			++			++		
	Maintenance	Low, Aiming			Low, Aiming			Low, Aiming			Med, Aiming, Adjustment		
PERFORMANCE	Lumens	1115			2104			2000			1122, 2303		
	Watts	13W			20W			21W			26W		
	Efficacy (maximum LPW)	85			100			89–94			85		
	Distribution	NEMA 6X6 Wide			NEMA 6X6 Wide			NEMA 6X6 Wide			NEMA 6X6 Wide		
	CCT	3000K			3000K			4000K			5000K		
	CRI	70			80			70			70		
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
	Product Life	60,000hrs.			60,000hrs.			60,000 hrs.			60,000hrs.		
	HID Equivalence	70W			100W			150W			120W		
Energy Savings (Based on HID Equivalence)	86%			85%			83%			86%			
Voltage	120V			120V			120–277V			120V			
CONTROLS	Basic occupancy	–			Yes			–			Yes		
	Occupancy and Daylight Harvesting	–			Yes			–			Yes		

DLC<sup>®</sup> (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at [www.designlights.org](http://www.designlights.org)