



FESTOON CABLE

FLAT, ROUND AND PENDANT CABLE

FLAT YELLOW PVC CABLE					
SIZE	MODEL #	DIMENSIONS - IN (MM)	WEIGHT		AMPACITY
			LBS/ MFT	KG/KM	
#16 / 4 C	GRF16/4	.225 X .650 (5.7 X 16.5)	99	147	17
#16 / 4 C SHD	GRF16/4 SHD	.25 X .80 (6.4 X 20.3)	140	208	17
#16 / 8 C	GRF16/8	.225 X 1.17 (5.7 X 29.7)	190	283	15
#16 / 12 C	GRF16/12	.225 X 1.7 (5.7 X 43.3)	271	403	15
#16 / 12 C SHD	GRF16/12 SHD	.25 X 2.13 (6.4 X 54.1)	408	607	15
#14 / 4C	GRF14/4	.24 X .69 (6.1 X 17.5)	134	199	20
#14 / 8 C	GRF14/8	.24 X 1.29 (6.1 X 32.8)	249	370	18
#14 / 12 C	GRF14/12	.24 X 1.825 (6.1 X 46.4)	379	564	18
#14 / 12 C SHD	GRF14/12 SHD	.27 X 2.2 (6.9 X 55.9)	460	685	18
#12 / 4 C	GRF12/4	.26 X .80 (6.6 X 20.3)	165	246	25
#12 / 8 C	GRF12/8	.26 X 1.44 (6.6 X 36.6)	318	473	22
#10 / 4 C	GRF10/4	.29 X .89 (7.4 X 22.6)	238	354	32
#8 / 4 C	GRF8/4	.375 X 1.225 (9.5 X 31.1)	420	625	45
#6 / 4 C	GRF6/4	.435 X 1.49 (11 X 37.8)	650	967	60
#4 / 4 C	GRF4/4	.515 X 1.75 (13.1 X 44)	910	1354	78
#2 / 4 C	GRF2/4	.575 X 1.975 (14.6 X 50.2)	1325	1972	104

DESCRIPTION: Jacket: PVC Yellow 302°F (150°C), UL / CSA approved. Conductors: Insulation: .03 - .06 in. Flexible Stranded Conductors 600 V / 150°F (66°C)

PENDANT CABLE					
SIZE	MODEL #	DIMENSIONS - IN (MM)	WEIGHT		AMPACITY
			LBS/MFT	KG/KM	
Nylon Round / PVC with two Galvanized Steel (1/16") Wires, Yellow, 194°F (90°C), 600 V, UL and CSA approved					
#16 / 8 C	GRR16/8SR	0.495 (12.6mm)	179	266	7
#16 / 12 C	GRR16/12SR	0.57 (14.4mm)	260	394	7
#16 / 16 C	GRR16/16SR	0.63 (16.0 mm)	319	510	7
#16 / 24 C	GRR16/24SR	0.765 (19.4 mm)	440	656	6
Nylon Round / PVC (No Strain Relief), Yellow, 194°F (90°C), 600 V, UL and CSA approved					
#16 / 8 C	GRR16/8	0.47 (11.93 mm)	138	206	7
#16 / 12 C	GRR16/12	0.55 (13.97 mm)	198	295	7
#16 / 16 C	GRR16/16	0.61 (15.49 mm)	225	335	7
#16 / 24 C	GRR16/24	0.745 (18.9 mm)	370	551	6

Round Cable continued on next page.

ROUND BLACK NEOPRENE CABLE

SIZE	MODEL #	DIMENSIONS - IN (MM)	WEIGHT		AMPACITY
			LBS/ MFT	KG/KM	
#16 / 2 C	GRR16/2	0.38 (9.65 mm)	81	121	16
#16 / 3 C	GRR16/3	0.40 (10.2 mm)	96	143	16
#16 / 4 C	GRR16/4	0.43 (10.9 mm)	106	158	13
#16 / 5 C	GRR16/5	0.505 (12.8 mm)	201	299	13
#16 / 6 C	GRR16/6	0.59 (15 mm)	201	299	13
#16 / 8 C	GRR16/8	0.70 (17.8 mm)	278	414	11
#16 / 10 C	GRR16/10	0.755 (19.2 mm)	299	445	11
#16 / 12 C	GRR16/12	0.775 (19.7 mm)	342	509	11
#16 / 14 C	GRR16/14	0.81 (20.6 mm)	382	569	11
#16 / 16 C	GRR16/16	0.845 (21.5 mm)	416	619	11
#16 / 20 C	GRR16/20	0.925 (23.5 mm)	506	753	11
#16 / 24 C	GRR16/24	1.04 (26.4 mm)	640	953	10
#16 / 30 C	GRR16/30	1.165 (29.6 mm)	823	1225	10
#16 / 36 C	GRR16/36	1.32 (33.5 mm)	1048	1560	10
#14 / 3 C	GRR14/3	0.54 (13.7 mm)	157	234	23
#14 / 4 C	GRR14/4	0.61 (15.5 mm)	135	201	12
#14 / 6 C	GRR14/6	0.775 (19.7 mm)	328	488	18
#14 / 8 C	GRR14/8	0.89 (22.6 mm)	447	665	16
#14 / 10 C	GRR14/10	0.99 (25.1 mm)	500	744	16
#14 / 12 C	GRR14/12	1.02 (25.9 mm)	568	846	16
#14 / 14 C	GRR14/14	1.065 (27.1 mm)	630	938	16
#14 / 16 C	GRR14/16	1.12 (28.4 mm)	714	1063	16
#14 / 20 C	GRR14/20	1.265 (32.1 mm)	897	1335	16
#14 / 24 C	GRR14/24	1.375 (34.9 mm)	1084	1614	14
#14 / 30 C	GRR14/30	1.55 (39.4 mm)	1403	2089	14
#14 / 36 C	GRR14/36	1.725 (43.8 mm)	1748	2602	14
#12 / 3 C	GRR12/3	0.62 (15.7 mm)	210	313	27
#12 / 4 C	GRR12/4	0.67 (17 mm)	267	398	22
#12 / 6 C	GRR12/6	0.835 (21.2 mm)	410	610	22
#12 / 8 C	GRR12/8	0.990 (25.1 mm)	591	880	19
#12 / 10 C	GRR12/10	1.070 (27.2 mm)	645	960	19
#12 / 12 C	GRR12/12	1.10 (27.9 mm)	708	1054	19
#12 / 14 C	GRR12/14	1.155 (29.3 mm)	806	1200	19
#12 / 16 C	GRR12/16	1.215 (30.9 mm)	899	1338	19
#12 / 20 C	GRR12/20	1.37 (34.8 mm)	1144	1703	19
#12 / 24 C	GRR12/24	1.495 (38 mm)	1378	2054	16
#12 / 30 C	GRR12/30	1.69 (42.9 mm)	1796	2674	16
#12 / 36 C	GRR12/36	1.94 (49.3 mm)	2374	3534	16
#10 / 4 C	GRR10/4	0.76 (19.8 mm)	355	528	20


Gleason Reel Corp.

600 South Clark St.
 Mayville, WI 53050
 Phone: 920-387-4120
 Fax: 920-387-4189

www.hubbell.com/gleasonreel/en