

OUTLETS and LIGHTS



HUBBELL® Brand

Model **FL-120**

Fluorescent Hand Lamp Includes: Protected switch, Cushioned End Cap, Polycarbonate Outer Tube and End Lens, Directed Light (from one side plus magnified from end), Integral Ballast, 13 watt, 900 lumen PLS-13 Lamp (included).

Fluorescent Hand Lamp only; does not include reel.



Model **EHL-120**

Hand Lamp Includes: Plastic Grip, Switch, Metal Guard/Reflector, Receptacle

Hand Lamp only; does not include reel.



Model **LED-120-A**

LED Lamp Includes: Cushioned Hand Cap with Internal Ballast, Covered ON/OFF Switch in Handle, Clear Polycarbonate Lens with Reflector Label and Cushioned Outer Ring, Produces 920 Lumens, 1/2 Watt LED's rated @ 50,000 hours, One-watt LED flashlight at the end of the fixture, 120 Volt, 0.65 Amps, 50-60 Hz.

LED Lamp only; does not include reel.



HUBBELL® Brand

Model **DR-GFCI**

High Impact Plastic Box with Hinged Cover, NEMA 3R 20 Amp Receptacle, Cord Grip, 20 Amp Ground Fault Module, Gasketed Cover Plates

Duplex Receptacle only; does not include reel.



HUBBELL® Brand

Model **SR-15A**

Single Outlet, 15 Amp

Receptacle only; does not include reel.



HUBBELL® Brand

Model **SR-20A**

Single Outlet, 20 Amp

Receptacle only; does not include reel.

