

Standard Service Poles

Aluminum service poles from Hubbell Canada provide the perfect solution when dropping communications and power cables from a ceiling plenum to workstations below. These high quality poles are rugged and fast to install. They have plenty of capacity to house bundles of cables and are aesthetically pleasing.

Standard service poles are offered in 3 configurations – *Communications Only* (Blank poles, no receptacles installed), *Power Only* (no knockouts for data frames), or *Power and Communications* (receptacles installed plus knockouts for data frames). Data knockouts and receptacles are positioned at standard heights which suit most applications, and poles are available in lengths up to 22ft! These poles come in 4 colour options and are available with a variety of receptacles. Our easy to use Part Logic allows you to specify the pole that is right for your application!

Need the data knockouts or receptacles at a different height or spacing? Need some specific devices not listed in our standard part logic?



Check out our Custom Service Pole offering!

FEATURES	BENEFITS
Made in Canada!	Short lead time on product. Select styles and quantities available within 24 hours.
Wide variety of finishes available	Attractive, durable finish
Internal Barrier isolates voice/data channel from power channel	Delivers greater flexibility and capacity per pole
Power and data devices are accessible from the same side of the pole	Easy to access devices regardless of pole location
Extruded aluminum design	Strong and lightweight



DEVICE CAPACITY

- Maximum of 4 circuits allowed, with a maximum of 4 duplex receptacles or 8 outlets per circuit. (32 outlets available on a 4 circuit pole)
- Receptacles with different ratings used in one service pole must have their own designated circuits
- Isolated ground applications must be wired on a designated circuit
- Receptacles are spaced a minimum of 4.0" apart on single and duplex devices.
 StyleLine[®] devices require 4.5" minimum spacing

PRODUCT DETAILS

Pole Extruded aluminum with painted or anodized finish

Barrier Steel

Base Foam, field configurable for a variety of floor finishes

T-Bar Mounting Bracket | Steel, powder coat white

Junction box Steel, 14, 16, or 21 cu. in. capacity, comes with blank cover

Circuit Wire #12 (20A) or #14 (15A) Copper Conductor

Approvals CSA certified

(1)

COLOUR OPTIONS

Standard colours are as follows:









Black

Clear Anodized

Consult Factory for custom coloured paint and anodizing options.

POWER ENTRY OPTIONS


RECEPTACLE OPTIONS

COMMUNICATIONS KNOCKOUTS



Molded Cord and Plug

Junction Box



Duplex Specification Grade



Duplex StyleLine®



Duplex Isolated Ground





ORDERING INFORMATION - STANDARD SERVICE POLE

A25	9 6	2	4	DIG	BJ	2CT	w
Series	Length in Feet and Inches	# of Data Knock outs	# of Outlets	Receptacle Type	Junction Box	# of Circuits	Colour
A25 TBar ceiling	Min. 3 ft. Max. 22 ft. (Please order in increments of 1 inch)	Increments of 1: 1,2, 3 etc	Increments of 2: 2, 4, 6 etc as 2 "outlets" = 1 Duplex receptacle	D = Duplex D2 = 20A Duplex DIG = Duplex Isolated Ground DSL = Style line Duplex	BJ = Junction Box IG receptacles MUST have Junction Box Blank = No Junction Box	1CT = Leave blank 2CT = 2 Circuit 3CT = 3 Circuit 4CT = 4 Circuit (Maximum is 4 Circuits)	Blank = Gray W = White AN = Anodized Aluminum BK - Black

PART NUMBER EXAMPLES

(Below are some common configurations of service poles in a painted gray finish)

A259624D A2510624D A2512624D	Service pole complete with two specification grade duplex receptacles pre-wired for one circuit, two StyleLine [®] data knockouts and 10ft molded cord and plug. Includes trim ring for ceiling tile, and non-slip base pad.	
A259624DSL A2510624DSL A2512624DSL	Service pole complete with two specification grade StyleLine [®] receptacles pre-wired for one circuit, two StyleLine [®] data knockouts and 10ft molded cord and plug. Includes trim ring for ceiling tile, and non-slip base pad.	
A2596222DRIGBJ A25106222DRIGBJ A25126222DRIGBJ	Service pole complete with one isolated ground orange duplex receptacle and one standard duplex receptacle pre-wired for two circuits, two StyleLine [®] data knockouts and junction box for easy termination of power wiring. Includes trim ring for ceiling tile, and non-slip base pad.	
A259600 A2510600 A2512600	Communications Only service pole with two StyleLine [®] communications knockouts. Includes trim ring for ceiling tile and non-slip base pad.	

Notes:

- 1) Above part numbers with power and data come with a 15A molded cord and plug entry. For Junction Box version simply add "BJ" to the end of the part number for example A259624DBJ
- 2) When ordering a service pole with a mix of standard duplex and Isolated Ground (IG) receptacles add "R" to indicate "regular duplex" for example A2596222DRIGBJ



OTHER DELIVERY SYSTEMS PRODUCTS BUILT BY HUBBELL CANADA













