



ACA Industrial & Industrial Weatherproof Cord Reels



Providing improved solutions through innovation

Hubbell's redesigned ACA Industrial and Industrial Weatherproof Cord Reels enhance user safety and maximize efficiency by managing cord and power in a safe and organized manner, while also meeting the demands of tough industrial environments.

ACA Industrial and Industrial Weatherproof Cord Reels are listed to UL 355 and CSA, C22.2 No. 308 with a durable, lightweight low profile cast aluminum construction. ACA reels also feature an improved mounting plate that allows customers to upgrade existing installations or use Hubbell's innovative mounting bracket for a quick, easy installation on any surface.

Features

ACA Industrial and Industrial Weatherproof Cord Reels

- Durable, corrosion resistant cast aluminum construction
- Yellow or white powder coat finish
- Movable guide arm can be mounted in two positions
- Positive latch mechanism automatically maintains desired cord length
- Ratchet lock can be disengaged in field for constant tension applications
- 16-10AWG, 3 & 4 conductor cord for greater current carrying capacity
- 10AWG fully rated at 30 amps
- Available in 25ft, 35ft and 45ft lengths
- Rugged, lightweight aluminum case

ACA Industrial Cord Reels

- UL Type 1
- 250V AC, Bare SJO Cable
- Plug-in 5ft long power cord requires no electrical wiring

WCA Industrial Weatherproof Cord Reels

- UL Type 4
- 600V AC, SOW Type Cable
- 3/4 NPT conduit hub



ACA Mounting Bracket

Labor Savings Are Reel

The ACA mounting bracket allows you to decrease or eliminate the additional labor associated with installing reels at the end of the job. By starting the installation during the earlier stages of the project when there are fewer time constraints, the ACA mounting bracket reduces trim-out to a fraction of the time.

Step 1

Secure the ACA mounting bracket during the rough-in process.



Step 2

Remove two of the hex bolts from the bracket. Slide the reel into the mounting bracket.



Step 3

Replace two hex bolts and secure screws to complete the job.



Series WCA Industrial Weatherproof Cord Reels (yellow)

Model	Accessory	Amps	Voltage	AWG	Cond.	Cord. Type	Length Ft. (m)	Weight Lbs. (kg)
WCA16345-BC	None	10	600V AC	16	3	SOW	45 (13.7)	23.6 (10.7)
WCA16445-BC	None	10	600V AC	16	4	SOW	45 (13.7)	25.6 (11.6)
WCA14345-BC	None	15	600V AC	14	3	SOW	45 (13.7)	28.2 (12.8)
WCA14445-BC	None	15	600V AC	14	4	SOW	45 (13.7)	30.0 (13.6)
WCA12345-BC	None	20	600V AC	12	3	SOW	45 (13.7)	31.3 (14.2)
WCA12440-BC	None	20	600V AC	12	4	SOW	40 (12.2)	32.2 (14.6)
WCA10340-BC	None	30	600V AC	10	3	SOW	40 (14.2)	33.3 (15.1)
WCA10435-BC	None	30	600V AC	10	4	SOW	35 (10.7)	34.2 (15.5)

Note: The above models are supplied without input or output end effectors. For shorter cable lengths, modify length indication in catalog number (i.e. WCA123XX); 35ft. & 25ft. Lengths available. For white reels, add "W" suffix to end of model number.

ACC Cable Reels

Model	Accessory	Amps	Voltage	AWG	Cond.	Cord. Type	Length Ft	Length M	Weight Lbs. (kg)
ACC12390-BC20	20A plug on non moving end	18A	250V	12	3	SJO	90	27.5	86.46(39.22)
ACC12370-BC20	20A plug on non moving end	18A	250V	12	3	SJO	70	21.3	79.64(36.12)
ACC12480-BC20	20A plug on non moving end	16A	250V	12	4	SJO	80	24.4	76.12(34.53)
ACC10370-BC20	20A plug on non moving end	25A	250V	10	3	SJO	80	24.4	104.28(47.30)
ACC10470-BC20	20A plug on non moving end	20A	250V	10	4	SJO	80	24.4	113.30(51.39)
WCC-12380-BC	None	18A	600V	12	3	SOW	80	24.4	97.46(44.21)
WCC-12475-BC	None	16A	600V	12	4	SOW	75	22.8	107.36(48.70)
WCC-12850-BC	None	14A	600V	12	8	SOW	45	13.7	110.44(50.09)
WCC-10375-BC	None	25A	600V	10	3	SOW	75	22.8	103.84(47.10)
WCC-10475-BC	None	20A	600V	10	4	SOW	75	22.8	116.16(52.69)
WCC-8360-BC	None	30A	600V	8	3	SOW	60	18.2	123.20(55.88)
WCC-8345-BC	None	40A	600V	8	3	SOW	45	13.7	106.48(48.30)
WCC-8445-BC	None	35A	600V	8	4	SOW	45	13.7	122.76(55.68)
WCC-6345-BC	None	55A	600V	6	3	SOW	45	13.7	122.98(55.78)
WCC-6445-BC	None	55A	600V	6	4	SOW	45	13.7	126.72(57.78)
WCC-141245-BC	None	6A	600V	14	12	SOW	45	13.7	113.52(51.49)

ACA CORD REELS

Series ACA Industrial Cord Reels (yellow)

Model	Accessory	Amps	Voltage	AWG	Cond.	Cord. Type	Length Ft. (m)	Weight Lbs. (kg)
ACA16445-BC	None	10A	250V AC	16	4	SJO	45 (13.7)	23.6 (10.7)
ACA14445-BC	None	15A	250V AC	14	4	SJO	45 (13.7)	25.6 (11.6)
ACA12445-BC	None	20A	250V AC	12	4	SJO	45 (13.7)	28.2 (12.8)
ACA10345-BC	None	20A	250V AC	10	3	SJO	45 (13.7)	30.0 (13.6)
ACA10440-BC	None	30A	250V AC	10	4	SJO	40 (12.2)	31.3 (14.2)

The above models are supplied without input or output end effectors.

For shorter cable lengths, modify length indication in catalog number (i.e. ACA124XX); 35 ft. & 25 ft. Lengths available.

For white reels, add "W" suffix to end of model number.

Series ACA Industrial Cord Reels (yellow)

Model	Accessory	Amps	Voltage	AWG	Cond.	Cord. Type	Length Ft. (m)	Weight Lbs. (kg)
ACA16345-SR15	Single Receptacle HBL5269C	10A	125V AC	12	3	SJO	45 (13.7)	22.9 (10.4)
ACA14345-SR15	Single Receptacle HBL5269C	15A	125V AC	12	3	SJO	45 (13.7)	24.0 (10.9)
ACA12345-SR20	Single Receptacle HBL5369C	20A	125V AC	12	3	SJO	45 (13.7)	26.5 (12.0)
ACA16345-DR15	Dual Receptacle GFCI Module & (1) 15A Duplex	10A	125V AC	12	3	SJO	45 (13.7)	22.9 (10.4)
ACA14345-DR15	Dual Receptacle GFCI Module & (1) 15A Duplex Receptacle	15A	125V AC	12	3	SJO	45 (13.7)	24.0 (10.9)
ACA12345-DR20	Dual Receptacle GFCI Module & (1) 20A Duplex Receptacle	20A	125V AC	12	3	SJO	45 (13.7)	26.5 (12.0)
ACA16345-BC15	Blind Cord No Output End Effector	10A	125V AC	12	3	SJO	45 (13.7)	22.9 (10.4)
ACA14345-BC15	Blind Cord No Output End Effector	15A	125V AC	12	3	SJO	45 (13.7)	24.0 (10.9)
ACA12345-BC20	Blind Cord No Output End Effector	20A	125V AC	12	3	SJO	45 (13.7)	26.5 (12.0)
ACA12345-TL20	Twist Lock HBL2313	20A	125V AC	12	3	SJO	45 (13.7)	26.5 (12.0)

10A & 15A reels are supplied with HBL5266C on the power supply cord. 20A reels are supplied with HBL5366C on the power supply cord.

For shorter cable lengths, modify length indication on in catalog number (i.e. ACA123XX); 35ft & 25ft. Lengths available.

For white reels, add "W" suffix to end of model number.

Series ACA Industrial Lighted Cord Reels (Yellow)

Model	Accessory	Amps	Voltage	AWG	Cond.	Cord. Type	Length Ft. (m)	Weight Lbs. (kg)
ACA16345-LED	LED Hand Lamp with end light	0.07A 8+1	120V AC	16	3	SJO	45 (13.7)	22.9 (10.4)
ACA16345-FL	Fluorescent Hand Lamp	0.3A 13	120V AC	16	3	SJO	45 (13.7)	22.9 (10.4)
ACA16345-HL	Incandescent Hand Lamp	0.8A 100	125V AC	16	3	SJO	45 (13.7)	22.9 (10.4)

15A reels are supplied with HBL5266C on the power supply cord.

For shorter cable lengths, modify length indication on in catalog number (i.e. ACA163XX); 35ft. & 25ft. Lengths available.

For white reels, add "W" suffix to end of model number.

WCA/ACA Mounting Accessories

Description	Weight lbs. (kg)	Model
Mounting bracket	2.5 (1.1)	HBLIMB
340° pivot base	3.5 (1.6)	HBLI340PB

WCA/ACA Replacement Parts

Description	Weight lbs. (kg)	Cable Type	Model
Replacement Stop	0.2 (.09)	16AWG	HBLI16B5
		14AWG	HBLI14B5
		12AWG	HBLI12B5
		10AWG	HBLI10B5

©2024 Gleason Reel. All rights reserved.

Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners.

600 S. Clark Street, Mayville, WI 53050

www.hubbell.com/gleasonreel | 920-387-4120

HHI-GR-BR-EN-01880 | 2/2024

A Hubbell brand

