




The new 2" Slot is our SLIMMEST fixture ever.

Featuring the same great performance and versatility as the existing MODx Family, all within a slim profile.



- VI technology
- Standard (Lambertian), Low Peak Angle (batwing) and Asymmetric distributions
- Magnetic end caps, simple row joining and captive reflectors ensure a quality installation
- Customize your fixture with several lens, color temperature, finish and control/sensor options
- Multiple size options available:

6"

Pendant 2L-P-ID









PENDANT, SURFACE, WALL

Feature	Options		
Series	2L		
Mounting	P	Pendant	
	S	Surface	
	W	Wall	
Fixture Distribution	D	Direct	
	ID	Indirect/Direct	
	AD	Asymmetric Direct	
	AID	Asymmetric Indirect/Direct	
Uplight Distribution	STD	Standard	
	LPA	Low Peak Angle (batwing)	
Max Length (in row)	02		
	03		
	04		
	05		
	06		
	08		
Downlight Diffuser	SOF	Soft Diffuse	
	RGL	Regressed	
	BWO	Blade Baffle with overlay	
	ASYM	Asymmetric	
Finish/Color	C1	Matte White	
	C2	Textured Matte White	
	C3	Light Silver	
	C4	Machined Aluminum	
	C5	Carbon Black	
	(6	Textured Camera Black	
	CC	Custom	
Color Temperature	30K	3000K	
	35K	3500K	
	40K	4000K	
	2230TD	2200K-3000K SpectraSync™ Dim-to-Warm 2700K-5000K SpectraSync™ Tunable White	
	2750T 2765T	2700K-6500K SpectraSync™ Tunable White	
Indirect Output/ft	1030 (min)	27 JOHN JUNE SPECIAL SYNC TUNABLE WHILE	
mairect output/ft			
Direct Output/ft	1125 (STD-max); 1090 (LPA-max) D030 (min)		
Direct Output/It	D100 (max)		
	ע וווע (ווואא)		

RECESSED

Feature	Options	
Series	2L	
Mounting	R	Recessed
Fixture Distribution	D	Direct
	AD	Asymmetric Direct
Row Length Adder (in inches)	/3	
	/6	
	/9	
Max Length (in row)	02	
	03	
	04	
	05	
	06	
	08	
Downlight Diffuser	SOF	Soft Diffuse
	RGL	Regressed
	BWO	Blade baffle with overlay
	ASYM	Asymmetric
Finish/Color	C1	Matte White
Color Temperature	30K	3000K
	35K	3500K
	40K	4000K
	2230TD	2200K-3000K SpectraSync™ Dim-to-Warm
	2750T	2700K-5000K SpectraSync™ Tunable White
	2765T	2700K-6500K SpectraSync™ Tunable White
Direct Output/ft	D030 (min)	
·	D085 (max)	

NOTE: Additional options include: Emergency battery, Occupancy sensor, Daylight sensor, dust cover, corners and **DLC Certified Distributed Intelligence Networks**. Review specification sheet for details.

NEW: Available across MODx Family







