LC6HL & LC8HL

LED DOWNLIGHTS AND RETROFIT

Liteframe Commercial LED HIGH LUMEN (HL)

Prescolite's Liteframe Commercial HL is designed to provide high outputs, high efficacies, and high performance at a price that makes LED the right choice over traditional sources.



- Two distinct output options of 4500 and 6000 lumens
- Minimum 50,000 hours life at 70% lumen maintenance
- Anodized Aluminum reflector
- Applicable for mounting heights up to 40ft.
- Replace 100 –150 watt MH with up to a 50% wattage consumption reduction



LC6HL

LC8HL







HUBBELL Lighting

LC6HL/LC8HL/RLC6HL/RLC8HL

The new High Lumen package uses a high power LED array which allows us to manage the heat by spreading the LED's over a larger surface area to minimize hotspots, while maintaining our color consistency from fixture to fixture.

Additional Features include:

- Choice of 80+ or 90+ CRI with 3 SDCM color consistency
- 2700K, 3000K, 3500K, 4000K, and 5000K color temperatures
- Universal voltage driver ranging from 120 277 volts
- 0-10V dimming is standard down to 5% light output
- Compatible with Prescolite sloped ceiling adapters



Contact a Prescolite sales representative today to learn more about growing capabilities in the high lumen downlight market, and how to specify LiteFrame Commercial HL for your next lighting project.

