

# HID to LED Upgrade Kits

LUMINAIRE			PICOPRISM®				PICOEMITTER®				
NAME	NOMEN-CLATURE	VOLTS - AC	CURRENT	SYS. WATTS	LUMEN RANGES	REPLACES	CURRENT	SYS. WATTS	LUMEN RANGES	REPLACES	
Warp9	WP9S	120 / 208 / 240 277 / 347 / 480	350mA	69	4679 to 7137	175W MH up to 250W PMH	350mA	66	4599 to 6601	175W MH up to 250W PMH	
			700mA	131	7621 to 12904	250W MH up to 320W PMH					
	WP9L		350mA	137	8960 to 14930	250W MH up to 320W PMH	350mA	132	9023 to 12611	250W MH up to 320W PMH	
			700mA	274	14577 to 25259	360W PMH up to 500W PMH					
The Archetype	SAR	120 / 208 / 240 277 / 347 / 480	350mA	46	3242 to 4930	100W MH up to 150W PMH	350mA	65	3156 to 5527	175W MH up to 250W PMH	
			700mA	93	5493 to 8447	150PMH up to 250W PMH					
	AR		350mA	95	6205 to 9984	150PMH up to 250W PMH	350mA	129	6636 to 11689	250W MH up to 320W PMH	
			700mA	188	11511 to 17891	400W MH					
Structural	STS	120 / 208 / 240 277 / 347 / 480	350mA	46	3242 to 4967	100W MH up to 150W PMH	350mA	68	3386 to 5934	175W MH up to 250W PMH	
			700mA	92	5493 to 8447	150PMH up to 250W PMH					
	STL		350mA	94	6205 to 9837	150PMH up to 250W PMH	350mA	130	6021 to 11012	250W MH up to 320W PMH	
			700mA	188	11511 to 17891	400W MH					
The Entablature	SET	120 / 208 / 240 277 / 347 / 480	350mA	46	3242 to 4930	100W MH up to 150W PMH	350mA	67	3112 to 5704	175W MH up to 250W PMH	
			700mA	93	5493 to 8447	150PMH up to 250W PMH					
	ET		350mA	94	6205 to 9699	150PMH up to 250W PMH	350mA	103	5029 to 9208	150W PMH up to 250W PMH	
			700mA	188	11511 to 17891	400W MH					
EKG	EKG401/ EKG501	120 / 208 / 240 277 / 347 / 480	350mA	94	5596 to 9004	150PMH up to 250W PMH	—	—	—	—	
			700mA	185	10337 to 16067	400W MH	—	—	—	—	
Curvilinear	CC17	120 / 208 / 240 277 / 347 / 480	—	—	—	—	350mA	67	3248 to 5581	175W MH up to 250W PMH	
	CC21		—	—	—	—	350mA	121	6638 to 11794	250W MH up to 320W PMH	
	CC25		350mA	111	7103 to 11691	150W PMH up to 250W PMH	—	—	—	—	
			700mA	228	12136 to 19867	360W PMH up to 500W PMH	—	—	—	—	
Solitaire	SRS1	120 / 208 / 240 277 / 347 / 480	—	—	—	—	350mA	67	3905 to 5680	175W MH up to 250W PMH	
NeoSphere	NSL	120 / 208 / 240 277 / 347 / 480	—	—	—	—	350mA	66	1996 to 4523	175W MH up to 250W PMH	
Bounce	BNS1	120 / 208 / 240 277 / 347 / 480	—	—	—	—	350mA	66	2941 to 4852	175W MH up to 250W PMH	
Era	RA17	120 / 208 / 240 277 / 347 / 480	—	—	—	—	350mA	68	3563 to 6016	175W MH up to 250W PMH	
	RA25		—	—	—	—	350mA	126	6556 to 11651	250W MH up to 320W PMH	
Era Bell	BE17	120 / 208 / 240 277 / 347 / 480	—	—	—	—	350mA	67	3354 to 5467	175W MH up to 250W PMH	
	BE21		—	—	—	—	350mA	128	6391 to 11381	250W MH up to 320W PMH	
Era Acorn	AE17	120 / 208 / 240 277 / 347 / 480	—	—	—	—	350mA	68	3987 to 6687	175W MH up to 250W PMH	
	AE21		—	—	—	—	350mA	126	8568 to 12758	250W MH up to 320W PMH	
Era Lantern	LE19	120 / 208 / 240 277 / 347 / 480	—	—	—	—	350mA	67	2951 to 5159	175W MH up to 250W PMH	
Wall Director	WD14	120 / 208 / 240 277 / 347 / 480	—	—	—	—	350mA	65	3823 to 5460	175W MH up to 250W PMH	
	WD18		—	—	—	—	350mA	127	6021 to 10070	250W MH up to 320W PMH	

