



Your guide to selecting the perfect fixtures for your space.

The lighting and ceiling fans you select for your home should not only be functional, it is your opportunity to express your personality and elevate each room's design aesthetic. While there are many choices to make during the selection process, it doesn't have to be overwhelming. This catalog is intentionally designed so you can quickly understand different options and characteristics of each fixture category. It is your guide to easily and efficiently plan functional, beautiful lighting for every room in your home.



Using this tool.



Go to the **Product Finder** starting on page 04 to search for your perfect fixture.



Use colored tabs to quickly turn to product sections.



Get more detailed information by searching the product number at: **ProgressLighting.com** 04 PRODUCT FINDER



DESIGN SERIES



106 COLLECTIONS

284 PENDANTS

344 CEILING FANS

458 CLOSE-TO-CEILING

484 SCONCES

498 BATH

618 OUTDOOR

736 FUNCTIONAL

738 Recessed Downlighting

749 Surface Mount Downlighting

756 Directionals


760 Undercabinet


766 Steplights

768 Egress


770 Reference Guide

778 Index


















Collections LED



PROGRESS LIGHTING


Pendants Hall & Foyer






Pendants Hall & Foyer






Pendants Medium





Pendants Medium






Pendants Mini





Pendants Mini





Pendants Mini






WISTENBrushed Nickel

250


Pendants LED










PROGRESS LIGHTING








PROGRESS LIGHTING















CATALOG 134


Ceiling Fans Indoor


WILLACY Black	WILLACY Painted Nickel
350	350

Ceiling Fans Outdoor





Ceiling Fans Outdoor







Ceiling Fans Outdoor





Close-to-Ceiling







Close-to-Ceiling COFIELD COFIELD COFIELD COFIELD COFIELD Vintage Brass Brushed Nickel Matte Black Polished Chrome Vintage Brass 460 460 460 460 DELAYNE DELAYNE **DELAYNE** DOME GLASS DOME GLASS Brushed Bronze Brushed Nickel Matte Black Antique Bronze Brushed Nickel 461 461 **DOME GLASS** DOME GLASS **DOME GLASS DOME GLASS** DOME GLASS Forged Black Polished Chrome White Antique Bronze Brushed Nickel 472 472 472












Close-to-Ceiling





Close-to-Ceiling



 VERTEX
 VERTEX

 Brushed Nickel
 Brushed Nickel


 465
 465

 465
 465

Close-to-Ceiling LED



Close-to-Ceiling LED



Wall Sconces LED



Wall Sconces LED




Wall Sconces



Wall Sconces



Wall Sconces



Wall Sconces Swing Arm



Wall Brackets

ADLEY ADLEY ADLEY **ADLEY ADLEY** Brushed Nickel Matte Black Polished Nickel Satin Brass Brushed Nickel 531 531 531 531 533 **ADLEY ADLEY ADORN ADORN ADORN** Satin Brass Matte Black Antique Bronze Brushed Nickel Polished Chrome 533 533 610 610 610 **AIKEN AIKEN ALABASTER GLASS** ALEXA **ALEXA** Brushed Nickel Vintage Brass Brushed Nickel Antique Bronze Brushed Nickel 563 602 602 **AMBROSE AMBROSE ANJOUX ANJOUX APPEAL** Matte Black Polished Chrome Antique Bronze Silver Ridge Brushed Nickel 581 581 577 577 600















ARCHIE










589









ARCHIE







BECKNER Matte Black	BOWMAN Matte Black	BRAMLETT Brushed Nickel	BRAMLETT Polished Chrome	BRAVO Antique Bronze
567	595	574	574	604
BRAVO Brushed Nickel	CAISSON Brushed Nickel	CAISSON Graphite	CALAIS Brushed Nickel	CALAIS Matte Black
604	553	553	527	527
CALAIS Vintage Brass	CALHOUN Antique Bronze	CALHOUN Brushed Nickel	CALHOUN Vintage Brass	CARISA Brushed Nickel
527	587	587	587	607
CARISA Vintage Gold	CASCADIA Antique Bronze	CASCADIA Polished Chrome	CLARION Brushed Nickel	CLARION Matte Black
607	600	600	534	534
CLARION Polished Chrome	CLARION Satin Brass	CLASSIC Brushed Nickel	CLASSIC Matte Black	CLIFTON HEIGHTS Antique Bronze
534	534	612	612	599
CLIFTON HEIGHTS Brushed Nickel	CLIFTON HEIGHTS Matte Black	CONWAY Brushed Nickel	CONWAY Matte Black	COPELAND Brushed Gold
599	599	555	555	541

Wall Brackets

COPELAND COWAN COWAN COWAN **COPELAND** Brushed Nickel Matte Black Brushed Nickel Matte Black Satin Brass 539 539 539 **DALTON** DALTON **ELARA ELARA ELARA** Brushed Nickel Matte Black Vintage Brass Polished Chrome Vintage Brass 584 584 529 529 529 **FESSLER FESSLER FESSLER** FLEET **FLEET** Brushed Nickel Matte Black Vintage Brass Brushed Nickel Polished Chrome 573 601 **FLUTED CLEAR GLASS FLUTED CLEAR GLASS FLUTED ETCHED GLASS FLUTED ETCHED GLASS GATHER** Polished Chrome Brushed Nickel Polished Chrome Antique Bronze





GATHER

613

Brushed Nickel





613















615

GILMOUR

Matte Black





613





GOODWIN








HAVEN Brushed Nickel	HAVEN Matte Black	HAVEN Vintage Brass	HEART Antique Bronze	HEART Brushed Nickel
543	543	543	611	611
HEART Polished Chrome	INSPIRE Antique Bronze	INSPIRE Brushed Nickel	INSPIRE Polished Chrome	INVITE Brushed Nickel
611	607	607	607	254
JOY Antique Bronze	JOY Brushed Nickel	JUDSON Antique Bronze	JUDSON Polished Nickel	LAIRD Antique Bronze
257	257	588	588	258
LAIRD Brushed Nickel	LEAGUE Brushed Nickel	LEAGUE Matte Black	LEAP Antique Bronze	LEAP Brushed Nickel
258	599	599	601	601
LITCHFIELD Polished Nickel	LYNZIE Brushed Gold	LYNZIE Matte Black	LYNZIE Polished Chrome	MADISON Antique Bronze
578	583	583	583	606
MADISON Brushed Nickel	MADISON Polished Chrome	MAST Antique Bronze	MAST Brushed Nickel	MERRY Brushed Nickel
606	606	193	193	260

Wall Brackets



VICTORIAN Polished Chrome	VICTORIAN Venetian Bronze	WINSLETT Brushed Nickel	WINSLETT Matte Black	WISTEN Brushed Nickel
610	610	594	594	602

Bath LED

ACE LED Polished Chrome	ARCH LED Brushed Nickel	BARRIL LED Brushed Nickel	BARRIL LED Matte Black	BATH LED Brushed Nickel
506	507	523	523	524
BEAM LED Architectural Bronze	BEAM LED Brushed Nickel	BEAM LED Polished Chrome	BLANCO LED Brushed Nickel	BLANCO LED Matte Black
514	514	514	511	511
BLANCO LED Satin Brass	CLOUD LED Opal White	COLONNADE LED Brushed Nickel	COLONNADE LED Polished Chrome	CONCOURSE LED Brushed Nickel
511	525	505	505	508
)
EVERLUME® VANITY LED Brushed Nickel	EVERLUME® VANITY LED Satin White	FRAME LED Brushed Nickel	GRID LED Black	GRID LED Silver Ridge
525	525	509	510	510
		***)	
PARALLEL LED Architectural Bronze	PARALLEL LED Brushed Nickel	PARALLEL LED Polished Chrome	PARALLEL LED Satin Brass	PEARL LED Matte Black
513	513	513	513	504
				000

Bath LED

PEARL LED Satin Brass	PHASE 1.1 LED Brushed Nickel	PHASE 1.2 LED Brushed Nickel	PHASE 2.1 LED Brushed Nickel	PHASE 2.2 LED Brushed Nickel
504	516	517	518	519
000				





Mirrors LED

CAPTARENT LED White	CAPTARENT LED White	CAPTARENT LED White	
503	503	503	

ADLEY Brushed Nickel	ADLEY Matte Black	ADLEY Polished Nickel	ADLEY Satin Brass	ADLEY Brushed Nickel
531	531	531	531	532
				The state of the s
ADLEY Matte Black	ADLEY Satin Brass	ADORN Antique Bronze	ADORN Brushed Nickel	ADORN Polished Chrome
532	532	610	610	610
AIKEN Brushed Nickel	AIKEN Vintage Brass	ALABASTER GLASS Brushed Nickel	ALEXA Antique Bronze	ALEXA Brushed Nickel
563	562	616	602	602
AMBROSE	AMBROSE Polished Chrome	ANJOUX	ANJOUX	APPEAL
Matte Black 581	581	Antique Bronze 577	Silver Ridge 577	Brushed Nickel 600
APPEAL Polished Chrome	ARCHIE Antique Nickel	ARCHIE Polished Chrome	ARCHIE Venetian Bronze	ARCHIE Vintage Brass
600	589	589	589	589

ARCHIVES Antique Bronze	ARCHIVES Antique Nickel	ASHFORD Brushed Nickel	ASHFORD Polished Chrome	AVALON Brushed Nickel
597	597	580	580	614
		na. n		
AXLE Antique Bronze	AXLE Brushed Nickel	BARNES MILL Antique Bronze	BECKNER Brushed Nickel	BECKNER Matte Black
585	585	592	567	567
BOWMAN Matte Black	BRAMLETT Brushed Nickel	BRAMLETT Polished Chrome	BRAVO Antique Bronze	BRAVO Brushed Nickel
595	574	574	604	604
		ň	T	
BRIARWOOD Antique Bronze	BRIARWOOD Graphite	CAISSON Brushed Nickel	CAISSON Graphite	CALAIS Brushed Nickel
591	591	553	553	527
CALAIS Matte Black	CALAIS Vintage Brass	CALHOUN Antique Bronze	CALHOUN Brushed Nickel	CALHOUN Vintage Brass

CARISA Brushed Nickel	CARISA Vintage Brass	CASCADIA Antique Bronze	CASCADIA Polished Chrome	CHANNEL GLASS White
607	607	600	600	614
			Ţ Ţ	
CLARION Brushed Nickel	CLARION Matte Black	CLARION Polished Chrome	CLARION Satin Brass	CLASSIC Brushed Nickel
535	535	535	535	612
				ry
CLASSIC Natte Black	CLEAR GLASS Brushed Nickel	CLEAR GLASS Matte Black	CLIFTON HEIGHTS Antique Bronze	CLIFTON HEIGHTS Brushed Nickel
512	616	616	599	599
CLIFTON HEIGHTS Matte Black	COFIELD Brushed Nickel	COFIELD Matte Black	COFIELD Polished Chrome	COFIELD Vintage Brass
99	596	596	596	596
COFIELD Brushed Nickel	COFIELD Matte Black	COFIELD Polished Chrome	COFIELD Vintage Brass	CONWAY Brushed Nickel
596	596	596	596	554

CONWAY Matte Black	COPELAND Brushed Gold	COPELAND Brushed Nickel	COPELAND Matte Black	COWAN Brushed Nickel
555	541	541	540	539
	774	the state of	<u> </u>	
COWAN Matte Black	COWAN Satin Brass	DALTON Polished Chrome	DALTON Vintage Brass	DELUXE BROADWAY Polished Chrome
539	538	584	584	617
ECONOMY BROADWAY Polished Chrome	ELARA Brushed Nickel	ELARA Matte Black	ELARA Vintage Brass	FESSLER Brushed Nickel
617	528	529	529	573
FESSLER Matte Black	FESSLER Vintage Brass	FLEET Brushed Nickel	FLEET Polished Chrome	FLUTED CLEAR GLAS Brushed Nickel
573	573	601	601	615
FLUTED CLEAR GLASS Polished Chrome	FLUTED ETCHED GLASS Brushed Nickel	FLUTED ETCHED GLASS Polished Chrome	GATHER Antique Bronze	GATHER Brushed Nickel
615	615	615	613	613
			A A	

GATHER Polished Chrome	GILMOUR Brushed Nickel	GILMOUR Matte Black	GOODWIN Brushed Nickel	GOODWIN Matte Black
613	571	571	598	598
GOODWIN Polished Chrome	GULLIVER Galvanized Finish	GULLIVER Graphite	HANSFORD Antique Bronze	HANSFORD Polished Nickel
598	593	593	590	590
	c c			
HANSFORD Vintage Brass	HEART Antique Bronze	HEART Brushed Nickel	HEART Polished Chrome	HINTON Brushed Nickel
590	611	611	611	561
HINTON Matte Black	HINTON Vintage Brass	INSPIRE Antique Bronze	INSPIRE Brushed Nickel	INSPIRE Polished Chrome
560	561	196	607	607
INVITE Brushed Nickel	JOY Antique Bronze	JOY Brushed Nickel	JUDSON Antique Bronze	JUDSON Polished Chrome
605	611	611	588	588
	Por			

KENE Brushed Nickel	KENE Graphite	LAIRD Antique Bronze	LAIRD Brushed Nickel	LASSITER Brushed Nickel
576	576	609	609	547
LASSITER Matte Black	LEAGUE Brushed Nickel	LEAGUE Matte Black	LEAP Antique Bronze	LEAP Brushed Nickel
547	599	599	601	601
LITCHFIELD Polished Chrome	LYNZIE Brushed Gold	LYNZIE Matte Black	LYNZIE Polished Chrome	MADISON Antique Bronze
578	582	583	583	606
MADISON Brushed Nickel	MADISON Polished Nickel	MAST Brushed Nickel	MERRY Brushed Nickel	MERRY Matte Black
606	606	575	603	603
				7 5
MERRY Polished Chrome	NORTHLAKE Brushed Nickel	NORTHLAKE Matte Black	NORTHLAKE Vintage Brass	PRESTON Brushed Nickel
603	557	557	557	565

PRESTON Matte Black	PRESTON Vintage Brass	RACETRACK BROADWAY Brushed Nickel	REISS Brushed Nickel	REISS Matte Black
565	564	617	545	544
REISS Polished Chrome	REPLAY Antique Bronze	REPLAY Brushed Nickel	REPLAY Polished Nickel	REPLAY Textured Black
45	608	608	608	608
	1.		er derive Cr. serden	
RILEY Brushed Nickel	RILEY Matte Black	RUSHTON Brushed Nickel	RUSHTON Graphite	SINGLETON Brushed Nickel
598	598	586	586	559
SINGLETON Matte Black	SINGLETON Vintage Brass	STATUS Polished Chrome	TRINITY Antique Bronze	TRINITY Brushed Nickel
59	558	579	606	606
		5 - 3	YOY	A
FRINITY Polished Chrome	VERTEX Brushed Gold	VERTEX Brushed Nickel	VERTEX Matte Black	VERTEX Brushed Gold
506	549	549	548	550
The state of the s				4

VERTEX Brushed Nickel	VERTEX Matte Black	VICTORIAN Brushed Nickel	VICTORIAN Polished Chrome	VICTORIAN Venetian Bronze
551	551	610	610	610
75				-0-

WINSLETT Brushed Nickel	WINSLETT Matte Black	WISTEN Brushed Nickel
594	594	602

Outdoor/Indoor




Outdoor



BEAUFORT BENTON HARBOR BIRKDALE BIRKDALE **BARNETT** Antique Bronze Textured Black Textured Black Antique Bronze Textured Black 662 691 637 640 640 **BOTTA BOXWOOD BROOKSIDE BROOKSIDE BROOKSIDE** Antique Bronze Antique Bronze Antique Nickel Copper Gilded Iron 695 658 690 690 690 POLYCARBONATE BULKHEADS **BULKHEADS BULKHEADS BULKHEADS BULKHEADS** Textured Black White Textured Black White White 716 716 716 716 716 POLYCARBONATE BULKHEADS POLYCARBONATE BULKHEADS POLYCARBONATE BULKHEADS **BURLINGTON CARDIFF** White White White Antique Bronze Textured Black 716 716 716 700 638 **CARRIAGE CLASSICS CARRIAGE CLASSICS CAST LATERN CEDAR SPRINGS CEDAR SPRINGS** Brushed Nickel Matte Black Textured Black Black Metallic Gray 707 710 684 684 707

Outdoor

CEDAR SPRINGS Navy	CEDAR SPRINGS Pistachio	CEDAR SPRINGS Red	CEDAR SPRINGS White	CEILING MOUNT Matte Black
584	684	684	684	714
EEILING MOUNT extured Black	CEILING MOUNT White	CERAMIC SCONCE White	CHILTON Textured Black	COMPEL Textured Black
714	714	703	644	692
CONOVER Antique Bronze	CONOVER Antique Pewter	CRAWFORD Oil Rubbed Bronze	CRAWFORD Textured Black	WALL MOUNTED DOW CYLINDERS 5" Multiple Finishes
571	671	675	675	723
VALL MOUNTED DOWN CYLINDERS 6" Multiple Finishes	WALL MOUNTED UP & DOWN CYLINDERS 5" Multiple Finishes	WALL MOUNTED UP & DOWN CYLINDERS 6" Multiple Finishes	CEILING MOUNT DOWN CYLINDERS 3" Multiple Finishes	CEILING MOUNT DOWN CYLINDERS 5" Multiple Finishes
725	726	728	730	730
EILING MOUNT DOWN CYLINDERS 6" fultiple Finishes	CORD SUSPENDED DOWN CYLINDERS 5" Multiple Finishes	CORD SUSPENDED DOWN CYLINDERS 6" Multiple Finishes	DERBY Espresso	DILLARD Antique Bronze
730	731	731	697	701



Outdoor

GLOBE LANTERN GRANDBURY GRANDBURY GREENE RIDGE GUNTHER Matte Black Antique Bronze Textured Black Textured Black Antique Bronze 710 633 633 688 710 **GUNTHER HASLETT HASLETT HAWTHORNE HOLCOMBE** Matte Black Antique Pewter Textured Black Textured Black Textured Black 710 670 670 692 668





HUTCHENCE









KEEGAN	

Matte	e Black
651	



MARQUETTE

Textured Black







MANSARD NON-METALLIC








MAISON

MCBEE Textured Black 694





MILFORD NON-METALLIC



Outdoor

ROMAN COACH ROMAN COACH ROMAN COACH SEAGROVE ROMAN COACH Antique Bronze Textured Black Antique Bronze Textured Black Textured Black 708 708 708 708 639 **SQUIRE SQUIRE STALLWORTH** STATURE STATURE Antique Bronze Matte Black Matte Black Oil Rubbed Bronze Textured Black 665 665 683 666 666 TRAFFORD NON-METALLIC TOWNSHIP **TREMONT** TREMONT UNISON Textured Black Matte Black Stainless Steel 649





UTILITY







UTILITY
Textured Black
714









WAKEF	ORD
Textured	Black
667	Q
	THE THEFT









FORD	WALCOTT	WALCOTT	WARD	WATCH HILL
d Black	Antique Bronze	Textured Black	Textured Black	Textured Black
	641	641	703	650

WELBOURNE
Textured Black
Textured White
Textured Black
Tostured Black

WESTPORT White WHITMIRE Matte Black 659 WILLIAMSTON Antique Bronze WILLIAMSTON Antique Pewter **WISH** Antique Bronze

704



661

561



WISH Textured Black

680



Outdoor LED

ARRIVE LED
Textured Black
Antique Bronze

Textured Graphite

Textured Graphite

BROOKSIDE LED
Gilded Iron
Multiple Finishes

715

715

715

717

717

Outdoor LED

BULKHEADS LED

Multiple Finishes

717



BULKHEADS LED

Multiple Finishes



CALLAHAN LED

Antique Bronze



CORNICE LED

Multiple Finishes

722



CORNICE LED

Multiple Finishes

697



WALL MOUNTED DOWN **CYLINDERS 3" LED**

Multiple Finishes

723



WALL MOUNTED DOWN **CYLINDERS 5" LED**

Multiple Finishes

723

WALL MOUNTED DOWN **CYLINDERS 6" LED**

Multiple Finishes



WALL MOUNTED UP & **DOWN CYLINDERS 3" LED**

Multiple Finishes



WALL MOUNTED UP & **DOWN CYLINDERS 5" LED**

Multiple Finishes

726



WALL MOUNTED UP & **DOWN CYLINDERS 6" LED**

Multiple Finishes 728



CEILING MOUNT DOWN CYLINDERS 3" LED



CEILING MOUNT DOWN CYLINDERS 5" LED Multiple Finishes

730



CEILING MOUNT DOWN CYLINDERS 6" LED





CORD SUSPENDED DOWN

CYLINDERS 5" LED

CORD SUSPENDED DOWN **CYLINDERS 6" LED**

Multiple Finishes



DERBY LED

Antique Bronze



DIE-CAST LED

Textured Black



DISTRICT LED

Antique Bronze



EAST HAVEN LED

Antique Bronze



EAST HAVEN LED

Textured Black

696

731



ENDORSE LED

Textured Black



HARD-NOX LED

Black



HARD-NOX LED

Satin White

717

HARD-NOX LED Black



HARD-NOX LED Satin White	HARD-NOX LED Black	HARD-NOX LED Satin White	HARD-NOX LED Satin White	STRATA LED Antique Bronze
717	717	717	717	722
STRATA LED Black	STRATA LED Metallic Gray	STRATA LED White	VALERA LED Architectural Bronze	VALERA LED Brushed Nickel
722	722	722	718	718
WESTPORT LED Textured Black	WISH LED Textured Black	Z-1010 LED Architectural Bronze	Z-1010 LED Textured Black	Z-1030 LED Antique Bronze
704	681	720	720	718
Z-1030 LED Metallic Gray	Z-1030 LED Textured Black	Z-1030 LED White	Z-1060 LED Textured Black	Z-1070 LED Textured Black
718	718	718	721	719
Z-1080 LED Metallic Gray	Z-1080 LED Textured Black	Z-1090 LED Matte Black	Z-2020 LED Multiple Finishes	Z-2025 LED Multiple Finishes
719	719	720	721	721

Recessed Downlighting

4" HOUSING NEW CONSTRUCTION Unfinished	4" TRIM Black	4" TRIM Satin White	4" TRIM Satin White	4" TRIM Satin White
739	739	739	739	739

5" HOUSING NEW CONSTRUCTION Unfinished	5" TRIM Black	5" TRIM Satin White	5" TRIM Clear Alzak	5" TRIM Satin White
740	740	740	740	740
			MIIM	

6" HOUSING NEW CONSTRUCTION Unfinished	6" TRIM Black	6" TRIM Satin White	6" TRIM Satin White	6" TRIM Satin White
743	743	743	743	743

6" SLOPED HOUSING NEW CONSTRUCTION Unfinished	6" SLOPED HOUSING NEW CONSTRUCTION Unfinished	6" SLOPED TRIM Antique Bronze	6" SLOPED TRIM Black	6" SLOPED TRIM Satin White
745	745	745	745	745

Recessed Downlighting LED

EVERLUME® RECESSED 4"
Satin White
Satin White

FUERLUME® RECESSED 6"
RECESSED 6"
Satin White
RECESSED 6"
Satin White
Satin White

FUERLUME® RECESSED 6"
RECESSED 6"
RECESSED 6"
RECESSED 6"
RECESSED ACCESSORY
RECESSED 6"
RECESSED 6"
RECESSED 6"
RECESSED 6"
RECESSED 6"
RECESSED ACCESSORY
RECESSED ACCESSORY
RECESSED ACCESSORY
RECESSED ACCESSORY
RECESSED 6"
RECESSED 6"
RECESSED 6"
RECESSED 6"
RECESSED ACCESSORY
RE



INTRINSIC RECESSED 4"
Antique Bronze

INTRINSIC RECESSED 4"
Satin White

INTRINSIC RECESSED 6"
Antique Bronze

INTRINSIC RECESSED 6"
Antique Bronze

INTRINSIC RECESSED 6"
Antique Bronze

747

747

747

747



Surface Mount Downlighting LED

EVERLUME® SURFACE White

754

EVERLUME® TRIM Antique Bronze



EVERLUME® TRIM

Black

EVERLUME® TRIM

Brushed Nickel



EVERLUME® SURFACE

White



EVERLUME® TRIM

Antique Bronze

753

EVERLUME® TRIM

753

EVERLUME® TRIM

Brushed Nickel

753

EMBLEM SURFACE 7.52" Antique Bronze



EMBLEM SURFACE 7.52"

Satin White



EMBLEM SURFACE 5.5"

Antique Bronze



EMBLEM SURFACE 5.5" Satin White



INTRINSIC SURFACE 5.5"

White 750

INTRINSIC SURFACE 7.25"

White

750



INTRINSIC SURFACE **DIRECTIONAL**

Antique Bronze

750



750

INTRINSIC DIRECTIONAL

Satin White

750

ROUND SURFACE 7.25"

751



GLASS DECORATIVE 7.25"

Brushed Nickel

752




GLASS DECORATIVE 5.5" Brushed Nickel

752



Directionals





ELEVATE YOUR HOME

Our Design Series fixtures feature on-trend designs, artistic influences and fashion-forward elements. The statement-making lighting found throughout the Design Series collections are the art piece that creates an overall elevated experience in the home. Included here is a product overview of the Design Series. Explore the entire collection in detail using our Design Series catalog, a companion piece to the Progress Lighting catalog.

VIEW THE CATALOG



POINT DUME® COLLECTION

CHANDELIERS AND PENDANTS

















SHEARWATER

SURFRIDER

WINDBLUFF







Maliblue

SURFRIDER





YERBA



YERBA



WANDERMERE Brushed Brass









JEFFREY ALAN MARKS

POINT DUME® COLLECTION

CLOSE-TO-CEILING

ROCKDANCE Aged Brass

ROCKDANCE Antique Nickel

SANDBAR Brushed Brass **SEQUIT POINT** Antique Nickel

SEQUIT POINT Brushed Brass







TAPIA TRAIL

Aged Brass

TAPIA TRAIL Brushed Nickel

YERBA









SCONCES AND WALL BRACKETS

LATIGO BAY Antique Bronze

LATIGO BAY Brushed Nickel

LOOKOUT Brushed Nickel

ONSHORE Brushed Brass









SANDBAR

Brushed Brass

SHEARWATER

Aged Brass

SHEARWATER

Antique Nickel







SURFRIDER

Antique Bronze

SURFRIDER

Galvanized

SURFRIDER White

YERBA Silver Ridge









POINT DUME® COLLECTION

OUTDOOR



HOOK POND

SEAMOOR





HOOK POND







HOOK POND

SEAMOOR Oil Rubbed Bronze



SHADMORE

HOOK POND

Oil Rubbed Bronze

HOOK POND









Matte Black

SHADMORE



WAKECREST LED

Galvanized



WAKECREST LED


Matte Black



WAKECREST LED

Shelter White

COLLECTIONS













COLLECTIONS









PENDANTS









PENDANTS



















CLOSE-TO-CEILING

ARYA Brushed Gold

ARYA Matte Black

ASTRA Antique Bronze

ASTRA Brushed Nickel

ASTRA Matte Black











ASTRA Satin Brass

BLAKELY Graphite

BLAKELY Brushed Bronze

BLAKELY Brushed Nickel

BRECKENRIDGE Aged Bronze











BRECKENRIDGE

Matte Black

BURGESS Aged Bronze

DEBUT

Brushed Nickel

ELEVATE LED

Brushed Bronze

BURGESS Matte Black

CHANDRA Matte Black + Rattan

CINQ Antique Bronze











CINQ Brushed Nickel

DEBUT Graphite

ELEVATE Brushed Bronze

GLAYSE

Antique Bronze

ELEVATE Matte Black











ELEVATE Polished Chrome





ELEVATE LED



GLAYSE Brushed Nickel



GLIMMER Antique Bronze



GLIMMER Silver Ridge



GRESHAM Graphite



LAILA Vintage Brass



LAILA Vintage Brass



LARAMIE Matte Black



LATTIMORE Aged Brass



LOWERY Matte Black



LOWERY Textured Black



MARCHE Polished Nickel



ORRIZO Matte Black



RATIO Antique Bronze



RATIO Brushed Nickel



SAUCEDO Architectural Bronze



SAUCEDO Matte Black



SILVA

Brushed Bronze



SILVA

Brushed Nickel



SPATIAL



TRIMBLE





SILVA Matte Black



Matte Black



Brushed Bronze



TRIMBLE

Brushed Nickel



TRIMBLE Brushed Bronze



TRIMBLE Brushed Nickel



TRIMBLE Brushed Bronze



TRIMBLE Brushed Nickel







SCONCES & WALL BRACKETS



GLAYSE GLAYSE GLIDE **GLIDE** GLIDE Antique Bronze Brushed Nickel Brushed Nickel Polished Chrome Rubbed Bronze **GLIMMER GLIMMER GRESHAM** LISBON LISBON Pollished Nickel Antique Bronze Silver Ridge Graphite Matte Black **LOWERY LOWERY** MARCHE **METRIC METRIC** Brushed Nickel Polished Chrome Matte Black Textured Black Polished Nickel **METRO METRO METRO METRO METRO** Antique Bronze Brushed Nickel Matte Black Polished Chrome Satin Brass



MOD



ORRIZO



PALACIO

Vintage Gold




SAFFERT



SAFFERT



SCONCES & WALL BRACKETS



BATH

CAHILL

Brushed Bronze



Brushed Nickel

DEBUT

Graphite



Brushed Bronze









ELEVATE

Matte Black

ELEVATE

Polished Chrome

FLIGHT

Brushed Nickel

FLIGHT

Polished Chrome









GLAYSE

Antique Bronze

GLAYSE

Brushed Nickel

GLANCE

Polished Chrome

GLIDE

Brushed Nickel









GLIDE

Oil Rubbed Bronze

GLIDE

Polished Chrome

LISBON

Matte Black

LISBON

Polished Nickel











$\overline{\mathrm{BATH}}$

METRICBrushed Nickel

METRICPolished Chrome

MODPolished Chrome

SPATIAL Matte Black









ZURA

Brushed Nickel

ZURAPolished Chrome

ZURA Matte Black









OUTDOOR

BRADSHAWAntique Copper

BRADSHAW Textured Black



CADENCEOil Rubbed Bronze



CADENCE Textured Black



CHATSWORTH

Textured Black



CREIGHTONTextured Black



CULLMAN Antique Bronze







<u>OUTDOOR</u>

GIBBES STREET

Antique Bronze



GIBBES STREET

Textured Black



JANSSEN

Oil Rubbed Bronze



KIAWAH

Textured Black



MAISON

Textured Black



PATEWOOD

Black



RICHMOND HILL

Textured Black



SANTEE



SANTEE

Matte Black



UNION SQUARE

Antique Copper



UNION SQUARE

Stainless Steel



VERDAE







Antique Bronze



VERDAE

Textured Black









ESIGN+SERES Featuring Point Dume™ Wandermere **ELEVATE** YOUR

HOME

VIEW THE






Collections

DISCOVER THE LATEST







STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Modern design emphasizes clean, uncluttered lines in furniture and nature-inspired, tactile furnishings. Substantial metal-toned lighting from the Parkhurst Collection features a solid yet elegant ring and crisp glass shades that balance curved furniture shapes.

1 In this section

You'll find a close up view for featured collections, as well as available products and finishes offered within a collection.



2 Quick selection

Use the **Product Finder**, page 4, to quickly see all collections offered in this catalog.



4 Complete the look

Look out for "**Also In**" to find expanded collections in other sections like Bath, Pendants, and Ceiling Fans.

(3) Want more?

Design Series offers more elevated product options. Use QR to view:


DESIGN+SERIES







Collections



P500371-109 Brushed Bronze 20" sq., 36" ht. 8 candelabra base, 60w max.



P500214-109 Brushed Bronze 14.37" sq., 24.37" ht. 4 candelabra base, 60w max.




P500213-109 Brushed Bronze 10.87" sq., 19.75" ht. 3 candelabra base, 60w max.



P400300-109 Brushed Bronze 42" L, 13" D, 15.12" ht. 6 candelabra base, 60w max.





This dining room offers a calm and soothing ambiance from plenty of natural light, furniture fashioned from warm wood, and simple décor. The Parkhurst chandelier strikes a bright note as it combines a warm brushed bronze finish with graceful curves and bold angles, creating an airy structure that defines the form and produces unobstructed layers of light.


STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**



P400296-109 Brushed Bronze
25.25" dia., 12.5" ht.
5 candelabra base, 60w max.







P710111-109 Brushed Bronze 7.5" W., 12" ht., 4" D. 2 medium base, 60w max.





P500361-109 Brushed Bronze 15.25" dia., 23.37" ht. 1 medium base, 60w max.



P500360-109 Brushed Bronze 11.5" dia., 16.75" ht. 1 medium base, 60w max.





P500371-31M Matte Black 20" sq., 36" ht. 8 candelabra base, 60w max.




P500214-031 Matte Black 14.37" sq., 24.37" ht. 4 candelabra base, 60w max.



P500213-031 Matte Black 10.87" sq., 19.75" ht. 3 candelabra base, 60w max.



P400300-31M Matte Black 42" L, 13" D, 15.12" ht. 6 candelabra base, 60w max.



Graceful curves and bold angles combine to create a softly structured look in Parkhurst. An airy frame defines the form to produce unobstructed layers of light.

FINISHES

009 Brushed Nickel



Matte Black



Brushed Bronze





P400296-31M Matte Black 25.25" dia., 12.5" ht. 5 candelabra base, 60w max.

P400295-31M Matte Black 21" dia., 12.25" ht. 3 medium base, 60w max.



P350255-31M Matte Black 11.25" dia., 5.12" ht. 2 medium base, 15w max.



P710111-31M Matte Black 7.5" W., 12" ht., 4" D. 2 medium base, 60w max.





P500361-31M Matte Black 15.25" dia., 23.37" ht. 1 medium base, 60w max.



P500360-31M Matte Black 11.5" dia., 16.75" ht. 1 medium base, 60w max.





P500371-009 Brushed Nickel 20" sq., 36" ht. 8 candelabra base, 60w max.



P500214-009 Brushed Nickel 14.37" sq., 24.37" ht. 4 candelabra base, 60w max.



P500213-009 Brushed Nickel 10.87" sq., 19.75" ht. 3 candelabra base, 60w max.



P400300-009 Brushed Nickel 42" L, 13" D, 15.12" ht. 6 candelabra base, 60w max.



Graceful curves and bold angles combine to create a softly structured look in Parkhurst. An airy frame defines the form to produce unobstructed layers of light.

FINISHES

009 Brushed Nickel



Matte Black



Brushed Bronze





P400296-009 Brushed Nickel 25.25" dia., 12.5" ht. 5 candelabra base, 60w max.

P400295-009 Brushed Nickel 21" dia., 12.25" ht. 3 medium base, 60w max.

P350255-009 Brushed Nickel 11.25" dia., 5.12" ht. 2 medium base, 15w max.



P710111-009 Brushed Nickel 7.5" W., 12" ht., 4" D. 2 medium base, 60w max.





P500361-009 Brushed Nickel 15.25" dia., 23.37" ht. 1 medium base, 60w max.



P500360-009 Brushed Nickel 11.5" dia., 16.75" ht. 1 medium base, 60w max.



Elara

Elara features a slender, chic form with a stylized finial inspired by a chess pawn for a classically modern style.

FINISHES





31M Matte Black



Vintage Brass



Elara



P500363-163 Vintage Brass 15" dia., 31.37" ht. 4 candelabra base, 60w max.





P710107-163 Vintage Brass 10.37" W., 16.62" ht., 4.37" D. 2 candelabra base, 60w max.



P710106-163 Vintage Brass 5.75" W., 16.62" ht., 4.37" D. 1 candelabra base, 60w max. shown with P860060-000 shade



ALSO IN



ACCESSORY SHADES

P860059-000

White Linen

Drum



Tapered

White Linen

P860060-000




P860061-068 Clear Glass

See p. 342 for details



P860061-029 Etched White Glass



Rich, luxurious blue and gold furniture and décor pop against a crisp white color palette. The versatile Elara Collection's slender, chic form has stylized finials inspired by a chess pawn. The lighting has a simple, elegant style when used without a shade, or easily change the fixture's look by selecting a clear glass shade for modern flair and linen or opal shades for a more traditional design (Shades sold separately).

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Elara



P500363-31M Matte Black 15" dia., 31.37" ht. 4 candelabra base, 60w max.





P710107-31M Matte Black 10.37" W., 16.62" ht., 4.37" D. 2 candelabra base, 60w max. shown with P860061-068 shade



P710106-31M Matte Black 5.75" W., 16.62" ht., 4.37" D. 1 candelabra base, 60w max.



ALSO IN



ACCESSORY SHADES

P860059-000

White Linen

Drum



P860060-000 Tapered White Linen



P860061-068 Clear Glass



P860061-029 Etched White Glass



Elara



P500363-009 Brushed Nickel 15" dia., 31.37" ht. 4 candelabra base, 60w max.





P710107-009 Brushed Nickel 10.37" W., 16.62" ht., 4.37" D. 2 candelabra base, 60w max. shown with P860059-000 shade



P710106-009 Brushed Nickel 5.75" W., 16.62" ht., 4.37" D. 1 candelabra base, 60w max.



ALSO IN



ACCESSORY SHADES

P860059-000

White Linen

Drum



P860060-000 Tapered White Linen



See p. 342 for details

P860061-068 Clear Glass



P860061-029 Etched White Glass

Landree

An inner light cluster appears to float inside a geometric outer cage. The frame is designed to dramatically surround each fixture, presenting depth, dimension and beauty. Mini-pendant and flush mount versions feature a white silk shade.

FINISHES



031 Matte Black



Silver Ridge



Landree

P400178-134 Silver Ridge 23" dia., 16" ht. 5 candelabra base, 60w max.



P500177-134 Silver Ridge 23" dia., 33.5" ht. 8 candelabra base, 60w max.



P400177-134 Silver Ridge 18.12" dia., 12" ht. 3 candelabra base, 60w max.




P500176-134 Silver Ridge 10" dia., 11.12" ht. 1 medium base, 75w max.



P350132-134 Silver Ridge 16" dia., 6.62" ht. 3 medium base, 60w max.





Provide a youthful balance to traditional furniture by choosing a pair of graceful, open Landree pendants in a fresh mixed metal finish. Use neutral hues not only on the walls but on the classically styled dining room set to showcase its curved forms and contribute a modern flair to the setting. Remember that less is more and pare down accessories to make a more significant impact in a room.

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Landree

P400178-031 Matte Black 23" dia., 16" ht. 5 candelabra base, 60w max.



P500177-031 Matte Black 23" dia., 33.5" ht. 8 candelabra base, 60w max.



P400177-031 Matte Black 18.12" dia., 12" ht. 3 candelabra base, 60w max.



P500176-031 Matte Black 10" dia., 11.12" ht. 1 medium base, 75w max.



P350132-031 Matte Black 16" dia., 6.62" ht. 3 medium base, 60w max.






Brandywine

P500069-134 Silver Ridge 28" dia., 31.87" ht. 6 candelabra base, 60w max.







P500068-134 Silver Ridge 16" dia., 19.75" ht. 3 candelabra base, 60w max.





Anchor a white color palette with warm wood furnishings and a graceful pendant. Whimsical and romantic, the Brandywine Collection features an interlocking sphere with carefully crafted decorative details, including wired accents. Its airy frame generates a divine glow over a dining room table for a statement-making style.

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**


Brandywine

P500069-020 Antique Bronze 28" dia., 31.87" ht. 6 candelabra base, 60w max.









Mariposa







Take a naturalistic approach to modern room design with organic décor. Soothing blue-sky walls and a clean white color palette create a calming backdrop punctuated by the stunning Mariposa chandelier. Mariposa's organic feel is balanced by the minimalist lines of its multi-directional light arrangement, making it a striking focal point.

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Mariposa







Thorpe

P400270-009 Brushed Nickel 27.62" dia., 23.87" ht. 5 medium base, 60w max.



P400270-012 Satin Brass 27.62" dia., 23.87" ht. 5 medium base, 60w max.



CATALOG 134

Atwell

Sharp lines, clear glass globes and geometric shapes define the Atwell collection's modern aesthetic, showcasing one-of-a-kind architectural designs that are both remarkable and enduring.

FINISHES



009 Brushed Nickel



Matte Black



Brushed Bronze



Atwell







P500283-109 Brushed Bronze 8.25" sq., 13.12" ht. 1 candelabra base, 60w max.



P350218-109 Brushed Bronze 12" W., 9.75" ht. 1 candelabra base, 60w max.



P350235-109 Brushed Bronze 22" dia., 10.62" ht. 3 candelabra base, 60w max.



P710114-109 Brushed Bronze 5.87" W., 18" ht., 6.75" D. 2 candelabra base, 60w max.





P350234-109 Brushed Bronze 5.87" dia., 7.87" ht. 1 candelabra base, 60w max.



ALSO IN






A small mudroom shines when it blends seamlessly with a home's décor, creating a stylish space with lots of storage. Create an inviting first impression with Atwell ceiling lights, whose central stem capped by clear glass delivers bright illumination. Add a complementary wall sconce to make a chic transition to the rest of the home.

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Atwell









P350234-31M Matte Black 5.87" L, 5.87" W., 7.87" ht. 1 candelabra base, 60w max.





CATALOG 134

Atwell

Sharp lines, clear glass globes and geometric shapes define the Atwell collection's modern aesthetic, showcasing one-of-a-kind architectural designs that are both remarkable and enduring.

FINISHES

009 Brushed Nickel



Matte Black



Brushed Bronze



Atwell



P500284-009 Brushed Nickel 13.5" sq., 20.5" ht. 2 candelabra base, 60w max.



P500283-009 Brushed Nickel 8.25" sq., 13.12" ht. 1 candelabra base, 60w max.



P350218-009 Brushed Nickel 12" W., 9.75" ht. 1 candelabra base, 60w max.



P350235-009 Brushed Nickel 22" dia., 10.62" ht. 3 candelabra base, 60w max.



P710114-009 Brushed Nickel 5.87" W., 18" ht., 6.75" D. 2 candelabra base, 60w max.





P350234-009 Brushed Nickel 5.87" dia., 7.87" ht. 1 candelabra base, 60w max.







Caisson







Gilliam

P400315-163 Vintage Brass 35.5" dia., 38.37" ht. 15 candelabra base, 60w max.







P500391-163 Vintage Brass 15" dia., 30.62" ht. 4 candelabra base, 60w max.



P500390-163 Vintage Brass 10" dia., 20.75" ht. 3 candelabra base, 60w max.



P350231-163 Vintage Brass 13" dia., 12.12" ht. 3 medium base, 15w max.







Mix wood tones in a room to enhance the organic appeal of natural accessories and a light color scheme. Feel free to pair dark lighting fixtures from complementary collections to ground the space. The Gilliam chandelier delivers an ethereal quality expressed by its slim circular silhouette, while a pair of Englewood wall sconces add an element of rustic craftsmanship.

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Gilliam

P400315-31M Matte Black 35.5" dia., 38.37" ht. 15 candelabra base, 60w max.









P500390-31M Matte Black 10" dia., 20.75" ht. 3 candelabra base, 60w max.



P350231-31M Matte Black 13" dia., 12.12" ht. 3 medium base, 15w max.







Gilliam

P400315-009 Brushed Nickel 35.5" dia., 38.37" ht. 15 candelabra base, 60w max.







P500391-009 Brushed Nickel 15" dia., 30.62" ht. 4 candelabra base, 60w max.

P500390-009 Brushed Nickel 10" dia., 20.75" ht. 3 candelabra base, 60w max.



P350231-009 Brushed Nickel 13" dia., 12.12" ht. 3 medium base, 15w max.





Balancing the best of modern and traditional, the Kellwyn Collection has a classic frame interpreted in a slender form. Clear glass shades complement the sleek design while adding a touch of luxury.

FINISHES



009 Brushed Nickel



Matte Black





P500315-031 Matte Black
18" dia., 31.75" ht.
4 candelabra base, 60w max.



P500314-031 Matte Black 5" dia., 8.87" ht. 1 medium base, 60w max.



P400250-031 Matte Black 16" dia., 14" ht. 3 candelabra base, 60w max.



Fixture can be installed as a chandelier using included hardware.

Balancing the best of modern and traditional, the Kellwyn Collection has a classic frame interpreted in a slender form. Clear glass shades complement the sleek design while adding a touch of luxury.

FINISHES

009 Brushed Nickel




Matte Black













Fixture can be installed as a chandelier using included hardware.



Lassiter



P400197-031 Matte Black 26" dia., 26" ht. 5 medium base, 60w max.



P500209-031 Matte Black 16.62" dia., 26" ht. 3 medium base, 60w max.



P500208-031 Matte Black 6.37" dia., 12.5" ht. 1 medium base, 60w max.



P350149-031 Matte Black 13" dia., 10.5" ht. 3 medium base, 60w max.



P710073-031 Matte Black 4.87" W., 19.25" ht., 6.5" D. 1 medium base, 60w max.



ALSO IN



Bath



Merge vibrant blues with neutral textures and colors for a simple elegance that has a place in both formal and modern settings.

Place contemporary art on classically crisp white walls, then complement it with slender Lassiter sconces, whose stylish clear glass shades perfectly harmonize with contemporary furnishings.

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Lassiter





P500209-009 Brushed Nickel 16.62" dia., 26" ht. 3 medium base, 60w max.



P500208-009 Brushed Nickel 6.37" dia., 12.5" ht. 1 medium base, 60w max.



P350149-009 Brushed Nickel 13" dia., 10.5" ht. 3 medium base, 60w max.



P710073-009 Brushed Nickel 4.87" W., 19.25" ht., 6.5" D. 1 medium base, 60w max.






Chadwick

P400225-031 Matte Black 40" L, 12" W., 8.75" ht. 3 medium base, 100w max.





P710089-031 Matte Black 5.5" sq., 18" ht., 5.37" D. 1 medium base, 100w max.




P350171-031 Matte Black 15.37" sq., 5.5" ht. 2 medium base, 60w max.



Chadwick

P400225-009 Brushed Nickel 40" L, 12" W., 8.75" ht. 3 medium base, 100w max.





P710089-009 Brushed Nickel 5.5" sq., 18" ht., 5.37" D. 1 medium base, 100w max.



P350171-009 Brushed Nickel 15.37" sq., 5.5" ht. 2 medium base, 60w max.





Kene

P400095-143 Graphite 27.25" dia., 22.5" ht. 5 medium base, 75w max.



P500103-143 Graphite 6" dia., 15.87" ht. 1 medium base, 75w max.



P300120-143 Graphite 4.75" W., 12.87" ht., 6.5" D. 1 medium base, 75w max.



P350098-143 Graphite 16" dia., 10.87" ht. 2 medium base, 75w max.



Fixture can be installed as a pendant using included hardware.



ALSO IN



Bath



Kene

P400095-009 Brushed Nickel 27.25" dia., 22.5" ht. 5 medium base, 75w max.



P500103-009 Brushed Nickel 6" dia., 15.87" ht. 1 medium base, 75w max.



P300120-009 Brushed Nickel 4.75" W., 12.87" ht., 6.5" D. 1 medium base, 75w max.



P350098-009 Brushed Nickel 16" dia., 10.87" ht. 2 medium base, 75w max.



Fixture can be installed as a pendant using included hardware.








Goodwin







P500410-31M Matte Black 7" dia., 16.75" ht. 1 medium base, 60w max.



P350239-31M Matte Black 13" dia., 9.87" ht. 2 medium base, 60w max.



Fixture can be installed as a pendant using included hardware.







Goodwin







P500410-009 Brushed Nickel 7" dia., 16.75" ht. 1 medium base, 60w max.



P350239-009 Brushed Nickel 13" dia., 9.87" ht. 2 medium base, 60w max.




Fixture can be installed as a pendant using included hardware.




ALSO IN



Bath



League









Pair brushed nickel cabinet hardware and lighting to create a pulled-together look in a room. Clean and elegant styling puts the League Collection in a class of its own. It features a distinctive slender strapping detail with a softened edge, lending a contemporary structure to its otherwise classic silhouette.

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

League







ALSO IN





Stockbrace

P400243-031 Matte Black 24" dia., 22.5" ht. 5 medium base, 60w max.



P350181-031 Matte Black 12.5" dia., 10" ht. 3 medium base, 60w max.



P710097-031 Matte Black 4.75" W., 13.5" ht., 5.5" D. 1 medium base, 60w max.





Bowman





ALSO IN



Winslett

The Winslett Collection is a fresh take on a classic light choice. Lightly seeded glass shades rest in shiny pedestal light bases that adds an unexpected, but welcomed dash of modern personality to this clean, traditional collection.

FINISHES

009 Brushed Nickel



Matte Black



Winslett



P400206-031 Matte Black 27.12" dia., 21.12" ht. 5 medium base, 60w max.

P500240-031 Matte Black 19.62" sq., 25" ht. 4 candelabra base, 60w max.



P500239-031 Matte Black 12.87" dia., 17.12" ht. 3 candelabra base, 60w max.



P500238-031 Matte Black 9.25" dia., 15.87" ht. 1 medium base, 60w max.



P350153-031 Matte Black 13.75" dia., 11.87" ht. 3 candelabra base, 60w max.



Fixture can be installed as a pendant using included hardware.



ALSO IN





Mix it up in a formal dining room, where beige is anything but boring in a color scheme that incorporates light colors using fun wall art and curvy chairs. The Winslett chandelier adds to the room's charm with its perfectly imperfect seeded glass shades and sweeping arms.

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Winslett





P500240-009 Brushed Nickel 19.62" sq., 25" ht. 4 candelabra base, 60w max.



P500239-009 Brushed Nickel 12.87" dia., 17.12" ht.

3 candelabra base, 60w max.



P500238-009 Brushed Nickel 9.25" dia., 15.87" ht. 1 medium base, 60w max.



P350153-009 Brushed Nickel 13.75" dia., 11.87" ht. 3 candelabra base, 60w max.



Fixture can be installed as a pendant using included hardware.



ALSO IN



Bath




Leyden









Elevate Modern Farmhouse style with a clean color palette and classic wood furnishings. The Leyden chandelier complements this look with gentle curves that soften its traditional form, providing an elegant, graceful look and offering plenty of light from its open design.


STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Leyden









Mast

P400190-009 Brushed Nickel 38" L, 4.87" W., 14.75" ht. 4 medium base, 100w max.



P500192-009 Brushed Nickel 6.25" dia., 14" ht. 1 medium base, 100w max.



P350144-009 Brushed Nickel 13" dia., 5.25" ht. 2 medium base, 60w max.



P710015-009 Brushed Nickel 5" W., 13" ht., 6.37" D. 1 medium base, 100w max.



P500192-020 Antique Bronze 6.25" dia., 14" ht. 1 medium base, 100w max.



P350144-020 Antique Bronze 13" dia., 5.25" ht. 2 medium base, 60w max.



P710015-020 Antique Bronze 5" W., 13" ht., 6.37" D. 1 medium base, 100w max.



ALSO IN



Bath

Durrell

The versatile Durrell Collection is perfect for coastal, modern farmhouse, or vintage settings. Featuring a variety of versatile materials including a sailcloth linen shade and wooden accents, Durrell showcases a welcoming, sophisticated style.

FINISHES

009 Brushed Nickel



Matte Black



Durrell



P500210-009 Brushed Nickel
18" dia., 28.5" ht.
4 candelabra base, 60w max.

P400218-009 Brushed Nickel 21" dia., 22.5" ht. 4 candelabra base, 60w max.

P350150-009 Brushed Nickel 16" dia., 13.5" ht. 3 candelabra base, 60w max.




P350151-009 Brushed Nickel 13" dia., 6.5" ht. 2 medium base, 60w max.



P710074-009 Brushed Nickel 4.5" W., 12" ht., 5" D. 1 candelabra base, 60w max.





Comfortable furnishings bring a well-rounded sophistication to the living room. The merest hint of red in the room's accessories balances soft and hard furnishings with warm and cool colors and textures. The large Durell pendant centers the room design with its open circular frame finished in dark tones for substance.

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Durrell



P500210-031 Matte Black 18" dia., 28.5" ht. 4 candelabra base, 60w max.





P350150-031 Matte Black 16" dia., 13.5" ht. 3 candelabra base, 60w max.



Fixture can be installed as a pendant using included hardware.



P350151-031 Matte Black 13" dia., 6.5" ht. 2 medium base, 60w max.



P710074-031 Matte Black 4.5" W., 12" ht., 5" D. 1 candelabra base, 60w max.





Galloway









P350224-009 Brushed Nickel 15" dia., 5.5" ht. 2 medium base, 60w max.



P710109-009 Brushed Nickel 5.5" W., 18.12" ht., 4.5" D. 1 candelabra base, 60w max.





Galloway





P500378-31M Matte Black 24" dia., 30.87" ht. 4 candelabra base, 60w max.



P500377-31M Matte Black 14.25" dia., 18.37" ht. 4 candelabra base, 60w max.



P350224-31M Matte Black 15" dia., 5.5" ht. 2 medium base, 60w max.



P710109-31M Matte Black 5.5" W., 18.12" ht., 4.5" D. 1 candelabra base, 60w max.



Canebrake

Canebrake embraces traditional forms with an artisanal flair. The generous scale creates an elegant focal point for any room.

FINISH



CATALOG 134

Canebrake



P400291-31M Matte Black 30.12" dia., 18" ht. 5 candelabra base, 60w max.



Bonn

The Bonn Collection personifies a stylishly simplistic industrial vibe. Smooth, thin bars curve and cross to form simple, open-caged structures that harbor light bases within appearing to daintily drip from the top of the light fixtures.

FINISH

031 Matte Black



Bonn

P500225-031 Matte Black 22" dia., 23.12" ht. 6 medium base, 60w max.



P500224-031 Matte Black 14.5" dia., 22.87" ht. 4 medium base, 60w max.



P500223-031 Matte Black 7" dia., 14.87" ht. 1 medium base, 60w max.



Chastain

Chastain draws upon the handcrafted artistry of basket-weaving. An airy frame offers a graceful silhouette. The artisanal style is enhanced by distressed faux wood finish and an impressive scale for an eyecatching element of form and function.

FINISHES

185 Bleached Oak

187

Cerused Black Oak



Chastain

P500344-185 Bleached Oak 20.87" dia., 25.25" ht. 3 medium base, 60 W., max.



P500343-185 Bleached Oak 14" dia., 17.25" ht. 1 medium base, 60 W., max.



P500344-187 Cerused Black Oak 20.87" dia., 25.25" ht. 3 medium base, 60 W., max.



P500343-187 Cerused Black Oak 14" dia., 17.25" ht. 1 medium base, 60 W., max.



The Briarwood Collection brings vintage farmhouse detailing into the present day with a classic cross brace pattern highlighting an airy, open-frame design. Hand-painted faux wood accentuates Briarwood's simple geometric form.

FINISHES

020 Antique Bronze



Textured Black



Galvanized Finish



Graphite











P500041-143 Graphite 10" sq., 9" ht.





P350039-143 Graphite 12" sq., 6" ht. 2 medium base, 60w max.



P710012-143 Graphite 6.87" W., 12" ht., 6" D. 1 medium base, 100w max.







ALSO IN







Wood tones, natural textures, and calming colors from nature are some of the forms and materials used to create a warm organic feel in the bedroom. The various faux wood finishes on the popular Briarwood Collection fixtures showcase a classic windowpane design and lend a charmingly organic look that elevates the aesthetic.

STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**



P500178-020 Antique Bronze 15.5" sq., 20.12" ht. 4 medium base, 60w max.




P500041-020 Antique Bronze 10" sq., 9" ht. 1 medium base, 100w max.



P350039-020 Antique Bronze 12" sq., 6" ht. 2 medium base, 60w max.

P350022-020 Antique Bronze 9.5" sq., 7.62" ht. 1 medium base, 60w max.









ALSO IN







P500178-141 Galvanized Finish 15.5" sq., 20.12" ht. 4 medium base, 60w max.




P500041-141 Galvanized Finish 10" sq., 9" ht. 1 medium base, 100w max.



P350039-141 Galvanized Finish 12" sq., 6" ht. 2 medium base, 60w max.



P350022-141 Galvanized Finish 9.5" sq., 7.62" ht. 1 medium base, 60w max.









ALSO IN



Ceiling Fans




P500178-031 Textured Black 15.5" sq., 20.12" ht. 4 medium base, 60w max.




P500041-031 Textured Black 10" sq., 9" ht. 1 medium base, 100w max.



P350039-031 Textured Black 12" sq., 6" ht. 2 medium base, 60w max.















Equinox

P3889-126 Burnished Silver 27.75" dia., 30" ht. 6 candelabra base, 60w max.



P3841-126 Burnished Silver 22" dia., 24.37" ht. 5 candelabra base, 60w max.




P3827-126 Burnished Silver 16" dia., 18.37" ht. 4 candelabra base, 60w max.



P5142-126 Burnished Silver 10.12" dia., 11.75" ht. 3 candelabra base, 60w max.



Equinox





P3841-20 Antique Bronze 22" dia., 24.37" ht. 5 candelabra base, 60w max.



P3827-20 Antique Bronze 16" dia., 18.37" ht. 4 candelabra base, 60w max.




P5142-20 Antique Bronze 10.12" dia., 11.75" ht. 3 candelabra base, 60w max.



Equinox







Conestee







Gulliver







ALSO IN



Ceiling Fans



Gulliver



P400158-141 Galvanized Finish
*P400158-143 Graphite
26" dia., 30" ht.
5 candelabra base, 60w max.



*P350117-141 Galvanized Finish P350117-143 Graphite 15.25" dia., 12.62" ht. 4 candelabra base, 60w max.



Fixture can be installed as a pendant using included hardware.

ACCESSORY SHADES



P8926-01 Off-White Linen Fabric Spring clip 5.5" dia., 4.87" ht.



P860042-000 Flax Linen 1" uno-style candle fitter 6" dia., 5.12" ht.

Hedgerow

Distressed Brass with faux Aged Oak accents or Brushed Nickel with faux Grey Washed Oak accents.

FINISHES

009 Brushed Nickel



Distressed Brass



Hedgerow



*P500317-009 Brushed Nickel P500317-175 Distressed Brass 10.37" sq., 19.37" ht. 1 medium base, 60w max.



P350197-009 Brushed Nickel ***P350197-175** Distressed Brass 10.37" sq., 8" ht. 1 medium base, 60w max.



Hemsworth

Textured Black with faux painted Aged Oak accents.

FINISH



031 Textured Black



Hemsworth








Barnes Mill









P300066-020 Antique Bronze 4.5" W., 11.87" ht., 5.87" D. 1 medium base, 100w max.





Lavelle

Artistry and texture combine in the Lavelle collection for the ultimate in global design. A softly curved, black frame complements the airy open weave of the earthy, mocha colored rattan shade.

FINISH



Textured Black



Lavelle



P500307-031 Matte Black 8" dia., 12.62" ht. 1 medium base, 60w max.



P350183-031 Matte Black 15.62" dia., 14.37" ht. 3 medium base, 60w max.



Fixture can be installed as a pendant using included hardware.





Cherish





P7172-09 Brushed Nickel 12" W., 9" ht., 6.5" D. 2 candelabra base, 60w max.



P7172-20 Antique Bronze 12" W., 9" ht., 6.5" D. 2 candelabra base, 60w max. *Shown with brass candles*



Shown with bronze candles





Judson

P400058-020 Antique Bronze 26" dia., 19.25" ht. 5 medium base, 75w max.



P400057-020 Antique Bronze 22" dia., 18.25" ht. 3 medium base, 75w max.



P500061-020 Antique Bronze 11" dia., 11.25" ht. 1 medium base, 75w max.



P500061-104 Polished Nickel 11" dia., 11.25" ht. 1 medium base, 75w max.



P350074-020 Antique Bronze 11" dia., 12" ht. 1 medium base, 75w max.



P350074-104 Polished Nickel 11" dia., 12" ht. 1 medium base, 75w max.



P350220-020 Antique Bronze 6.5" dia., 8" ht. 1 medium base, 60w max.



P350220-104 Polished Nickel 6.5" dia., 8" ht. 1 medium base, 60w max.



ALSO IN



Bath


is composed of angular forms to create a bold design that perfectly complements modern interiors.

009 Brushed Nickel



CATALOG 134

Vertex





P400343-191 Brushed Gold 22.5" dia., 15.25" ht. 5 medium base, 60w max.



P500432-191 Brushed Gold 15" sq., 28" ht. 4 candelabra base, 60w max.

Accessory shade options shown below.



P500431-191 Brushed Gold 12" sq., 22.5" ht.

1 medium base, 100w max.



P500433-191 Brushed Gold 12" sq., 22.5" ht.

12" sq., 22.5" nt. 1 medium base, 100w max.



P400340-191 Brushed Gold 18" dia., 16.75" ht. 3 medium base, 60w max.













P350258-191 Brushed Gold 7.37" W., 11.62" ht. 1 medium base, 60w max.

Bath



P350259-191 Brushed Gold 7.37" W., 11.62" ht. 1 medium base, 60w max.




ALSO IN





P860061-068 Clear Glass **P860061-029** Etched White Glass

Vertex







P: 12 11

P500431-009 Brushed Nickel 12" sq., 22.5" ht. 1 medium base, 100w max.



P500433-009 Brushed Nickel 12" sq., 22.5" ht. 1 medium base, 100w max.



P400340-009 Brushed Nickel 18" dia., 16.75" ht. 3 medium base, 60w max.





P400342-009 Brushed Nickel 18" dia., 16.75" ht. 3 medium base, 60w max.







P350258-009 Brushed Nickel 7.37" W., 11.62" ht.. 1 medium base, 60w max.



P350259-009 Brushed Nickel 7.37" W., 11.62" ht. 1 medium base, 60w max.



P500432 ACCESSORY SHADES

P860061-068 Clear Glass **P860061-029** Etched White Glass







Vertex

P400341-31M Matte Black 22.5" dia., 15.25" ht. 5 medium base, 60w max.



P400343-31M Matte Black 22.5" dia., 15.25" ht. 5 medium base, 60w max.



P500432-31M Matte Black 15" sq., 28" ht. 4 candelabra base, 60w max. Accessory shade options shown below.



P500431-31M Matte Black 12" sq., 22.5" ht. 1 medium base, 100w max.



P500433-31M Matte Black 12" sq., 22.5" ht. 1 medium base, 100w max.



P400340-31M Matte Black 18" dia., 16.75" ht. 3 medium base, 60w max.





P400342-31M Matte Black 18" dia., 16.75" ht. 3 medium base, 60w max.







P350258-31M Matte Black 7.37" W., 11.62" ht.. 1 medium base, 60w max.



P350259-31M Matte Black 7.37" W., 11.62" ht. 1 medium base, 60w max.



ALSO IN

P500432 ACCESSORY SHADES



P860061-068 Clear Glass **P860061-029** Etched White Glass



Adley




P400350-31M Matte Black 22.87" dia., 17.25" ht. 5 medium base, 60w max.



P400349-31M Matte Black 18.12" dia., 16.12" ht. 3 medium base, 60w max.



Fixture can be installed as a chandelier using included hardware.





ALSO IN





Close-to-Ceiling

Adley



P400350-009 Brushed Nickel 22.87" dia., 17.25" ht. 5 medium base, 60w max.



P400349-009 Brushed Nickel 18.12" dia., 16.12" ht.



Fixture can be installed as a chandelier using included hardware.









Adley







P400348-012 Satin Brass 26" L., 17" ht., 4" D. 3 medium base, 60w max.








Whisp





Cirrine

Etched white glass. Antique Bronze with Vintage Brass accents.







P5082-20 Antique Bronze 6" dia., 9.75" ht. 1 medium base, 100w max.



P7149-20 Antique Bronze 8" W., 8" ht., 4" D. 1 medium base, 75w max.





Torino

Brushed Nickel with etched white glass and Forged Bronze with etched tea-stained glass.



09 Brushed Nickel



Forged Bronze







*P4405-09 Brushed Nickel P4405-77 Forged Bronze 19.12" dia., 21.62" ht. 3 medium base, 100w max.

P5153-09 Brushed Nickel ***P5153-77** Forged Bronze 7.5" dia., 11" ht. 1 medium base, 100w max.



*P3184-09 Brushed Nickel P3184-77 Forged Bronze 14.62" dia., 7.12" ht. 2 medium base, 75w max.



P3843-09 Brushed Nickel ***P3843-77** Forged Bronze 18" dia., 18.5" ht.

3 medium base, 75w max.





*P7181-09 Brushed Nickel P7181-77 Forged Bronze 9.5" W., 6.75" ht., 4.75" D. 1 medium base, 100w max.



Clifton Heights

Etched white glass.





Antique Bronze



Matte Black



P400118-009 Brushed Nickel
*P400118-020 Antique Bronze
P400118-31M Matte Black
21" dia., 23.5" ht.
4 medium base, 100w max.



*P500125-009 Brushed Nickel P500125-020 Antique Bronze P500125-31M Matte Black 5.5" sq., 7.25" ht. 1 medium base, 100w max.



P350107-009 Brushed Nickel ***P350107-020** Antique Bronze **P350107-31M** Matte Black 12.75" sq., 11" ht.

12.75" sq., 11" ht. 2 medium base, 100w max.



P3852-20 Antique Bronze ***P3852-09** Brushed Nickel 15" sq., 7.12" ht. 2 medium base, 100w max.



*P3854-20 Antique Bronze P3854-09 Brushed Nickel 12.5" sq., 6.12" ht. 1 medium base, 100w max.







Madison

Etched white glass.



09 Brushed Nickel



Antique Bronze





P3663-09 Brushed Nickel 20.75" dia., 14" ht. 3 medium base, 60w max.



P3312-09 Brushed Nickel 15.75" dia., 8.25" ht. 2 medium base, 60w max.



P3311-09 Brushed Nickel 12" dia., 7" ht. 1 medium base, 60w max.



ALSO IN



Bath



Brushed Nickel with etched white linen glass and Antique Bronze with etched umber linen glass.



Brushed Nickel



Antique Bronze







*P2851-09 Brushed Nickel P2851-20 Antique Bronze 12.25" dia., 10.87" ht. 2 medium base, 100w max.



P3620-09 Brushed Nickel ***P3620-20** Antique Bronze 12.25" dia., 6.37" ht. 2 medium base, 60w max.





Bravo

Etched white glass.





Antique Bronze



P4623-09 Brushed Nickel *P4623-20W Antique Bronze 27" dia., 23" ht. 5 medium base, 100w max.



*P3821-20W Antique Bronze 3 candelabra base, 60w max.

*P3912-09 Brushed Nickel P3912-20W Antique Bronze 21" dia., 23.5" ht. 3 medium base, 100w max.



P5300-09 Brushed Nickel *P5300-20W Antique Bronze 7.25" dia., 6.5" ht. 1 medium base, 100w max.



ALSO IN



Bath

Wisten

Etched white glass.



Brushed Nickel



Antique Bronze












P3757-09 Brushed Nickel 18.12" dia., 25" ht. 3 medium base, 100w max.



P5167-09 Brushed Nickel ***P5167-20** Antique Bronze 3.87" dia., 9.75" ht. 1 medium base, 100w max.

*P5108-09 Brushed Nickel P5108-20 Antique Bronze 4" dia., 6.75" ht. 1 medium base, 100w max.









Etched white glass.



009 Brushed Nickel



020 Antique Bronze

P400044-009 Brushed Nickel 26.37" dia., 37" ht. 9 medium base, 100w max.




P400043-009 Brushed Nickel 25" dia., 30" ht. 5 medium base, 100w max.



P400042-009 Brushed Nickel 21" dia., 27.62" ht. 3 medium base, 100w max.



P500030-009 Brushed Nickel 18" dia., 21" ht.





P500029-009 Brushed Nickel ***P500029-020** Antique Bronze 5" dia., 6.5" ht.


1 medium base, 100w max.

P350060-009 Brushed Nickel ***P350060-020** Antique Bronze 14" dia., 8.87" ht. 2 medium base, 100w max.



Fixture can be installed as a pendant using included hardware.

*P350061-009 Brushed Nickel P350061-020 Antique Bronze 14" dia., 6.62" ht.






ALSO IN



Bath













Cascadia

Etched glass.





Antique Bronze



*P4612-15 Polished Chrome
P4612-20 Antique Bronze
21" dia., 16.75" ht.
3 medium base, 100w max.

***P5066-15** Polished Chrome **P5066-20** Antique Bronze 5.87" dia., 6.75" ht. 1 medium base, 100w max.



P3644-15 Polished Chrome ***P3644-20** Antique Bronze 14" dia., 10" ht.

2 medium base, 100w max.



Fixture can be installed as a pendant using included hardware.



P3633-15 Polished Chrome ***P3633-20** Antique Bronze 14" dia., 6" ht. 2 medium base, 100w max.



*P2146-15 Polished Chrome P2146-20 Antique Bronze 5.87" W., 8" ht., 6.5" D. One medium base, 100w max.



ALSO IN



Invite

Inner etched white glass and outer sheer organza shade.



Brushed Nickel



P4696-09 Brushed Nickel 25.25" dia., 20.75" ht. 5 medium base, 100w max.



P2041-09 Brushed Nickel 6.5" W., 11.5" ht. One medium base, 100w max.



P3694-09 Brushed Nickel 15" dia., 5.25" ht. 3 medium base, 100w max.



Fixture can be installed

as a pendant using

included hardware.

P3693-09 Brushed Nickel 12" dia., 5.37" ht. 2 medium base, 100w max.



ALSO IN



Inspire

Off-white linen shade.



Brushed Nickel



Polished Chrome



Antique Bronze

*P4638-09 Brushed Nickel P4638-20 Antique Bronze 29.37" dia., 31" ht. 9 candelabra base, 60w max.



P4739-09 Brushed Nickel
*P4739-20 Antique Bronze
30" dia., 22" ht.
6 candelabra base, 60w max.



*P4632-09 Brushed Nickel
P4632-20 Antique Bronze
16.81" dia., 18" ht.
3 candelabra base, 60w max.

P2018-09 Brushed Nickel **P2018-15** Polished Chrome ***P2018-20** Antique Bronze 4.62" W., 7.62" ht., 7.37" D. 1 medium base, 100w max.



*P3799-09 Brushed Nickel P3799-20 Antique Bronze 14.75" dia., 20.25" ht. 1 medium base, 100w max.



P3931-09 Brushed Nickel ***P3931-20** Antique Bronze 19" dia., 21.5" ht. 3 medium base, 75w max.



*P5065-09 Brushed Nickel P5065-20 Antique Bronze 6.5" dia., 6.25" ht. 1 medium base, 100w max.



ALSO IN



Bath



Close-to-Ceiling

Trinity

Etched glass.



09 Brushed Nickel



Antique Bronze



P4329-09 Brushed Nickel *P4329-20 Antique Bronze 30" dia., 33" ht. 9 medium base, 100w max.





5 medium base, 100w max.



*P4324-09 Brushed Nickel P4324-20 Antique Bronze 19" dia., 20" ht.

3 medium base, 100w max.



P3806-09 Brushed Nickel *P3806-20 Antique Bronze 12" dia., 18" ht. 2 candelabra base, 60w max.



*P3474-09 Brushed Nickel P3474-20 Antique Bronze 18" dia., 24" ht.

3 medium base, 100w max.



P5095-09 Brushed Nickel *P5095-20 Antique Bronze 18" dia., 9.5" ht. 1 medium base, 150w max.

*P3473-09 Brushed Nickel P3473-20 Antique Bronze 16" dia., 15" ht. 2 medium base, 100w max.



Fixture can be installed as a pendant using included hardware.





P5096-09 Brushed Nickel *P5096-20 Antique Bronze 6.5" dia., 7" ht. 1 medium base, 100w max.



*P3475-09 Brushed Nickel P3475-20 Antique Bronze

12.5" dia., 7.37" ht. 1 medium base, 100w max.



P3476-09 Brushed Nickel *P3476-20 Antique Bronze

15" dia., 7.5" ht. 2 medium base, 60w max.



ALSO IN





Etched white glass.



09 Brushed Nickel



Antique Bronze



P4492-09 Brushed Nickel
*P4492-20W Antique Bronze
28" dia., 27.75" ht.
9 medium base, 100w max.



*P3587-09 Brushed Nickel P3587-20W Antique Bronze 14.62" dia., 17" ht. 3 candelabra base, 60w max.



P4489-09 Brushed Nickel
*P4489-20W Antique Bronze
20" dia., 16.37" ht.
3 medium base, 100w max.





P3864-09 Brushed Nickel ***P3864-20W** Antique Bronze 16.62" dia., 12.12" ht. 3 medium base, 100w max.





Fixture can be installed as a pendant using included hardware.

P5270-09 Brushed Nickel ***P5270-20W** Antique Bronze 6" dia., 7.12" ht. 1 medium base, 100w max.

ALSO IN



Bath



*P3855-09 Brushed Nickel P3855-20W Antique Bronze 13.31" dia., 9.56" ht. 2 medium base, 100w max.



P2000-09 Brushed Nickel ***P2000-20W** Antique Bronze 6" W., 9.5" ht., 1 medium base, 100w max.



Laird


Etched glass.



009 Brushed Nickel



Antique Bronze



P350136-009 Brushed Nickel ***P350136-020** Antique Bronze 15.62" dia., 11.75" ht. 3 medium base, 100w max.





*P500071-009 Brushed Nickel P500071-020 Antique Bronze 17" dia., 20.75" ht. 3 medium base, 100w max.



*P350057-009 Brushed Nickel P350057-020 Antique Bronze 13" dia., 9.87" ht. 2 medium base, 100w max.





Fixture can be
installed as a
pendant using
included hardware.

P300095-009 Brushed Nickel
P300095-020 Antique Bronze
5.75" W., 9" ht.
1 medium base, 100w max.



ALSO IN



Bath

Gather

Etched glass.



Brushed Nickel



Polished Chrome



Antique Bronze







P4440-09 Brushed Nickel *P4440-20 Antique Bronze 18.5" dia., 15" ht. 3 medium base, 100w max.



*P4734-09 Brushed Nickel P4734-20 Antique Bronze 19.5" dia., 16.5" ht. 3 medium base, 100w max.




P5113-09 Brushed Nickel *P5113-20 Antique Bronze 4" dia., 5.75" ht. 1 medium base, 100w max.



*P3929-09 Brushed Nickel P3929-20 Antique Bronze 15" dia., 24" ht. 6 candelabra base, 60w max.



P3928-09 Brushed Nickel *P3928-20 Antique Bronze 10" dia., 16" ht.






*P3914-09 Brushed Nickel P3914-20 Antique Bronze 15" dia., 20.62" ht. 2 medium base, 100w max.



P3748-09 Brushed Nickel *P3748-20 Antique Bronze 12.87" dia., 10.37" ht. 2 medium base, 100w max.



Fixture can be installed as a pendant using





ALSO IN



Bath

*Shown in finish

Merry

Etched glass.



009 Brushed Nickel



Polished Chrome



031 Matte Black



P500333-009 Brushed Nickel *P500333-031 Matte Black 15" dia., 23" ht. 1 medium base, 100w max.





*P400274-009 Brushed Nickel **P400274-031** Matte Black 18" dia., 16.37" ht. 3 medium base, 100w max.



*P300327-009 Brushed Nickel P300327-015 Polished Chrome **P300327-031** Matte Black 4.38" W., 8.25" ht., 5.75" D. 1 medium base, 100w max.



ALSO IN



Riley

Clear glass. Pendant with an organza shade.



009 Brushed Nickel



031 Matte Black







*P710082-009 Brushed Nickel **P710082-031** Matte Black 5" W., 14.5" ht., 4.62" D. 1 candelabra base, 60w max.



ALSO IN



Bath

Drum Shade

009 Brushed Nickel



Antique Bronze



Matte Black



Brushed Bronze

P4217-009 Brushed Nickel 21.62" dia., 21.12" ht. 5 candelabra base, 60w max. White linen fabric shade.



P4217-20 Antique Bronze 21.62" dia., 21.12" ht. 5 candelabra base, 60w max. White linen fabric shade.



P4217-109 Brushed Bronze 21.62" dia., 21.12" ht. 5 candelabra base, 60w max.

White linen fabric shade.



P400193-031 Matte Black 21.62" dia., 21.12" ht. 5 candelabra base, 60w max.

Harvest linen fabric shade.



Five-Light



Brushed Nickel



Antique Bronze



Textured Black

P4008-09 Brushed Nickel 21" dia., 16" ht. 5 candelabra base, 60w max.



P4008-31 Textured Black 21" dia., 16" ht. 5 candelabra base, 60w max.



P4009-09 Brushed Nickel 17.5" dia., 15.37" ht. 5 candelabra base, 60w max.



P4009-20 Antique Bronze 17.5" dia., 15.37" ht. 5 candelabra base, 60w max.



Classic

Etched glass.



Brushed Nickel



Polished Chrome



Antique Bronze

P4757-09 Brushed Nickel 23" dia., 17.25" ht. 5 medium base, 100w max.



P4770-09 Brushed Nickel ***P4770-20** Antique Bronze 21.87" dia., 17.25" ht. 5 medium base, 100w max.



P4762-09 Brushed Nickel 18" dia., 17.25" ht. 3 medium base, 100w max.



P500288-009 Brushed Nickel ***P500288-015** Polished Chrome **P500288-020** Antique Bronze 5.12" dia., 7" ht. 1 medium base, 100w max.



ALSO IN



Rath



Pendants

*Shown in finish

Seeded Glass



Brushed Nickel



Antique Bronze

P3753-09 Brushed Nickel 9.75" dia., 24.5" ht. 3 candelabra base, 60w max.



P3753-20 Antique Bronze 9.75" dia., 24.5" ht. 3 candelabra base, 60w max.




Eclipse

Satin white glass.



Brushed Nickel









P3561-09 Brushed Nickel 15.25" dia., 4.62" ht. 2 medium base, 60w max.



P7170-09 Brushed Nickel 15.25" W., 7.56" ht., 4" D. 1 medium base, 100w max.





Mingle

Metal and etched parchment glass.



Brushed Nickel



P5038-09 Brushed Nickel 6" dia., 6.37" ht. 1 medium base, 100w max.



Collections



Pivot LED

The Pivot LED Collection showcases angled arms rotating around a central axis for a bold architectural form highlighted by lustrous LED lightbars. An integrated downlight shines from the bottom of the center column to illuminate surfaces below.

FINISHES



Matte Black



186 Burnished Nickel



Pivot LED












Kylo LED








Quadrant LED

P400264-031-30 Matte Black 26.12" dia., 26.12" ht. 24w integrated LED, 3000K, 90 CRI, 1346 delivered lumens.



P350209-031-30 Matte Black 20.06" dia., 4" ht. 25w integrated LED, 3000K, 90 CRI, 1261 delivered lumens.



P710103-031-30 Matte Black 8.06" W., 24" ht., 3.3" D. 13w integrated LED, 3000K, 90 CRI, 686 delivered lumens.









shown wall mounted

Geodesic LED

The Geodesic LED Collection radiates a magical beauty throughout a room. Diffused edge-lit LED dispenses even illumination through the open diamond-patterned frame while a simple cable suspension adds to the clean style.

FINISH





031 Matte Black



Geodesic LED

P500320-031-30 Matte Black 27.1" dia., 12.3" ht. 38w integrated LED, 3000K, 90 CRI, 3373 delivered lumens.





P350229-31M-30 Matte Black 18" dia., 8" ht. 30w integrated LED, 3000K, 90 CRI, 1872 delivered lumens.



3

Inverse LED

A simple halo suspended by airy cables brings a minimal contemporary style to Inverse LED. Indirect illumination provided by integrated LED light source creates an inner glow that gently lights the surroundings.

FINISHES



009 Brushed Nickel



Matte Black

Inverse LED

P500370-009-30 Brushed Nickel 30" dia., 2.4" ht. 38w integrated LED, 3000K, 90 CRI, 2369 delivered lumens.



P500369-009-30 Brushed Nickel 20" dia., 2.4" ht. 27w integrated LED, 3000K, 90 CRI, 1641 delivered lumens.



P500370-31M-30 Matte Black 30" dia., 2.4" ht. 38w integrated LED, 3000K, 90 CRI, 2369 delivered lumens.




P500369-31M-30 Matte Black 20" dia., 2.4" ht. 27w integrated LED, 3000K, 90 CRI, 1641 delivered lumens.



Radian LED

Give any room an industrial vibe with Radian LED. A domed metal shade is supported by a contrasting cap and is finished inside with a reflective coating that casts a warm glow of light.

FINISHES









Radian LED

P500373-009-30 Brushed Nickel
16" dia., 14" ht.
30w integrated LED, 3000K,
90 CRI, 1546 delivered lumens.

P500373-028-30 Satin White
16" dia., 14" ht.
30w integrated LED, 3000K,
90 CRI, 1546 delivered lumens.

P500373-31M-30 Matte Black
16" dia., 14" ht.
30w integrated LED, 3000K,
90 CRI, 1546 delivered lumens.



CATALOG 134

Everlume® LED

Edge-lit diffuser.

FINISHES



009 Brushed Nickel



Matte Black



P500366-009-30



Spoke LED

Clear diffuser with laser-etched pattern.

FINISHES



009 Brushed Nickel



Matte Black



P500318-031-30





Globe LED

White opal glass shade.

FINISHES

009 Brushed Nickel



109 Brushed Bronze



P500148-109-30

P500148-009-30 Brushed Nickel
11.62" dia., 13.5" ht.
17w LED module, 3000K,
90 CRI, 1276 source lumens.

P500148-031-30 Matte Black
11.62" dia., 13.5" ht.
17w LED module, 3000K,
90 CRI, 1276 source lumens.

P500148-109-30 Brushed Bronze
11.62" dia., 13.5" ht.
17w LED module, 3000K,
90 CRI, 1276 source lumens.

P500147-009-30 Brushed Nickel 8" dia., 9.75" ht. 9w LED module, 3000K, 90 CRI, 624 source lumens.

P500147-031-30 Matte Black 8" dia., 9.75" ht. 9w LED module, 3000K, 90 CRI, 624 source lumens.

P500147-109-30 Brushed Bronze 8" dia., 9.75" ht. 9w LED module, 3000K, 90 CRI, 624 source lumens.



P5341-2030K9



16" dia., 8.87" ht.
17w LED module 3000K,
90 CRI, 1211 source lumens.

All fixtures:

P5341-3030K9 White





Planck LED



009 Brushed Nickel



031 Matte Black

P500276-031-30 Matte Black 47.25" L, 1.75" W., 1.37" ht. 39w integrated LED, 3000K, 90 CRI, 2900 delivered lumens.





P500276-009-30 Brushed Nickel 47.25" L, 1.75" W., 1.37" ht. 39w integrated LED, 3000K, 90 CRI, 2900 delivered lumens.





P710051-009-30 Brushed Nickel 4.75" W., 16" ht., 3" D. 16w integrated LED, 3000K, 90 CRI, 600 delivered lumens.





P710052-009-30 Brushed Nickel 4.75" W., 24" ht., 3" D. 32w integrated LED, 3000K, 90 CRI, 1100 delivered lumens.









shown vertical



Pendants

DISCOVER THE LATEST







STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

White kitchen cabinets and a dark center island drama, and sophistication to a kitchen. They create a striking contrast when paired with light wood countertops and a brick backsplash. The clean lines of a trio of Garris clear glass pendants add an airy but grounding feel to the space.

Pendants

1 Complete Selection

View our complete offering of pendants. Use the **Product Finder** in the beginning of the catalog (a number of pendants are found in Collections). We have conveniently grouped pendants by size:

p. 12 p. 16 p. 20

2 Get Creative

View our canopy options to pair multiple pendants or mix and match collections of pendants on a canopy for a striking focal point that will transform your space.



3 Want more?

Design Series offers more elevated product options. Use QR to view:

DESIGN+SERIES





Parkhurst

The Parkhurst pendant features a crisp dome metal shade suspended by an elegant ring. Light gleams softly from within, casting a soft glow on the surfaces below. This pendant is ideal for new traditional, modern farmhouse, and transitional interiors.

FINISHES



009 Brushed Nickel



Matte Black



Brushed Bronze



Parkhurst

P500367-009 Brushed Nickel 12.37" dia., 11.87" ht. 1 medium base, 100w max.



P500368-009 Brushed Nickel 17.87" dia., 15.25" ht. 3 medium base, 60w max.



P500367-31M Matte Black 12.37" dia., 11.87" ht. 1 medium base, 100w max.



P500368-31M Matte Black 17.87" dia., 15.25" ht. 3 medium base, 60w max.



P500367-109 Brushed Bronze 12.37" dia., 11.87" ht. 1 medium base, 100w max.



P500368-109 Brushed Bronze 17.87" dia., 15.25" ht. 3 medium base, 60w max.



Delayne

A softly curved fitted metal framework encases an opal glass globe in Delayne. The pendant offers a refined mid-century design enhanced by gently diffused light that creates an ambient glow.

FINISHES

009 Brushed Nickel



Brushed Bronze



Delayne

P500358-009 Brushed Nickel 9.37" dia., 12.37" ht. 1 medium base, 100w max.



P500359-009 Brushed Nickel 16.12" dia., 21.62" ht. 1 medium base, 100w max.



P500358-31M Matte Black 9.37" dia., 12.37" ht. 1 medium base, 100w max.



P500359-31M Matte Black 16.12" dia., 21.62" ht. 1 medium base, 100w max.



P500358-109 Brushed Bronze 9.37" dia., 12.37" ht. 1 medium base, 100w max.



P500359-109 Brushed Bronze 16.12" dia., 21.62" ht. 1 medium base, 100w max.



Clarion

The versatile Clarion Collection features a simple etched opal glass or clear glass diffuser for a design that embraces minimalist modernity and functional task lighting.

FINISHES

009 Brushed Nickel



Matte Black

104 Polished Nickel



Clarion

P500429-009 Brushed Nickel 9" dia., 11.37" ht. 1 medium base, 60w max.



P500430-009 Brushed Nickel 10.5" dia., 15.87" ht. 1 medium base, 60w max.



P500429-012 Satin Brass 9" dia., 11.37" ht. 1 medium base, 60w max.



P500430-012 Satin Brass 10.5" dia., 15.87" ht. 1 medium base, 60w max.



P500429-31M Matte Black 9" dia., 11.37" ht. 1 medium base, 60w max.



P500430-31M Matte Black 10.5" dia., 15.87" ht. 1 medium base, 60w max.



P500429-104 Polished Nickel 9" dia., 11.37" ht. 1 medium base, 60w max.



P500430-104 Polished Nickel 10.5" dia., 15.87" ht. 1 medium base, 60w max.





Clarion

P500241-009 Brushed Nickel 9" dia., 11.37" ht. 1 medium base, 60w max.



P500242-009 Brushed Nickel 10.5" dia., 15.87" ht. 1 medium base, 60w max.



P500241-012 Satin Brass 9" dia., 11.37" ht. 1 medium base, 60w max.



P500242-012 Satin Brass 10.5" dia., 15.87" ht. 1 medium base, 60w max.



P500241-031 Matte Black 9" dia., 11.37" ht. 1 medium base, 60w max.



P500242-031 Matte Black 10.5" dia., 15.87" ht. 1 medium base, 60w max.



P500241-104 Polished Nickel 9" dia., 11.37" ht. 1 medium base, 60w max.




P500242-104 Polished Nickel 10.5" dia., 15.87" ht. 1 medium base, 60w max.





P500365-186







P500409-191





Perimeter

Perimeter has an iconic modern design defined by an elegant metal dome that makes a bold statement. Light is cast generously from the circular open shade.

FINISHES

009 Brushed Nickel





31M Matte Black



Brushed Gold



Perimeter





Atwell







Cayce

Cayce's capsule silhouette showcases an interior candelabra cluster. An interlocking hexagonal design gracefully adorns the middle of the glass to add visual interest.

FINISHES

015

Polished Chrome



Vintage Gold



P500156-078

P500156-015 Polished Chrome 9" dia., 18.25" ht. 3 candelabra base, 60w max.



P500156-078 Vintage Gold 9" dia., 18.25" ht. 3 candelabra base, 60w max.





Terrazzo

The Terrazzo Collection features a polished concrete composite shade flecked with warm earthy hues offering a sophisticated contrast to its clean metal stem suspension. Terrazzo expresses an artistic sensibility perfect for eclectic settings.

FINISHES



143 Graphite



Distressed Brass



P500313-143

P500313-143 Graphite 10" dia., 9.37" ht. 1 medium base, 75w max.



P500313-175 Distressed Brass 10" dia., 9.37" ht. 1 medium base, 75w max.







Hinton





P500385-009 Brushed Nickel 16" dia., 14" ht. 1 medium base, 100w max.



P500384-31M Matte Black 16" dia., 14" ht. 1 medium base, 100w max.



P500385-31M Matte Black 16" dia., 14" ht.

1 medium base, 100w max.



P500384-163 Vintage Brass 16" dia., 14" ht. 1 medium base, 100w max.



P500385-163 Vintage Brass 16" dia., 14" ht. 1 medium base, 100w max.



Hinton

P500324-009 Brushed Nickel 12" dia., 12.5" ht. 1 medium base, 100w max.



P500325-009 Brushed Nickel 12.25" dia., 12.75" ht. 1 medium base, 100w max.



P500324-031 Matte Black 12" dia., 12.5" ht. 1 medium base, 100w max.



P500325-031 Matte Black 12.25" dia., 12.75" ht. 1 medium base, 100w max.



P500324-104 Polished Nickel 12" dia., 12.5" ht. 1 medium base, 100w max.



P500325-104 Polished Nickel 12.25" dia., 12.75" ht. 1 medium base, 100w max.



P500324-163 Vintage Brass 12" dia., 12.5" ht. 1 medium base, 100w max.



P500325-163 Vintage Brass 12.25" dia., 12.75" ht. 1 medium base, 100w max.



Hinton

P500382-009 Brushed Nickel 8" dia., 8.62" ht. 1 medium base, 60w max.



P500383-009 Brushed Nickel 8.25" dia., 8.62" ht. 1 medium base, 60w max.



P500382-31M Matte Black 8" dia., 8.62" ht. 1 medium base, 60w max.



P500383-31M Matte Black 8.25" dia., 8.62" ht. 1 medium base, 60w max.



P500382-163 Vintage Brass 8" dia., 8.62" ht. 1 medium base, 60w max.



P500383-163 Vintage Brass 8.25" dia., 8.62" ht. 1 medium base, 60w max.



Medal

A smoothly curved metal shade ornamented with a star motif medallion holds a headlight-style glass diffuser, reminiscent of a vintage automobile engine.

FINISHES

009 Brushed Nickel

Graphite

Coastal Blue



P500212-164





Rushton

The Rushton collection features exposed bulbs that glow elegantly from within clear glass. Mechanicalinspired fittings complete the industrial theme to make a bold statement in your home.

FINISHES

009 Brushed Nickel



Graphite



P500329-143


P500329-009 Brushed Nickel 8.5" dia., 16.87" ht. 1 medium base, 100w max.



P500329-143 Graphite 8.5" dia., 16.87" ht. 1 medium base, 100w max.









Latrobe

Introduce a pop of personality with the Latrobe Collection. A bottle inspired design adds an unexpected twist to a simple, understated industrial style that brings the collection's vintage charm to the forefront of your home's lighting design.

FINISHES

009 Brushed Nickel

Matte Black



P500231-031

P500229-009 Brushed Nickel 7" dia., 17" ht. 1 medium base, 60w max.



P500230-009 Brushed Nickel 9.43" dia., 15.5" ht. 1 medium base, 60w max.



P500231-009 Brushed Nickel 12.25" dia., 14" ht. 1 medium base, 60w max.



P500229-031 Matte Black 7" dia., 17" ht. 1 medium base, 60w max.



P500230-031 Matte Black 9.43" dia., 15.5" ht. 1 medium base, 60w max.



P500231-031 Matte Black 12.25" dia., 14" ht. 1 medium base, 60w max.



Penn

Penn offers a modern take on vintage design. Turnkey details clear glass globes are enhanced by a Polished Nickel or Natural Brass finish.

FINISHES



104 Polished Nickel



Natural Brass



P5328-104

P5067-104 Polished Nickel 6.87" dia., 9.5" ht. 1 medium base, 100w max.



P5070-104 Polished Nickel 9.75" dia., 12.75" ht. 1 medium base, 100w max.



P5328-104 Polished Nickel 12" dia., 15" ht. 1 medium base, 100w max.



P5067-137 Natural Brass 6.87" dia., 9.5" ht. 1 medium base, 100w max.



P5070-137 Natural Brass 9.75" dia., 12.75" ht. 1 medium base, 100w max.



P5328-137 Natural Brass 12" dia., 15" ht. 1 medium base, 100w max.



CATALOG 134

Range

The Range Collection features a simple geometric glass outlined with a slender frame and finished with a bottom metal accent ring.

FINISHES

009 Brushed Nickel



Antique Bronze



Polished Nickel



Graphite



P500135-020

P500135-009 Brushed Nickel 13" dia., 13" ht.

1 medium base, 60w max.



P500135-020 Antique Bronze 13" dia., 13" ht. 1 medium base, 60w max.



P500135-104 Polished Nickel 13" dia., 13" ht. 1 medium base, 60w max.



P500135-143 Graphite 13" dia., 13" ht. 1 medium base, 60w max.



Calhoun

An apothecary style clear glass diffuser is held in place with a mechanical latch from a spice container. The glass shade showcases a thickened profile to create a vintage-style surface for a classic handmade appearance.

FINISHES

009 Brushed Nickel



Antique Bronze



P500152-020

P500055-009 Brushed Nickel 4.75" dia., 9" ht. 1 medium base, 100w max.



P500055-020 Antique Bronze 4.75" dia., 9" ht. 1 medium base, 100w max.



P500152-009 Brushed Nickel 12" dia., 9.37" ht. 1 medium base, 60w max.



P500152-020 Antique Bronze 12" dia., 9.37" ht. 1 medium base, 60w max.



Bastille

A basket-inspired dual-toned metal shade suspended by a simple chain encloses a single bulb socket.

FINISHES



White



Aged Brass



Coastal Blue



P500236-030





P500053-143





Fresnel LED

Industrial roots in form and function. Antiqueinspired Fresnel glass lens in Brushed Nickel, or Oil Rubbed Bronze.

FINISHES

09


Brushed Nickel



Oil Rubbed Bronze



Fresnel/Fresnel LED







P5190-20

P5180-20 Antique Bronze 14" dia., 17.25" ht. 1 medium base, 60w max.



P5190-20 Antique Bronze 20" dia., 23.25" ht. 4 medium base, 60w max.



Tally

Tally Collection embraces a simplified classic form that is updated with modern inspiration. The open foyer pendant offers visual interest and enhances relaxed environments.

FINISHES

09 Brushed Nickel

Antique Bronze



P3787-20

P3786-09 Brushed Nickel 11.87" dia., 19.25" ht. 4 candelabra base, 60w max.



P3787-09 Brushed Nickel 16.75" dia., 26.5" ht. 4 candelabra base, 60w max.



P3786-20 Antique Bronze 11.87" dia., 19.25" ht. 4 candelabra base, 60w max.



P3787-20 Antique Bronze 16.75" dia., 26.5" ht. 4 candelabra base, 60w max.





Markor







White Linen

P500386-193 Black Parchment 12" dia., 10" ht. 1 medium base, 100w max.



P500387-193 Black Parchment 18.12" dia., 10" ht. 3 medium base, 60w max.



P500386-194 Ecru Linen 12" dia., 10" ht. 1 medium base, 100w max.



P500387-194 Ecru Linen 18.12" dia., 10" ht. 3 medium base, 60w max.



P500386-195 White Linen 12" dia., 10" ht. 1 medium base, 100w max.



P500387-195 White Linen 18.12" dia., 10" ht. 3 medium base, 60w max.



INCLUDED







-163 Vintage Brass

Archives

Antique Bronze with a Natural Brass accent and Antique Nickel with a Brushed Nickel accent.





P5161-20 Antique Bronze 9" dia., 5.12" ht. 1 medium base, 100w max.



P5161-81 Antique Nickel 9" dia., 5.12" ht. 1 medium base, 100w max.



Trestle

Gilded Iron with hand-painted oak accent.

71 Gilded Iron



P5315-71 Gilded Iron 7.87" dia., 6.37" ht. 1 medium base, 60w max.



P4720-71 Gilded Iron 32.5" W., 20.37" ht. 4 medium base, 60w max.



Double Glass

Etched white glass within a clear seeded glass outer shade.



Graphite

P500018-015 Polished Chrome 5.87" dia., 10" ht. 1 medium base, 100w max.



P500018-143 Graphite 5.87" dia., 10" ht. 1 medium base, 100w max.



P500019-015 Polished Chrome 7.75" dia., 13.5" ht. 1 medium base, 100w max.



P500019-143 Graphite 7.75" dia., 13.5" ht. 1 medium base, 100w max.



Clear Glass



104 Polished Nickel

Litchfield



Polished Chrome

P5184-104 Polished Nickel 8" dia., 8.75" ht. 1 medium base, 100w max.



P500113-015 Polished Chrome 4.75" dia., 9.37" ht. 1 medium base, 60w max.



Neat LE

Opal glass.

009 Brushed Nickel

P500065-009-30 Brushed Nickel 4.37" dia., 13.5" ht. 9w LED module, 3000K, 90 CRI, 624 source lumens.









Clear or etched glass.



009 Brushed Nickel



Polished Chrome



31M Matte Black



Vintage Brass

P500403-009 Brushed Nickel 4" dia., 9.75" ht. 1 medium base, 60w max.



P500404-009 Brushed Nickel 4" dia., 9.75" ht. 1 medium base, 60w max.



P500403-015 Polished Chrome 4" dia., 9.75" ht. 1 medium base, 60w max.



P500404-015 Polished Chrome 4" dia., 9.75" ht. 1 medium base, 60w max.



P500403-31M Matte Black 4" dia., 9.75" ht. 1 medium base, 60w max.




P500404-31M Matte Black 4" dia., 9.75" ht. 1 medium base, 60w max.



P500403-163 Vintage Brass 4" dia., 9.75" ht. 1 medium base, 60w max.



P500404-163 Vintage Brass 4" dia., 9.75" ht. 1 medium base 60w max.





Garris

Clear or etched opal glass.



009 Brushed Nickel



31M Matte Black



Vintage Brass

P500405-009 Brushed Nickel 8" dia., 8.25" ht. 1 medium base, 60w max.



P500406-009 Brushed Nickel 8" dia., 8.25" ht. 1 medium base, 60w max.



P500405-31M Matte Black 8" dia., 8.25" ht. 1 medium base, 60w max.




P500406-31M Matte Black 8" dia., 8.25" ht. 1 medium base, 60w max.



P500405-163 Vintage Brass 8" dia., 8.25" ht. 1 medium base, 60w max.



P500406-163 Vintage Brass 8" dia., 8.25" ht.





Chambers

031

031 Matte Black



Galvanized Finish

P500281-031 Matte Black 10" dia., 11" ht. 1 medium base, 100w max.



P500281-141 Galvanized Finish 10" dia., 11" ht. 1 medium base, 100w max.



Gauge

Graphite with Brushed Nickel accent.



Arden

Etched glass

09

Brushed Nickel

P500021-143 Graphite 6.12" dia., 9.5" ht. 1 medium base, 60w max.



P5092-09 Brushed Nickel 5.87" dia., 9.62" ht., 1 medium base, 100w max.



Bay Court

Etched white and clear water glass.



Brushed Nickel

P3701-09 Brushed Nickel 11.75" dia., 18.25" ht. 1 medium base, 100w max.



P5589-09 Brushed Nickel 8.75" dia., 12.75" ht. 1 medium base, 100w max.





Clear glass.



009 Brushed Nickel



Antique Bronze

P500137-009 Brushed Nickel 7.25" dia., 8" ht. 1 medium base, 60w max.



P500137-020 Antique Bronze 7.25" dia., 8" ht. 1 medium base, 60w max.



Schoolhouse

White opal glass.



09 Brushed Nickel



031 Matte Black



163 Vintage Brass

P5196-09 Brushed Nickel 8" dia., 9" ht. 1 medium base, 100w max.



P5196-31M Matte Black 8" dia., 9" ht. 1 medium base, 100w max.



P5196-163 Vintage Brass 8" dia., 9" ht. 1 medium base, 100w max.



Prismatic

Prismatic glass.






P5182-09 Brushed Nickel 12.75" dia., 11" ht. 1 medium base, 100w max.



Prismatic LED

Prismatic glass.



P5143-0930K9 Brushed Nickel 12.75" dia., 10.87" ht. 9w LED module 3000K, 90 CRI, 623 source lumens.





Archie

Clear double-prismatic glass.

74 Venetian Bronze



***P5026-74** Venetian Bronze **P5026-81** Antique Nickel 10.5" dia., 9.25" ht. 1 medium base, 100w max.



P5173-74 Venetian Bronze ***P5173-81** Antique Nickel 5.75" dia., 8.75" ht. 1 medium base, 100w max.





Etched glass cone and clear glass shade.





P5012-09 Brushed Nickel 20" dia., 7.5" ht. 1 medium base, 150w max.

Avant LED

Polished and etched glass.

009 Brushed Nickel

Antique Bronze

P5072-0930K9 Brushed Nickel 9" dia., 4.75" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.





P5072-0930K9 Brushed Nickel 9" dia., 4.75" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.





Alabaster Glass



Brushed Nickel

Satin Opal Glass



Brushed Nickel





P5013-09 Brushed Nickel 16.62" dia., 8.87" ht. 1 medium base, 100w max.



Brookside/Brookside LED

09 Brushed Nickel

P5024-09 Brushed Nickel 12" dia., 9.12" ht. 1 medium base, 150w max.



P5024-0930K9 Brushed Nickel 12" dia., 9.25" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.





Classic Dome

Etched glass.









P500149-009 Brushed Nickel 15" dia., 8.12" ht. 1 medium base, 100w max.



P500149-015 Polished Chrome 15" dia., 8.12" ht. 1 medium base, 100w max.



P500149-020 Antique Bronze 15" dia., 8.12" ht. 1 medium base, 100w max.



P500149-31M Matte Black 15" dia., 8.12" ht. 1 medium base, 100w max.









White



Matte Black



Dark Green



Venetian Bronze



P5094-31M Matte Black 16" dia., 7.5" ht. 1 medium base, 150w max.



P5094-45 Dark Green 16" dia., 7.5" ht. 1 medium base, 150w max.



P5094-74 Venetian Bronze 16" dia., 7.5" ht. 1 medium base, 150w max.



P5094-09 Brushed Nickel 16" dia., 7.5" ht. 1 medium base, 150w max.



P5087-09 Brushed Nickel 10.12" dia., 6.5" ht. 1 medium base, 100w max.



Warehouse Pendant LED



Brushed Nickel

P5094-0930K9 Brushed Nickel 16" dia., 8" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.







Etched glass.



09 Brushed Nickel



Antique Bronze

P5131-09 Brushed Nickel 5.81" dia., 6" ht. 1 medium base, 100w max.



P5131-20 Antique Bronze 5.81" dia., 6" ht. 1 medium base, 100w max.



Etched and Clear Glass



09 Brushed Nickel



Alabaster glass.



Brushed Nickel

P5158-09 Brushed Nickel 5.31" dia., 7.25" ht. 1 medium base, 100w max.



P5068-09 Brushed Nickel 7.75" dia., 6.25" ht. 1 medium base, 100w max.



Opal Glass

White opal glass.



White

P4406-29 White 13.87" dia., 14" ht. 1 medium base, 150w max.



P4403-29 White 11.87" dia., 12" ht. 1 medium base, 150w max.




P4402-29 White 9.87" dia., 10" ht. 1 medium base, 100w max.



P4401-29 White 7.87" dia., 8" ht. 1 medium base, 60w max.





STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Progress Lighting's canopy accessory offers a convenient way to mount groupings of pendants. Pair multiple pendants or mix and match collections of pendants on a canopy for a striking focal point that will transform your space.

Linear Canopy

009 Brushed Nickel







Graphite

FIVE-LIGHT LINEAR
P860004-009 Brushed Nickel
P860004-020 Antique Bronze
P860004-31M Matte Black
P860004-143 Graphite
60" L, 6" W., 1" ht.



THREE-LIGHT LINEAR

P8404-09 Brushed Nickel P8404-20 Antique Bronze P8404-31M Matte Black P8404-109 Brushed Bronze P8404-143 Graphite

23.25" L, 4.25" W., 0.75" ht.





Round Canopy











THREE-LIGHT ROUND P8403-09 Brushed Nickel P8403-20 Antique Bronze P8403-31M Matte Black P8403-109 Brushed Bronze P8403-143 Graphite 15.5" dia., 1.37" ht.



Shades

P8926-01

Drum Off-White Linen 5.5" dia., 4.87" ht.

P860042-000

Tapered Flax Linen 6" dia., 5.12" ht.

P860059-000

Drum White Linen 5" dia., 5" ht.

P860060-000

Tapered White Linen 5.5" dia., 5.5" ht.

P860061-068

Clear Glass 3" dia., 8.75" ht.

P860061-029

Etched White Glass 3" dia., 8.75" ht.














Chain

9-Gauge Square Profile Chain


P8755-09 Brushed Nickel P8755-30 White P8755-31M Matte Black P8755-81 Antique Nicke P8755-108 Oil Rubbed Bronze P8755-134 Silver Ridge P8755-141 Galvanized Finish P8755-160 Brushed Brass P8755-161 Aged Brass P8755-192 Shelter White

- 4 feet of 9 gauge square chain permits installation of large chain-hung fixtures on high ceilings.
- Maximum fixture weight 50 lbs.



9-Gauge Chain

P8757-09 Brushed Nickel P8757-15 Polished Chrome P8757-20 Antique Bronze P8757-31 Textured Black **P8757-71** Gilded Iron P8757-74 Venetian Bronze P8757-77 Forged Bronze P8757-78 Vintage Gold P8757-81 Antique Nickel P8757-104 Polished Nickel P8757-108 Oil Rubbed Bronze P8757-109 Brushed Bronze P8757-126 Burnished Silver **P8757-134** Silver Ridge P8757-137 Natural Brass **P8757-141** Galvanized **P8757-143** Graphite P8757-151 Cottage White P8757-160 Brushed Brass



 10 feet of 9 gauge chain permits installation of large chain-hung fixtures on high ceilings.

P8757-161 Aged Brass

• Maximum fixture weight - 50 lbs.

P8758-163 Vintage Brass P8758-175 Distressed Brass P8758-196 Aged Bronze P8758-31M Matte Black

- 4 feet of 9 gauge chain permits installation of large chain-hung fixtures on high ceilings.
- Maximum fixture weight 50 lbs.



Pendant Accessories

Socket Collar Tool

The socket collar tool provides extra leverage and eliminates a loose fit when installing glass shades. Working like a wrench, the socket collar tool extends into the shade and tightens the socket ring, securing the shade in place, and can reverse to loosen the ring to remove the shade. This accessory can be used on a variety of fixtures, including chandeliers, mini-pendants, sconces and wall brackets.

P8685-01 Socket Collar Tool 2-5/8" dia., 7-7/8" tall.















Stem Kits

Contains (2) 12" and (2) 15" stems and couplings.

P8601-09 Brushed Nickel P8601-12 Satin Brass P8601-15 Polished Chrome P8601-20 Antique Bronze P8601-31 Black **P8601-71** Gilded Iron P8601-74 Venetian Bronze P8601-77 Forged Bronze P8601-78 Vintage Gold P8601-81 Antique Nickel


P8601-104 Polished Nickel P8601-108 Oil Rubbed Bronze P8601-109 Brushed Bronze P8601-134 Silver Ridge P8601-137 Natural Brass **P8601-141** Galvanized **P8601-143** Graphite P8601-151 Cottage White P8601-160 Brushed Brass

Contains (2) 6" and (1) 12" stems and couplings.

P8602-09 Brushed Nickel P8602-20 Antique Bronze P8602-31M Matte Black P8602-163 Vintage Brass P8602-168 Antique Gold

P8602-175 Distressed Brass P8602-176 Gilded Silver P8602-191 Brushed Gold **P8602-196** Aged Bronze

P8601-161 Aged Brass







P8601-137

P8601-141

Socket/Cord Kit for Higher Ceilings

Provides additional length to cord-hung fixtures (only) for installations on high ceilings and in stairwells. For use with P4401, P4402, P4403, P4406, and P5094.

P8625-30 White 15' cord with socket for replacement on cordhung pendants.





P8625-30

Loop and Chain Kit

Converts any stem-hung pendant to sloped ceiling applications. Kit includes (6) chain links, (2) 1/8" I.P. loops, (2) 1/8" I.P. x 9/16" nipples, (1) hex nut, (1) int. lock washer, and (1) 12" piece of fiberglass sleeving.

P8678-09 Brushed Nickel P8678-20 Antique Bronze 7/8" dia., 9-1/2" ht.







Ceiling Fans

DISCOVER THE LATEST





STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Accent a feature ceiling with a fan that complements its warm wood tones. The Upshur ceiling fan delivers a modern look from three hand-finished ABS blades in gray weathered wood. The blades have a distinctive, angled design and are mounted directly to the flywheel to complete the fan's sleek style.

1 In this section

Our indoor and outdoor ceiling fans complement various design trends while controlling airflow year-round.

Indoor pages 348 - 425



2 Reversible Blades

Fan blades are finished on both sides, offering two options to coordinate with a room's design aesthetic.



Watch this video to find the perfect fan featuring Steve Register, Progress Lighting Sr. Product Manager.







(4) Fan Icons

Important icons to know the meaning. Complete descriptions are on page 777.



Energy Star certified



Dry/Indoor only



Damp location okay



Wet location okay



WiFi compatible



CCT Selectable

Efficiency



cUL listed, available for Canada

LED tested, listed in CA Appliance Database

Fan has DC motor

California Appliance



WiFi control included

SUP.

Vernal



031 Black



Architectural Bronze



Painted Nickel

P250059-031-30 Black 60" dia., 13.63" ht. Shown with Matte Black blades



Matte Black



P250059-129-30 Architectural Bronze 60" dia., 13.63" ht. Shown with Koa Woodgrain blades Koa Woodgrain



P250059-152-30 Painted Nickel 60" dia., 13.63" ht. Shown with Painted Nickel blades Painted Nickel

ENERGY INFORMATION

Airflow 6,810 cubic feet per minute **Electricity Use** 34 watts (excludes lights)

DOE Weighted CFM/W 242 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- · ABS blades
- Opal shatterproof shade
- Damp Rated
- · WiFi enabled
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI, 1600 source lumens, dimmable.













Ryne

(028) Satin White



Architectural Bronze

P250060-028-30 Satin White 52" dia., 13.5" ht. Shown with Satin White blades



Satin White



P250060-031-30 Black 52" dia., 13.5" ht. Shown with Matte Black blades



Matte Black



P250060-129-30 Architectural Bronze 52" dia., 13.5" ht. Shown with Koa Woodgrain blades



Koa Woodgrain



ENERGY INFORMATION

Airflow 5,802 cubic feet per minute **Electricity Use** 33 watts (excludes lights)

DOE Weighted CFM/W 204 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Damp Rated
- · Remote control with batteries included
- Add a P2673-01 WiFi module to convert to a smart fan

LAMPING

18w LED Module, 3000K, 90 CRI, 1600 source lumens, dimmable.









Willacy





Painted Nickel

P250063-031 Black 48" dia., 14.5" ht. Shown with Matte Black blades





P250063-152 Painted Nickel 48" dia., 14.5" ht Shown with Painted Nickel blades



Painted Nickel



ENERGY INFORMATION

Airflow 4,544 cubic feet per minute **Electricity Use** 14 watts (excludes lights)

DOE Weighted CFM/W 318 CFM/W



Full Function Remote Control Included Six-speed fan operation Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- ABS blades
- Damp Rated
- WiFi enabled
- · Remote control with batteries included









Bastrop

009 Brushed Nickel



31M Matte Black



Graphite

P250096-009 Brushed Nickel 26" dia., 13.6" ht. Shown with Grey Weathered Wood blades



Grey Weathered Wood



P250096-31M Matte Black 26" dia., 13.6" ht. Shown with Rustic Charcoal blades



Rustic Charcoal



P250096-143 Graphite 26" dia., 13.6" ht. Shown with Aged Oak blades



Aged Oak



ENERGY INFORMATION

Airflow 1474 cubic feet per minute

Electricity Use 11 watts DOE Weighted CFM/W 100 CFM/W



Three-speed Remote Control Included Three-speed fan operation

FEATURES

- · Limited Lifetime warranty
- AC Motor
- · ABS blades
- Damp Rated
- · Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control







Belva





Cottage White

P250068-31M-WB Matte Black 25.25" dia., 17.87" ht. Shown with Mocha colored wicker





P250068-151-WB CottageWhite 25.25" dia., 17.87" ht. Shown with Whitewashed wicker



Cottage White



ENERGY INFORMATION

Airflow 1,125 cubic feet per minute **Electricity Use** 37 watts (excludes lights) DOE Weighted CFM/W 37 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Damp Rated
- · Remote control with batteries included
- Add a P2630-30 or P2613-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

Four medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 5.5w LED max/socket.









Gulliver





P250012-141-22 Galvanized Finish 23.5" dia., 18.12" ht. Shown with Antique White Wood



Antique White Wood



P250012-143-22 Graphite 23.5" dia., 18.12" ht. Shown with Gray Wood



Gray Wood



ENERGY INFORMATION

Airflow **Electricity Use Airflow Efficiency** 1,297 cubic feet per minute 39 watts (excludes lights) 33 cubic feet per minute per watt

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible Motor
- Rust-proof non-metallic blades
- Damp Rated
- · Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING

Three medium base 2200K 5.5w vintage LED lamps included. 500 lumens/ lamp, 80 CRI, dimmable. 5.5w LED max/socket.

All fixtures:











Three-speed fan operation Full-range dimming for light

Remote Control Included

Briarwood







141 Galvanized Finish



Graphite

P250067-020-WB Antique Bronze 22" sq., 22" sq., 17" ht. Shown with Rich Oak faux wood



P250067-31M-WB Matte Black 22" sq., 22" sq., 17" ht. Shown with Ceruse Black Oak faux wood



P250067-141-WB Galvanized Finish 22" sq., 22" sq., 17" ht. Shown with Bleached Oak faux wood



P250067-143-WB Graphite 22" sq., 22" sq., 17" ht.

Shown with White Washed faux wood



ENERGY INFORMATION

Airflow 1,145 cubic feet per minute **Electricity Use** 31 watts (excludes lights) DOE Weighted CFM/W 37 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- · Damp Rated
- · Remote control with batteries included
- Add a P2630-30 or P2613-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

LAMPING

Four medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 5.5w LED max/socket.







Sanford



09 Brushed Nickel



Architectural Bronze

P2594-0930K Brushed Nickel 22.87" dia., 17.75" ht.



P2594-12930K Architectural Bronze 22.87" dia., 17.75" ht.



ENERGY INFORMATION

Airflow 1,008 cubic feet per minute **Electricity Use** 37 watts (excludes lights)

DOE Weighted CFM/W 27 CFM/W



Three-speed Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Metal blades
- · Damp Rated
- Remote control with batteries included
- · Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

26w LED module, 3000K, 90 CRI, 2638 source lumens, dimmable.







52" Springer



Matte Black



Antique Nickel



Architectural Bronze

P250065-31M Matte Black 52" dia., 17.37" ht. Shown with Rustic Charcoal blades



Rustic Charcoal



P250065-081 Antique Nickel 52" dia., 17.37" ht. Shown with White Barnwood blades



White Barnwood



P250065-129 Architectural Bronze 52" dia., 17.37" ht. Shown with Distressed Walnut blades



Distressed Walnut



ENERGY INFORMATION

Airflow 6,296 cubic feet per minute **Electricity Use** 30 watts (excludes lights)

DOE Weighted CFM/W 245 CFM/W



Full Function Remote Control Included Six-speed fan operation Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-22°)
- DC Motor
- · Plywood blades
- · Remote control with batteries included
- Add a P2673-01 WiFi module to convert











LAMPING

11.87" dia., 7.5" ht.

2 medium base, 7w max.



P260000-129-WB Architectural Bronze

P260000-31M-WB Matte Black

P260000-081-WB Antique Nickel



60" Springer



Matte Black



Antique Nickel



Architectural Bronze

P250000-31M Matte Black 60" dia., 17.37" ht.



Rustic Charcoal



P250000-081 Antique Nickel 60" dia., 17.37" ht. Shown with White Barnwood blades



White Barnwood



P250000-129 Architectural Bronze 60" dia., 17.37" ht. Shown with Distressed Walnut blades



Distressed Walnut



ENERGY INFORMATION

Airflow 6,377 cubic feet per minute **Electricity Use** 33 watts (excludes lights)

DOE Weighted CFM/W 206 CFM/W



Full Function Remote Control Included Six-speed fan operation Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-22°)
- DC Motor
- · Plywood blades
- · Remote control with batteries included
- Add a P2673-01 WiFi module to convert to a smart fan









ALSO IN: LIGHT KITS

P260000-31M-WB Matte Black P260000-081-WB Antique Nickel P260000-129-WB Architectural Bronze 11.87" dia., 7.5" ht.

2 medium base, 7w max.







Kaysville



Antique Nickel



Graphite

P250003-081-30 Antique Nickel 56" dia., 17.25" ht. *Shown with Chesnut blades*



Chestnut



P250003-143-30 Graphite

56" dia., 17.25" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



ENERGY INFORMATION

Airflow 9,650 cubic feet per minute **Electricity Use** 31 watts (excludes lights)

DOE Weighted CFM/W 361 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass shade
- Damp Rated
- Remote control with batteries included

LAMPING

24w LED Module, 3000K, 90 CRI, 2000 source lumens, dimmable.









Freestone



009 Brushed Nickel



020 Antique Bronze



Matte Black

P250095-009-WB Brushed Nickel

52" dia., 15" ht.

Shown with Silver blades



Silver



Gray Weathered Wood



P250095-020-WB Antique Bronze

52" dia., 15" ht. Shown with Walnut blades



Walnut



Distressed Walnut



P250095-31M-WB Matte Black

52" dia., 15" ht.

Shown with Matte Black blades



Matte Black



Gray Weathered Wood



ENERGY INFORMATION

Airflow 3236 cubic feet per minute **Electricity Use** 36 watts (excludes lights)

DOE Weighted CFM/W 90 CFM/W

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal shatterproof shade
- 3 Speed pull chain switches
- Add the P2667-31 WiFi remote control

LAMPING

2 medium base, 3000K, 6w LED lamps included, 500 lumens/lamp, dimmable.







Mesilla



020 Antique Bronze



Antique Nickel



Flat Black

P250073-020 Antique Bronze 60" dia., 14.25" ht. Shown with Antique Wood blades



Antique Wood



P250073-081 Antique Nickel 60" dia., 14.25" ht. Shown with White Barnwood blades



White Barnwood



P250073-182 Flat Black 60" dia., 14.25" ht Shown with Gray Weathered Wood blades



Gray Weathered Wood



ENERGY INFORMATION

Airflow 6,966 cubic feet per minute **Electricity Use** 38 watts (excludes lights)

DOE Weighted CFM/W 217 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- · ABS blades
- Damp Rated
- · Remote control with batteries included







Alleron



Antique Nickel



P250009-081-30 Antique Nickel 56" dia., 16" ht.



Gray Weathered Wood



P250009-182-30 Flat Black

56" dia., 16" ht. Shown with Antique Black blades



Antique Black



ENERGY INFORMATION

Airflow 7,801 cubic feet per minute **Electricity Use** 20 watts (excludes lights)

DOE Weighted CFM/W 423 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- · White opal glass shade
- Damp Rated
- · Remote control with batteries included

LAMPING

24w LED Module, 3000K, 90 CRI, 2000 source lumens, dimmable.









Byars



009 Brushed Nickel



Matte Black

P250061-009-30 Brushed Nickel

54" dia., 16" ht.

Shown with American Walnut blades



American Walnut



Chesnut



P250061-31M-30 Matte Black

54" dia., 16" ht. Shown with Black blades



Black



Antique Black



ENERGY INFORMATION

Airflow 6,477 cubic feet per minute **Electricity Use** 30 watts (excludes lights)

DOE Weighted CFM/W 250 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- DC Motor
- Reversible plywood blades
- Up and down light
- · Double lens shades
- Remote control with batteries included

LAMPING

Downlight - 18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable. Uplight - 12w LED Module, 3000K, 90 CRI, 1100 source lumens, dimmable.







Gillen



31M Matte Black



Vintage Brass



Blistered Iron

P250075-31M-WB Matte Black 56" dia., 21.65" ht. Shown with Rustic Charcoal blades



Rustic Charcoal



P250075-163-WB Vintage Brass 56" dia., 21.65" ht. Shown with Chesnut blades



Chesnut



P250075-171-WB Blistered Iron 56" dia., 21.65" ht. Shown with Grey Weathered Wood blades



Grey Weathered Wood



ENERGY INFORMATION

Airflow 6,500 cubic feet per minute **Electricity Use** 35 watts (excludes lights)

DOE Weighted CFM/W 198 CFM/W



Full Function Remote Control Included Six-speed fan operation Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- DC Motor
- · Plywood blades
- Clear glass lens shade
- Damp Rated
- · Remote control with batteries included

LAMPING

7w LED lamp included, 2700K, 90 CRI, 600 source lumens, dimmable.







Spicer



009 Brushed Nickel



020 Antique Bronze



Matte Black

P250071-009 Brushed Nickel 54" dia., 11.5" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



P250071-020 Antique Bronze 54" dia., 11.5" ht.

Shown with Antique Wood blades



Antique Wood



P250071-31M Matte Black 54" dia., 11.5" ht. Shown with Antique Black blades



Antique Black



ENERGY INFORMATION

Airflow 4,521 cubic feet per minute **Electricity Use** 35 watts (excludes lights)

DOE Weighted CFM/W 158 CFM/W



Full Function Remote Control Included Six-speed fan operation Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Damp Rated
- Remote control with batteries included







Ellwood



09 Brushed Nickel



Antique Bronze

P2546-09 Brushed Nickel 68" dia., 15.7" ht. Shown with Driftwood blades



Driftwood



P2546-20 Antique Bronze 68" dia., 15.7" ht. Shown with Walnut blades



Walnut



ENERGY INFORMATION

Airflow 7,587 cubic feet per minute **Electricity Use** 90 watts (excludes lights)

DOE Weighted CFM/W 92 CFM/W



Full Function Remote Control Included Three-speed fan operation Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented carved wood blades
- · Compatible with universal light kits
- · Remote control with batteries included
- · Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote control





Caleb



09 Brushed Nickel



Antique Bronze



Black

P2560-09WW Brushed Nickel
68" dia., 18" ht.
Shown with Gray Weathered Wood blades

Gray Weathered Wood

P2560-20 Antique Bronze 68" dia., 18" ht. Shown with Walnut blades



Walnut



P2560-20AW Antique Bronze 68" dia., 18" ht.
Shown with Antique Wood blades



Antique Wood



ENERGY INFORMATION

Airflow 7,045 cubic feet per minute
Electricity Use 86 watts (excludes lights)

DOE Weighted CFM/W 91 CFM/W



Full Function Remote Control Included Three-speed fan operation Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented bent carved wood blades
- Compatible with universal light kits
- Remote control with batteries included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote control





Huff

009 Brushed Nickel



(028) Satin White









ENERGY INFORMATION

Airflow 14,482 cubic feet per minute **Electricity Use** 49 watts (excludes lights)

DOE Weighted CFM/W 344 CFM/W



Full Function Remote Control Included Six-speed fan operation Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Rated
- Compatible with universal light kit
- · Remote control with batteries included





Vast



09 Brushed Nickel



Antique Bronze



White



Black

P2550-0930K Brushed Nickel 72" dia., 16.75" ht. Shown with Brushed Nickel blades



Brushed Nickel



P2550-2030K Antique Bronze 72" dia., 16.75" ht. Shown with Antique Bronze blades



Antique Bronze



P2550-3030K White 72" dia., 16.75" ht.

Shown with White blades



White



P2550-3130K Black 72" dia., 16.75" ht. Shown with Black blades



Black



ENERGY INFORMATION

Airflow 8,163 cubic feet per minute
Electricity Use 35 watts (excludes lights)

DOE Weighted CFN/W 262 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- · Aluminum blades
- White opal glass shade
- Damp Rated
- · Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









Arlo



009 Brushed Nickel



Black

P250026-009-30 Brushed Nickel 60" dia., 18.57" ht. Shown with Brushed Nickel blades



Brushed Nickel



P250026-031-30 Black 60" dia., 18.57" ht. Shown with Black blades



Black



ENERGY INFORMATION

Airflow 7,558 cubic feet per minute **Electricity Use** 29 watts (excludes lights)

DOE Weighted CFM/W 282 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminium blades
- · White opal glass shade
- Damp Rated
- · Remote control with batteries included

LAMPING

24w LED Module, 3000K, 90 CRI, 2000 source lumens, dimmable.











Manvel



Antique Bronze



31M Matte Black



Antique Nickel



Cottage White

P250069-020 Antique Bronze 60" dia., 11.25" ht.

Shown with Dark Walnut blades



Dark Walnut



P250069-31M Matte Black 60" dia., 11.25" ht. Shown with Rustic Charcoal blades



Rustic Charcoal



P250069-081 Antique Nickel 60" dia., 11.25" ht. Shown with Antique Nickel Wood blades



Antique Wood



P250069-151 Cottage White 60" dia., 11.25" ht. Shown with Salt Aged Cypress blades



Salt Aged Cypress



ENERGY INFORMATION

Airflow 6,127 cubic feet per minute

Electricity Use 20 watts
DOE Weighted CFN/W 310 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Rated
- Remote control with batteries included





Farris



009 Brushed Nickel



Oil Rubbed Bronze



Graphite

P250002-009-30 Brushed Nickel 60" dia., 15.5" ht. Shown with Gray Weathered Wood blades



Gray Weathered Wood



P250002-108-30 Oil Rubbed Bronze 60" dia., 15.5" ht. Shown with Walnut blades and light kit removed using blank plate



Walnut



P250002-143-30 Graphite 60" dia., 15.5" ht. Shown with Driftwood blades



Driftwood



ENERGY INFORMATION

Airflow 7,047 cubic feet per minute **Electricity Use** 32 watts (excludes lights)

DOE Weighted CFM/W 223 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-13°)
- DC Motor
- Carved wood blades
- Removable light kit
- White opal shatterproof shade
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









Carrollwood



009 Brushed Nickel





Matte Black

P250074-009-30 Brushed Nickel

56" dia., 18" ht.

Shown with American Walnut blades and Chrome accent bands



American Walnut



Silver



P250074-030-30 White

56" dia., 18" ht. Shown with Natural Cherry blades and Vintage Gold accent bands



Natural Cherry



Matte White



P250074-31M-30 Matte Black

56" dia., 18" ht. Shown with Chestnut blades and Vintage Gold accent bands



Chestnut



Matte Black



ENERGY INFORMATION

Airflow 6,857 cubic feet per minute **Electricity Use** 42 watts (excludes lights)

DOE Weighted CFM/W 224 CFM/W



Full Function Remote Control Included Six-speed fan operation Reverse direction control Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- · White opal shatterproof shade
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









Dallam



009 Brushed Nickel









ENERGY INFORMATION

Airflow **Electricity Use** DOE Weighted CFM/W

n/a cubic feet per minute n/a watts (excludes lights) n/a cubic feet per minute per watt (Data not available at time of printing)

Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included

LAMPING

20w LED Module, 2700K, 3000K, 5000K, 90 CRI, 1700 source lumens, dimmable.









CATALOG 134

52" Tarsus



009 Brushed Nickel



Matte Black

P250102-009-CS Brushed Nickel

52" dia., 14.75" ht.

Shown with Chestnut blades



Silver



Chestnut

P250102-31M-CS Matte Black

52" dia., 14.75" ht. Shown with Rustic Charcoal blades



Rustic Charcoal



Matte Black





ENERGY INFORMATION

Airflow 4,950 cubic feet per minute **Electricity Use** 60 watts (excludes lights)

DOE Weighted CFM/W 94 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included

LAMPING

25w LED Module, 90 CRI + 10w Linear LED Module, 80 CRI, 2700K, 3000K, 5000K, 2000 source lumens, dimmable.









Gaze



Brushed Nickel



Polished Chrome



Antique Bronze



Black

P2554-0930K Brushed Nickel

60" dia., 13.12" ht. Shown with Silver blades



Silver



Cherry



P2554-1530K Polished Chrome

60" dia., 13.12" ht.

Shown with White Washed blades



White Washed



Cherry



P2554-2030K Antique Bronze

60" dia., 13.12" ht. Shown with Cherry blades



Walnut



Cherry



P2554-3130K Black

60" dia., 13.12" ht.

Shown with Matte Black blades



Matte Black



Distressed Ebony



ENERGY INFORMATION

Airflow 5,902 cubic feet per minute **Electricity Use** 75 watts (excludes lights)

DOE Weighted CFM/W 87 CFM/W



Three-speed Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- · White shatterproof lens
- Remote control with batteries included
- · Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









Spades



Brushed Nickel



Polished Chrome



Graphite

P2570-09 Brushed Nickel 56" dia., 18.12" ht. Shown with Silver blades



Silver



P2570-15 Polished Chrome 56" dia., 18.12" ht. Shown with Black blades



Black



P2570-143 Graphite 56" dia., 18.12" ht. Shown with Graphite blades



Graphite



ENERGY INFORMATION

Airflow 6,746 cubic feet per minute **Electricity Use** 32 watts (excludes lights)

DOE Weighted CFM/W 215 CFM/W

Full Fu Six-spe Revers

Full Function Remote Control Included Six-speed fan operation Reverse direction control

FEATURES

• Limited Lifetime Warranty

• Dual Mount (flat or sloped ceiling-17°)

• Close-to-ceiling installation

• DC Motor

• Non-reversible ABS blades


Remote control with batteries included











Oriole



09 Brushed Nickel



31 Black



Architectural Bronze

P2592-0930K Brushed Nickel 60" dia., 14.5" ht. Shown with Silver blades



Silver



P2592-3130K Black 60" dia., 14.5" ht. Shown with Black blades and light kit removed using blank plate



Black



P2592-12930K Architectural Bronze 60" dia., 14.5" ht. Shown with Architectural Bronze blades



Architectural Bronze



ENERGY INFORMATION

Airflow 6,171 cubic feet per minute **Electricity Use** 51 watts (excludes lights) DOE Weighted CFM/W 132 CFM/W



Three-speed Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- · ABS blades
- · White opal glass shade
- · Remote control with batteries included
- · Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.











Bedwin

081

Antique Nickel



Graphite

P250024-081 Antique Nickel 56" dia., 15.4055" ht. Shown with Driftwood blades



Driftwood



Classic Walnut



P250024-143 Graphite 56" dia., 15.4055" ht. Shown with Graphite blades



Graphite



Gray Weathered Wood



ENERGY INFORMATION

Airflow 6,044 cubic feet per minute **Electricity Use** 34 watts (excludes lights)

DOE Weighted CFM/W 192 CFM/W



Full Function Remote Control Included Six-speed fan operation Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries included







Glandon





Antique Nickel

P2586-7130K Gilded Iron 60" dia., 17.12" ht. Shown with Toasted Oak blades



Toasted Oak



Driftwood



P2586-8130K Antique Nickel 60" dia., 17.12" ht. Shown with Classic Walnut blades



Classic Walnut



Driftwood



ENERGY INFORMATION

Airflow 6,036 cubic feet per minute **Electricity Use** 84 watts (excludes lights)

DOE Weighted CFM/W 96 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- · White opal glass shade
- Remote control with batteries included
- Add the P2667-31 WIFI remote control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.











Greer





Shown with Driftwood blades

P2584-71 Gilded Iron 54" dia., 20" ht. Shown with Toasted Oak blades



Toasted Oak



Driftwood



ENERGY INFORMATION

Airflow 4,794 cubic feet per minute **Electricity Use** 65 watts (excludes lights)

DOE Weighted CFM/W 82 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-45°)
- AC Motor
- Reversible plywood blades
- · Wire basket shade light kit
- Remote control with batteries included
- · Remote control may be replaced with P2630-30 wall control

LAMPING

Two medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 6.5w LED or 60W incandescent max/socket.





Claret



009 Brushed Nickel



108

Oil Rubbed Bronze

P250007-009-30 Brushed Nickel

54" dia., 15.15" ht.

Shown with American Walnut blades



American Walnut



Matte Black



P250007-031-30 Black

54" dia., 15.15" ht. Shown with Distressed Ebony blades



Gray Weathered Wood



Distressed Ebony



P250007-108-30 Oil Rubbed Bronze

54" dia., 15.15" ht.

Shown with Antique Wood blades



Antique Wood



Chestnut



ENERGY INFORMATION

Airflow 5,553 cubic feet per minute Electricity Use 61 watts (excludes lights)

DOE Weighted CFM/W 106 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









CEILING FANS

Glenfalls



009 Brushed Nickel



Satin White



Black

P250021-009-30 Brushed Nickel

56" dia., 14.87" ht. Shown with Brushed Nickel accents





P250021-028-30 Satin White

56" dia., 14.87" ht.

Shown with Brushed Nickel accents



Satin White



P250021-031-30 Black

56" dia., 14.87" ht. Shown with Brushed Nickel accents



Matte Black



ENERGY INFORMATION

Airflow 6,393 cubic feet per minute **Electricity Use** 85 watts (excludes lights)

DOE Weighted CFM/W 84 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- · Plywood blades
- White opal glass shade
- Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING

24w LED Module, 3000K, 90 CRI, 2000 source lumens, dimmable.









Soar



09 Brushed Nickel



White

P2542-0930K Brushed Nickel 54" dia., 14.5" ht.

Shown with Black blades



Black



P2542-3030K White

54" dia., 14.5" ht. Shown with White blades



White



ENERGY INFORMATION

Airflow 4,814 cubic feet per minute Electricity Use 65 watts (excludes lights)

DOE Weighted CFM/W 83 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- White opal shatterproof lens
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









52" Tompkins



009 Brushed Nickel



Matte Black

P250104-009-CS Brushed Nickel

52" dia., 17" ht.

Shown with American Walnut blades



Silver



American Walnut



P250104-31M-CS Matte Black

52" dia., 17" ht. Shown with Toasted Oak blades




Toasted Oak



Matte Black





ENERGY INFORMATION

Airflow 4,660 cubic feet per minute **Electricity Use** 61 watts (excludes lights)

DOE Weighted CFM/W 86 CFM/W



Three-speed Remote Control Included Three-speed fan operation Full-range dimming for light Three-CCT selectable

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Hammered clear glass shade
- Damp Rated
- Remote control with batteries included

LAMPING

24w LED Module, 2700K, 3000K, 5000K, 90 CRI, 1900 source lumens, dimmable.







Gust



09 Brushed Nickel



Antique Bronze



Graphite

P2582-0930K Brushed Nickel 54" dia., 16" ht. Shown with Silver blades



Silver



P2582-2030K Antique Bronze 54" dia., 16" ht. Shown with Walnut blades



Walnut



P2582-14330K Graphite 54" dia., 16" ht. Shown with Graphite blades



Graphite



ENERGY INFORMATION

Airflow 5,242 cubic feet per minute **Electricity Use** 65 watts (excludes lights)

DOE Weighted CFM/W 87 CFM/W



Three-speed Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- · AC Motor
- · White opal glass shade
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









CEILING FANS

Billows



09 Brushed Nickel



Antique Bronze



Forged Black

P2552-09 Brushed Nickel 52" dia., 17.5" ht. shown with Silver blades



White Washed



Silver



P2552-20 Antique Bronze 52" dia., 17.5" ht. shown with American Walnut blades



Cherry



American Walnut



P2552-80 Forged Black 52" dia., 17.5" ht. shown with Toasted Oak blades



Black



Toasted Oak



ENERGY INFORMATION

Airflow 4,682 cubic feet per minute
Electricity Use 59 watts (excludes lights)
DOE Weighted CFM/W 92 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

LAMPING

Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI, dimmable (with added remote wall control). 10w LED max/socket.







Fresno

09

09 Brushed Nickel



Antique Bronze



White

P2548-0930K Brushed Nickel 60" dia., 17.25" ht. shown with Silver blades



Black



Silver



P2548-2030K Antique Bronze 60" dia., 17.25" ht. shown with Dark Walnut blades



Dark Walnut



Cherry



P2548-3030K White 60" dia., 17.25" ht. shown with White blades



White



ENERGY INFORMATION

Airflow 5,718 cubic feet per minute **Electricity Use** 79 watts (excludes lights)

DOE Weighted CFM/W 80 CFM/W



Full Function Remote Control Included Three-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-17.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included, receiver mounted in motor
- Remote control may be replaced with P2631-30 wall control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.







Tempt





Shown with Dark Cherry blades

P2578-16330K Vintage Brass 52" dia., 16.25" ht. Shown with Chesnut blades



Dark Cherry



Chestnut



ENERGY INFORMATION

Airflow 4,314 cubic feet per minute **Electricity Use** 63 watts (excludes lights)

DOE Weighted CFM/W

78 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Clear double prismatic glass shade
- Remote control with batteries included
- · Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









Graceful





Shown with Toasted Oak blades

P2544-1530K Polished Chrome 54" dia., 16.9" ht. Shown with Silver blades



Silver



Toasted Oak



Airflow 4,454 cubic feet per minute **Electricity Use** 60 watts (excludes lights) 83 CFM/W

DOE Weighted CFM/W

Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- · White opal glass shade
- · Remote control with batteries included
- · Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.











Harranvale







Graphite

P2540-2030K Antique Bronze 54" dia., 15.5" ht. Shown with Medium Cherry blades and Brushed Bronze accent



Classic Walnut



Medium Cherry



P2540-3030K White

54" dia., 15.5" ht. Shown with White blades and Brushed Nickel accent



White



P2540-14330K Graphite

54" dia., 15.5" ht. Shown with Graphite blades and Brushed Nickel accent



Graphite



American Walnut



ENERGY INFORMATION

Airflow 5,121 cubic feet per minute **Electricity Use** 66 watts (excludes lights)

DOE Weighted CFM/W 87 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- · AC Motor
- Reversible plywood blades
- · White opal glass shade
- Remote control with batteries included
- · Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.







Brazas



009 Brushed Nickel



P250100-009 Brushed Nickel

56" dia., 13" ht.

Shown with Gray Weathered Wood blades



Grey Weathered Wood



P250100-31M Matte Black

56" dia., 13" ht.

Shown with Distressed Ebony blades



Distressed Ebony



ENERGY INFORMATION

Airflow6,621 cubic feet per minuteElectricity Use31 watts (excludes lights)

DOE Weighted CFM/W 245 CFM/W

Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- ABS blades
- Damp Rated
- Remote control with batteries included







McLennan II





P250089-009-WB Brushed Nickel 52" dia., 14.31" ht.



Silver

Shown with Silver blades



Walnut



ENERGY INFORMATION

Airflow 4,040 cubic feet per minute Electricity Use 34 Watts (excludes lights)

DOE Weighted CFM/W 85 CFM/W

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal shatterproof shade
- 3 Speed pull chain switches
- Add a P2630-30 or P2613-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

2 medium base base, 3000K, 6w LED lamps included, 90 CRI, 500 lumens/lamp, dimmable.







Trevina II 44"

09

Brushed Nickel



Satin White



Black

P2555-0930K Brushed Nickel 44" dia., 15.62" ht. Shown with Silver blades



Silver



P2555-2830K Satin White 44" dia., 15.62" ht. Shown with White blades



White



P2555-3130K Black

44" dia., 15.62" ht. Shown with Distressed Ebony blades



Distressed Ebony



Black



BLANK PLATE P2668-09 Brushed Nickel **P2668-28** Satin White **P2668-31** Black
8" dia., 1.6" ht.







ENERGY INFORMATION

Airflow 4306 cubic feet per minute **Electricity Use** 42 watts (excludes lights)

DOE Weighted CFM/W 122 CFM/W



Wall Control Included Four-speed fan operation Full-range dimming for light Includes switch plate cover

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible MDF blades
- White opal glass shade
- Compatible with remote or hardwired wall controls (P2630, P2661-01, P2662-01, P2663-01, P2665 (sold separately)

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









Trevina V Energy Star



Satin White



31M Matte Black



Painted Nickel

P250076-028-WB Satin White

52" dia., 16.5" ht.

Shown with Natural Cherry blades



Natural Cherry



Matte White



P250076-31M-WB Matte Black

52" dia., 16.5" ht.

Shown with Distressed Ebony blades



Distressed Ebony



Matte Black



P250076-152-WB Painted Nickel

52" dia., 16.5" ht. Shown with Black blades



Black



Silver



ENERGY INFORMATION

Airflow 4,364 cubic feet per minute **Electricity Use** 14 watts (excludes lights)

DOE Weighted CFM/W 116 CFM/W

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- · White opal glass shade
- · Add a P2663-01 remote or P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

Two 9w LED Lamps, 3000K, 90 CRI, 800 source lumens, dimmable.









Trevina II 52"





P2553-129WB Architectural Bronze 52" dia., 15.75" ht. Shown with Medium Cherry blades



Medium Cherry



Classic Walnut



P2553-152WB Painted Nickel 52" dia., 15.75" ht. *Shown with Black blades*



Black



Silver



ENERGY INFORMATION

Airflow Electricity Use DOE Weighted CFM/W 5,296 cubic feet per minute 56 watts (excludes lights) 112 CFM/W

FEATURES

- Limited Lifetime Warranty (LED model)
- Dual Mount (flat or sloped ceiling)
- AC Motor
- Close-to-ceiling installation
- Reversible plywood blades
- · White opal glass shade
- No wall control included. Add a wall or remote control to adjust fan speed and light kit function
- Compatible with remote control or hardwired wall controls (P2618-01, P2630, P2662-01, sold separately)
- Add the P2667-31 WiFi remote control

LAMPING

Two medium base 3000K 9.5w LED lamps included. 800 lumens/lamp, 80 CRI, dimmable. 60w max/socket.











CATALOG 134

Trevina II 52" LED



09 Brushed Nickel



Antique Bronze



White

P2556-0930K Brushed Nickel 52" dia., 15.75" ht.



Silver

Shown with Silver blades



P2556-2030K Antique Bronze

52" dia., 15.75" ht. Shown with Medium Cherry blades



Medium Cherry



Classic Walnut



P2556-3030K White

52" dia., 15.75" ht. Shown with White blades



White



Natural Cherry



ENERGY INFORMATION

Airflow 4,916 cubic feet per minute **Electricity Use** 62 watts (excludes lights) 89 CFM/W

DOE Weighted CFM/W

Wall Control Included Four-speed fan operation Full-range dimming for light Includes switch plate cover

FEATURES

- Limited Lifetime Warranty (LED model)
- · Dual Mount (flat or sloped ceiling-30°)
- Close-to-ceiling installation
- · AC Motor
- · Reversible plywood blades
- White opal glass shade

LAMPING

17w LED Module, 3000K. 90 CRI, 1400 source lumens, dimmable.











Trevina IV





Shown with Walnut blades

P250093-152-WB Painted Nickel

52" dia., 13.8125" ht. Shown with Silver blades



Walnut



Silver



ENERGY INFORMATION

Airflow 4085 cubic feet per minute Electricity Use 31 watts (excludes lights)

DOE Weighted CFM/W 88 CFM/W



Wall Control Included Three-speed selection and a light switch.

FEATURES

- · Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal shatterproof shade
- Wall control is included
- Add the P2667-31 WiFi remote control

LAMPING

2 medium base base, 3000K, 6w LED lamps included, 90 CRI, 500 lumens/lamp.







Signature Plus II



09 Brushed Nickel



Antique Bronze



White

P2539-0930K Brushed Nickel 54" dia., 15.25" ht.



Silver

Shown with Silver blades



Driftwood



P2539-2030K Antique Bronze 54" dia., 15.25" ht. Shown with Medium Cherry blades



Medium Cherry



Classic Walnut



P2539-3030K White

54" dia., 15.25" ht. Shown with White blades



White



ENERGY INFORMATION

DOE Weighted CFM/W

Airflow 5,331 cubic feet per minute **Electricity Use** 65 watts (excludes lights)

92 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- 45° Canopy
- · Downrod mount only
- AC Motor
- · Reversible MDF blades
- · Opal shatterproof shade
- · Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









Signature Plus



09 Brushed Nickel



Antique Bronze



White

P2530-09 Brushed Nickel 54" dia., 15" ht. Shown with Silver blades



Silver



Natural Cherry



P2530-20 Antique Bronze 54" dia., 15" ht. Shown with Classic Walnut blades



Classic Walnut



Medium Cherry



P2530-30W White 54" dia., 15" ht. Shown with White blades



White



ENERGY INFORMATION

Airflow 4,716 cubic feet per minute **Electricity Use** 65 watts (excludes lights) DOE Weighted CFM/W 84 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Downrod mount only
- · AC Motor
- Reversible MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2662-01 hand-held remote control

• Add the P2667-31 WiFi remote control











009 Brushed Nickel



Polished Chrome



Antique Bronze

P250080-009 Brushed Nickel

52" dia., 12.6" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



Silver



P250080-015 Polished Chrome

52" dia., 12.6" ht. Shown with Black blades



Black



Rustic Charcoal



P250080-020 Antique Bronze

52" dia., 12.6" ht.

Shown with Classic Walnut blades



Classic Walnut



Distressed Walnut



ENERGY INFORMATION

Airflow 4,591 cubic feet per minute **Electricity Use** 58 watts (excludes lights)

DOE Weighted CFM/W 93 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- · Add a P2630 wall control or
- P2663-01 hand-held remote control
- Add the P2667-31 WiFi remote control







AIRPRO®



(**030**) White





Graphite

P250080-030 White

52" dia., 12.6" ht. Shown with White blades



White



Antique Wood

P250080-31M Matte Black 52" dia., 12.6" ht. Shown with Matte Black blades



Matte Black



Rustic Charcoal



P250080-143 Graphite

52" dia., 12.6" ht. Shown with Graphite blades



Graphite



Matte Black



ENERGY INFORMATION

Airflow 4,591 cubic feet per minute **Electricity Use** 58 watts (excludes lights) DOE Weighted CFM/W 93 CFM/W

FEATURES

• 30-year limited warranty



• Reversible plywood blades

• Compatible with universal light kits

· Add a P2630 wall control or

P2663-01 hand-held remote control · Add the P2667-31 WiFi remote control







52" Builder Fan



Polished Chrome



Antique Bronze



Graphite

P2501-15 Polished Chrome 52" dia., 13.5" ht. Shown with Driftwood blades



Driftwood



Black



P2501-20 Antique Bronze 52" dia., 13.5" ht. Shown with Medium Cherry blades



Medium Cherry



Classic Walnut



P2501-143 Graphite 52" dia., 13.5" ht. Shown with Black blades



Black



Graphite



ENERGY INFORMATION

Airflow Electricity Use DOE Weighted CFM/W 4,991 cubic feet per minute 63 watts (excludes lights) 98 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation with the addition of the P2666 Canopy
- SureConnect® System
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Add a P2630 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control











52" Builder Fan



09 Brushed Nickel



White

P2501-09 Brushed Nickel 52" dia., 13.5" ht. Shown with Cherry blades



Cherry



Natural Cherry



P2501-30W White

52" dia., 13.5" ht. Shown with White blades



White



P2501-30 White

52" dia., 13.5" ht. Shown with Washed Oak blades



White



Washed Oak



ENERGY INFORMATION

Airflow **Electricity Use** DOE Weighted CFM/W 4,991 cubic feet per minute 63 watts (excludes lights) 98 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation with the addition of the P2666 Canopy
- SureConnect® System
- · AC Motor
- · Reversible plywood blades
- Compatible with universal light kits
- Add a P2630 wall control or P2662-01 hand-held remote control

· Add the P2667-31 WiFi remote control

All fixtures:









Clifton Heights



Brushed Nickel



Antique Bronze

P2531-09 Brushed Nickel 52" dia., 15.75" ht. *Shown with Natural Cherry blades*



Natural Cherry



Cherry



P2531-20 Antique Bronze 52" dia., 15.75" ht. Shown with Cherry blades



Cherry



Classic Walnut



ENERGY INFORMATION

Airflow 4,373 cubic feet per minute
Electricity Use 55 watts (excludes lights)
DOE Weighted CFM/W 89 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation with the addition of the P2666 Canopy
- SureConnect System
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control











Signature

09 Brushed Nickel



20 Antique Bronze



Forged Black

P2521-09 Brushed Nickel 52" dia., 14.62" ht. Shown with White blades



White



Natural Cherry



P2521-20 Antique Bronze 52" dia., 14.62" ht. Shown with Classic Walnut blades



Classic Walnut



Medium Cherry



P2521-80 Forged Black 52" dia., 14.62" ht. Shown with Dark Cherry blades



Dark Cherry



Dark Walnut



ENERGY INFORMATION

Airflow **Electricity Use** DOE Weighted CFM/W

4,701 cubic feet per minute 65 watts (excludes lights) 84 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- · Close-to-ceiling installation with the addition of the P2666 Canopy
- SureConnect® System
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Three speed pull-chain switch
- · Add a P2630-30 wall control or P2614-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:









52" Performance



Brushed Nickel



Antique Bronze



White

P2503-09 Brushed Nickel 52" dia., 15.25" ht. shown with Natural Cherry blades



Natural Cherry



Medium Cherry



P2503-20 Antique Bronze 52" dia., 15.25" ht. shown with Medium Cherry blades



Medium Cherry



Classic Walnut



P2503-30W White 52" dia., 15.25" ht. shown with White blades



White



ENERGY INFORMATION

Airflow **Electricity Use** DOE Weighted CFM/W 5,143 cubic feet per minute 70 watts (excludes lights) 85 CFM/W

FEATURES

- · Limited Lifetime Warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- Reversible plywood blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2663-01 hand-held remote control
- · Add the P2667-31 WiFi remote control

All fixtures:









52" Builder Fan with Light kit

09 Brushed Nickel



White

Architectural Bronze

P2599-09 Brushed Nickel 52" dia., 19.12" ht. x Shown with Cherry blades



Cherry



Medium Cherry



P2599-30 White 52" dia., 19.12" ht. Shown with White blades



White



P2599-129 Architectural Bronze 52" dia., 19.12" ht. Shown with Classic Walnut blades



Classic Walnut



Medium Cherry



ENERGY INFORMATION

Airflow **Electricity Use** DOE Weighted CFM/W 4,474 cubic feet per minute 65 watts (excludes lights)

82 CFM/W

FEATURES

- 30-year limited warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- MDF/Plywood hybrid blades
- · Frosted white glass shade
- Three speed pull-chain switch
- · Add a P2630-30 wall control or P2663-01 hand-held remote control

LAMPING

Two medium base, 3000K, 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.





CATALOG 134

AIRPRO®



009 Brushed Nickel



(**030**) White



P250082-009-WB Brushed Nickel

52" dia., 16.7" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



Silver



P250082-030-WB White

52" dia., 16.7" ht. Shown with White blades



White



Antique Wood



P250082-31M-WB Matte Black

52" dia., 16.7" ht. Shown with Black blades



Black



Rustic Charcoal



ENERGY INFORMATION

Airflow 4,494 cubic feet per minute **Electricity Use** 58 watts (excludes lights)

DOE Weighted CFM/W 92 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- Includes shatterproof shade
- Add a P2630 wall control or P2663-01 hand-held remote control

LAMPING

Two medium base, 3000K, 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.



AIRPRO®



009 Brushed Nickel



Matte Black

P250081-009-WB Brushed Nickel

52" dia., 18.7" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



Silver



P250081-030-WB White

52" dia., 18.7" ht. Shown with White blades



White



Antique Wood



P250081-31M-WB Matte Black

52" dia., 18.7" ht. Shown with Black blades



Black



Rustic Charcoal



ENERGY INFORMATION

Airflow 4,857 cubic feet per minute **Electricity Use** 58 watts (excludes lights)

DOE Weighted CFM/W 93 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- P250081 series has white opal shatterproof shades
- P250085 series has clear seeded glass shades
- Add a P2630 wall control or P2663-01 hand-held remote control

LAMPING

Four medium base, 3000K, 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.



AIRPRO®



009 Brushed Nickel



(**030**) White



P250085-009-WB Brushed Nickel

52" dia., 18.7" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



Silver



P250085-030-WB White

52" dia., 18.7" ht. Shown with White blades



White



Antique Wood



P250085-31M-WB Matte Black

52" dia., 18.7" ht. Shown with Black blades



Black



Rustic Charcoal



ENERGY INFORMATION

Airflow 4,857 cubic feet per minute
Electricity Use 58 watts (excludes lights)

DOE Weighted CFM/W 93 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- P250081 series has white opal shatterproof shades
- P250085 series has clear seeded glass shades
- Add a P2630 wall control or P2663-01 hand-held remote control

LAMPING

Four medium base, 3000K, 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.



AIRPRO® Energy Star



009 Brushed Nickel





Matte Black

P250084-009 Brushed Nickel

52" dia., 12.5" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



Silver



P250084-030 White

52" dia., 12.5" ht. Shown with White blades



White



Antique Wood



P250084-31M Matte Black

52" dia., 12.5" ht. Shown with Black blades



Black



Rustic Charcoal



ENERGY INFORMATION

Airflow 4,337 cubic feet per minute **Electricity Use** 45 watts (excludes lights)

DOE Weighted CFM/W 112 CFM/W

FEATURES

• 30-year limited warranty

- AC Motor
- Reversible plywood blades
- Add a P2630 wall control or P2663-01 hand-held remote control
- · Will accept a universal Energy Star rated light kit





AIRPRO® Energy Star



009 Brushed Nickel





Matte Black

P250066-009 Brushed Nickel 52" dia., 13.5" ht. Shown with Natural Cherry blades



Natural Cherry



Cherry



P250066-030 White

52" dia., 13.5" ht. Shown with White blades



White



Washed Oak



P250066-31M Matte Black

52" dia., 13.5" ht. Shown with Matte Black blades



Matte Black



Rustic Charcoal



ENERGY INFORMATION

Airflow 4986 cubic feet per minute **Electricity Use** 44 watts (excludes lights)

DOE Weighted CFM/W 134 CFM/W

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- Reversible plywood blades
- Add a P2630-30 or P2613-30 wall control or P2663-01 hand-held remote control
- · Add the P2667-31 WiFi remote control







Edgefield



009 Brushed Nickel



White

29 Architectural Bronze

P250016-009 Brushed Nickel 52" dia., 14.62" ht. Shown with American Walnut blades



American Walnut



Cherry



P250016-030 White

52" dia., 14.62" ht. Shown with White blades



White



P250016-129 Architectural Bronze 52" dia., 14.62" ht. Shown with Medium Cherry blades



Medium Cherry



Classic Walnut



ENERGY INFORMATION

Airflow Electricity Use DOE Weighted CFM/W 5,741 cubic feet per minute 34 watts (excludes lights) 179 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- DC motor
- MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Will not accept a wall or remote control









CATALOG 134

AIRPRO® Energy Star



009 Brushed Nickel



(030) White

Matte Black

P250077-009-WB Brushed Nickel

52" dia., 18.7" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



Silver



P250077-030-WB White

52" dia., 18.7" ht. Shown with White blades



White



Antique Wood



P250077-31M-WB Matte Black

52" dia., 18.7" ht. Shown with Matte Black blades



Matte Black



Rustic Charcoal



ENERGY INFORMATION

Airflow 4,311 cubic feet per minute **Electricity Use** 45 watts (excludes lights)

DOE Weighted CFM/W 111 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- · Includes shatterproof shades
- Add a P2630 wall control or P2663-01 hand-held remote control

LAMPING

Four medium base, 3000K, 9w LED lamps included. 800 lumens/lamp, 90 CRI, dimmable.





AIRPRO® Energy Star



009 Brushed Nickel





Matte Black

P250078-009-WB Brushed Nickel

52" dia., 16.7" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



Silver



P250078-030-WB White

52" dia., 16.7" ht. Shown with White blades



White



Antique Wood



P250078-31M-WB Matte Black

52" dia., 16.7" ht. Shown with Black blades



Black



Rustic Charcoal



ENERGY INFORMATION

Airflow 4,311 cubic feet per minute **Electricity Use** 45 watts (excludes lights)

DOE Weighted CFM/W 111 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- · Includes shatterproof shade
- Add a P2630 wall control or P2663-01 hand-held remote control
- · Add the P2667-31 WiFi remote control

LAMPING

Two medium base, 3000K. 9w LED lamps included. 800 lumens/lamp, 90 CRI, dimmable.









42" Builder Fan



09 Brushed Nickel



Antique Bronze



White

P2500-09 Brushed Nickel 42" dia., 12.37" ht. Shown with Cherry blades



Cherry



Natural Cherry



P2500-20 Antique Bronze 42" dia., 12.37" ht. Shown with Classic Walnut blades



Classic Walnut



Medium Cherry



P2500-30 White 42" dia., 12.37" ht. Shown with White blades



White



Washed Oak



FEATURES

ENERGY INFORMATION

Airflow **Electricity Use** DOE Weighted CFM/W 64 CFM/W

3,053 cubic feet per minute 46 watts (excludes lights)

- 15-year limited warranty
- 23° Canopy
- · Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- · Three speed pull-chain switch
- Add a P2630 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:











Drift



009 Brushed Nickel





Architectural Bronze

P250008-009 Brushed Nickel 32" dia., 14.37" ht. Shown with Driftwood blades



Driftwood



Silver



P250008-030 White

32" dia., 14.37" ht. Shown with Driftwood blades



Driftwood



White



P250008-129 Architectural Bronze 32" dia., 14.37" ht. Shown with Classic Walnut blades



Classic Walnut



Medium Cherry



ENERGY INFORMATION

Airflow **Electricity Use** DOE Weighted CFM/W 2,518 cubic feet per minute 35 watts (excludes lights) 88 CFM/W

FEATURES

• Limited Lifetime Warranty

- Dual Mount (flat or sloped ceiling-30°)
- · Close-to-ceiling installation
- AC Motor
- Reversible MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- · Add a P2630-30 or wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:









Bexar



009 Brushed Nickel



Matte Black

P250099-009-30 Brushed Nickel 54" dia., 11.5" ht.

Shown with Dark Cherry blades



Silver



Dark Cherry

P250099-31M-30 Matte Black

54" dia., 11.5" ht.

Shown with Distressed Ebony blades



Distressed Ebony



Matte Black



ENERGY INFORMATION

Airflow 3,576 cubic feet per minute **Electricity Use** 64 Watts (excludes lights)

DOE Weighted CFM/W 64 CFM/W



Three-speed Remote Control Included Three-speed fan operation

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal glass shade
- · Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1600 source lumens, dimmable.









44" Braden



009 Brushed Nickel





P250058-009-30 Brushed Nickel 44" dia., 9.81" ht. Shown with Brushed Nickel blades



Brushed Nickel



American Walnut



P250058-028-30 Satin White 44" dia., 9.81" ht. Shown with Natural Cherry blades



Natural Cherry



Matte White



P250058-031-30 Black

44" dia., 9.81" ht. Shown with Black blades



Black



Distressed Ebony



ENERGY INFORMATION

Airflow 3,212 cubic feet per minute **Electricity Use** 45 watts (excludes lights)

DOE Weighted CFM/W 78 CFM/W



Full Function Remote Control Included Three-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- · Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Frosted shatterproof shade
- Remote control with batteries included
- · Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









56" Braden



Brushed Nickel



Polished Chrome



Architectural Bronze

P2588-0930K Brushed Nickel

56" dia., 9.87" ht.

Shown with American Walnut blades



American Walnut



Silver



P2588-1530K Polished Chrome 56" dia., 9.87" ht.

Shown with Black blades



Black



American Walnut



P2588-12930K Architectural Bronze 56" dia., 9.87" ht. Shown with Medium Cherry blades



Medium Cherry



Classic Walnut



ENERGY INFORMATION

Airflow 4,263 cubic feet per minute **Electricity Use** 55 watts (excludes lights)

DOE Weighted CFM/W 85 CFM/W



Full Function Remote Control Included Three-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- · Hugger low profile mounting
- · AC Motor
- Reversible plywood blades
- · White opal glass shade
- · Full function remote control with batteries included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









56" Braden





P2588-2830K Satin White 56" dia., 9.75" ht. Shown with Natural Cherry blades



Natural Cherry



Matte White



P2588-31M30K Matte Black

56" dia., 9.75" ht. Shown with Matte Black blades



Matte Black



Distressed Ebony



ENERGY INFORMATION

Airflow 4,263 cubic feet per minute
Electricity Use 55 watts (excludes lights)

DOE Weighted CFM/W 85 CFM/W



Full Function Remote Control Included Three-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- · Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Full function remote control with batteries included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.















09 Brushed Nickel



Antique Bronze



White

P2572-0930K Brushed Nickel 52" dia., 11.62" ht. Shown with Medium Cherry blades



Medium Cherry



P2572-2030K Antique Bronze

52" dia., 11.62" ht. Shown with American Walnut blades



American Walnut



P2572-3030K White

52" dia., 11.62" ht. Shown with White blades



White



ENERGY INFORMATION

Airflow 4,276 cubic feet per minute **Electricity Use** 62 watts (excludes lights)

DOE Weighted CFM/W 76 CFM/W



Full Function Remote Control Included Three-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- · Hugger low profile mounting
- AC Motor
- White opal glass shade
- · Full function remote control with batteries included
- · Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









Lindale



Antique Nickel



Architectural Bronze

P250028-081 Antique Nickel 52" dia., 11.18" ht. Shown with White Barnwood blades



White Barnwood



Driftwood



P250028-129 Architectural Bronze 52" dia., 11.18" ht. Shown with Distressed Walnut blades and optional P2669-129 Light Kit



Distressed Walnut



Classic Walnut



LINDALE LIGHT KIT P2669-028 Satin White P2669-081 Antique Nickel P2669-129 Architectural Bronze



P2669-028



P2669-081



P2669-129

ENERGY INFORMATION

Airflow 4,642 cubic feet per minute **Electricity Use** 60 watts (excludes lights)

DOE Weighted CFM/W 87 CFM/W



Three-speed Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- · Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- · Accepts P2669 light kit, sold separately
- Remote control with batteries included · Remote control may be replaced with
- P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

24w LED Module, 3000K, 90 CRI, 2000 source lumens, dimmable.







52" Hugger Fan



09 Brushed Nickel



White

P2525-09 Brushed Nickel 52" dia., 8.12" ht. Shown with Cherry blades



Cherry



Natural Cherry



P2525-30 White 52" dia., 8.12" ht. Shown with white blades



White



ENERGY INFORMATION

Airflow 3,229 cubic feet per minute
Electricity Use 56 watts (excludes lights)
DOE Weighted CFM/W 58 CFM/W

FEATURES

- 15-year limited warranty
- · Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Cannot be used with remote control
- Add a P2630-30 wall control
- Add the P2667-31 WiFi remote control







42" Hugger Fan



09 Brushed Nickel



White

P2524-09 Brushed Nickel 42" dia., 8.31" ht. Shown with Natural Cherry blades



Natural Cherry



Cherry



P2524-30 White 42" dia., 8.31" ht. Shown with White blades



White



ENERGY INFORMATION

Airflow 2,639 cubic feet per minute **Electricity Use** 44 watts (excludes lights)

DOE Weighted CFM/W 72 CFM/W

FEATURES

• 15-year limited warranty

· Hugger low profile mounting

AC Motor

• Reversible plywood blades

• Compatible with universal light kits

• Cannot be used with remote control

· Add the P2630-30 wall control

· Add the P2667-31 WiFi remote control











Outdoor Ceiling Fans

Springer II



Matte Black



Antique Nickel



Architectural Bronze

P250098-31M Matte Black 60" dia., 16.26" ht. Shown with Distressed Charcoal blades



Distressed Charcoal



P250098-081 Antique Nickel 60" dia., 16.26" ht. Shown with Galvanized blades



Galvanized



P250098-129 Architectural Bronze 60" dia., 16.26" ht. Shown with Distressed blades



Distressed Walnut



ENERGY INFORMATION

Airflow 6,158 cubic feet per minute **Electricity Use** 35 Watts (excludes lights)

DOE Weighted CFM/W 205 CFM/W



Full Function Remote Control Included Six-speed fan operation Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- Hand painted aluminum blades
- Damp Rated
- · Remote control with batteries included
- Add the P2673 WiFi remote

ALSO IN: LIGHT KITS











52" Schaal





P250101-028-30 Satin White 52" dia., 16" ht. Shown with Chestnut blades and Synthetic rope accent



Matte White



Chestnut

P250101-31M-30 Matte Black

52" dia., 16" ht. Shown with Rustic Charcoal blades and Synthetic rope accent



Rustic Charcoal



Matte Black



ENERGY INFORMATION

Airflow 4,687 cubic feet per minute **Electricity Use** 59 watts (excludes lights)

DOE Weighted CFM/W 89 CFM/W



Full Function Remote Control Included Three-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- Reversible plywood blades
- · White opal shade
- Damp Rated
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI, 1600 source lumens, dimmable.









Kasota



Oil Rubbed Bronze



Graphite



Painted Nickel

P250072-108-30 Oil Rubbed Bronze 56" dia., 15" ht. Shown with Tan Linen blades



Tan Linen



P250072-143-30 Graphite 56" dia., 15" ht.

Shown with Charcoal Linen blades



Charcoal Linen



P250072-152-30 Painted Nickel 56" dia., 15" ht. Shown with Charcoal Linen blades



Charcoal Linen



ENERGY INFORMATION

Airflow 4,844 cubic feet per minute Electricity Use 31 watts (excludes lights)

DOE Weighted CFM/W 188 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal shatterproof shade
- Damp Rated
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.







Upshur

009 Brushed Nickel



020 Antique Bronze



Matte Black

P250094-009-30 Brushed Nickel

52" dia., 13.7" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



P250094-020-30 Antique Bronze 52" dia., 13.7" ht. Shown with Walnut blades



Walnut



P250094-31M-30 Matte Black 52" dia., 13.7" ht. Shown with Rustic Charcoal blades



Rustic Charcoal



ENERGY INFORMATION

Airflow 4,631 cubic feet per minute **Electricity Use** 34 watts (excludes lights)

DOE Weighted CFM/W 102 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
- AC Motor
- · ABS blades
- White opal shatterproof shade
- Damp Rated
- · Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1500 source lumens, dimmable.











Schaffer II





Matte Black



Antique Nickel

P250097-028-30 Satin White

56" dia., 15.5" ht. Shown with Natural Cherry blades and Natural Jute rope accent



Matte White



Natural Cherry

P250097-31M-30 Matte Black

56" dia., 15.5" ht. Shown with Rustic Charcoal blades, Natural Jute rope accent and light kit removed using blank plate



Rustic Charcoal



Matte Black

P250097-081-30 Antique Nickel

56" dia., 15.5" ht. Shown with Classic Walnut blades and Natural Jute rope accent



Classic Walnut



Grey Weathered Wood



ENERGY INFORMATION

Airflow 6,177 cubic feet per minute **Electricity Use** 67 watts (excludes lights)

DOE Weighted CFM/W 98 CFM/W



Three-speed Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- · AC Motor
- · Reversible plywood blades
- White opal glass shade
- Damp Rated
- · Remote control with batteries included
- · Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1600 source lumens, dimmable.







Midvale

(028) Matte White

141 Galvanized Finish



Blistered Iron

P250011-028-WB Matte White 56" dia., 20.37" ht. Shown with Matte White blades

Matte White



P250011-141-WB Galvanized Finish 56" dia., 20.37" ht. Shown with Galvanized Finish blades



Galvanized Finish



P250011-171-WB Blistered Iron 56" dia., 20.37" ht. Shown with Blistered Iron blades



Blistered Iron



ENERGY INFORMATION

Airflow 7,627 cubic feet per minute **Electricity Use** 84 watts (excludes lights)

DOE Weighted CFM/W 98 CFM/W



Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- · ABS blades
- Clear seeded glass shade
- Damp Rated
- · Remote control with batteries included
- Remote control may be replaced with P2667-31 WiFi remote control

LAMPING

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.













CEILING FANS

Edwidge



Satin White





Painted Nickel

P250062-028-30 Satin White 52" dia., 13.55" ht. Shown with Satin White blades



Satin White



P250062-031-30 Black 52" dia., 13.55" ht. Shown with Black blades



Black



P250062-152-30 Painted Nickel 52" dia., 13.55" ht. Shown with Painted Nickel blades



Painted Nickel



ENERGY INFORMATION

Airflow 5,873 cubic feet per minute **Electricity Use** 20 watts (excludes lights)

DOE Weighted CFM/W 328 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- · ABS blades
- White opal glass shade
- Damp Rated
- · Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.









Whirl

Antique Bronze



Forged Black



Antique Nickel

P2574-2030K Antique Bronze 60" dia., 15.87" ht. Shown with Walnut blades



Walnut



P2574-8030K Forged Black 60" dia., 15.87" ht. Shown with Toasted Oak blades



Toasted Oak



P2574-8130K Antique Nickel 60" dia., 15.87" ht. Shown with Driftwood blades



Driftwood



ENERGY INFORMATION

Airflow Electricity Use DOE Weighted CFM/W 6,549 cubic feet per minute 70 watts (excludes lights) 106 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- · ABS all weather blades
- White frosted glass shade
- Three speed pull-chain switch (fan)
- On/off pull-chain switch (light)
- Damp Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- · Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable (with added remote wall control).









Alfresco





P250034-129-WB Architectural Bronze 54" dia., 19.25" ht. Shown with Dark Bamboo blades



Dark Bamboo



P250034-171-WB Blistered Iron 54" dia., 19.25" ht. Shown with Pewter blades



Pewter



ENERGY INFORMATION

Airflow 5,724 cubic feet per minute **Electricity Use** 68 watts (excludes lights)

DOE Weighted CFM/W 90 CFM/W



Three-speed Remote Control Included Three-speed fan operation Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- · ABS blades
- Clear seeded glass shade
- Damp Rated
- · Remote control with batteries included
- · Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.







Smyrna

Antique Bronze



Forged Black

P2576-2030K Antique Bronze 52" dia., 19.5" ht. Shown with Walnut blades



Walnut



P2576-8030K Forged Black 52" dia., 19.5" ht. Shown with Toasted Oak blades



Toasted Oak



ENERGY INFORMATION

Airflow 4,585 cubic feet per minute **Electricity Use** 58 watts (excludes lights)

DOE Weighted CFM/W 91 CFM/W



Wall Control Included Four-speed fan operation Full-range dimming for light Includes switch plate cover

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- · ABS all weather blades
- Clear hammered glass shade
- Wet Rated

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.







Montague



Antique Bronze



White



Forged Black

P2564-2030K Antique Bronze 60" dia., 17.62" ht. Shown with Walnut blades



Walnut



P2564-3030K White 60" dia., 17.62" ht.

Shown with White blades



White



P2564-8030K Forged Black 60" dia., 17.62" ht. Shown with Toasted Oak blades



Toasted Oak



ENERGY INFORMATION

Airflow 6,693 cubic feet per minute **Electricity Use** 75 watts (excludes lights)

DOE Weighted CFM/W 96 CFM/W



Full Function Remote Control Included Three-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- · Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- · ABS all weather blades
- · White opal glass shade
- Wet Rated
- · Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.







Albin





Architectural Bronze

P250036-031-30 Black 54" dia., 15.61" ht. Shown with Toasted Oak blades



Toasted Oak



P250036-129-30 Architectural Bronze 54" dia., 15.61" ht. Shown with Distressed Walnut blades



Distressed Walnut



ENERGY INFORMATION

Airflow 5,740 cubic feet per minute **Electricity Use** 67 watts (excludes lights)

95 CFM/W DOE Weighted CFM/W



Three-speed Remote Control Included Three-speed fan operation Full range dimming with light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- · White opal glass shade
- Damp Rated
- · Remote control with batteries included
- · Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

24w LED Module, 3000K, 90 CRI, 2000 source lumens, dimmable.









Kennedale



(028) Satin White



31M Matte Black



Painted Nickel





Driftwood



Matte White



P250070-31M Matte Black

72" dia., 18" ht.

Shown with Black blades



Black



Rustic Charcoal



P250070-152 Painted Nickel

72" dia., 18" ht.

Shown with Gray Weathered Wood blades



Gray Weathered Wood



Painted Nickel



ENERGY INFORMATION

Airflow 8760 cubic feet per minute **Electricity Use** 33 watts (excludes lights)

DOE Weighted CFM/W

293 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-25°)
- DC Motor
- Reversible plywood blades
- · Will accept a light kit
- Damp Rated
- · Remote control with batteries included

All fixtures:







Full Function Remote Control Included Six-speed fan operation Reverse direction control

Lakehurst



Antique Bronze



White

Forged Black

P2562-20 Antique Bronze 60" dia., 15.75" ht. Shown with Walnut blades



Walnut



P2562-30 White 60" dia., 15.75" ht. Shown with White blades



White



P2562-80 Forged Black 60" dia., 15.75" ht. Shown with Toasted Oak blades



Toasted Oak



ENERGY INFORMATION

Airflow **Electricity Use** DOE Weighted CFM/W 6,440 cubic feet per minute 71 watts (excludes lights) 105 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- 3 Speed pull chain switch
- Wet Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control







Decorative Patio Fan



P2526-20 Antique Bronze 52" dia., 17.37" ht. Shown with Washed Walnut blades



Washed Walnut



P2526-20 Antique Bronze 52" dia., 17.37" ht. Shown with Washed Walnut blades and with P2636-20WB accessory light kit



Washed Walnut



ENERGY INFORMATION

Airflow 4,150 cubic feet per minute
Electricity Use 70 watts (excludes lights)
DOE Weighted CFM/W 77 CFM/W

FEATURES

- 15-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- Damp Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control

All fixtures:







INSTALLATION



54" Patio Fan





P2533-20 Antique Bronze 54" dia., 18.25" ht. Shown with Toasted Oak blades and with P2636-20WB accessory light kit



Toasted Oak



Airflow 4,986 cubic feet per minute **Electricity Use** 65 watts (excludes lights)

DOE Weighted CFM/W 74 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- SureConnect® System
- AC Motor
- · ABS all weather blades
- Compatible with universal light kits
- Wet Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control

INSTALLATION













52" Patio Fan



Antique Bronze



White



Forged Black

P2502-20 Antique Bronze 52" dia., 11" ht. Shown with Oak blades



Oak



P2502-30 White 52" dia., 11" ht. Shown with White blades



White



P2502-80 Forged Black 52" dia., 11" ht. Shown with Toasted Oak blades



Toasted Oak



ENERGY INFORMATION

Airflow 4,991 cubic feet per minute
Electricity Use 64 watts (excludes lights)
DOE Weighted CFM/W 89 CFM/W

FEATURES

• 15-year limited warranty

- Dual Mount (flat or sloped ceiling-23°)
- Close-to-ceiling installation
- SureConnect® System
- Quick-Install canopy
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Wet Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control

All fixtures:







INSTALLATION

Ceiling Fans Accessories



Indoor/Outdoor



Antique Bronze



White



80 Forged Black

SCHOOLHOUSE P2601-20WB Antique Bronze **P2601-30WB** White P2601-80WB Forged Black with opal glass. 8.5" dia., 7" ht. One medium base, 3000K, LED lamp included. 800 lumens/lamp, 90 CRI, dimmable. Universal-style with

quick-connect wiring.







LOW PROFILE P2611-20WB Antique Bronze **P2611-30WB** White P2611-80WB Forged Black with opal glass. 10.5" dia., 4.5" ht. Two medium base, 3000K, LED lamp included. 800 lumens/lamp, 90 CRI, dimmable.







ASHMORE P2636-20WB Antique Bronze 11" dia., 8.25" ht. 2 medium base, 9w max.





AIRPRO® Edgelit LED **Light Kit**



Matte Black



Painted Nickel

P260002-028-30 Satin White P260002-31M-30 Matte Black P260002-152-30 Painted Nickel 7.45" dia., 1" ht. 14w LED Module, 3000K, 90 CRI, 1000 source lumens, dimmable.

All fixtures:















Springer II



12" dia., 11" ht. 2 medium base, 7w LED. Only for use with P250000, P250065 and P250098.

All fixtures:









Matte Black



Architectural Bronze

009 Brushed Nickel

Antique Nickel







Antique Bronze



White



P2612-01WB

with alabaster glass. Included Finials:

Universal Bowl

009 Brushed Nickel

020 Antique Bronze

030 White

015 Polished Chrome

143 Graphite

10.75" dia., 5.5" ht.

Two medium base, 7w max. Universal-style with

quick-connect wiring.







Clifton Heights



009 Brushed Nickel



Antique Bronze

P2654-01WB

with etched glass. Included Finials: 009 Brushed Nickel 020 Antique Bronze 12.25" dia., 6.25" ht. 2 medium base, 9w max 800 lumens/lamp, 90 CRI. Indoor use only. dimmable Universal-style with quick-connect wiring.







Torino



009 Brushed Nickel



Antique Bronze



Forged Black

P2645-01WB

with etched glass. Included Finials:

009 Brushed Nickel **020** Antique Bronze

080 Forged Black

12" dia., 5.75" ht. 2 medium base, 9w max 800 lumens/lamp, 90 CRI. Indoor use only. dimmable Universal-style with quick-connect wiring.







Gather, Bravo & Joy



009 Brushed Nickel



Antique Bronze

P2650-01WB

with etched glass. Included Finials: 009 Brushed Nickel **020** Antique Bronze 11" dia., 5.5" ht. 2 medium base, 9w max 800 lumens/lamp, 90 CRI. Indoor use only. dimmable Universal-style with quick-connect wiring.









Four Light Universal

09 Brushed Nickel



Antique Bronze



White

P2643-09WB Brushed Nickel P2643-20WB Antique Bronze **P2643-30WB** White 13.75" dia., 8" ht. 4 medium base, 9w max 800 lumens/lamp, 90 CRI. Indoor use only. dimmable Universal-style with quick-connect wiring.







Three Light Universal

Brushed Nickel



White

P2642-09WB Brushed Nickel **P2642-30WB** White 13.62" dia., 7" ht.

3 medium base, 9w max 800 lumens/lamp, 90 CRI. Indoor use only. dimmable Universal-style with quick-connect wiring.





Brushed Nickel



Polished Chrome

Low Profile



Antique Bronze



White



P2602-09WB Brushed Nickel P2602-15WB Polished Chrome P2602-20WB Antique Bronze **P2602-30WB** White P2602-143WB Graphite With White Opal glass 10.5" dia., 3.81" ht. 2 medium base, 9w max 800 lumens/lamp, 90 CRI. Indoor use only. dimmable Universal-style with quick-connect wiring.









LED Light Kits



09 Brushed Nickel



Antique Bronze

P2659-09 Brushed Nickel P2659-20 Antique Bronze with etched white glass. 12.25" dia., 4" ht. One 16w 3000K LED module included. 1265 source lumens, 960 delivered lumens, 90 CRI, dimmable. Indoor use only.





Trinity



09 Brushed Nickel



031 Matte Black



Antique Bronze



White

P2628-01WB Unfinished with etched glass. Included Finials: 09 Brushed Nickel 031 Matte Black 20 Antique Bronze

30 White

13.37" dia., 6.37" ht. 2 medium base, 9w max Indoor use only.







09 Brushed Nickel



Polished Chrome

Four Light Alabaster



Antique Bronze



White



P2610-09WB Brushed Nickel P2610-15WB Polished Chrome P2610-20WB Antique Bronze P2610-30WB White P2610-143WB Graphite with alabaster glass. 15" dia., 6.25" ht. Four medium base, 3000K, LED lamps included. 800 lumens/lamp, 90 CRI, dimmable. Indoor use only.



Three Light Alabaster



Brushed Nickel



Antique Bronze



White

P2600-09WB Brushed Nickel P2600-20WB Antique Bronze P2600-30WB White with alabaster glass. 15" dia.. 6.62" ht.

with alabaster glass. 15" dia., 6.62" ht. 3 medium base, 9w max Indoor use only.



Schoolhouse



09 Brushed Nickel

P2644-09WB Brushed Nickel With White Opal glass 8.5" dia., 6.5" ht. One medium base, 3000K, LED lamp included. 800 lumens/lamp, 90 CRI, dimmable. Indoor use only.










Accessory Downrods

3/4" diameter; approximately 1" outside diameter.							
CEILING HT. DOWNROD L.	9'-10' 12"	10'-11' 18"	11'-12' 24"	12'-14' 36"	13'-15' 48"	14'-16' 60"	15'-17' 72"
Brushed Nickel	P2603-09	P2604-09	P2605-09	P2606-09	P2607-09	P2608-09	P2609-09
Polished Chrome	P2603-15	P2604-15	P2605-15	P2606-15	P2607-15	P2608-15	P2609-15
Antique Bronze	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Matte White	P2603-28	P2604-28	P2605-28	P2606-28	P2607-28	-	-
White	P2603-30	P2604-30	P2605-30	P2606-30	P2607-30	P2608-30	P2609-30
Matte Black	P2603-31	P2604-31	P2605-31	P2606-31	P2607-31	-	-
Gilded Iron	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Forged Black	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Antique Nickel	P2603-81	P2604-81	P2605-81	P2606-81	P2607-81	P2608-81	P2609-81
Architectural Bronze	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Galvanized	P2603-141	P2604-141	P2605-141	P2606-141	P2607-141	-	-
Graphite	P2603-143	P2604-143	P2605-143	P2606-143	P2607-143	P2608-143	P2609-143
Painted Nickel	P2603-152	P2604-152	P2605-152	P2606-152	P2607-152	-	-
Vintage Brass	P2603-163	P2604-163	P2605-163	P2606-163	P2607-163	-	-
Blistered Iron	P2603-171	P2604-171	P2605-171	P2606-171	P2607-171	-	-

Downrod Selection Guide





Easily control your fan with your smartphone, tablet, voice or hand-held remote.

Visit progresslighting.com for more details.

WiFi COMPATIBLE



Remotes and Wall Controls



P2662-01 Fan/Light Remote 2.37" L, 0.87" D, 4.5" ht.

Universal remote operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four "dip" switches and 16 code options to avoid the chance of interference from other remotes.



P2667-031 WiFi Fan/Light Remote 1.75" L, 0.5" D, 4.37" ht.

Universal WiFi remote control for AC motor fans. Control your ceiling fan or light kit via WiFi from anywhere. Pairs with Alexa, Google Home, or app on your phone or tablet. Voice control the fan with three speeds and the light with full range dimming. App control the fan with three speeds or four timer selections or full range dimming control of the light. Can be controlled with the hand held remote included with the kit.



P2663-01 Fan/Light Remote 1.75" L, 0.5" D, 4.37" ht.

Universal remote with two, four or eight-hour timer option, operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring many code combination options to avoid the chance of interference from other remotes.



P2618-01 Fan/Light Remote 2.12" L, 1.12" D, 4.75" ht.

Provides fan speed and light control from convenient hand-held remote. Compatible with non-dimmable compact fluorescent lamps. For single pole applications. Receiver fits in fan canopy.





P2661-01 Universal Fan/Light Remote 2.75" L, 0.87" D, 4.56" ht.

Provides fan speed and full range light dimming control from a convenient hand held remote control. For single pole applications. Includes a wall plate for added storage convenience. Receiver fits in the fan canopy.





P2665-30 White

Universal remote includes a wall mount transmitter, ideal for multi-family applications, that operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four "dip" switches and 16 code options to avoid the chance of interference from other remotes.





P2631-30 White

Full-function wall control transmitter (receiver sold with ceiling fan). Use with, or in place of, hand-held remote included with fans that have a downlight. Includes switch plate cover.



P2630-30 White

Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.





P2613-30 White Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.





P2673-01 Unfinished

DC Fan WiFi Module

Add the WiFi module to your Ryne or 52" Springer ceiling fan ceiling fan for control at your fingertips. You can easily control your fan with a hand-held remote; or a smart phone, tablet, voice assistant (Amazon Alexa and Google Home) via the Smart By Bond app. 2" L, 2" D, 0.9" ht.

45° Canopies

P2666-09 Brushed Nickel 6.62" dia., 4" ht.



P2666-15 Polished Chrome 6.62" dia., 4" ht.



P2666-30 White 6.62" dia., 4" ht.



P2666-31M Matte Black 6.62" dia., 4" ht.



P2666-129 Architectural Bronze 6.62" dia., 4" ht.



P2666-143 Graphite 6.62" dia., 4" ht.



This accessory is for use with any Progress Lighting ceiling fans with a hanging weight of 25 lbs or less. Includes ceiling bracket, canopy, hanger ball, trim ring, and CTC mounting hardware. The only fans that can be CTC mounted are P2501, P2503, P2521, P2536, and P2531.

Close-to-Ceiling Guide

1 Complete Selection

View our complete offering of close-to-ceiling fixtures.
Use the **Product Finder** in the beginning of the catalog
(a number of close-to-ceiling fixtures are found in Collections).







Design Series offers more elevated product options. Use QR to view:

DESIGN+SERIES*







Close-to-Ceiling

DISCOVER THE LATEST



Cofield

Clear or etched white glass.





Matte Black



Polished Chrome



Vintage Brass

P350237-009 Brushed Nickel 12" dia., 7.75" ht. 3 medium base, 60w max.



P350238-009 Brushed Nickel 12" dia., 7.75" ht. 3 medium base, 60w max.



P350237-015 Polished Chrome 12" dia., 7.75" ht. 3 medium base, 60w max.



P350238-015 Polished Chrome 12" dia., 7.75" ht. 3 medium base, 60w max.



P350237-31M Matte Black 12" dia., 7.75" ht. 3 medium base, 60w max.



P350238-31M Matte Black 12" dia., 7.75" ht. 3 medium base, 60w max.



P350237-163 Vintage Brass 12" dia., 7.75" ht. 3 medium base, 60w max.



P350238-163 Vintage Brass 12" dia., 7.75" ht. 3 medium base, 60w max.



Delayne



009 Brushed Nickel



Matte Black



Brushed Bronze

P350219-009 Brushed Nickel 16" dia., 5.62" ht. 5 candelabra base, 60w max.



P350219-109 Brushed Bronze 16" dia., 5.62" ht. 5 candelabra base, 60w max.



P350219-31M Matte Black 16" dia., 5.62" ht. 5 candelabra base, 60w max.



Perimeter



009 Brushed Nickel



Satin Brass



Matte Black

P350200-009 Brushed Nickel 12" sq., 4.5" ht. 2 medium base, 60w max.



P350200-031 Matte Black 12" sq., 4.5" ht. 2 medium base, 60w max.



P350200-012 Satin Brass 12" sq., 4.5" ht. 2 medium base, 60w max.



Parkhurst

Etched opal glass.



009 Brushed Nickel



Matte Black



Brushed Bronze

P350255-009 Brushed Nickel 11.25" dia., 5.12" ht. 2 medium base LED, 15w max.



P350255-31M Matte Black 11.25" dia., 5.12" ht. 2 medium base LED, 15w max.



P350255-109 Brushed Bronze 11.25" dia., 5.12" ht. 2 medium base LED, 15w max.



Hinton

Clear seeded glass or metal shade.



009 Brushed Nickel



031 Matte Black



Vintage Brass

P350198-009 Brushed Nickel 8" dia., 10" ht. 1 medium base, 60w. max.



P350198-163 Vintage Brass 8" dia., 10" ht. 1 medium base, 60w max.



P350198-031 Matte Black 8" dia., 10" ht. 1 medium base, 60w max.

Shown tilted



P350199-009 Brushed Nickel 8.25" dia., 10" ht. 1 medium base, 60w max.



P350199-163 Vintage Brass 8.25" dia., 10" ht. 1 medium base, 60w max.



P350199-031 Matte Black 8.25" dia., 10" ht. 1 medium base, 60w max.

Shown tilted



Hansford

Clear glass.



Antique Bronze



Polished Nickel



Vintage Brass

P350046-020 Antique Bronze 10" dia., 12.62" ht. 1 medium base, 100 w max.



P350046-104 Polished Nickel 10" dia., 12.62" ht. 1 medium base, 100w max.



P350046-163 Vintage Brass 10" dia., 12.62" ht.. 1 medium base, 100w max.



Singleton

Clear glass.



009 Brushed Nickel



31M Matte Black



Vintage Brass

P350226-009 Brushed Nickel 7.62" dia., 7" ht. 1 medium base, 60w max.



P350226-163 Vintage Brass 7.62" dia., 7" ht. 1 medium base, 60w max.



P350226-31M Matte Black 7.62" dia., 7" ht. 1 medium base, 60w max.



P350227-009 Brushed Nickel 14" dia., 8.5" ht. 1 medium base, 60w max.



P350227-163 Vintage Brass 14" dia., 8.5" ht. 1 medium base, 60w max.



P350227-31M Matte Black 14" dia., 8.5" ht. 1 medium base, 60w max.



Aiken

Clearl glass.

009

009 Brushed Nickel



Vintage Brass

P350214-009 Brushed Nickel 9" dia., 9" ht. 1 medium base, 60w max.



P350214-163 Vintage Brass 9" dia., 9" ht. 1 medium base, 60w max.





Clear or etched opal glass.



009 Brushed Nickel



Polished Nickel



Satin Brass



Matte Black

P350213-009 Brushed Nickel 8.62" dia., 7.37" ht. 1 medium base, 60w max.



P350260-009 Brushed Nickel 8.62" dia., 7.37" ht. 1 medium base, 60w max.



P350213-012 Satin Brass 8.62" dia., 7.37" ht. 1 medium base, 60w max.



P350260-012 Satin Brass 8.62" dia., 7.37" ht. 1 medium base, 60w max.



P350213-31M Matte Black 8.62" dia., 7.37" ht. 1 medium base, 60w max.



P350260-31M Matte Black 8.62" dia., 7.37" ht. 1 medium base, 60w max.



P350213-104 Polished Nickel 8.62" dia., 7.37" ht. 1 medium base, 60w max.



Carisa

Gloss white opal glass.



009 Brushed Nickel



Vintage Gold

P350075-009 Brushed Nickel 7.37" dia., 8.75" ht. 1 medium base, 75w max.



P350075-078 Vintage Gold 7.37" dia., 8.75" ht. 1 medium base, 75w max.



Vertex

Clear or etched white glass.



009 Brushed Nickel



Matte Black



Brushed Gold

P350258-009 Brushed Nickel 7.37" W., 11.62" ht.. 1 medium base, 60w max.



P350258-31M Matte Black 7.37" W., 11.62" ht.. 1 medium base, 60w max.



P350258-191 Brushed Gold 7.37" W., 11.62" ht.. 1 medium base, 60w max.



P350259-009 Brushed Nickel 7.37" W., 11.62" ht.. 1 medium base, 60w max.



***P350259-31M** Matte Black 7.37" W., 11.62" ht.. 1 medium base, 60w max.



P350259-191 Brushed Gold 7.37" W., 11.62" ht.. 1 medium base, 60w max.



Gilliam

Clear or etched white glass.



009 Brushed Nickel



Matte Black



Vintage Brass

P350253-009 Brushed Nickel 12.62" dia., 4.37" ht. 2 medium base LED, 15w max.



P350253-31M Matte Black 12.62" dia., 4.37" ht. 2 medium base LED, 15w max.



P350253-163 Vintage Brass 12.62" dia., 4.37" ht. 2 medium base LED, 15w max.



P350254-009 Brushed Nickel 12.62" dia., 4.62" ht. 2 medium base LED, 15w max.



P350254-31M Matte Black 12.62" dia., 4.62" ht. 2 medium base LED, 15w max.



P350254-163 Vintage Brass 12.62" dia., 4.62" ht. 2 medium base LED, 15w max.



Matte Black with Brushed Bronze canopy and Coastal Blue with Brushed Nickel canopy.



Matte Black



164 Coastal Blue

P350217-31M Matte Black 7.37" dia., 4.5" ht. 1 medium base, 60w max.



P350217-164 Coastal Blue 7.37" dia., 4.5" ht. 1 medium base, 60w max.



Medal

Graphite with Graphite cage and Coastal Blue with Brushed Nickel cage.



Graphite



Coastal Blue

P350195-143 Graphite 14.5" dia., 7.88" ht. 2 medium base, 60w max.



P350195-164 Coastal Blue 14.5" dia., 7.88" ht. 2 medium base, 60w max.



Gauge



Graphite **Swing** Mesh metal shade.



Antique Bronze

P350037-143 Graphite 14" dia., 6.75" ht. 2 medium base, 60w max.



P3452-20 Antique Bronze 15" dia., 8.5" ht. 3 medium base, 60w max.



Bay Court



009 Brushed Nickel

Rushton



009 Brushed Nickel



Graphite

P3942-09 Brushed Nickel 15" dia., 7.37" ht. 2 medium base, 60w max.



P350205-009 Brushed Nickel 12" dia., 6.87" ht. 2 medium base, 60w max.



P350205-143 Graphite 12" dia., 6.87" ht. 2 medium base, 60w max.



Tobin

Etched white glass.



009 Brushed Nickel



Matte Black

P350137-009 Brushed Nickel 12.25" dia., 10.12" ht. 2 medium base, 100w max.



P350137-031 Matte Black 12.25" dia., 10.12" ht. 2 medium base, 100w max.



Kempsey



009 Brushed Nickel



Antique Bronze

P350110-009 Brushed Nickel 21.75" dia., 11" ht. 3 medium base, 60w max. Summer linen fabric shade.



P350110-020 Antique Bronze 21.75" dia., 11" ht. 3 medium base, 60w max. Harvest linen fabric shade.



Fixtures can be installed as a pendant using included hardware.



Clear double prismatic glass.

15 Polished Chrome



Antique Nickel



Venetian Bronze



Vintage Brass

P3740-15 Polished Chrome 12.37" dia., 6.25" ht. 2 medium base, 75w max.



P3740-74 Venetian Bronze 12.37" dia., 6.25" ht. 2 medium base, 75w max.



P3740-81 Antique Nickel 12.37" dia., 6.25" ht. 2 medium base, 75w max.



P3740-163 Vintage Brass 12.37" dia., 6.25" ht. 2 medium base, 75w max.



Inspire



009 Brushed Nickel



Satin Brass



Antique Bronze



Graphite

*P350130-009 Brushed Nickel P350130-143 Graphite P350130-012 Satin Brass 13" dia., 5.5" ht. 2 medium base, 60w max. Summer linen fabric shade.



*P3713-20 Antique Bronze P3713-09 Brushed Nickel 13" dia., 5.5" ht. 2 medium base, 60w max. Off-white linen fabric shade.



P350129-009 Brushed Nickel *P350129-143 Graphite P350129-012 Satin Brass 13" dia., 10.12" ht. 2 medium base, 75w max. Summer linen fabric shade.



P3712-20 Antique Bronze ***P3712-09** Brushed Nickel 13" dia., 10.12" ht. 2 medium base, 75w max. Off-white linen fabric shade.



P350167-009 Brushed Nickel P350167-143 Graphite *P350167-012 Satin Brass 18" dia., 11.5" ht. 3 medium base, 60w max. Summer linen fabric shade.



*P350168-020 Antique Bronze P350168-009 Brushed Nickel 18" dia., 11.5" ht. 3 medium base, 60w max. Off-white linen fabric shade.



Glass Domes

Etched glass.



P350044-009 Brushed Nickel 14" dia., 6.5" ht. 2 medium base, 75w max.



Semi-Flush

Alabaster glass.



20

Antique Bronze

P3460-09 Brushed Nickel 13.25" dia., 13.75" ht. 2 medium base, 60w max.



P3460-20 Antique Bronze 13.25" dia., 13.75" ht. 2 medium base, 60w max.



Arden

Summer linen shade.



P3739-09 Brushed Nickel 14" dia., 6.62" ht. 2 medium base, 60w max.



P3720-09 Brushed Nickel 14" dia., 11.37" ht. 2 medium base, 100w max.



Etched Glass Etched white glass.



009 Brushed Nickel



Satin Brass



Matte Black

P350146-009 Brushed Nickel 11.5" dia., 3.75" ht. 1 medium base, 60w max.



P350146-012 Satin Brass 11.5" dia., 3.75" ht. 1 medium base, 60w max.



P350146-031 Matte Black 11.5" dia., 3.75" ht. 1 medium base, 60w max.



P350147-009 Brushed Nickel 14" dia., 4.62" ht. 2 medium base, 60w max.



P350147-012 Satin Brass 14" dia., 4.63" ht. 2 medium base, 60w max.



P350147-031 Matte Black 14" dia., 4.62" ht. 2 medium base, 60w max.



Alabaster Glass



Brushed Nickel



Antique Bronze



White

P3688-09 Brushed Nickel 11.5" dia., 3.75" ht. 1 medium base, 60w max.



P3688-30 White 11.5" dia., 3.75" ht. 1 medium base, 60w max.



P3688-20 Antique Bronze 11.5" dia., 3.75" ht. 1 medium base, 60w max.



P3689-09 Brushed Nickel 14" dia., 4.62" ht. 2 medium base, 60w max.



P3689-30 White 14" dia., 4.62" ht. 2 medium base, 60w max.



P3689-20 Antique Bronze 14" dia., 4.62" ht. 2 medium base, 60w max.



P3697-09 Brushed Nickel 16.62" dia., 5.40" ht. 3 medium base, 60w max.



P3697-30 White 16.62" dia., 5.40" ht. 3 medium base, 60w max.



P3697-20 Antique Bronze 16.62" dia., 5.40" ht. 3 medium base, 60w max.



Appeal

Etched opal glass.



Brushed Nickel



Polished Chrome



Antique Bronze

P3991-09 Brushed Nickel 7.5" sq., 3.5" ht. 1 medium base, 75w max.



P3991-15 Polished Chrome 7.5" sq., 3.5" ht. 1 medium base, 75w max.




P3991-20 Antique Bronze 7.5" sq., 3.5" ht. 1 medium base, 75w max.



P3549-09 Brushed Nickel 9" sq., 3.75" ht. 2 medium base, 60w max.



P3549-15 Polished Chrome 9" sq., 3.75" ht.





P3549-20 Antique Bronze 9" sq., 3.75" ht. 2 medium base, 60w max.



P3511-09 Brushed Nickel 11" sq., 3.75" ht. 2 medium base, 75w max.



P3511-15 Polished Chrome 11" sq., 3.75" ht. 2 medium base, 75w max.



P3511-20 Antique Bronze 11" sq., 3.75" ht. 2 medium base, 75w max.



P3992-09 Brushed Nickel 13" sq., 5" ht. 3 medium base, 60w max.



P3992-15 Polished Chrome 13" sq., 5" ht. 3 medium base, 60w max.



P3992-20 Antique Bronze 13" sq., 5" ht. 3 medium base, 60w max.



Linen Dome

Etched linen glass.



P350170-009 Brushed Nickel 12.25" dia., 4" ht. 2 medium base LED, 15w max.



P350178-009 Brushed Nickel 16.25" dia., 4.12" ht. 3 medium base LED, 15w max.



P350179-009 Brushed Nickel 20.12" dia., 4.12" ht. 4 medium base LED, 15w max.



Dome Glass

09 Brushed Nickel

20 Antique Bronze





80

Forged Black

P3924-09 Brushed Nickel *P3924-20 Antique Bronze P3924-30 White P3924-80 Forged Black 11.37" dia., 5.5" ht. 1 medium base, 60w max. Alabaster glass.



P3924-09ET Brushed Nickel *P3924-15ET Polished Chrome P3924-20ET Antique Bronze 11.37" dia., 5.5" ht. 1 medium base, 60w max. Etched glass.



*P3925-09 Brushed Nickel P3925-20 Antique Bronze P3925-80 Forged Black 13.25" dia., 5.87" ht. 2 medium base, 75w max. Alabaster glass.



P3925-09ET Brushed Nickel ***P3925-20ET** Antique Bronze 13.25" dia., 5.87" ht. 2 medium base, 75w max. Etched glass.



P3925-30 White 13.25" dia., 5.87" ht. 2 medium base, 75w max. Alabaster glass.



P3925-20EUL Antique Bronze 13.25" dia., 5.81" ht. 2 medium base, 75w max. Etched umber linen glass.



P3926-09 Brushed Nickel P3926-20 Antique Bronze P3926-30 White *P3926-80 Forged Black 15.25" dia., 6.62" ht. 3 medium base, 60w max. Alabaster glass.



*P3926-09ET Brushed Nickel P3926-15ET Polished Chrome P3926-20ET Antique Bronze 15.25" dia., 6.62" ht. 3 medium base, 60w max. Etched glass.



P3927-09 Brushed Nickel ***P3927-20** Antique Bronze 13.18" dia., 11.31" ht. 2 medium base, 100w max. Alabaster glass.



P3927-15ET Polished Chrome 13.18" dia., 11.31" ht. 2 medium base, 100w max. Etched glass.



Melon Glass

Etched glass.



09 Brushed Nickel



Antique Bronze



White

P3817-09 Brushed Nickel *P3817-20 Antique Bronze **P3817-30** White 13.25" dia., 7" ht. 2 medium base, 75w max.



*P3816-09 Brushed Nickel P3816-20 Antique Bronze **P3816-30** White 11.37" dia., 6" ht. 1 medium base, 75w max.



P3818-09 Brushed Nickel P3818-20 Antique Bronze *P3818-30 White 15.25" dia., 7.5" ht. 3 medium base, 60w max.



P3876-09 Brushed Nickel *P3876-20 Antique Bronze 13.25" dia., 12.5" ht. 2 medium base, 100w max.



*Shown in finish

Beveled Glass Clear glass.



Brushed Nickel



Polished Brass



Antique Bronze

P5788-09 Brushed Nickel 9.75" dia., 6" ht. 3 candelabra base, 25w max.



P5788-10 Polished Brass 9.75" dia., 6" ht. 3 candelabra base, 25w max.



P5788-20 Antique Bronze 9.75" dia., 6" ht. 3 candelabra base, 25w max.



P5789-09 Brushed Nickel 11.12" dia., 6.25" ht. 4 candelabra base, 25w max.



P5789-10 Polished Brass 11.12" dia., 6.25" ht. 4 candelabra base, 25w max.



P5789-20 Antique Bronze 11.12" dia., 6.25" ht. 4 candelabra base, 25w max.



Fitter

White glass.





Antique Bronze



White

P3408-09 Brushed Nickel 7.5" dia., 4.87" ht. 1 medium base, 60w max.



*P3408-20 Antique Bronze **P3408-30** White 7.5" dia., 4.62" ht. 1 medium base, 60w max.



P3410-09 Brushed Nickel *P3410-20 Antique Bronze **P3410-30** White 9.5" dia., 5.25" ht. 2 medium base, 60w max.



P3412-30 White 11.75" dia., 5.25" ht. 2 medium base, 75w max.



*Shown in finish

Prismatic Glass

Clear glass.



White

P3405-30 White 7.5" dia., 4.75" ht. 1 medium base, 60w max.



P3406-30 White 9.5" dia., 5.25" ht. 2 medium base, 60w max.



White Glass



White

P3518-30 White 8.75" dia., 5" ht. 2 medium base, 60w max.



P3520-30 White 10.75" dia., 5.37" ht. 2 medium base, 75w max.



Glass Globes

White or clear glass.



09 Brushed Nickel



Antique Bronze



White

P3401-09 Brushed Nickel ***P3401-20** Antique Bronze 6" dia., 7.25" ht. 1 medium base, 60w max.



P3203-30 White 6" dia., 7" ht. 1 medium base, 60w max.



*P3599-09 Brushed Nickel P3599-20 Antique Bronze P3599-30 White 6.37" dia., 7.25" ht. 1 medium base, 60w max.



*P3605-30 White P3605-30SW White 6" dia., 7.25" ht. 1 medium base, 60w max.



*Shown in finish

Round Glass

White glass.



White

P4609-30 White 12" dia., 5.5" ht. 2 medium base, 60w max.



P4610-30 White 14.5" dia., 7" ht. 3 medium base, 100w max.



Square Glass

White or patterned white glass.



P4961-30 White 12" sq., 5.75" ht. 2 medium base, 60w max.



P4962-30 White 12" sq., 5.75" ht. 2 medium base, 60w max.



Mingle LED

Metal outer shade with an etched parchment glass inner shade.



P2318-0930K9 Brushed Nickel 11" dia., 5.87" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.



P2320-0930K9 Brushed Nickel 14" dia., 10.5" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.



All fixtures:

Polished Chrome



Portal LED



White acrylic diffuser.



P3631-1530K9 Polished Chrome 9" dia., 2.5" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens. White acrylic diffuser.



Brushed Nickel

P3632-0930K9 Brushed Nickel 13" dia., 2.5" ht. 29w LED module, 3000K, 90 CRI, 2197 source lumens. White acrylic diffuser.



P3632-1530K9 Polished Chrome 13" dia., 2.5" ht. 29w LED module, 3000K, 90 CRI, 2197 source lumens. White acrylic diffuser.



P3658-0930K9 Brushed Nickel 11" dia., 4.12" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens. Etched glass.





Inspire LED



009 Brushed Nickel



Antique Bronze



Graphite

P350135-009-30 Brushed Nickel 13" dia., 6" ht. 17w LED module, 3000K, 90 CRI, 1452 source lumens. Summer linen fabric shade.



P350134-009-30 Brushed Nickel 13" dia., 10.62" ht. 17w LED module, 3000K, 90 CRI, 1452 source lumens. Summer linen fabric shade.



P350135-143-30 Graphite 13" dia., 6" ht. 17w LED module, 3000K, 90 CRI, 1452 source lumens. Summer linen fabric shade.



P350134-143-30 Graphite 13" dia., 10.62" ht. 17w LED module, 3000K, 90 CRI, 1452 source lumens. Summer linen fabric shade.



P3696-0930K9 Brushed Nickel 13" dia., 6" ht. 17w LED module, 3000K, 90 CRI, 1452 source lumens. Off-white linen fabric shade.



P3683-0930K9 Brushed Nickel 13" dia., 10.62" ht. 17w LED module, 3000K, 90 CRI, 1452 source lumens. Off-white linen fabric shade.



P3696-2030K9 Antique Bronze 13" dia., 6" ht. 17w LED module, 3000K, 90 CRI, 1452 source lumens. Off-white linen fabric shade.



P3683-2030K9 Antique Bronze 13" dia., 10.62" ht. 17w LED module, 3000K, 90 CRI, 1452 source lumens. Off-white linen fabric shade.







Bezel LED

Etched white glass.



009 Brushed Nickel



Polished Chrome

P350085-009-30 Brushed Nickel 10.5" dia., 3.5" ht. 17w LED module, 3000K, 90 CRI, 1276 source lumens.



P350085-015-30 Polished Chrome 10.5" dia., 3.5" ht. 17w LED module, 3000K, 90 CRI, 1276 source lumens.



P350086-009-30 Brushed Nickel 13" dia., 3.87" ht. 25w LED module, 3000K, 90 CRI, 1770 source lumens.



All fixtures:



009 Brushed Nickel



Polished Chrome



Antique Bronze

Flush Mount LED

Etched glass.

P350051-009-30 Brushed Nickel 11" dia., 4.18" ht. 17w LED module, 3000K, 90 CRI, 1452 source lumens.



P350053-009-30 Brushed Nickel 11" dia., 4" ht. 17w LED module, 3000K, 90 CRI, 1452 source lumens.



P350100-009-30 Brushed Nickel P350100-015-30 Polished Chrome *P350100-020-30 Antique Bronze 11" dia., 4.25" ht. 17w LED module, 3000K, 90 CRI, 1276 source lumens.



P350052-009-30 Brushed Nickel 12.5" dia., 4.5" ht. 25w LED module, 3000K, 90 CRI, 2015 source lumens.



P350054-009-30 Brushed Nickel 13.25" dia., 4.75" ht. 25w LED module, 3000K, 90 CRI, 2015 source lumens.



P350101-009-30 Brushed Nickel *P350101-015-30 Polished Chrome P350101-020-30 Antique Bronze 13.5" dia., 4.5" ht. 25w LED module, 3000K, 90 CRI, 1770 source lumens.



All fixtures:



Dome LED

Etched linen glass.



009 Brushed Nickel

P350055-009-30 Brushed Nickel 12" dia., 4.25" ht. 20w integrated LED, 3000K,

90 CRI, 1000 delivered lumens. Non-dimmable.



P350056-009-30 Brushed Nickel 16" dia., 4.5" ht. 24w integrated LED, 3000K, 90 CRI, 1144 delivered lumens. Non-dimmable.



Linen LED

White linen glass.



P350005-009-30 Brushed Nickel 11" dia., 4.62" ht. 21w integrated LED, 3000K, 90 CRI, 921 delivered lumens.



P350006-009-30 Brushed Nickel 13" dia., 5.37" ht. 21w integrated LED, 3000K, 90 CRI, 1152 delivered lumens.



P350007-009-30 Brushed Nickel 15" dia., 5.87" ht. 28w integrated LED, 3000K, 90 CRI, 1389 delivered lumens.



P350008-009-30 Brushed Nickel 19" dia., 7.12" ht. 30w integrated LED, 3000K,



All fixtures:





Weaver LED

Linen fabric shade with a linen glass diffuser.



P3610-0930K9 Brushed Nickel 10" dia., 3.43" ht. 17w integrated LED, 3000K, 90 CRI, 1211 source lumens.



P3611-0930K9 Brushed Nickel 16" dia., 4" ht. Two 17w LED modules, 3000K, 90 CRI, 1211 source lumens per module.



P3612-0930K9 Brushed Nickel 22" dia., 4.43" ht. Three 17w LED modules, 3000K, 90 CRI, 1211 source lumens per module.





Surface Mount LED

White acrylic diffuser.





*P7249-0930K9 Brushed Nickel P7249-17430K9 Urban Bronze 10.37" dia., 3.5" ht. 21.7w integrated LED, 3000K, 90 CRI, 1027 delivered lumens.



P7253-0930K9 Brushed Nickel *P7253-17430K9 Urban Bronze 14" dia., 3.75" ht. 22w integrated LED, 3000K, 90 CRI, 1184 delivered lumens.



P7250-0930K9 Brushed Nickel *P7250-17430K9 Urban Bronze 17.75" dia., 4.75" ht. 30w integrated LED, 3000K, 90 CRI, 1765 delivered lumens.



*P7251-0930K9 Brushed Nickel P7251-17430K9 Urban Bronze 32.5" L, 18" W., 4.75" ht. 39w integrated LED, 3000K, 90 CRI, 2649 delivered lumens, 120-277V. *Shown in finish





Helm LED

White acrylic diffuser.

Brushed Nickel



Antique Bronze

*P3447-0930K9 Brushed Nickel P3447-2030K9 Antique Bronze 11" sq., 3.75" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.



P3448-0930K9 Brushed Nickel *P3448-2030K9 Antique Bronze 14" sq., 3.75" ht. Two 17w LED modules, 3000K, 90 CRI, 1211 source lumens, per module.



*Shown in finish All fixtures:



Apogee LED

Etched white glass.

009 Brushed Nickel

P350070-009-30 Brushed Nickel 15" dia., 3.68" ht. 30w integrated LED, 3000K, 90 CRI. 1660 delivered lumens.

120-277V, 0-10V dimming.



P350071-009-30 Brushed Nickel 21" dia., 4.5" ht. 45w integrated LED, 3000K, 90 CRI, 2550 delivered lumens, 120-277V, 0-10V dimming.









Maier LED

White acrylic diffuser.



009 Brushed Nickel



(**030**) White

P350076-009-30 Brushed Nickel 9.06" dia., 4.31" ht. 20.5w integrated LED, 3000K, 90 CRI, 1354 delivered lumens.



P350076-030-30 White 9.06" dia., 4.31" ht. 20.5w integrated LED, 3000K, 90 CRI, 1354 delivered lumens.



P350077-009-30 Brushed Nickel 14" dia., 4.75" ht. 26w integrated LED, 3000K, 90 CRI, 2016 delivered lumens.



P350077-030-30 White 14" dia., 4.75" ht. 26w integrated LED, 3000K, 90 CRI, 2016 delivered lumens.



P350078-009-30 Brushed Nickel

18" dia., 5.25" ht. 28.5w integrated LED, 3000K, 90 CRI, 2064 delivered lumens.



P350078-030-30 White

18" dia., 5.25" ht. 28.5w integrated LED, 3000K, 90 CRI, 2064 delivered lumens.



All fixtures:







Etched glass.



P350088-009-30 Brushed Nickel 12.87" dia., 10.37" ht. 17w LED module, 3000K, 90 CRI, 1276 source lumens.









Drum LED

White acrylic diffuser.



White



P730005-030-30 White *P730005-031-30 Black

11" dia., 4.12" ht. 21w integrated LED, 3000K, 90 CRI, 1680 delivered lumens.



P730008-030-30 White

21w integrated LED, 3000K,

90 CRI, 1575 delivered lumens.

10.81" dia., 4" ht.

P730002-030-30 White

13.56" dia., 4.12" ht. 22.5w integrated LED, 3000K, 90 CRI, 2025 delivered lumens.



P730003-030-30 White

16.93" dia., 4.12" ht. 28w integrated LED, 3000K, 90 CRI, 2520 delivered lumens.



*Shown in finish All fixtures:



030



White



White acrylic diffuser.

P730006-030-30 White 13.68" dia., 4.12" ht. 22.5w integrated LED, 3000K, 90 CRI, 1845 delivered lumens.



P730007-030-30 White

17" dia., 4.12" ht. 28w integrated LED, 3000K, 90 CRI, 2548 delivered lumens.







Beyond LED

White acrylic diffuser.



Brushed Nickel

P2308-0930K9 Brushed Nickel 12" dia., 2.87" ht., 2.88" D. 17w LED module, 3000K, 90 CRI, 1211 source lumens. Ceiling or Wall Mount.



shown wall mounted



All fixtures:





30



White

Fitter LED

White glass.

P3408-3030K9 White 7.5" dia., 4.87" ht.

17w LED module, 3000K, 90 CRI, 1211 source lumens.



09 Brushed Nickel

P3408-0930K9 Brushed Nickel 7.5" dia., 4.87" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.



Linear Cloud LED

White acrylic diffuser.



P7278-3030K9 White 26" L, 10.25" W., 3.25" ht. 27w integrated LED, 3000K, 90 CRI, 1974 delivered lumens.



P7279-3030K9 White

51" L, 10.25" W., 3.25" ht. 40w integrated LED, 3000K, 90 CRI, 2908 delivered lumens.



Strip & Wrap LED

White acrylic diffuser.




P730000-030-30 White 23.661" L, 2.126" W., 2.392" ht. 21w integrated LED, 3000K, 90 CRI, 1600 lumens.



P730001-030-30 White 47.283" L, 2.126" W., 2.392" ht. 36w integrated LED, 3000K,

90 CRI, 3200 lumens.





P730012-030-30 White 47.346" L, 6.156" W., 2.992" ht. 36w integrated LED, 3000K, 90 CRI, 3400 lumens.









Sconces Guide

1 Complete Selection

View our complete offering of sconces and wall brackets.

Use the **Product Finder** in the beginning of the catalog
(a number of sconces and wall brackets are found in Collections).

WALL SCONCES LED WALL SCONCES

SWING ARM

p. 55

WALL BRACKETS

p. 51

p. 52









2 Perfect Pairings

Sconces and wall brackets complement other lighting in the room. They not only look beautiful, but they also add a layer of light providing the ideal illumination for any space.



Design Series offers more elevated product options. Use QR to view:

DESIGN+SERIES**







Sconces

DISCOVER THE LATEST





Hinton



009 Brushed Nickel



031 Matte Black



Vintage Brass

P710084-009 Brushed Nickel 8" W., 9.62" ht., 12" D. 1 medium base, 60w max.



P710084-031 Matte Black 8" W., 9.62" ht., 12" D. 1 medium base, 60w max.



P710084-163 Vintage Brass 8" W., 9.62" ht., 12" D. 1 medium base, 60w max.



P710085-009 Brushed Nickel 8.25" W., 9.62" ht., 12.12" D. 1 medium base, 60w max.



P710085-031 Matte Black 8.25" W., 9.62" ht., 12.12" D. 1 medium base, 60w max.



P710085-163 Vintage Brass 8.25" W., 9.62" ht., 12.12" D. 1 medium base, 60w max.



P710094-009 Brushed Nickel 8" W., 14.37" ht., 18.25" D. 1 medium base, 60w max.



P710094-031 Matte Black 8" W., 14.37" ht., 18.25" D. 1 medium base, 60w max.



P710094-163 Vintage Brass 8" W., 14.37" ht., 18.25" D. 1 medium base, 60w max.



P710095-009 Brushed Nickel 8.25" W., 14.37" ht., 18.37" D. 1 medium base, 60w max.



P710095-031 Matte Black 8.25" W., 14.37" ht., 18.37" D. 1 medium base, 60w max.



P710095-163 Vintage Brass 8.25" W., 14.37" ht., 18.37" D. 1 medium base, 60w max.





Carrick



009 Brushed Nickel



31M Matte Black



Vintage Brass

P710104-009 Brushed Nickel 10" W., 11.75" ht., 10.87" D. 1 medium base, 60w max.



P710104-163 Vintage Brass 10" W., 11.75" ht., 10.87" D. 1 medium base, 60w max.



P710104-31M Matte Black 10" W., 11.75" ht., 10.87" D. 1 medium base, 60w max.



Kempsey



009 Brushed Nickel



Antique Bronze

P710045-009 Brushed Nickel 12" W., 19.75" ht., 23.62" D. 1 medium base, 75w max.



P710045-020 Antique Bronze 12" W., 19.75" ht., 23.62" D. 1 medium base, 75w max.



Milner



009 Brushed Nickel



Matte Black

P710086-009 Brushed Nickel 5.62" W., 9" ht., 10.37" D. 1 medium base, 60w max.



P710086-031 Matte Black 5.62" W., 9" ht., 10.37" D. 1 medium base, 60w max.



Hartwick



009 Brushed Nickel



Satin Brass



Matte Black

P710088-009 Brushed Nickel 5" W., 18" ht., 4" D. 1 medium base, 60w max.



P710088-012 Satin Brass 5" W., 18" ht., 4" D. 1 medium base, 60w max.



P710088-031 Matte Black 5" W., 18" ht., 4" D. 1 medium base, 60w max.



P710087-009 Brushed Nickel 4.5" W., 13.5" ht., 4" D. 1 medium base, 60w max.



P710087-012 Satin Brass 4.5" W., 13.5" ht., 4" D. 1 medium base, 60w max.



P710087-031 Matte Black 4.5" W., 13.5" ht., 4" D. 1 medium base, 60w max.



All fixtures:







009 Brushed Nickel



Matte Black



Brushed Bronze

P710111-009 Brushed Nickel 7.5" W., 12" ht., 4" D. 2 medium base, 60w max.



P710111-109 Brushed Bronze 7.5" W., 12" ht., 4" D. 2 medium base, 60w max.



P710111-31M Matte Black 7.5" W., 12" ht., 4" D. 2 medium base, 60w max.





Linen Glass



009 Brushed Nickel



031 Matte Black

P710072-009 Brushed Nickel 6" W., 12" ht., 4" D. 1 medium base, 75w max.



P710072-031 Matte Black 6" W., 12" ht., 4" D. 1 medium base, 75w max.



All fixtures:



Modern Glass



009 Brushed Nickel



Matte Black

P710118-009 Brushed Nickel 12" W., 7.5" ht., 4" D. 2 medium base, 60w max.



P710118-31M Matte Black 12" W., 7.5" ht., 4" D. 2 medium base, 60w max.



All fixtures:



Tobin



009 Brushed Nickel



Matte Black

P300222-009 Brushed Nickel 5" W., 15.5" ht., 5.87" D. 1 medium base, 100w max.



P300222-031 Matte Black 5" W., 15.5" ht., 5.87" D. 1 medium base, 100w max.



Torino



09 Brushed Nickel





Forged Bronze

P7181-09 Brushed Nickel 9.5" W., 6.75" ht., 4.75" D. 1 medium base, 100w max.



P7185-20 Antique Bronze 9.5" W., 6.75" ht., 4.68" D. 1 medium base, 100w max.



P7181-77 Forged Bronze 9.5" W., 6.75" ht., 4.75" D. 1 medium base, 100w max.



Opal Glass



Brushed Nickel





Antique Bronze



Matte Black

P7153-09W Brushed Nickel 15.37" W., 7" ht., 7.5" D. 1 medium base, 60w max.











White Glass



o) White

Louver





Matte Black

P7112-30 White 11.5" W., 5" ht., 5.75" D. 1 medium base, 100w max.



P7103-30 White 14" W., 7" ht., 7" D. 1 medium base, 100w max.



P7103-31 Matte Black 14" W., 7" ht., 7" D. 1 medium base, 100w max.



Blanco LED



009 Brushed Nickel



Satin Brass



Matte Black

P710047-009-30 Brushed Nickel 4.75" W., 11.75" ht., 3.62" D. 16w Integrated LED, 3000K, 90 CRI, 823 delivered lumens.



P710047-031-30 Matte Black 4.75" W., 11.75" ht., 3.62" D. 16w Integrated LED, 3000K, 90 CRI, 823 delivered lumens.







Beam LED



009 Brushed Nickel




Polished Chrome



Architectural Bronze

P710049-009-30 Brushed Nickel 4.75" W., 10.5" ht., 3.25" D. 16w integrated LED, 3000K, 90 CRI, 1000 delivered lumens.





P710049-129-30 Architectural Bronze 4.75" W., 10.5" ht., 3.25" D. 16w integrated LED, 3000K, 90 CRI, 1000 delivered lumens.











Parallel LED

009 Brushed Nickel



Polished Chrome



Satin Brass



Architectural Bronze

P710050-009-30 Brushed Nickel 4.75" W., 11" ht., 2.75" D. 16w integrated LED, 3000K, 90 CRI, 930 delivered lumens.



P710050-012-30 Satin Brass 4.75" W., 11" ht., 2.75" D. 16w integrated LED, 3000K, 90 CRI, 930 delivered lumens.



P710050-015-30 Polished Chrome 4.75" W., 11" ht., 2.75" D. 16w integrated LED, 3000K, 90 CRI, 930 delivered lumens.



P710050-129-30 Architectural Bronze 4.75" W., 11" ht., 2.75" D. 16w integrated LED, 3000K, 90 CRI, 930 delivered lumens.



All fixtures:





Pearl LED



Satin Brass



P710105-012-30 Satin Brass 5.75" W., 12.06" ht., 5.43" D. 6.5w integrated LED, 3000K, 90 CRI, 412 delivered lumens.



P710105-031-30 Matte Black 5.75" W., 12.06" ht., 5.43" D. 6.5w integrated LED, 3000K, 90 CRI, 412 delivered lumens.





Alabaster Stone LED



009 Brushed Nickel



Matte Black

P710081-009-30 Brushed Nickel 8" W., 8.5" ht., 3.25" D. 9.5w Integrated LED, 3000K, 90 CRI, 387 delivered lumens.



P710081-031-30 Matte Black 8" W., 8.5" ht., 3.25" D. 9.5w Integrated LED, 3000K, 90 CRI, 387 delivered lumens.



All fixtures:





Stone Glass LED



009 Brushed Nickel



Matte Black

P710080-009-30 Brushed Nickel 8" W., 8.5" ht., 3.25" D. 9.5w Integrated LED, 3000K, 90 CRI, 433 delivered lumens.



P710080-031-30 Matte Black 8" W., 8.5" ht., 3.25" D. 9.5w Integrated LED, 3000K, 90 CRI, 433 delivered lumens.



All fixtures:





Frame LED



Brushed Nickel

P2781-0930K9 Brushed Nickel 4.75" W., 12" ht., 3.5" D. 15w integrated LED, 3000K, 90 CRI, 577 delivered lumens.









Sconces LED



009 Brushed Nickel



White



Architectural Bronze

P7092-0930K9 Brushed Nickel 8" W., 10.62" ht., 4" D. 17w LED module, 3000K, 90 CRI, 1211 source lumens.







P7083-0930K9 Brushed Nickel 8.87" W., 10.62" ht., 4" D. 17w LED module, 3000K, 90 CRI, 1211 source lumens.







P7085-0930K9 Brushed Nickel 9.5" W., 10.62" ht., 3.75" D. 17w LED module, 3000K, 90 CRI, 1211 source lumens.







P7088-0930K9 Brushed Nickel 8" W., 10.62" ht., 3.87" D. 17w LED module, 3000K, 90 CRI, 1211 source lumens.







P710010-009-30 Brushed Nickel 6.75" W., 12" ht., 4" D. 9w LED module, 3000K, 90 CRI, 624 source lumens.









P710010-129-30 Architectural Bronze 6.75" W., 12" ht., 4" D. 9w LED module, 3000K, 90 CRI, 624 source lumens.









P7093-3030K9 White 11.37" W., 11.12" ht., 3.37" D. 17w LED module, 3000K, 90 CRI, 1211 source lumens.







Shown with Brushed Nickel finials (included)



Shown with Bronze finials (included)



Shown with White finials (included)

Inspire LED



(030) Summer Linen



Off White Linen

P710071-030-30 Summer Linen 6.25" W., 9" ht., 3.87" D. 9w LED module, 3000K, 90 CRI, 624 source lumens.









P710071-159-30 Off White Linen 6.25" W., 9" ht., 3.87" D. 9w LED module, 3000K, 90 CRI, 624 source lumens.









Curve LED



Opal White Eclipse LED



009 Brushed Nickel

Architectural Bronze

P710102-060-30 Opal White 8" W., 8" ht., 3.62" D. 10w Integrated LED, 3000K, 90 CRI, 744 delivered lumens. Includes finals in 3 finishes (Matte Black, Brushed Nickel, and Architectural Bronze).













Detail of Architectural Bronze finial

P710090-009-30 Brushed Nickel

15.5" W., 7.5" ht., 4" D. 17w LED module, 3000K, 90 CRI, 1276 source lumens.









Apogee LED

P710036-009-30 Brushed Nickel 15" W., 7.5" ht., 3.68" D. 20w integrated LED, 3000K, 90 CRI, 940 delivered lumens, 120-277V, 0-10V dimming.









009 Brushed Nickel

15" W., 7.5" ht., 3.68" D. 20w integrated LED, 3000K, 90 CRI, 940 delivered lumens, 120-277V, 0-10V dimming.

P710036-129-30 Architectural Bronze











DISCOVER THE LATEST







STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Highlight a neutral bathroom palette with lighting that delivers tactile appeal. The Beckner Collection reflects mid-century and industrial style with mechanical knobs and hooded lights. Its versatile design can be mounted facing up for ambient illumination or pointing down to deliver task lighting.

1 In this section

These icons depict whether a vanity light has flexible mounting options.



Mounts up or down









2 Quick selection

Use the **Product Finder**, page 62, to quickly see all bath fixtures offered in this catalog.







Design Series offers more elevated product options. Use QR to view:

DESIGN+SERIES'



Bath Guide




Captarent LED

The Captarent LED Illuminated Mirror has frosted LEDs that highlights the mirror's curved profile and provides a balanced wash of soft illumination.

FINISH





P300454-030-30

P300454-030-30 White 24" dia., 1.65" D. 24w integrated LED, 3000K, 90 CRI, 841 delivered lumens.



P300455-030-30 White 30" W., 36" ht., 1.81" D. 30w integrated LED, 3000K, 90 CRI, 1258 delivered lumens.



P300456-030-30 White 22" W., 28" ht., 1.61" D. 24w integrated LED, 3000K, 90 CRI, 658 delivered lumens.



All fixtures:





Pearl LED

Opal glass.


FINISHES



Satin Brass



Matte Black



P300312-012-30

P300312-012-30 Satin Brass •**P300312-031-30** Matte Black 18" W., 5" ht. 19.5w integrated LED, 3000K, 90 CRI, 1292 delivered lumens.



P710105-012-30 Satin Brass **P710105-031-30** Matte Black 5.75" W., 12.06" ht., 5.43" D. 6.5w integrated LED, 3000K, 90 CRI, 412 delivered lumens.





*P300313-012-30 Satin Brass P300313-031-30 Matte Black 23.87" W., 5" ht. 24w integrated LED, 3000K, 90 CRI, 1692 delivered lumens.



*Shown in finish All fixtures:



Colonnade LED

Etched white glass.









P300186-009-30

*P300187-009-30 Brushed Nickel P300187-015-30 Polished Chrome 22" W., 7.5" ht. 28.5w integrated LED, 3000K, 90 CRI, 1500 delivered lumens.



P300186-009-30 Brushed Nickel ***P300186-015-30** Polished Chrome 13.25" W., 7.5" ht. 19w integrated LED, 3000K, 90 CRI, 1000 delivered lumens.



P300185-009-30 Brushed Nickel ***P300185-015-30** Polished Chrome 4.75" W., 7.5" ht., 5.43" D. 9.5w integrated LED, 3000K, 90 CRI, 500 delivered lumens.



P300188-015-30 Polished Chrome 31.37" W., 7.5" ht. 38w integrated LED, 3000K, 90 CRI, 2000 delivered lumens.

*P300188-009-30 Brushed Nickel



*Shown in finish *All fixtures:*





Ace LED

Etched glass.

FINISH



15 Polished Chrome



P2143-1530K9

P2144-1530K9 Polished Chrome 24" W., 4.75" ht. Three 9w LED modules, 3000K, 90 CRI, 623 source lumens per module.



P2143-1530K9 Polished Chrome 15.5" W., 4.75" ht. Two 9w LED modules, 3000K, 90 CRI, 623 source lumens per module.



P2145-1530K9 Polished Chrome 32.5" W., 4.75" ht. Four 9w LED modules, 3000K, 90 CRI, 623 source lumens per module.



Arch LED

Etched glass.

FINISH



009 Brushed Nickel



P300291-009-30

P300291-009-30 Brushed Nickel 20.5" W., 5" ht. Three 10w integrated LED, 3000K, 90 CRI, 1508 delivered lumens.



P300290-009-30 Brushed Nickel 13.25" W., 5" ht. Two 10w integrated LED, 3000K, 90 CRI, 1057 delivered lumens.









Concourse LED

Etched white glass.

FINISH



009 Brushed Nickel



P300093-009-30

P300093-009-30 Brushed Nickel 24" W., 4.75" ht., 3.5" D. 37w LED module, 3000K, 90 CRI, 2191 delivered lumens.



P300094-009-30 Brushed Nickel 36" W., 4.75" ht., 3.5" D. 53w LED module, 3000K, 90 CRI, 2969 delivered lumens.













Frame LED

Etched white glass.

FINISH



09 Brushed Nickel



P2781-0930K9

P2782-0930K9 Brushed Nickel 24" W., 4.75" ht., 3.5" D. 35w integrated LED, 3000K, 90 CRI, 1659 delivered lumens.



P2781-0930K9 Brushed Nickel 12" W., 4.75" ht., 3.5" D. 15w integrated LED, 3000K, 90 CRI, 577 delivered lumens.



shown vertical







All fixtures:





Grid LED

White etched linen diffuser.

FINISHES





134 Silver Ridge



P300331-031-30

P300333-031-30 Black *P300333-134-30 Silver Ridge 30" W., 4.75" ht., 3.13" D. 34w integrated LED, 3000K 90 CRI, 1639 delivered lumens.



*P300332-031-30 Black **P300332-134-30** Silver Ridge 22" W., 4.75" ht., 3.13" D. 22w integrated LED, 3000K 90 CRI, 1033 delivered lumens.







P300331-031-30 Black **P300331-134-30** Silver Ridge 14" W., 4.75" ht., 3.13" D. 14w integrated LED, 3000K 90 CRI, 569 delivered lumens.















Blanco LED

Etched white glass.

FINISHES



009 Brushed Nickel



Satin Brass



Matte Black



P300150-012-30

P300151-012-30 Satin Brass *P300151-031-30 Matte Black

P300151-009-30 Brushed Nickel 32.37" W., 4.75" ht., 3.62" D. 53w integrated LED, 3000K, 90 CRI, 2768 delivered lumens.





*P300150-009-30 Brushed Nickel 22.25" W., 4.75" ht., 3.62" D. **P300150-012-30** Satin Brass P300150-031-30 Matte Black

36w integrated LED, 3000K, 90 CRI, 1942 delivered lumens.









P710047-009-30 Brushed Nickel *P710047-012-30 Satin Brass **P710047-031-30** Matte Black 4.75" W., 11.75" ht., 3.62" D. 16w integrated LED, 3000K, 90 CRI, 823 delivered lumens.



*Shown in finish All fixtures:





Planck LED

Brushed Nickel finish with linear chrome accents.


FINISH



009 Brushed Nickel



P710052-009-30









Parallel LED

Etched white glass.

FINISHES











P300183-129-30

*P300184-009-30 Brushed Nickel P300184-012-30 Satin Brass P300184-015-30 Polished Chrome P300184-129-30 Architectural Bronze 32" W., 4.75" ht., 2.75" D. 53w integrated LED, 3000K, 90 CRI, 2872 delivered lumens. **P300183-009-30** Brushed Nickel ***P300183-012-30** Satin Brass **P300183-015-30** Polished Chrome **P300183-129-30** Architectural Bronze

22.37" W., 4.75" ht., 2.75" D. 36w integrated LED, 3000K, 90 CRI, 2166 delivered lumens.








P710050-009-30 Brushed Nickel **P710050-012-30** Satin Brass ***P710050-015-30** Polished Chrome

P710050-129-30 Architectural Bronze

4.75" W., 11" ht., 2.75" D. 16w integrated LED, 3000K, 90 CRI, 930 delivered lumens.



*Shown in finish All fixtures:






Beam LED

Etched opal glass.

FINISHES










P300182-015-30



All fixtures:







Phase 1.1 LED

White acrylic shade.

FINISH



009 Brushed Nickel



P300223-009-30



P300225-009-30 Brushed Nickel 48" W., 4.75" ht., 4" D. 42w integrated LED, 3000K, 90 CRI, 3500 delivered lumens.









Phase 1.2 LED

White acrylic shade.

FINISH



009 Brushed Nickel



P300205-009-30 shown with decorative geometric accent

P300206-009-30 Brushed Nickel 36" W., 4.75" ht., 4.5" D. 33w integrated LED, 3000K, 90 CRI, 2475 delivered lumens. shown with decorative geometric accent



P300205-009-30 Brushed Nickel 24" W., 4.75" ht., 4.5" D. 22w integrated LED, 3000K, 90 CRI, 1575 delivered lumens. shown with faux stone accent



shown vertical



P300207-009-30 Brushed Nickel 48" W., 4.75" ht., 4.5" D. 42w integrated LED, 3000K, 90 CRI, 3400 delivered lumens. shown with faux stone accent









Detail of geometric accent









Phase 2.1 LED

White acrylic shade.

FINISH



009 Brushed Nickel



P300208-009-30



P300210-009-30 Brushed Nickel 48" W., 4.75" ht., 3.5" D. 44w integrated LED, 3000K, 90 CRI, 3300 delivered lumens.









Phase 2.2 LED

White acrylic shade.

FINISH



009 Brushed Nickel



P300211-009-30



P300213-009-30 Brushed Nickel 48" W., 4.75" ht., 4" D. 44w integrated LED, 3000K, 90 CRI, 3250 delivered lumens.



All fixtures:









Phase 3 LED

3-CCT 4000K **SELECTABLE** 5000K

White acrylic diffuser.


FINISHES



009 Brushed Nickel



Matte Black



P300410-31M-CS

*P300410-009-CS Brushed Nickel P300410-31M-CS Matte Black 16" W., 5.78" ht., 3" D. 11w integrated LED, 3000K, 4000K, 5000K, 90 CRI, 1083 delivered lumens.



P300411-31M-CS Matte Black P300411-009-CS Brushed Nickel 24" W., 5.78" ht., 3" D. 18w integrated LED, 3000K, 4000K, 5000K, 90 CRI, 1644 delivered lumens.





shown vertical

P300412-009-CS Brushed Nickel P300412-31M-CS Matte Black 32" W., 5.78" ht., 3" D. 22w integrated LED, 3000K, 4000K, 5000K, 90 CRI, 1948 delivered lumens.



*Shown in finish All fixtures:









Phase 4 LED

3-CCT 3000K 4000K **SELECTABLE** 5000K

White acrylic diffuser.

FINISHES



009 Brushed Nickel



Matte Black



P300403-009-CS

P300403-009-CS Brushed Nickel P300403-31M-CS Matte Black 16" W., 4.84" ht., 2.09" D. 11w integrated LED, 3000K, 4000K, 5000K, 90 CRI, 727 delivered lumens.









*P300404-009-CS Brushed Nickel P300404-31M-CS Matte Black

24" W., 4.84" ht., 2.09" D. 18w integrated LED, 3000K, 4000K, 5000K, 90 CRI, 1231 delivered lumens.





P300405-009-CS Brushed Nickel *P300405-31M-CS Matte Black

32" W., 4.84" ht., 2.09" D. 22w integrated LED, 3000K, 4000K, 5000K, 90 CRI, 1647 delivered lumens.





*P710110-009-CS Brushed Nickel P710110-31M-CS Matte Black 4.84" W., 16" ht., 2.09" D. 11w integrated LED,

3000K, 4000K, 5000K, 90 CRI, 827 delivered lumens.



*Shown in finish All fixtures:










Semblance LED



Clear acrylic edgelit diffuser.

FINISHES



009 Brushed Nickel



Matte Black



P300406-009-CS

P300406-009-CS Brushed Nickel P300406-31M-CS Matte Black 24" W., 4.84" ht., 3" D. 22w integrated LED, 3000K, 4000K, 5000K, 90 CRI, 1605 delivered lumens.





P300407-009-CS Brushed Nickel P300407-31M-CS Matte Black 32" W., 4.84" ht., 3" D. 30w integrated LED, 3000K, 4000K, 5000K, 90 CRI, 2543 delivered lumens.









Barril LED

White acrylic diffuser.

FINISHES



009 Brushed Nickel



Matte Black



P300408-31M-30



P300409-009-30 Brushed Nickel **P300409-31M-30** Matte Black 32" W., 4.76" ht., 2.33" D. 30w integrated LED, 3000K, 90 CRI, 2593 delivered lumens.





All fixtures:







Bath LED

White acrylic diffuser.

FINISH



009 Brushed Nickel



P300243-009-30

P300243-009-30 Brushed Nickel 24" W., 5.93" ht., 4.25" D 23w integrated LED, 3000K, 90 CRI, 1798 delivered lumens.



P300244-009-30 Brushed Nickel 48" W., 5.93" ht., 4.25" D. 37w integrated LED, 3000K, 90 CRI, 3040 delivered lumens.







Everlume® LE





P300304-009-CS Brushed Nickel *P300304-028-CS Satin White 16" W., 1.38" ht., 5" D. 17w integrated LED, 3000K, 4000K, 90 CRI, 1386 delivered lumens.



P300305-009-CS Brushed Nickel *P300305-028-CS Satin White 24" W., 1.38" ht., 5" D. 26w integrated LED, 3000K, 4000K, 90 CRI, 2182 delivered lumens.





*P300306-009-CS Brushed Nickel P300306-028-CS Satin White 32" W., 1.38" ht., 5" D. 32w integrated LED, 3000K, 4000K, 90 CRI, 2808 delivered lumens.

*Shown in finish All fixtures:












Cloud LED



P300239-060-CS Opal White 26.37" W., 4.63" ht., 6.12" D. 23w integrated LED, CCT selectable (3000K, 4000K, 5000K), 90 CRI, 2124 delivered lumens.





P300240-060-CS Opal White 38.25" W., 4.63" ht., 6.12" D. 32w integrated LED, CCT selectable (3000K, 4000K, 5000K), 90 CRI, 2760 delivered lumens.



*Shown in finish All fixtures:







Calais

Timeless details create an enduring silhouette for Calais. Clear glass and an elegantly simple frame provide a contemporary take on traditional style.

FINISHES



009 Brushed Nickel



Matte Black



Vintage Brass



P300361-163

P300363-009 Brushed Nickel **P300363-31M** Matte Black **P300363-163** Vintage Brass 34" W., 8.5" ht. 4 medium base, 60w max.







Calais

P300362-009 Brushed Nickel **P300362-31M** Matte Black **P300362-163** Vintage Brass 24.25" W., 8.5" ht. 3 medium base, 60w max.







P300361-009 Brushed Nickel **P300361-31M** Matte Black **P300361-163** Vintage Brass 14.62" W., 8.5" ht. 2 medium base, 60w max.







P300360-009 Brushed Nickel **P300360-31M** Matte Black **P300360-163** Vintage Brass 5" W., 8.5" ht., 7" D. 1 medium base, 60w max.









Elara

Elara features a slender, chic form with a stylized finial inspired by a chess pawn for a classically modern style.

FINISHES



009 Brushed Nickel



Matte Black



Vintage Brass



P300357-009

P300359-009 Brushed Nickel P300359-31M Matte Black **P300359-163** Vintage Brass 31.65" W., 11.5" ht. 4 candelabra base, 60w max.



Elara

P300358-009 Brushed Nickel **P300358-31M** Matte Black **P300358-163** Vintage Brass 22.12" W., 11.5" ht. 3 candelabra base, 60w max.











P300357-009 Brushed Nickel

P300357-31M Matte Black

P300357-163 Vintage Brass





P300356-009 Brushed Nickel **P300356-31M** Matte Black **P300356-163** Vintage Brass 4.75" W., 11.5" ht., 5" D. 1 candelabra base, 60w max.







Adley combines a clear glass shade with a curved rectangular backplate. Adley is a universal choice for New Traditional and Transitional settings.

FINISHES

009 Brushed Nickel









P300155-031

P300372-009 Brushed Nickel **P300372-012** Satin Brass **P300372-031** Matte Black 48.5" W., 7.62" ht. 6 medium base, 60w max.



P300157-009 Brushed Nickel **P300157-012** Satin Brass **P300157-031** Matte Black **P300157-104** Polished Nickel 32" W., 7.62" ht. 4 medium base, 60w max. **P300156-009** Brushed Nickel **P300156-012** Satin Brass **P300156-031** Matte Black **P300156-104** Polished Nickel 23" W., 7.62" ht. 3 medium base, 60w max.





P300155-009 Brushed Nickel **P300155-012** Satin Brass **P300155-031** Matte Black **P300155-104** Polished Nickel 13.87" W., 7.62" ht. 2 medium base, 60w max.

P300154-009 Brushed Nickel **P300154-012** Satin Brass **P300154-031** Matte Black **P300154-104** Polished Nickel

4.5" W., 7.75" ht., 6" D. 1 medium base, 60w max.

















All fixtures:



Adley combines an etched opal glass shade with a curved rectangular backplate. Adley is a universal choice for New Traditional and Transitional settings.

FINISHES









P300466-012

P300468-009 Brushed Nickel **P300468-012** Satin Brass **P300468-31M** Matte Black 32" W., 7.62" ht. 4 medium base, 60w max.







P300467-009 Brushed Nickel **P300467-012** Satin Brass **P300467-31M** Matte Black 23" W., 7.62" ht. 3 medium base, 60w max.







P300466-009 Brushed Nickel **P300466-012** Satin Brass **P300466-31M** Matte Black 13.87" W., 7.62" ht. 2 medium base, 60w max.







P300465-009 Brushed Nickel **P300465-012** Satin Brass **P300465-31M** Matte Black 4.5" W., 7.75" ht., 6" D. 1 medium base, 60w max.









Clarion

Clarion embraces a minimalist simplicity, with a clear, tubular glass shade secured by a sleek cylindrical base for a precision look.

FINISHES



009 Brushed Nickel



Satin Brass



Polished Chrome



Matte Black



P300299-009

P300299-009 Brushed Nickel **P300299-012** Satin Brass P300299-015 Polished Chrome **P300299-031** Matte Black 5" W., 12.62" ht., 4.25" D. 1 medium base T10, 60w max.









Clarion

P300300-009 Brushed Nickel **P300300-012** Satin Brass **P300300-015** Polished Chrom **P300300-031** Matte Black 20.37 " W., 5" ht. 2 medium base T10, 60w max.











shown vertical











Atwell

Long lines ending in clear glass globe shades define Atwell's modern aesthetic. One central stem holds bold linear rods capped by clear glass, creating bright illumination from the light source glowing within.

FINISHES









P710114-31M

P710114-009 Brushed Nickel **P710114-31M** Matte Black **P710114-109** Brushed Bronze 5.87" W., 18" ht., 6.75" D. 2 candelabra base, 60w max.











Cowan

Cowan boasts contemporary curved edges and simple square etched opal glass shades with gently rounded corners that complements the form.

FINISHES



009 Brushed Nickel



Satin Brass



Matte Black



P300369-012

P300371-009 Brushed Nickel **P300371-012** Satin Brass P300371-31M Matte Black 33.5" W., 8.5" ht. 4 medium base, 100w max.



Cowan

P300370-009 Brushed Nickel **P300370-012** Satin Brass **P300370-31M** Matte Black 23.5" W., 8.5" ht. 3 medium base, 100w max.















P300368-009 Brushed Nickel **P300368-012** Satin Brass **P300368-31M** Matte Black 4.75" W., 8.5" ht., 5.5" D. 1 medium base, 100w max.









Copeland

A softened diamond silhouette brings modern appeal to the Copeland Collection. The geometric opal glass shade delivers elegant illumination.

FINISHES









P300431-31M

P300433-009 Brushed Nickel **P300433-31M** Matte Black **P300433-191** Brushed Gold 33" W., 7.5" ht. 4 medium base, 75w max.



Copeland

P300432-009 Brushed Nickel P300432-31M Matte Black P300432-191 Brushed Gold 24" W., 7.5" ht. 3 medium base, 75w max.



P300431-009 Brushed Nickel **P300431-31M** Matte Black P300431-191 Brushed Gold 15" W., 7.5" ht. 2 medium base, 75w max.













P300430-009 Brushed Nickel P300430-31M Matte Black P300430-191 Brushed Gold 6" W., 8" ht., 7" D. 1 medium base, 75w max.









Haven

The Haven Collection is practical and stylish with a modern color blocking silhouette. The metal shade is suspended around etched opal glass to create a pleasing softened glow.

FINISHES









P300443-009

P300445-009 Brushed Nickel **P300445-31M** Matte Black **P300445-163** Vintage Brass 34" W., 7" ht.

4 medium base, 100w max.



Haven

P300444-009 Brushed Nickel **P300444-31M** Matte Black **P300444-163** Vintage Brass 24" W., 7" ht. 3 medium base, 100w max.

P300443-009 Brushed Nickel **P300443-31M** Matte Black **P300443-163** Vintage Brass 16" W., 7" ht. 2 medium base, 100w max.













P300442-009 Brushed Nickel **P300442-31M** Matte Black **P300442-163** Vintage Brass 4.75" W., 7.87" ht., 6.75" D. 1 medium base, 100w max.









Reiss

Bring a refreshed sense of style to the bath with Reiss. A polished concentric band accents a simple white glass shade, bringing an elegant appeal to the modern design.



P300414-31M

P300416-009 Brushed Nickel **P300416-015** Polished Chrome **P300416-31M** Matte Black 31.62" W., 7" ht. 4 medium base, 100w max.



Reiss

P300415-009 Brushed Nickel **P300415-015** Polished Chrome **P300415-31M** Matte Black 22.75" W., 7" ht. 3 medium base, 100w max.

P300414-009 Brushed Nickel **P300414-015** Polished Chrome **P300414-31M** Matte Black 13.75" W., 7" ht. 2 medium base, 100w max.













P300413-009 Brushed Nickel **P300413-015** Polished Chrome **P300413-31M** Matte Black 5" W., 7.87" ht., 5.75" D. 1 medium base, 100w max.









Lassiter

The Lassiter Collection features square tubing with clean, sharp angles, vintage light sockets and sophisticated clear glass shades.

FINISHES



009 Brushed Nickel



Matte Black



P300258-009

P300259-009 Brushed Nickel P300259-031 Matte Black 34" W., 8" ht. 4 medium base, 60w max.





Lassiter

P300258-009 Brushed Nickel **P300258-031** Matte Black 24" W., 8" ht. 3 medium base, 60w max.

P300257-009 Brushed Nickel **P300257-031** Matte Black 16" W., 8" ht. 2 medium base, 60w max.









P710073-009 Brushed Nickel **P710073-031** Matte Black 4.87" W., 19.25" ht., 6.5" D. 1 medium base, 60w max.







Elegantly extended, the Vertex Collection is composed of angular forms and clear glass shades to create a bold design that perfectly complements modern interiors.

FINISHES



009 Brushed Nickel



Matte Black



Brushed Gold



P300458-31M

P300460-009 Brushed Nickel P300460-31M Matte Black P300460-191 Brushed Gold 29" W., 7.5" ht. 4 medium base, 60w max.







P300459-009 Brushed Nickel **P300459-31M** Matte Black **P300459-191** Brushed Gold 20.87" W., 7.5" ht. 3 medium base, 60w max.







P300458-009 Brushed Nickel **P300458-31M** Matte Black **P300458-191** Brushed Gold 12.87" W., 7.5" ht. 2 medium base, 60w max.







P300457-009 Brushed Nickel **P300457-31M** Matte Black **P300457-191** Brushed Gold 4.75" W., 7.5" ht., 6.25" D. 1 medium base, 60w max.









Elegantly extended, the Vertex Collection is composed of angular forms and etched glass shades to create a bold design that perfectly complements modern interiors.

FINISHES



009 Brushed Nickel



Matte Black



Brushed Gold



P300462-191

P300464-009 Brushed Nickel **P300464-31M** Matte Black P300464-191 Brushed Gold 29" W., 7.5" ht. 4 medium base, 60w max.







P300463-009 Brushed Nickel **P300463-31M** Matte Black **P300463-191** Brushed Gold 20.87" W., 7.5" ht. 3 medium base, 60w max.







P300462-009 Brushed Nickel **P300462-31M** Matte Black **P300462-191** Brushed Gold 12.87" W., 7.5" ht. 2 medium base, 60w max.







P300461-009 Brushed Nickel **P300461-31M** Matte Black **P300461-191** Brushed Gold 4.75" W., 7.5" ht., 6.25" D. 1 medium base, 60w max.









Caisson

The Caisson Collection has a unique frame design inspired by mechanical fittings and artisan clear glass shades with an inwardly rolled rim.

FINISHES



009 Brushed Nickel



Graphite



P300347-143


P300348-009 Brushed Nickel **P300348-143** Graphite 31.87" W., 8.87" ht. 4 medium base, 60w max.





Caisson

P300347-009 Brushed Nickel **P300347-143** Graphite 23.25" W., 8.87" ht. 3 medium base, 60w max.











P300345-009 Brushed Nickel **P300345-143** Graphite 6" W., 9.12" ht., 7.5" D. 1 medium base, 60w max.

P300215-009 Brushed Nickel **P300215-143** Graphite 7.87" W., 14.75" ht., 10" D. 1 medium base, 60w max.











Conway

The Conway Collection has seaside charm, from a bell-shaped frame with a nautical air that pairs seeded glass with a hand painted wood-style accent.

FINISHES



009 Brushed Nickel



Matte Black



P300296-009

P300298-009 Brushed Nickel **P300298-031** Matte Black 33" W., 8.25" ht. 4 medium base, 100w max.





Conway

P300297-009 Brushed Nickel **P300297-031** Matte Black 24" W., 8.25" ht. 3 medium base, 100w max.

P300296-009 Brushed Nickel **P300296-031** Matte Black 15" W., 8.25" ht. 2 medium base, 100w max.









P300295-009 Brushed Nickel **P300295-031** Matte Black 6" W., 8.25" ht., 7" D. 1 medium base, 100w max.







Northlake

The nostalgic Northlake Collection combines classic design influences with nautical inspiration. The rounded diffuser and layered caps are reminiscent of floating buoys and weekends on a mountain lake.

FINISHES









P300435-31M

P300437-009 Brushed Nickel P300437-31M Matte Black **P300437-163** Vintage Brass 32.5" W., 8" ht. 4 medium base, 60w max.



Northlake

P300436-009 Brushed Nickel **P300436-31M** Matte Black **P300436-163** Vintage Brass 24" W., 8" ht. 3 medium base, 60w max.

P300435-009 Brushed Nickel **P300435-31M** Matte Black **P300435-163** Vintage Brass 15.5" W., 8" ht. 2 medium base, 60w max.













P300434-009 Brushed Nickel **P300434-31M** Matte Black **P300434-163** Vintage Brass 5.87" W., 8" ht., 7.5" D. 1 medium base, 60w max.









Singleton

The Singleton Collection has oversized warehouse shades fabricated from clear glass and vintageinspired metal fittings creating a timeless design.

FINISHES



009 Brushed Nickel



Matte Black



Vintage Brass



P300396-163

P300398-009 Brushed Nickel **P300398-31M** Matte Black **P300398-163** Vintage Brass 36" W., 8" ht. 4 medium base, 60w max.







Singleton

P300397-009 Brushed Nickel **P300397-31M** Matte Black **P300397-163** Vintage Brass 26.5" W., 8" ht. 3 medium base, 60w max.

P300396-009 Brushed Nickel **P300396-31M** Matte Black **P300396-163** Vintage Brass 17" W., 8" ht. 2 medium base, 60w max.













P300395-009 Brushed Nickel **P300395-31M** Matte Black **P300395-163** Vintage Brass 7.62" W., 8" ht., 9" D. 1 medium base, 60w max.









Hinton

Embrace stylish simplicity with Hinton, whose industrial demeanor is softened by clear seeded glass suspended from clean metal fittings. Installed over bathroom mirrors, the fixture provides effective task lighting and focused illumination.

FINISHES



009 Brushed Nickel



Matte Black



Vintage Brass



P300349-31M

P300351-009 Brushed Nickel **P300351-31M** Matte Black **P300351-163** Vintage Brass 33.5" W., 7.75" ht. 4 medium base, 60w max.







Hinton

P300350-009 Brushed Nickel **P300350-31M** Matte Black **P300350-163** Vintage Brass 24.5" W., 7.75" ht. 3 medium base, 60w max.







P300349-009 Brushed Nickel **P300349-31M** Matte Black **P300349-163** Vintage Brass 15.5" W., 7.75" ht. 2 medium base, 60w max.









Aiken

Delightful details pair with clear glass creating the charm of the Aiken Collection. Vintage-style caps top globes reminiscent of an apothecary bottle that has been repurposed for a new life as a light fixture.

FINISHES

009 Brushed Nickel



Vintage Brass



P300321-163

P300323-009 Brushed Nickel **P300323-163** Vintage Brass 32.25" W., 9.87" ht. 4 medium base, 60w max.





Aiken

P300322-009 Brushed Nickel **P300322-163** Vintage Brass 23.37" W., 9.87" ht. 3 medium base, 60w max.





P300321-009 Brushed Nickel **P300321-163** Vintage Brass 14.62" W., 9.87" ht. 2 medium base, 60w max.





P300320-009 Brushed Nickel **P300320-163** Vintage Brass 4.5" W., 9.87" ht., 7" D. 1 medium base, 60w max.







Preston

Preston features industrial inspired details paired with elegant opal glass for comfortable illumination. The decorative frame includes a softly curved metal support with authentically crafted hardware elements.

FINISHES

009 Brushed Nickel



Matte Black



Vintage Brass



P300427-163

P300429-009 Brushed Nickel **P300429-31M** Matte Black **P300429-163** Vintage Brass 30.5" W., 9" ht.

4 medium base, 100w max.







Preston

P300428-009 Brushed Nickel **P300428-31M** Matte Black **P300428-163** Vintage Brass 22.12" W., 9" ht. 3 medium base, 100w max.















P300426-009 Brushed Nickel **P300426-31M** Matte Black **P300426-163** Vintage Brass 5.75" W., 9" ht., 7.5" D. 1 medium base, 100w max.









Beckner

The Beckner Collection reflects mid-century and industrial design, with mechanical knobs and hooded lights. Its tactile appeal welcomes curiosity and adds depth to any space.

FINISHES

009 Brushed Nickel





P300423-31M

P300425-009 Brushed Nickel **P300425-31M** Matte Black 33.75" W., 8.37" ht. 4 medium base, 60w max.





Beckner

P300424-009 Brushed Nickel **P300424-31M** Matte Black 24.12" W., 8.37" ht. 3 medium base, 60w max.

P300423-009 Brushed Nickel **P300423-31M** Matte Black 14.62" W., 8.37" ht. 2 medium base, 60w max.









P300422-009 Brushed Nickel **P300422-31M** Matte Black 5" W., 8.62" ht., 6.37" D. 1 medium base, 60w max.









Gilmour

Stoic squared elements are the prevailing theme of Gilmour. Clear glass shades are paired with a smooth metal arm and backplate to create a classic look with modern sensibility.

FINISHES



009 Brushed Nickel



Matte Black



P300378-009

P300380-009 Brushed Nickel **P300380-31M** Matte Black 27.87" W., 7" ht. 4 medium base, 60w max.





Gilmour

P300379-009 Brushed Nickel **P300379-31M** Matte Black 20.12" W., 7" ht. 3 medium base, 60w max.

P300378-009 Brushed Nickel **P300378-31M** Matte Black 12.25" W., 7" ht. 2 medium base, 60w max.









P300377-009 Brushed Nickel **P300377-31M** Matte Black 4.5" W., 7" ht., 5.5" D. 1 medium base, 60w max.







Fessler

Distinctive mechanical details establish a nostalgic flair in the elegant Fessler collection. Opal glass shades deliver comfortable diffuse illumination.

FINISHES



009 Brushed Nickel



Matte Black



Vintage Brass



P300439-163

P300441-009 Brushed Nickel **P300441-31M** Matte Black **P300441-163** Vintage Brass 29.12" W., 9.12" ht. 4 medium base, 60w max.



Fessler

P300440-009 Brushed Nickel **P300440-31M** Matte Black **P300440-163** Vintage Brass 21.12" W., 9.12" ht. 3 medium base, 60w max.







P300439-009 Brushed Nickel **P300439-31M** Matte Black **P300439-163** Vintage Brass 13" W., 9.12" ht. 2 medium base, 60w max.







P300438-009 Brushed Nickel **P300438-31M** Matte Black **P300438-163** Vintage Brass 5" W., 9" ht., 7" D. 1 medium base, 60w max.









Bramlett

Graphite with Brushed Nickel accents and Gloss White with Polished Chrome accents.

FINISHES



009 Brushed Nickel



Polished Chrome



P300041-009

P300041-009 Brushed Nickel *P300041-015 Polished Chrome 24.25" W., 8.37" ht. 3 medium base, 100w max.



*P300040-009 Brushed Nickel P300040-015 Polished Chrome 15.12" W., 8.37" ht. 2 medium base, 100w max.



*P300203-009 Brushed Nickel P300203-015 Polished Chrome 33.37" W., 8.25" ht. 4 medium base, 100w max.



P300039-009 Brushed Nickel *P300039-015 Polished Chrome 6" W., 8.12" ht., 7.12" D. 1 medium base, 100w max.



*Shown in finish All fixtures:



Mast

Etched opal glass diffuser surrounded by clear outer shade.

FINISHES



009 Brushed Nickel



Antique Bronze



P300216-009

P300217-009 Brushed Nickel 24" W., 7.75" ht. 3 medium base, 100w max.



P300216-009 Brushed Nickel 13.87" W., 7.62" ht. 2 medium base, 100w max.



P300218-009 Brushed Nickel 33.87" W., 7.75" ht. 4 medium base, 100w max.



P710015-009 Brushed Nickel *P710015-020 Antique Bronze 5" W., 13" ht., 6.37" D. 1 medium base, 100w max.





Kene

Etched glass diffuser surrounded by clear outer shade.

FINISHES



009 Brushed Nickel



Graphite



P300121-143

*P300122-009 Brushed Nickel P300122-143 Graphite 23.37" W., 7.37" ht. 3 medium base, 75w max.



P300121-009 Brushed Nickel *P300121-143 Graphite 16.25" W., 7.37" ht. 2 medium base, 75w max.



P300123-009 Brushed Nickel *P300123-143 Graphite 30.75" W., 7.37" ht. 4 medium base, 75w max.



*P300120-009 Brushed Nickel **P300120-143** Graphite 4.75" W., 12.87" ht., 6.5" D. 1 medium base, 75w max.



All fixtures:



Anjoux

Clear water glass.

FINISHES



Antique Bronze



134 Silver Ridge



P300118-134

*P300118-020 Antique Bronze **P300118-134** Silver Ridge 23" W., 7.5" ht. 3 medium base, 100w max.



P300117-020 Antique Bronze *P300117-134 Silver Ridge 14" W., 7.5" ht. 2 medium base, 100w max.



P300119-020 Antique Bronze *P300119-134 Silver Ridge 32" W., 7.5" ht. 4 medium base, 100w max.



*P300116-020 Antique Bronze **P300116-134** Silver Ridge 5" W., 8.62" ht., 6.87" D. 1 medium base, 100w max.





Litchfield

Clear glass.

FINISH



015 Polished Chrome



P300138-015

P300139-015 Polished Chrome 24.37" W., 9.25" ht. 3 medium base, 60w max.



P300138-015 Polished Chrome 15.37" W., 9.25" ht. 2 medium base, 60w max.



P300140-015 Polished Chrome 33.37" W., 9.25" ht. 4 medium base, 60w max.



P300137-015 Polished Chrome 5" W., 9.25" ht., 7.37" D. 1 medium base, 60w max.



All fixtures:



Status

Etched white linen glass or 1-light sconce with Summer Linen fabric shade.

FINISH



Polished Chrome



P2775-15

P2776-15 Polished Chrome 23.75" W., 10.12" ht. 3 medium base, 100w max.





P2775-15 Polished Chrome 13.87" W., 10.12" ht. 2 medium base, 100w max.





P2777-15 Polished Chrome 33.87" W., 10.12" ht. 4 medium base, 100w max.





P2060-15 Polished Chrome 6" W., 15.5" ht., 7.37" D. 1 medium base, 75w max.



Ashford

Opal glass.

FINISHES



009 Brushed Nickel



015 Polished Chrome



P300315-009

*P300316-009 Brushed Nickel P300316-015 Polished Chrome 24" W., 10" ht. 3 medium base, 100w max.



P300315-009 Brushed Nickel *P300315-015 Polished Chrome 14.5" W., 10" ht. 2 medium base, 100w max.



P300317-009 Brushed Nickel *P300317-015 Polished Chrome 33.5" W., 10" ht. 4 medium base, 100w max.



*P300314-009 Brushed Nickel P300314-015 Polished Chrome 5.37" W., 10" ht., 8" D. 1 medium base, 100w max.





Ambrose

Clear glass.

FINISHES



015 Polished Chrome



Matte Black



P300374-31M

P300375-015 Polished Chrome ***P300375-31M** Matte Black 21" W., 7.88" ht. 3 medium base, 60w max.



*P300374-015 Polished Chrome P300374-31M Matte Black 13" W., 7.88" ht. 2 medium base, 60w max.



*P300376-015 Polished Chrome P300376-31M Matte Black 29" W., 7.88" ht. 4 medium base, 60w max.



P300373-015 Polished Chrome ***P300373-31M** Matte Black 5" W., 7.88" ht., 6.5" D. 1 medium base, 60w max.





Lynzie

A clean, crisp design serves as the cornerstone for the Lynzie Collection. Elegant, etched opal glass shades affix to smooth, simple bars. A beautiful oval backplate serves as the foundation for each design.

FINISHES



Polished Chrome



Matte Black



Brushed Gold



P2802-191

P2804-015 Polished Chrome **P2804-31M** Matte Black **P28041-191** Brushed Gold 33.25" W., 11.12" ht. 4 medium base, 100w max.



All fixtures:



Lynzie

P2803-015 Polished Chrome P2803-31M Matte Black **P2803-191** Brushed Gold 23.87" W., 11.12" ht. 3 medium base, 100w max.









P2802-015 Polished Chrome





P2801-015 Polished Chrome P2801-31M Matte Black P2801-191 Brushed Gold 5.25" W., 10.5" ht., 5.62" D. 1 medium base, 100w max.







All fixtures:



Dalton

Polished Chrome finish with Coastal Blue shade and Vintage Brass finish with Matte Black shade.

FINISHES



Polished Chrome



Vintage Brass



P300382-163

P300383-015 Polished Chrome ***P300383-163** Vintage Brass 24" W., 9" ht. 3 medium base, 100w max.



*P300382-015 Polished Chrome P300382-163 Vintage Brass 14.75" W., 9" ht. 2 medium base, 100w max.



*P300384-015 Polished Chrome P300384-163 Vintage Brass 33" W., 9" ht. 4 medium base, 100w max.



P300381-015 Polished Chrome ***P300381-163** Vintage Brass 5.5" W., 9" ht., 7.37" D. 1 medium base, 100w max.





Axle

Brushed Nickle with a black gooseneck and Antique Bronze with a Satin Brass accents.

FINISHES

009 Brushed Nickel



Antique Bronze



P300189-009

P300191-009 Brushed Nickel **P300191-020** Antique Bronze 24" W., 6.75" ht. 3 medium base, 60w max.





P300189-009 Brushed Nickel **P300189-020** Antique Bronze 6.13" W., 6.75" ht., 7" D. 1 medium base, 60w max.





All fixtures:



Rushton

Clear glass. Brushed Nickel with Black accents or Graphite with Antique Brass accents.

FINISHES





Graphite



P300227-143

*P300228-009 Brushed Nickel P300228-143 Graphite 24" W., 9.5" ht. 3 medium base, 60w max.



P300227-009 Brushed Nickel ***P300227-143** Graphite 16" W., 9.5" ht. 2 medium base, 60w max.



P300229-009 Brushed Nickel ***P300229-143** Graphite 32" W., 9.5" ht. 4 medium base, 60w max.



*P300226-009 Brushed Nickel P300226-143 Graphite 5" W., 9.5" ht., 6" D. 1 medium base, 60w max.





Calhoun

Clear glass.

FINISHES









P300046-163

*P300047-009 Brushed Nickel P300047-020 Antique Bronze P300047-163 Vintage Brass 21.62" W., 8.62" ht. 3 medium base, 100w max.



P300046-009 Brushed Nickel ***P300046-020** Antique Bronze **P300046-163** Vintage Brass 13.25" W., 8.62" ht. 2 medium base, 100w max.



P300048-009 Brushed Nickel **P300048-020** Antique Bronze ***P300048-163** Vintage Brass 30.25" W., 8.62" ht. 4 medium base, 100w max.



*P300045-009 Brushed Nickel P300045-020 Antique Bronze P300045-163 Vintage Brass 5" W., 8.62" ht., 6.87" D. 1 medium base, 100w max.





Judson

Clear glass.

FINISHES



P300082-104

*P300082-020 Antique Bronze P300082-104 Polished Nickel 26" W., 11.25" ht. 3 medium base, 75w max.



P300081-020 Antique Bronze ***P300081-104** Polished Nickel 16.25" W., 11.25" ht. 2 medium base, 75w max.



P300083-020 Antique Bronze ***P300083-104** Polished Nickel 35.75" W., 11.25" ht. 4 medium base, 75w max.



*P300080-020 Antique Bronze P300080-104 Polished Nickel 6.5" W., 11.25" ht., 8.5" D. 1 medium base, 75w max.





Archie

Clear double prismatic glass.

FINISHES











P2991-74

P2992-15 Polished Chrome **P2992-74** Venetian Bronze **P2992-81** Antique Nickel ***P2992-163** Vintage Brass 26.25" W., 8.75" ht. 3 medium base, 100w max.



*P2991-15 Polished Chrome P2991-74 Venetian Bronze P2991-81 Antique Nickel P2991-163 Vintage Brass 17" W., 8.75" ht. 2 medium base, 100w max.



P2997-15 Polished Chrome **P2997-74** Venetian Bronze ***P2997-81** Antique Nickel **P2997-163** Vintage Brass 35.5" W., 8.75" ht. 4 medium base, 100w max.



P2989-15 Polished Chrome ***P2989-74** Venetian Bronze **P2989-81** Antique Nickel **P2989-163** Vintage Brass 5.75" W., 8.25" ht., 7.25" D. 1 medium base, 100w max.





Hansford

Clear glass. Polished Nickel, Vintage Brass or Antique Bronze with Vintage Brass accents.



P300051-020

P300051-020 Antique Bronze **P300051-104** Polished Nickel ***P300051-163** Vintage Brass 24.5" W., 10.87" ht. 3 medium base, 100w max.



P300050-020 Antique Bronze ***P300050-104** Polished Nickel **P300050-163** Vintage Brass 15.5" W., 10.87" ht. 2 medium base, 100w max.



*P300052-020 Antique Bronze P300052-104 Polished Nickel P300052-163 Vintage Brass 33.5" W., 10.87" ht. 4 medium base, 100w max.



P300049-020 Antique Bronze **P300049-104** Polished Nickel ***P300049-163** Vintage Brass 6.5" W., 9.5" ht., 7.25" D. 1 medium base, 100w max.





Briarwood

Antique Bronze with faux painted oak or Graphite with faux painted white-washed wood.

FINISHES



Antique Bronze



Graphite



P300230-143

P300231-020 Antique Bronze *P300231-143 Graphite 24.75" W., 8.25" ht. 3 medium base, 60w max.



*P300230-020 Antique Bronze **P300230-143** Graphite 14.75" W., 8.25" ht. 2 medium base, 60w max.



*P300232-020 Antique Bronze **P300232-143** Graphite 34.75" W., 8.25" ht. 4 medium base, 60w max.



*Shown in finish All fixtures:





P710012-020 Antique Bronze

*P710012-143 Graphite

6.87" W., 12" ht., 6" D.

1 medium base, 100w max.





Barnes Mill

Clear seeded glass. Antique Bronze finish with faux-painted wooden plank.

FINISH



020 Antique Bronze



P300068-020

P300068-020 Antique Bronze 24" W., 8" ht. 3 medium base, 100w max.



P300067-020 Antique Bronze 13.37" W., 8" ht. 2 medium base, 100w max.



P300069-020 Antique Bronze 32.25" W., 8" ht. 4 medium base, 100w max.



P300066-020 Antique Bronze 4.5" W., 11.87" ht., 5.87" D. 1 medium base, 100w max.



All fixtures:



Gulliver

Clear seeded glass. Galvanized finish with painted faux Antique White wood and Graphite with painted faux Weathered Driftwood.

FINISHES



141 Galvanized Finish



Graphite



P300124-141

P300125-141 Galvanized *P300125-143 Graphite 24" W., 8.5" ht. 3 medium base, 60w max.



*P300124-141 Galvanized P300124-143 Graphite 15.5" W., 8.5" ht. 2 medium base, 60w max.



*P300126-141 Galvanized P300126-143 Graphite 32.87" W., 8.5" ht. 4 medium base, 60w max.



*Shown in finish All fixtures:



P710031-141 Galvanized *P710031-143 Graphite 6" W., 12" ht., 7" D. 1 medium base, 75w max.





Winslett

Clear seeded glass.

FINISHES



009 Brushed Nickel



Matte Black



P300273-009

P300274-009 Brushed Nickel *P300274-031 Matte Black 23.75" W., 7.25" ht. 3 medium base, 60w max.



*P300273-009 Brushed Nickel P300273-031 Matte Black 14.25" W., 7.25" ht. 2 medium base, 60w max.



*P300275-009 Brushed Nickel P300275-031 Matte Black 33.25" W., 7.25" ht. 4 medium base, 60w max.



P300272-009 Brushed Nickel *P300272-031 Matte Black 4.75" W., 9.5" ht., 6.75" D. 1 medium base, 60w max.





Bowman

Clear chiseled glass.

FINISH



031 Matte Black



P300254-031


P300255-031 Matte Black 25" W., 7.75" ht. 3 medium base, 60w max.



P300254-031 Matte Black 16.37" W., 7.75" ht. 2 medium base, 60w max.



P300256-031 Matte Black 33.62" W., 7.75" ht. 4 medium base, 60w max.







All fixtures:



Cofield

Clear or etched white glass.

FINISHES











P710116-015





Archives

Clear glass.

FINISHES







P2809-20

P2809-20 Antique Bronze **P2809-81** Antique Nickel 18.5" W., 4.75" ht., 7" D. 2 medium base, 100w max.







shown vertical





P7156-20 Antique Bronze **P7156-81** Antique Nickel 9" W., 7" ht., 10" D. 1 medium base, 100w max.





Goodwin

Clear glass.



009 Brushed Nickel



Polished Chrome



Matte Black

*P300386-009 Brushed Nickel P300386-015 Polished Chrome P300386-31M Matte Black 4.5" W., 8.37" ht., 5" D. 1 medium base, 60w max.



P300387-009 Brushed Nickel ***P300387-015** Polished Chrome **P300387-31M** Matte Black 12.87" W., 8.25" ht. 2 medium base, 60w max.



P300388-009 Brushed Nickel **P300388-015** Polished Chrome ***P300388-31M** Matte Black 21" W., 8.25" ht. 3 medium base, 60w max.



*P300389-009 Brushed Nickel P300389-015 Polished Chrome P300389-31M Matte Black 29.25" W., 8.25" ht. 4 medium base, 60w max.



*Shown in finish All fixtures:



Riley

Clear glass.



009 Brushed Nickel



031 Matte Black

***P710082-009** Brushed Nickel **P710082-031** Matte Black 5" W., 14.5" ht., 4.62" D. 1 candelabra base, 60w max.



P300277-009 Brushed Nickel ***P300277-031** Matte Black 16.12" W., 8.25" ht. 2 medium base, 60w max.





P300278-009 Brushed Nickel ***P300278-031** Matte Black 25.25" W., 8.25" ht. 3 medium base, 60w max.





*P300279-009 Brushed Nickel P300279-031 Matte Black 34.37" W., 8.25" ht. 4 medium base, 60w max.









League

Etched white glass.



31

Matte Black

P300341-009 Brushed Nickel ***P300341-31M** Matte Black 4.5" W., 8" ht., 5.5" D. 1 medium base, 100w max.



*P300342-009 Brushed Nickel P300342-31M Matte Black 13.62" W., 7.62" ht. 1 medium base, 100w max.



*P300343-009 Brushed Nickel P300343-31M Matte Black 23" W., 7.62" ht. 3 medium base, 100w max.



P300344-009 Brushed Nickel ***P300344-31M** Matte Black 32.5" W., 7.62" ht. 4 medium base, 100w max.



*Shown in finish . All fixtures:



009 Brushed Nickel





Clifton Heights

*P300158-009 Brushed Nickel

P300158-020 Antique Bronze **P300158-31M** Matte Black 5.5" W., 8.37" ht., 7.12" D. 1 medium base, 100w max.



P300159-009 Brushed Nickel ***P300159-020** Antique Bronze **P300159-31M** Matte Black 14.25" W., 8.37" ht. 2 medium base, 100w max.

Etched glass.



P300160-009 Brushed Nickel **P300160-020** Antique Bronze ***P300160-31M** Matte Black 23" W., 8.37" ht. 3 medium base, 100w max.



*P300161-009 Brushed Nickel P300161-020 Antique Bronze P300161-31M Matte Black 31.87" W., 8.37" ht. 4 medium base, 100w max.





Cascadia

Etched glass.

Polished Chrome

Antique Bronze

*P2146-15 Polished Chrome P2146-20 Antique Bronze 5.87" W., 8" ht., 6.5" D. 1 medium base, 100w max.



P2147-15 Polished Chrome ***P2147-20** Antique Bronze 16" W., 8" ht. 2 medium base, 100w max.



P2148-15 Polished Chrome *P2148-20 Antique Bronze 24.12" W., 8" ht. 3 medium base, 100w max.



*P2149-15 Polished Chrome P2149-20 Antique Bronze 32" W., 8" ht. 4 medium base, 100w max.



*Shown in finish All fixtures:



Appeal

Etched opal glass.



09 Brushed Nickel



Polished Chrome

*P2700-09 Brushed Nickel P2700-15 Polished Chrome 5.62" W., 6.25" ht., 7.25" D. 1 medium base, 100w max.



P2701-09 Brushed Nickel *P2701-15 Polished Chrome 14.62" W., 6.25" ht. 2 medium base, 100w max.



P2702-09 Brushed Nickel *P2702-15 Polished Chrome 24" W., 6.25" ht. 3 medium base, 100w max.



*P2703-09 Brushed Nickel P2703-15 Polished Chrome 33.5" W., 6.25" ht. 4 medium base, 100w max.





Fleet

Etched opal glass.

09

09 Brushed Nickel



Polished Chrome

*P2165-09 Brushed Nickel P2165-15 Polished Chrome 5.25" W., 7.25" ht., 6.5" D. 1 medium base, 100w max.



P2166-09 Brushed Nickel ***P2166-15** Polished Chrome 14.12" W., 7.18" ht. 2 medium base, 100w max.



P2167-09 Brushed Nickel ***P2167-15** Polished Chrome 23" W., 7.18" ht. 3 medium base, 100w max.



*P2168-09 Brushed Nickel P2168-15 Polished Chrome 32" W., 7.18" ht. 4 medium base, 100w max.



*Shown in finish All fixtures:





Etched glass.



009 Brushed Nickel



Antique Bronze

P300131-009 Brushed Nickel ***P300131-020** Antique Bronze 5" W., 8.12" ht., 6.12" D. 1 medium base, 100w max.



*P300132-009 Brushed Nickel P300132-020 Antique Bronze 13.87" W., 8.37" ht. 2 medium base, 100w max.



*P300133-009 Brushed Nickel P300133-020 Antique Bronze 22.87" W., 8.37" ht. 3 medium base, 100w max.



P300134-009 Brushed Nickel ***P300134-020** Antique Bronze 31.75" W., 8.37" ht. 4 medium base, 100w max.





Alexa

Brushed Nickel with etched white linen glass and Antique Bronze with etched umber linen glass.



09 Brushed Nickel



Antique Bronze

*P2959-09 Brushed Nickel P2959-20 Antique Bronze 4.5" W., 9.37" ht., 6.12" D. 1 medium base, 100w max.



P2977-09 Brushed Nickel *P2977-20 Antique Bronze 13" W., 9.5" ht. 2 medium base, 100w max.



P2978-09 Brushed Nickel *P2978-20 Antique Bronze 22" W., 9.43" ht. 3 medium base, 100w max.



*P2998-09 Brushed Nickel P2998-20 Antique Bronze 31" W., 9.43" ht. 4 medium base, 100w max.



*Shown in finish All fixtures:



Wisten

Etched glass.



Brushed Nickel

P2794-09 Brushed Nickel 4.5" W., 8.37" ht., 6.25" D. 1 medium base, 100w max.



P2795-09 Brushed Nickel 12.5" W., 8.25" ht. 2 medium base, 100w max.



P2796-09 Brushed Nickel 21" W., 8.25" ht. 3 medium base, 100w max.



P2797-09 Brushed Nickel 29.5" W., 8.25" ht. 4 medium base, 100w max.







Etched glass.

009 Brushed Nickel



Polished Chrome



031 Matte Black

P300327-009 Brushed Nickel P300327-015 Polished Chrome *P300327-031 Matte Black 4.38" W., 8.25" ht., 5.75" D. 1 medium base, 100w max.



*P300328-009 Brushed Nickel P300328-015 Polished Chrome P300328-031 Matte Black 12" W., 8.25" ht. 2 medium base, 100w max.



P300329-009 Brushed Nickel *P300329-015 Polished Chrome P300329-031 Matte Black 24" W., 8.25" ht. 3 medium base, 100w max.



P300330-009 Brushed Nickel P300330-015 Polished Chrome *P300330-031 Matte Black 30" W., 8.25" ht. 4 medium base, 100w max.



*P300421-009 Brushed Nickel P300421-015 Polished Chrome **P300421-031** Matte Black 48" W., 8.25" ht. 6 medium base, 100w max.







Bravo

Etched glass.



09 Brushed Nickel



Antique Bronze

P2004-09 Brushed Nickel ***P2004-20W** Antique Bronze 7.25" W., 9" ht., 8.75" D. 1 medium base, 100w max.



*P2005-09 Brushed Nickel P2005-20W Antique Bronze 17" W., 8.5" ht. 2 medium base, 100w max.



*P2006-09 Brushed Nickel P2006-20W Antique Bronze 26.75" W., 8.75" ht. 3 medium base, 100w max.







*P2016-09 Brushed Nickel P2016-20W Antique Bronze 46.25" W., 8.87" ht. 5 medium base, 100w max.







Inner etched glass and outer organza shade.

09 Brushed Nickel

P2041-09 Brushed Nickel 6.5" W., 11.5" ht., 8.25" D. 1 medium base, 100w max.



P2078-09 Brushed Nickel 14.5" W., 7.37" ht. 2 medium base, 100w max.



P2079-09 Brushed Nickel 23.5" W., 7.37" ht. 3 medium base, 100w max.



P2080-09 Brushed Nickel 32.5" W., 7.37" ht. 4 medium base, 100w max.



P2081-09 Brushed Nickel 41.5" W., 7.37" ht. 5 medium base, 100w max.





Trinity

Etched glass.



Brushed Nickel



Polished Chrome



Antique Bronze

P3190-09 Brushed Nickel **P3190-15** Polished Chrome ***P3190-20** Antique Bronze 6.5" W., 7.5" ht., 9" D. 1 medium base, 100w max.



P3191-09 Brushed Nickel ***P3191-15** Polished Chrome **P3191-20** Antique Bronze 17.25" W., 8.12" ht. 2 medium base, 100w max.



*P3192-09 Brushed Nickel P3192-15 Polished Chrome P3192-20 Antique Bronze 24" W., 8.12" ht. 3 medium base, 100w max.







*Shown in finish All fixtures:



Madison

Etched glass.



Brushed Nickel



Polished Chrome



Antique Bronze

P3161-09 Brushed Nickel **P3161-15** Polished Chrome ***P3161-20** Antique Bronze 7.62" W., 8" ht., 9.25" D. 1 medium base, 100w max.



*P3162-09 Brushed Nickel P3162-15 Polished Chrome P3162-20 Antique Bronze 17.5" W., 8" ht. 2 medium base, 100w max.



P3163-09 Brushed Nickel ***P3163-15** Polished Chrome **P3163-20** Antique Bronze 27.5" W., 8" ht. 3 medium base, 100w max.



P3164-09 Brushed Nickel **P3164-15** Polished Chrome ***P3163-20** Antique Bronze 37.5" W., 8" ht. 4 medium base, 100w max.





Inspire

Etched glass.

Brushed Nickel



Polished Chrome



Antique Bronze

*P2018-09 Brushed Nickel P2018-15 Polished Chrome P2018-20 Antique Bronze 4.62" W., 7.62" ht., 7.37" D. 1 medium base, 100w max.



P2019-09 Brushed Nickel P2019-15 Polished Chrome *P2019-20 Antique Bronze 15" W., 8.5" ht. 2 medium base, 100w max.



P2020-09 Brushed Nickel *P2020-15 Polished Chrome P2020-20 Antique Bronze 22.37" W., 8.18" ht. 3 medium base, 100w max.



*Shown in finish All fixtures:



*P2021-09 Brushed Nickel P2021-15 Polished Chrome P2021-20 Antique Bronze 31.37" W., 8.5" ht. 4 medium base, 100w max.



Carisa

Gloss white opal glass.



009 Brushed Nickel



Vintage Gold

P300084-009 Brushed Nickel *P300084-078 Vintage Gold 6.5" W., 10" ht., 8.5" D. 1 medium base, 75w max.



*P300085-009 Brushed Nickel **P300085-078** Vintage Gold 15.25" W., 10" ht. 2 medium base, 75w max.



*P300086-009 Brushed Nickel **P300086-078** Vintage Gold 25" W., 10" ht. 3 medium base, 75w max.



*Shown in finish



P300087-009 Brushed Nickel *P300087-078 Vintage Gold 32.75" W., 10" ht. 4 medium base, 75w max.



Replay

Etched white glass.





Textured Black



Antique Bronze



Polished Nickel

P2131-09 Brushed Nickel ***P2131-20** Antique Bronze **P2131-31** Textured Black **P2131-104** Polished Nickel 5.12" W., 9.75" ht., 5.87" D. 1 medium base, 100w max.



P2158-09 Brushed Nickel P2158-20 Antique Bronze P2158-31 Textured Black *P2158-104 Polished Nickel 13" W., 7.87" ht. 2 medium base, 100w max.



P2159-09 Brushed Nickel **P2159-20** Antique Bronze ***P2159-31** Textured Black **P2159-104** Polished Nickel 22" W., 7.87" ht. 3 medium base, 100w max.







*P300385-020 Antique Bronze P300385-009 Brushed Nickel P300385-031 Textured Black P300385-104 Polished Nickel 48" W., 7.62" ht. 6 medium base, 100w max.





Laird

Etched glass.





P300095-009 Brushed Nickel *P300095-020 Antique Bronze 5.75" W., 9" ht., 8" D. 1 medium base, 100w max.







*P300096-009 Brushed Nickel

*P300097-009 Brushed Nickel P300097-020 Antique Bronze 23.75" W., 8" ht. 3 medium base, 100w max.

P300098-009 Brushed Nickel *P300098-020 Antique Bronze 33" W., 8.25" ht. 4 medium base, 100w max.





*P300099-009 Brushed Nickel P300099-020 Antique Bronze 41.62" W., 8" ht. 5 medium base, 100w max.







Victorian

Gloss white opal glass.



09 Brushed Nickel



Polished Chrome



Venetian Bronze

P3027-09 Brushed Nickel ***P3027-15** Polished Chrome **P3027-74** Venetian Bronze 5.62" W., 8.75" ht., 7.25" D. 1 medium base, 100w max.



P3028-09 Brushed Nickel **P3028-15** Polished Chrome ***P3028-74** Venetian Bronze 16.62" W., 8.75" ht. 2 medium base, 100w max.



P3029-09 Brushed Nickel **P3029-15** Polished Chrome ***P3028-74** Venetian Bronze 24.5" W., 8.75" ht. 3 medium base, 100w max.



*P3041-09 Brushed Nickel P3041-15 Polished Chrome P3041-74 Venetian Bronze 32.5" W., 8.62" ht. 4 medium base, 100w max.



*Shown in finish

All fixtures:



Adorn

Etched white glass.



Brushed Nickel



Polished Chrome



Antique Bronze

P2008-09 Brushed Nickel ***P2008-15** Polished Chrome **P2008-20W** Antique Bronze 5.25" W., 6.75" ht., 7" D. 1 medium base, 100w max.



P2009-09 Brushed Nickel **P2009-15** Polished Chrome ***P2009-20W** Antique Bronze 13.25" W., 6.62" ht. 2 medium base, 100w max.



P2010-09 Brushed Nickel P2010-15 Polished Chrome *P2010-20W Antique Bronze 21.5" W., 6.62" ht. 3 medium base, 100w max.



*P2011-09 Brushed Nickel P2011-15 Polished Chrome P2011-20W Antique Bronze 28.25" W., 6.62" ht. 4 medium base, 100w max.







Etched white glass.



09 Brushed Nickel



Antique Bronze

P2000-09 Brushed Nickel ***P2000-20W** Antique Bronze 6" W., 9.5" ht., 7" D. 1 medium base, 100w max.



*P2001-09 Brushed Nickel P2001-20W Antique Bronze 14" W., 7.62" ht. 2 medium base, 100w max.



*P2002-09 Brushed Nickel P2002-20W Antique Bronze 22" W., 7.62" ht. 3 medium base, 100w max.



*Shown in finish All fixtures:



P2003-09 Brushed Nickel ***P2003-20W** Antique Bronze 30" W., 7.62" ht. 4 medium base, 100w max.



Heart

Etched glass.



Brushed Nickel



Polished Chrome



Antique Bronze

*P2913-09 Brushed Nickel P2913-15 Polished Chrome P2913-20 Antique Bronze 5.75" W., 9" ht., 8" D. 1 medium base, 100w max.



P2915-09 Brushed Nickel **P2915-15** Polished Chrome ***P2915-20** Antique Bronze 13.68" W., 8.25" ht. 2 medium base, 100w max.



P2919-09 Brushed Nickel **P2919-15** Polished Chrome ***P2919-20** Antique Bronze 21.62" W., 8.25" ht. 3 medium base, 100w max.



*Shown in finish All fixtures:



P2928-09 Brushed Nickel ***P2928-15** Polished Chrome **P2928-20** Antique Bronze 29.87" W., 8.25" ht. 4 medium base, 100w max.



Classic

Etched glass.



009 Brushed Nickel



Matte Black

P300233-009 Brushed Nickel ***P300233-031** Matte Black 5" W., 8" ht., 7" D. 1 medium base, 100w max.



*P300234-009 Brushed Nickel P300234-031 Matte Black 13" W., 7.87" ht. 2 medium base, 100w max.



*P300235-009 Brushed Nickel P300235-031 Matte Black 24" W., 7.87" ht. 3 medium base, 100w max.



P300236-009 Brushed Nickel ***P300236-031** Matte Black 30" W., 7.87" ht. 4 medium base, 100w max.



P300237-009 Brushed Nickel ***P300237-031** Matte Black 36" W., 7.87" ht. 5 medium base, 100w max.



*P300238-009 Brushed Nickel P300238-031 Matte Black 48" W., 7.87" ht. 6 medium base, 100w max.



*Shown in finish All fixtures:



Gather

Etched glass.

09

Brushed Nickel



Polished Chrome



Antique Bronze

*P2706-09 Brushed Nickel P2706-15 Polished Chrome P2706-20 Antique Bronze 5" W., 7.5" ht., 6.5" D. 1 medium base, 100w max.



P2707-09 Brushed Nickel **P2707-15** Polished Chrome ***P2707-20** Antique Bronze 12" W., 7.5" ht. 2 medium base, 100w max.



P2708-09 Brushed Nickel **P2708-15** Polished Chrome ***P2708-20** Antique Bronze 24" W., 7.5" ht. 3 medium base, 100w max.



P2709-09 Brushed Nickel ***P2709-15** Polished Chrome **P2709-20** Antique Bronze 30" W., 7.5" ht. 4 medium base, 100w max.



*P2713-09 Brushed Nickel P2713-15 Polished Chrome P2713-20 Antique Bronze 36" W., 7.5" ht. 5 medium base, 100w max.



P2714-09 Brushed Nickel **P2714-15** Polished Chrome ***P2714-20** Antique Bronze 48" W., 7.5" ht. 6 medium base, 100w max.



*Shown in finish *All fixtures:*





Alabaster glass.

09 Brushed Nickel

P3267-09 Brushed Nickel 18" W., 7" ht. 2 medium base, 100w max.



P3268-09 Brushed Nickel 24.75" W., 7" ht. 3 medium base, 100w max.



P3269-09 Brushed Nickel 36" W., 7" ht. 4 medium base, 100w max.



*Shown in finish All fixtures:



Channel Glass

White glass.



White

P3813-30 White 4.25" W., 7.5" ht., 4.25" D. 1 medium base, 100w max.



P3111-30 White 14" W., 4.5" ht. 2 medium base, 75w max.



P3110-30 White 24" W., 4.25" ht. 4 medium base, 75w max.



Clear Fluted Glass



Brushed Nickel



Polished Chrome

*P3287-09 Brushed Nickel P3287-15 Polished Chrome 4.87" W., 8.25" ht., 8" D. 1 medium base, 100w max.



P3288-09 Brushed Nickel ***P3288-15** Polished Chrome 11.75" W., 8.31" ht. 2 medium base, 100w max.



P3289-09 Brushed Nickel **P3289-15** Polished Chrome 16.12" W., 8.43" ht. 3 medium base, 100w max.





*Shown in finish All fixtures:



Etched Fluted Glass



Brushed Nickel



Polished Chrome

P3287-09ET Brushed Nickel ***P3287-15ET** Polished Chrome 4.87" W., 8.25" ht., 8" D. 1 medium base, 100w max.



*P3288-09ET Brushed Nickel P3288-15ET Polished Chrome 11.75" W., 8.31" ht. 2 medium base, 100w max.



P3289-09ET Brushed Nickel **P3289-15ET** Polished Chrome 16.12" W., 8.43" ht. 3 medium base, 100w max.





*Shown in finish All fixtures:



Clear Glass



009 Brushed Nickel



Matte Black

P300390-009 Brushed Nickel ***P300390-31M** Matte Black 18" W., 8.37" ht. 2 medium base, 60w max.



*P300391-009 Brushed Nickel P300391-31M Matte Black 24" W., 8.37" ht. 3 medium base, 60w max.



P300392-009 Brushed Nickel ***P300392-31M** Matte Black 30" W., 8.37" ht. 4 medium base, 60w max.



P300393-009 Brushed Nickel ***P300393-31M** Matte Black 36" W., 8.37" ht. 5 medium base, 60w max.



*P300394-009 Brushed Nickel P300394-31M Matte Black 48" W., 8.37" ht. 6 medium base, 60w max.



*Shown in finish

All fixtures:



Alabaster Glass



Brushed Nickel

P3051-09 Brushed Nickel 5.25" W., 9" ht., 7.37" D. 1 medium base, 100w max.



P3052-09 Brushed Nickel 18" W., 7.25" ht. 2 medium base, 100w max.



P3053-09 Brushed Nickel 24" W., 7.25" ht. 3 medium base, 100w max.



P3054-09 Brushed Nickel 30" W., 7.25" ht. 4 medium base, 100w max.



P3055-09 Brushed Nickel 36" W., 7.25" ht. 5 medium base, 100w max.



P3056-09 Brushed Nickel 48" W., 7.25" ht. 6 medium base, 100w max.



All fixtures:



Deluxe Broadway



P3333-15 Polished Chrome 18" W., 4.25" ht. 3 medium base, 60w max.



P3298-15 Polished Chrome 24" W., 4.25" ht. 4 medium base, 60w max.



P3335-15 Polished Chrome 30" W., 4.25" ht. 5 medium base, 60w max.



P3299-15 Polished Chrome 36" W., 4.25" ht. 6 medium base, 60w max.



P3300-15 Polished Chrome 48" W., 4.25" ht. 8 medium base, 60w max.



All fixtures:



Racetrack Broadway



P3025-09 Brushed Nickel 24" W., 4.75" ht. 4 medium base, 60w max.





P3026-09 Brushed Nickel 36" W., 4.75" ht. 6 medium base, 60w max.



Economy Broadway



P3114-15 Polished Chrome 24" W., 4.25" ht. 3 medium base, 60w max.



P3115-15 Polished Chrome 30" W., 4.25" ht. 4 medium base, 60w max.



P3116-15 Polished Chrome 36" W., 4.25" ht. 5 medium base, 60w max.



P3117-15 Polished Chrome 48" W., 4.25" ht. 6 medium base, 60w max.



P3118-15 Polished Chrome 60" W., 4.25" ht. 8 medium base, 60w max.











Outdoor

DISCOVER THE LATEST







STYLE YOUR ROOM

Find inspiration for your next project on **progresslighting.com**

Modern design elements are reinvented as sleek outdoor lighting pieces with strong geometric lines and airy open frames. The Stallworth Collection is a contemporary take on classic lantern styling using angular lines and a Dark Sky Friendly cylindrical metal shade to project a wash of warm downlight.





Outdoor collections with Progress Lighting **DURASHIELD** are built to last. High performance materials hold up in all conditions and resists rust and corrosion and fading. Look for the DURASHIELD icon in this Outdoor section.

GRANDBURY

GABLES

BENTON HARBOR

p. 632












2 Quick selection

Use the **Product Finder**, page 72, to quickly see all outdoor fixtures offered in this catalog.







Design Series offers more elevated

DESIGN+SERIES







Swansea

P550129-31M Matte Black 36" W., 11" ht. 4 medium base, 60w max.









P550131-031

P550131-031 Textured Black 18.12" sq., 22.12" ht. 4 candelabra base, 60w max.



Brenham

The Brenham Collection offers a true farmhouse feel with its mixed elements design. Wood accent rings bookend the top and bottom of each fixture as a black metal frame with simple metal bars and ribbon-like metal arms reach down from a central metal link chain. This collection is perfect for illuminating a covered patio during a warm summer evening.

FINISH



031 Matte Black



P500235-031

P500235-031 Matte Black 16" dia., 20.62" H 3 candelabra base, 60w max.



P500234-031 Matte Black 10" dia., 15" H 1 medium base, 100w max.





P550111-31M



Navarre

Navarre has a contemporary angular silhouette defined by nested rectangular cubes and shimmering seeded glass panels that cast a pleasing glow.

FINISH



031 Matte Black



P550089-031

P550089-031 Matte Black 10" W., 28.62" ht. 1 medium base, 60w max.



P350256-31M Matte Black 19.87" sq., 12" ht. 1 medium base, 60w max.





P550126-31M





Manteo

Manteo features a densely woven, doubleshade design that infuses outdoor spaces with a rugged style.

FINISH

(151)

Cottage White



P550084-151

P550084-151 Cottage White 12" dia., 16.62" ht. 1 medium base, 100w max.



Pawley

Pawley has a graceful, lattice-like design with a lovely, hand-applied finish. The woven structure comfortably diffuses light through etched glass.

FINISHES



031 Matte Black



Galvanized



P550083-031

P550083-031 Matte Black 12" dia., 16" ht. 1 medium base, 100w max.



P550083-141 Galvanized 12" dia., 16" ht. 1 medium base, 100w max.



Grandbury

The Grandbury Collection has a beautiful square frame featuring a half loop on top of the structure and is accented by clear glass panes. Made with **DURASHIELD**.

FINISHES



Antique Bronze



Textured Black



P560176-031

P550064-020 Antique Bronze **P550064-031** Textured Black 7" sq., 15.37" ht. 1 medium base, 75w max.





P540064-020 Antique Bronze **P540064-031** Textured Black 7" sq., 15.62" ht. 1 medium base, 75w max. Fits 3" post (sold separately)





All fixtures:



Grandbury

P560174-020 Antique Bronze **P560174-031** Textured Black 5.5" W., 11.87" ht. 1 medium base, 60w max.





P560175-020 Antique Bronze **P560175-031** Textured Black 7.12" W., 13.62" ht. 1 medium base, 75w max.





P560176-020 Antique Bronze **P560176-031** Textured Black 9" W., 17.12" ht. 2 medium base, 60w max.









Gables

Curves soften the frame of the Gables Collection, creating a distinctive silhouette. A clear glass diffuser enhances the classic design. Made with **DURASHIELD**.

FINISHES



020 Antique Bronze



Satin White



P560088-028

P550050-020 Antique Bronze P550050-028 Satin White 7.5" dia., 14.12" ht. 1 medium base, 75w max.







Gables

P560087-020 Antique Bronze **P560087-028** Satin White 5.87" W., 11.37" ht. 1 medium base, 60w max.





P560088-020 Antique Bronze **P560088-028** Satin White 7.5" W., 14.12" ht. 1 medium base, 100w max.





P540033-020 Antique Bronze **P540033-028** Satin White 7.5" dia., 16.75" ht. 1 medium base, 75w max. Fits 3" post (sold separately)









OUTDOOR

Marquette

The Marquette Collection has traditional lantern frames holding a beautiful water glass shade to add charming character to the timeless design. Made with **DURASHIELD**.

FINISH



031 Textured Black



P560172-031

P560173-031 Textured Black 10.12" W., 18.62" ht. 1 medium base, 100w max.



P550062-031 Textured Black 8.62" sq., 15.12" ht. 1 medium base, 75w max.



P540062-031 Textured Black 8.62" sq., 18.62" ht. 1 medium base, 75w max. Fits 3" post (sold separately)



P560172-031 Textured Black 8.62" W., 16" ht. 1 medium base, 75w max.



P560171-031 Textured Black 7.12" W., 13" ht. 1 medium base, 60w max.



All fixtures:



Benton Harbor

The Benton Harbor Collection is expertly crafted with classic black frames with thin bars holding clear glass shades for a seaside-living vibe. Made with **DURASHIELD**.

FINISH



031 Textured Black



P560185-031

P560185-031 Textured Black 8.75" W., 13" ht. 1 medium base, 100w max.



P550065-031 Textured Black 8.75" dia., 13.25" ht. 1 medium base, 75w max.



P540065-031 Textured Black 9.12" dia., 16.37" ht. 1 medium base, 75w max. Fits 3" post (sold separately)



P560178-031 Textured Black 7.5" W., 11" ht. 1 medium base, 75w max.



P560177-031 Textured Black 6.25" W., 9.75" ht. 1 medium base, 60w max.







Cardiff

The Cardiff Collection has clear seeded glass panes resting in timeless, traditional frames that are corrosion resistant for excellent longevity. Made with **DURASHIELD**.

FINISH



031 Textured Black



P560166-031

P560166-031 Textured Black 7" W., 12.5" ht. 1 medium base, 60w max.



P560167-031 Textured Black 9" W., 16.5" ht. 1 medium base, 75w max.



P540039-031 Textured Black 9" sq., 20" ht. 1 medium base, 75w max. Fits 3" post (sold separately)



All fixtures:



Port Royal

The Port Royal Collection features a texture black frame with elongated, clear glass shades resting inside, adding to its modern flair. Made with **DURASHIELD**.

031 Textured Black

P550061-031 Textured Black 6.25" dia., 14" ht. 1 medium base, 60w max.



P560168-031 Textured Black 6.25" W., 12.5" ht. 1 medium base, 60w max.



All fixtures:



Seagrove

The Seagrove Collection features clear seeded glass panes and an x-brace design that adds an extra pinch of rustic character. Made with **DURASHIELD**.



P560164-031 Textured Black 7.5" W., 12.5" ht. 1 medium base, 60w max.





Birkdale

Birkdale features open geometric cage paired with a stately roof to lend robust style. The design minimizes glare and reduces light trespass.

FINISHES



Antique Bronze



Textured Black



P560316-031

P560316-020 Antique Bronze **P560316-031** Textured Black 5.75" W., 18.37" ht. 1 medium base, 100w max.





P560317-020 Antique Bronze **P560317-031** Textured Black 7" W., 23.25" ht. 1 medium base, 100w max.





All fixtures:



OUTDOOR

Walcott

Walcott lanterns combine a stately elegance with modern style. A distinctive vertical frame is glazed with clear glass panels to add vintage charm.

FINISHES



Antique Bronze



Textured Black



P560286-020

P560287-020 Antique Bronze **P560287-031** Textured Black 8.25" W., 20" ht. 1 medium base, 60w max.





P540090-020 Antique Bronze **P540090-031** Textured Black 8.25" W., 21.37" ht. 1 medium base, 60w max. Fits 3" post (sold separately)





P560286-020 Antique Bronze **P560286-031** Textured Black 7.12" W., 14" ht. 1 medium base, 60w max.





Ramsey

An elongated silhouette and clear glass panels create a distinctive design and adds modern sophistication to the Ramsey Collection.

FINISH




Textured Black



P560338-031

P550132-031 Textured Black 9" W., 21" ht.





P540104-031 Textured Black 9" W., 20.87" ht. 3 candelabra base, 60w max. Fits 3" post (sold separately)



P560337-031 Textured Black 6" W., 12.5" ht. 1 medium base, 100w max.



P560338-031 Textured Black 7.5" W., 15.5" ht. 2 candelabra base, 60w max.



P560339-031 Textured Black 9" W., 18.5" ht. 3 candelabra base,

60w max.



Exton

Architectural influences blend harmoniously in Exton, resulting in a modern design that works in both urban and suburban landscapes. Clean lines and geometric forms interact in its textured black frame, culminating in an iconic peaked roof. Exton brings bold design and visual unity to contemporary elevations.

FINISH

031 Textured Black



P560273-031

P540097-031 Textured Black 11.12" dia., 17.12" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P560273-031 Textured Black 9.12" W., 12" ht. 1 medium base, 100w max.



Chilton

The Chilton Collection presents a frosted glass cylinder suspended inside an open frame giving Chilton an airy form. and creating a modern impression.

FINISH



031 Textured Black



P560313-031

P560315-031 Textured Black 11" W., 21.62" ht.

1 medium base, 100w max.



P550120-031 Textured Black 11" sq., 17.5" ht. 1 medium base, 100w max.



P540120-031 Textured Black

11" sq., 21.12" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P560314-031 Textured Black 8.87" W., 17.75" ht. 1 medium base, 100w max.



P560313-031 Textured Black 7.5" W., 14.87" ht. 1 medium base, 60w max.



Irondale

Incorporate memorable, modern lighting with the Irondale collection. A matte black frame holds a clear glass shade that harbors an etched glass diffuser inside ready to provide a main door or foyer with a lovely, timeless ambiance.

FINISH



Matte Black



P560148-031

P560150-031 Matte Black 9" W., 18.5" ht. 1 medium base,

100w max.



P550054-031 Matte Black 9.5" dia., 18.5" ht. 1 medium base, 100w max.



P540054-031 Matte Black 9.5" dia., 20.5" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P560149-031 Matte Black 7.87" W., 15.5" ht. 1 medium base, 100w max.



P560148-031 Matte Black 6.5" W., 12" ht. 1 medium base, 100w max.



Arrive LED

Arrive LED lanterns feature a die-cast aluminum powder coated frame and heavily textured glass to create a unique visual effect.

FINISH



Textured Black



P6069-3130K9

P6069-3130K9 Textured Black 9" W., 13" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.



P6427-3130K9 Textured Black 9" sq., 15.87" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens. Fits 3" post (sold separately)



P6068-3130K9 Textured Black 7.5" W., 11.12" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



P6067-3130K9 Textured Black 6" W., 8.75" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.











Endorse LED

Endorse celebrates the traditional form of a gas-powered coach light with illumination from a modern LED source. A die-cast aluminum, powder coated frame creates an intriguing visual effect with clear beveled glass.

FINISH

31

Textured Black



P6058-3130K9

P6058-3130K9 Textured Black 10.75" W., 17.75" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



P6057-3130K9 Textured Black 8.75" W., 14.75" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



P6056-3130K9 Textured Black 6.75" W., 12" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.









Penfield

Reinvent exterior areas with smooth curves. Highlighted by clear glass exterior surrounding an opal glass interior diffuser. Aluminum and brass construction.

FINISH



108 Oil Rubbed Bronze



P5896-108

P5899-108 Oil Rubbed Bronze 8" W., 24" ht. 2 medium base, 100w max.



P5896-108 Oil Rubbed Bronze 8" W., 11.75" ht. 1 medium base, 100w max.



P5895-108 Oil Rubbed Bronze 6.5" W., 9.75" ht. 1 medium base, 100w max.



Unison

Crisp lines and sharp angles define the sleek silhouette of the Unison Collection. Their stately form holds etched, seeded glass diffusers that deliver a mellow glow, making a grand statement at a home's entrance.

FINISH



31M Matte Black



P560356-31M

P550141-31M Matte Black 7" sq., 19.37" ht. 1 medium base, 100w max.



P560357-31M Matte Black 7" W., 24" ht. 2 medium base, 60w max.



P560356-31M Matte Black 6" W., 18" ht. 2 medium base, 60w max.



Watch Hill

Watch Hill features an elongated design, highlighted by slender arms curving gracefully around a seeded glass shade. With design elements inspired by Victorian-era gaslight fittings, Watch Hill has a timeless style that complements a variety of home styles.

FINISH



Textured Black



P560255-031

P560257-031 Textured Black 8.5" W., 19.37" ht. 1 medium base, 60w max.



P550292-031 Textured Black 7.5" dia., 15.37" ht. 1 medium base, 60w max.



P540292-031 Textured Black 8.12" dia., 18.25" ht. 1 medium base, 60w max. Fits 3" post (sold separately)



P550110-031 Textured Black 8.5" dia., 11.62" ht. 1 medium base, 60w max.



P560255-031 Textured Black 6.12" W., 12.75" ht. 1 medium base, 60w max.



P560256-031 Textured Black 7.5" W., 17" ht. 1 medium base, 60w max.



Keegan

Redefine modern coastal style with the Keegan Collection, whose breezy silhouette takes a cue from a lighthouse. A ribbed glass, Fresnel-style shade is nestled within a protective wire frame, creating a beacon in the night.

FINISH



Matte Black



P560340-31M

P550134-31M Matte Black 13" dia., 9.62" ht. 1 medium base, 100w max.



P550133-31M Matte Black 9.75" dia., 8.65" ht. 1 medium base, 100w max.



P560340-31M Matte Black 7.25" W., 9.5" ht. 1 medium base, 100w max.



Parrish

Etched and clear glass panels.

FINISH



31M Matte Black



P560342-31M

P560343-31M Matte Black 8.37" W., 18" ht.

1 medium base, 60w max.



P550135-31M Matte Black 8.37" sq., 18" ht.



P540105-31M Matte Black 8.37" sq., 20.5" ht. 1 medium base, 60w max. Fits 3" post (sold separately)



P560342-31M Matte Black 6.5" W., 14" ht. 1 medium base, 60w max.



P560341-31M Matte Black 4.62" W., 10" ht. 1 medium base, 60w max.



P550136-31M Matte Black 11" sq., 4.62" ht. 2 medium base, 60w max.



Felton

Clear ribbed glass.

FINISH



031 Matte Black



P560131-031

P560131-031 Matte Black 7" W., 18.25" ht. 1 medium base, 100w max.



P550047-031 Matte Black 7" sq., 17.62" ht. 1 medium base, 100w max.



P540024-031 Matte Black 7.25" sq., 18.75" ht. 1 medium base, 100w max. Fits 3" post

(sold separately)



P560130-031 Matte Black 5.63" W., 15.38" ht. 1 medium base, 100w max.



P560129-031 Matte Black 4.5" W., 12.75" ht. 1 medium base, 100w max.



Endicott

Antique Bronze with umber linen glass or Black with clear seeded glass.

FINISHES



31 Textured Black



P5610-31

P5613-20 Antique Bronze ***P5613-31** Textured Black 8.87" W., 18" ht. 1 medium base, 100w max.



*P5500-20 Antique Bronze P5500-31 Textured Black 7.37" dia., 15.25" ht. 1 medium base, 100w max.



P5400-20 Antique Bronze *P5400-31 Textured Black 7.37" dia., 17.75" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



*P5610-20 Antique Bronze P5610-31 Textured Black 7.25" W., 14.25" ht. 1 medium base, 100w max.



P5605-20 Antique Bronze ***P5605-31** Textured Black 7.25" W., 10.5" ht. 1 medium base, 100w max.



Residence

Umber textured art glass.

FINISH



Antique Bronze



P6054-20

P6055-20 Antique Bronze 12" dia., 5" ht. 2 medium base, 75w max.



P6054-20 Antique Bronze 10" W., 15.31" ht. 1 medium base, 100w max.



P6452-20 Antique Bronze 8" sq., 15.68" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P6053-20 Antique Bronze 8" W., 12.18" ht. 1 medium base, 100w max.



P6052-20 Antique Bronze 6" W., 9.18" ht. 1 medium base, 100w max.







Boxwood

Clear seeded glass.

FINISH





P560112-020

P560112-020 Antique Bronze 9" W., 16.5" ht. 1 medium base, 60w max.



P550039-020 Antique Bronze 8.87" sq., 17.5" ht. 1 medium base, 60w max.



P540010-020 Antique Bronze 9" sq., 18.25" ht. 1 medium base, 60w max.



P560111-020 Antique Bronze 7.62" W., 14.12" ht. 1 medium base, 60w max.



P560110-020 Antique Bronze 6.25" W., 11.75" ht. 1 medium base, 60w max.



P550038-020 Antique Bronze 11.37" sq., 4.5" ht. 2 medium base, 60w max.



Whitmire

Clear seeded glass.

FINISH



31M Matte Black



P560282-31M

P560282-31M Matte Black 7.37" W., 14.5" ht. 1 medium base, 60w max.



P540094-31M Matte Black 7.37" dia., 15.63" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P560281-31M Matte Black 6.37" W., 13" ht. 1 medium base, 60w max.



P550109-31M Matte Black 7.37" dia., 8" ht. 1 medium base, 60w max.



Abbott

Clear seeded glass.

FINISHES



Antique Bronze



Antique Pewter



P560115-020

P560115-020 Antique Bronze ***P560115-103** Antique Pewter 10.37" W., 20.25" ht. 1 medium base, 100w max.



*P550040-020 Antique Bronze P550040-103 Antique Pewter 8.25" sq., 15.25" ht. 1 medium base, 100w max.



P540011-020 Antique Bronze ***P540011-103** Antique Pewter 8.25" sq., 18.5" ht. 1 medium base, 100w max.

Fits 3" post (sold separately)



***P560114-020** Antique Bronze **P560114-103** Antique Pewter 8.25" W., 16.25" ht. 1 medium base, 100w max.



P560113-020 Antique Bronze ***P560113-103** Antique Pewter 6.25" W., 12.25" ht. 1 medium base, 100w max.



Williamston

Clear glass.

FINISHES



Antique Bronze



Antique Pewter



P560266-103

*P560266-020 Antique Bronze P560266-103 Antique Pewter 7" W., 18" ht. 1 medium base, 100w max.



P540095-020 Antique Bronze *P540095-103 Antique Pewter 7" sq., 20.25" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P560265-020 Antique Bronze *P560265-103 Antique Pewter 6" W., 14.25" ht. 1 medium base, 100w max.



*P560264-020 Antique Bronze P560264-103 Antique Pewter 5" W., 12" ht. 1 medium base, 60w max.



Barnett

Clear glass. Antique Bronze with a brass-tone accent.

FINISH



020 Antique Bronze



P560078-020

P560079-020 Antique Bronze 11.25" W., 23.62" ht. 2 medium base, 60w max.



P550028-020 Antique Bronze 11.25" W., 26.87" ht. 2 medium base, 60w max.



P540028-020 Antique Bronze 11.25" W., 27" ht. 2 medium base, 60w max. Fits 3" post (sold separately)



P560078-020 Antique Bronze 9" W., 18.87" ht. 1 medium base, 100w max.



P560077-020 Antique Bronze 6.5" W., 15.12" ht. 1 medium base, 100w max.



Refuge

Clear and etched umber glass.

FINISH



108 Oil Rubbed Bronze



P6031-108

P6032-108 Oil Rubbed Bronze 10.5" W., 21" ht.

1 medium base, 100w max.



P6531-108 Oil Rubbed Bronze 8" dia., 16" ht.

1 medium base, 100w max.



P6431-108 Oil Rubbed Bronze 8" W., 18.62" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P6031-108 Oil Rubbed Bronze 8" W., 16" ht. 1 medium base, 100w max.



P6030-108 Oil Rubbed Bronze 6.5" W., 13.25" ht. 1 medium base, 100w max.



Barlowe

Clear seeded glass. Stainless Steel with White accents or Antique Bronze with Antique Copper accents.

FINISHES



Antique Bronze



Stainless Steel



P560158-020

*P560158-020 Antique Bronze P560158-135 Stainless Steel 9.12" W., 19" ht.

1 medium base, 100w max.



P550068-020 Antique Bronze ***P550068-135** Stainless Steel 9" sq., 21" ht. 1 medium base, 100w max.



***P540068-020** Antique Bronze **P540068-135** Stainless Steel 9" sq., 20" ht.

1 medium base, 100w max. Fits 3" post (sold separately)



P560157-020 Antique Bronze ***P560157-135** Stainless Steel 7.5" W., 16" ht. 1 medium base, 100w max.



***P560156-020** Antique Bronze **P560156-135** Stainless Steel 6.5" W., 13" ht.

1 medium base, 100w max.



P550069-020 Antique Bronze ***P550069-135** Stainless Steel 11.5" W., 5.5" ht. 2 medium base, 60w max.



Squire

Clear glass. Antique Bronze with Vintage Brass accents or Matte Black with Stainless Steel accents.

FINISHES



Antique Bronze



Matte Black



*P560038-020 Antique Bronze P560038-031 Matte Black 9.87" W., 22.75" ht. 3 candelabra base, 60w max.



P550012-020 Antique Bronze ***P550012-031** Matte Black 9.87" dia., 20.25" ht. 3 candelabra base, 60w max.



*P540012-020 Antique Bronze P540012-031 Matte Black 9.87" dia., 22.62" ht. 3 candelabra base, 60w max. Fits 3" post (sold separately)



P560037-020 Antique Bronze ***P560037-031** Matte Black 8" W., 19.25" ht. 2 candelabra base, 60w max.



*P560036-020 Antique Bronze P560036-031 Matte Black 6" W., 14.75" ht. 1 medium base, 100w max.



P550011-020 Antique Bronze ***P550011-031** Matte Black 9.87" dia., 11" ht. 3 candelabra base, 60w max.



Stature

Clear glass.

FINISHES



031 Textured Black



Oil Rubbed Bronze



P560269-108

*P560269-031 Textured Black P560269-108 Oil Rubbed Bronze 9" W., 21" ht. 2 candelabra base, 60w max.



P560268-031 Textured Black ***P560268-108** Oil Rubbed Bronze 8" W., 16" ht. 2 candelabra base, 60w max.



Wakeford

Clear water glass.

FINISHES



Textured Black



Antique Copper



P560262-169

*P560262-031 Textured Black P560262-169 Antique Copper 10" W., 21.5" ht. 1 medium base, 60w max.



P560261-031 Textured Black ***P560261-169** Antique Copper 8" W., 17.88" ht. 1 medium base, 60w max.



Holcombe

Clear seeded glass.

FINISH



031 Textured Black



P560066-031

P560067-031 Textured Black 10.5" W., 16" ht. 1 medium base, 100w max.



P550025-031 Textured Black 10.5" dia., 16.75" ht. 1 medium base, 100w max.



P540025-031 Textured Black

10.5" dia., 18.25" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P560066-031 Textured Black 8.25" W., 13.62" ht. 1 medium base, 100w max.



P560065-031 Textured Black 6.37" W., 10.62" ht. 1 medium base, 100w max.



669 OUTDOOR

Hollingsworth

Clear seeded glass.

FINISH



031 Textured Black



P560081-031

P560082-031 Textured Black 10" W., 24" ht. 1 medium base, 100w max.



P550029-031 Textured Black 10" dia., 20.25" ht. 1 medium base, 100w max.



P540029-031 Textured Black 10" dia., 23" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P560081-031 Textured Black 8" W., 19" ht. 1 medium base, 100w max.



P560080-031 Textured Black 6" W., 14.5" ht. 1 medium base, 100w max.



Haslett

Clear seeded glass.

FINISHES



031 Textured Black



Antique Pewter



P560094-103

*P560096-031 Textured Black P560096-103 Antique Pewter 9.37" W., 22.12" ht. 1 medium base, 100w max.



P550031-031 Textured Black *P550031-103 Antique Pewter 7.5" dia., 16.25" ht. 1 medium base, 100w max.



*P540031-031 Textured Black P540031-103 Antique Pewter 7.5" dia., 18" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P560095-031 Textured Black *P560095-103 Antique Pewter 7.5" W., 18.12" ht. 1 medium base, 100w max.



*P560094-031 Textured Black P560094-103 Antique Pewter 6.5" W., 14" ht. 1 medium base, 100w max.



Conover

Clear seeded glass.

FINISHES



Antique Bronze



Antique Pewter



P560084-020

***P560085-020** Antique Bronze **P560085-103** Antique Pewter 10.87" W., 21" ht. 1 medium base, 100w max.



P550030-020 Antique Bronze ***P550030-103** Antique Pewter 10.87" dia., 15.5" ht. 1 medium base, 100w max.



*P540030-020 Antique Bronze P540030-103 Antique Pewter 10.87" dia., 19" ht. 1 medium base, 100w max. Fits 3" post

(sold separately)



P560084-020 Antique Bronze ***P560084-103** Antique Pewter 8.62" W., 16" ht. 1 medium base, 100w max.



*P560083-020 Antique Bronze P560083-103 Antique Pewter 7" W., 14.25" ht. 1 medium base, 100w max.



Township

Clear beveled glass.

FINISH



108 Oil Rubbed Bronze



P5693-108

P5699-108 Oil Rubbed Bronze 8" W., 22" ht.

3 candelabra base, 60w max.



P5504-108 Oil Rubbed Bronze 8" dia., 19.75" ht. 3 candelabra base, 60w max.



P5404-108 Oil Rubbed Bronze 8" dia., 22.5" ht.

3 candelabra base, 60w max. Fits 3" post (sold separately)



P5693-108 Oil Rubbed Bronze 6.5" W., 17.5" ht. 2 candelabra base, 60w max.



P5692-108 Oil Rubbed Bronze 5.5" W., 14.75" ht. 1 medium base, 60w max.



Maison

Water seeded glass.

FINISHES







P5754-31

*P5755-31 Textured Black P5755-108 Oil Rubbed Bronze 8.5" W., 23.75" ht. 3 candelabra base, 60w max.



P6432-31 Textured Black ***P6432-108** Oil Rubbed Bronze 7.25" sq., 20.62" ht. 2 candelabra base, 60w max. Fits 3" post (sold separately)



P5754-31 Textured Black ***P5754-108** Oil Rubbed Bronze 7.25" W., 20" ht. 2 candelabra base, 60w max.



*P5753-31 Textured Black P5753-108 Oil Rubbed Bronze 5.75" W., 16.25" ht. 1 medium base, 100w max.



*Shown in finish Hinged door for easy relamping. Crawford

Etched or clear beveled glass.

FINISHES



31M Textured Black



Oil Rubbed Bronze



P5686-31MD

P6630-31MD Textured Black 6.5" W., 12.5" ht. 1 medium base, 100w max.



P6631-31MD Textured Black 8.5" W., 20.5" ht. 1 medium base, 100w max.



P6440-31MD Textured Black 9.87" dia., 24.62" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



Crawford

P5686-31MD Textured Black 8.5" W., 16.75" ht. 1 medium base, 100w max.



P5686-108MD Oil Rubbed Bronze 8.5" W., 16.75" ht. 1 medium base, 100w max.



P5670-108 Oil Rubbed Bronze 6.5" W., 12.5" ht. 1 medium base, 100w max. Clear beveled glass.



P5671-108 Oil Rubbed Bronze 8.5" W., 16.75" ht. 2 candelabra base, 60w max. Clear beveled glass.



P5672-108 Oil Rubbed Bronze 9.87" W., 28.87" ht. 3 candelabra base, 60w max. Clear beveled glass.



P5474-108 Oil Rubbed Bronze 12" dia., 28.37" ht. 4 candelabra base, 60w max. Fits 3" post (sold separately) Clear beveled glass.



Ashmore

Seeded water glass.

FINISHES



Antique Bronze



Textured Black



P5550-31

*P5550-20 Antique Bronze P5550-31 Textured Black 9.62" dia., 17.75" ht. 3 candelabra base, 60w max.



P5562-20 Antique Bronze ***P5562-31** Textured Black 10.5" dia., 9.75" ht. 2 candelabra base, 60w max.



Ashmore

***P5651-20** Antique Bronze **P5651-31** Textured Black 9.62" W., 20.5" ht. 3 candelabra base, 60w max.



P5650-20 Antique Bronze ***P5650-31** Textured Black 8.37" W., 16.5" ht. 3 candelabra base, 60w max.



P5649-20 Antique Bronze ***P5649-31** Textured Black 6.62" W., 14.81" ht. 2 candelabra base, 60w max.



P5875-20MD Antique Bronze 8.37" W., 16.62" ht. 1 medium base, 100w max.



P5652-31 Textured Black 8.37" W., 26.25" ht. 3 candelabra base, 60w max.



*P5450-20 Antique Bronze P5450-31 Textured Black 9.5" dia., 23.75" ht. 3 candelabra base, 60w max. Fits 3" post (sold separately)



Andover

Clear beveled glass.

FINISH



Antique Bronze



P5688-20

P5627-20 Antique Bronze 12.5" W., 34.25" ht. 4 candelabra base, 60w max.



P5587-20 Antique Bronze 9.5" dia., 19.5" ht. 3 candelabra base, 60w max.



P5487-20 Antique Bronze 9.5" dia., 22.37" ht. 3 candelabra base, 60w max. Fits 3" post (sold separately)



P5689-20 Antique Bronze 9" W., 26" ht. 3 candelabra base, 60w max.



P5688-20 Antique Bronze 7.5" W., 21.25" ht. 2 candelabra base, 60w max.



P5687-20 Antique Bronze 5.5" W., 12.5" ht. 1 medium base, 100w max.



Resort

Etched umber glass.

FINISH



122 Aged Copper



P5987-122

P5989-122 Aged Copper 10.5" W., 19.75" ht. 1 medium base, 100w max.



P6404-122 Aged Copper 8.5" dia., 17.37" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P5988-122 Aged Copper 8.5" W., 15.87" ht. 1 medium base, 100w max.



P5987-122 Aged Copper 6.5" W., 10.87" ht. 1 medium base, 100w max.



Wish

Etched white linen glass.

FINISHES



Antique Bronze



Textured Black



P6085-20

P6085-20 Antique Bronze ***P6085-31** Textured Black 9" W, 12.5" ht. 1 medium base, 100w max.





***P6084-20** Antique Bronze **P6084-31** Textured Black 7" W, 10.37" ht. 1 medium base, 75w max.





*P6424-20 Antique Bronze P6424-31 Textured Black 9" dia., 14.81" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



Wish LED

Etched white linen glass.

FINISH



31 Textured Black



P6085-3130K9

P6085-3130K9 Textured Black 9" W., 12.5" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.





P6084-3130K9 Textured Black 7" W., 10.37" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.





P6424-3130K9 Textured Black 9" dia., 14.81" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens. Fits 3" post (sold separately)



All fixtures:





Hutchence

Modern cottage style adorns exteriors in the Hutchence Collection, whose open arched frame encloses a contrasting shade. An ample wash of warm light is delicately cast downward from this Dark Sky friendly wall lantern.

FINISH





P560335-020

P560336-020 Antique Bronze 9.5" W., 18" ht. 1 medium base, 100w max.



P560335-020 Antique Bronze 6.75" W., 12" ht. 1 medium base, 100w max.



All fixtures:



Stallworth

Establish a bold statement with the modern Stallworth Collection, whose minimalistic design offers maximum visual interest. Its open framework is a contemporary take on classic lantern styling with angular lines and a cylindrical metal shade that projects a wash of warm downlight from this Dark Sky friendly wall lantern.

FINISH



31M Matte Black



P560334-31M

P560334-31M Matte Black 9" W., 18" ht. 1 medium base, 100w max.



P560333-31M Matte Black 6.5" W., 12.5" ht. 1 medium base, 100w max.







Cedar **Springs**

A fun take on the traditional warehouse shade, the Cedar Springs Collection features a signature gooseneck arm and a smooth, simple, metal shade. This modern collection provides excellent task lighting for reading a book in your bedroom or illuminating a doorway in your home. Dark Sky Compliant.







Black



Red



Pistachio



Metallic Gray



Navy



P550116-039

P550116-030 White *P550116-031 Black **P550116-039** Red 13.19" dia., 7.5" ht. 1 medium base, 100w max.



P540103-031 Gloss Black **P540103-039** Red 13.25" dia., 17" ht. 1 medium base, 100w max. Fits 3" post (sold separately)

*P540103-030 White



*Shown in finish All fixtures:



Cedar Springs

P550070-030 White 13.25" dia., 9.5" ht. 1 medium base, 100w max.



P550070-031 Gloss Black 13.25" dia., 9.5" ht. 1 medium base, 100w max.



P550070-039 Red 13.25" dia., 9.5" ht.



P550070-079 Pistachio 13.25" dia., 9.5" ht.



P550070-082 Metallic Gray 13.25" dia., 9.5" ht. 1 medium base, 100w max.



P550070-091 Navy 13.25" dia., 9.5" ht. 1 medium base, 100w max.







Lighting fixtures can help protect the beauty of the nighttime sky by limiting illumination that is cast upwards.

Progress Lighting lanterns identified with the Dark Sky icon deliver this feature by providing a full-cutoff design with no light cast above the fixture and upward reflected light limited to <10% of the delivered lumens. When selecting a light bulb, choose one that is 3000K or less as recommended by international dark sky intiatives.

Cedar Springs

P560091-030 White 13.25" W., 11.25" ht. 1 medium base, 100w max.



P560091-031 Gloss Black 13.25" W., 11.25" ht. 1 medium base, 100w max.



P560091-039 Red



P560091-079 Pistachio



P560091-082 Metallic Gray 13.25" W., 11.25" ht.



P560091-091 Navy







Englewood

Antique Bronze and Textured Black with a Metallic Copper inner shade. Antique Pewter with a Metallic Silver inner shade.

FINISHES



Antique Bronze



Textured Black



Antique Pewter



P550032-020

P550032-020 Antique Bronze P550032-031 Textured Black *P550032-103 Antique Pewter 12" dia., 8" ht. 1 medium base, 100w max.



P540032-020 Antique Bronze *P540032-031 Textured Black P540032-103 Antique Pewter 16" W., 13.43" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



***P560098-020** Antique Bronze P560098-031 Textured Black P560098-103 Antique Pewter 12" dia., 10.37" ht. 1 medium base, 100w max.



P560097-020 Antique Bronze P560097-031 Textured Black *P560097-103 Antique Pewter 8" W., 9.75" ht.

1 medium base, 100w max.



*Shown in finish All fixtures:



Callahan LED

Callahan draws inspiration from farmhouse decor. Hidden within this vintage frame is a modern LED light source that delivers energy-efficient performance. The inner surface of the shade is accented with a contrasting finish to complete the nostalgic look.

FINISH



Antique Bronze



P560053-020-30

P560053-020-30 Antique Bronze 11" W., 11.5" ht. 17w LED module, 3000K, 90 CRI, 1273 source lumens.



P560052-020-30 Antique Bronze 8.5" W., 10" ht. 9w LED module , 3000K, 90 CRI, 624 source lumens.



All fixtures:







Brookside



Copper



Gilded Iron



Antique Nickel

P5723-14 Copper **P5723-71** Gilded Iron ***P5723-81** Antique Nickel 12" W., 12.37" ht. 1 medium base, 100w max. *P5722-14 Copper P5722-71 Gilded Iron P5722-81 Antique Nickel 10" W., 10.75" ht. 1 medium base, 75w max.









*Shown in finish All fixtures:



Brookside LED



Gilded Iron

P5723-7130K9 Gilded Iron 12" W., 12.25" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.









Beaufort

Clear seeded glass.

031 Textured Black





P560050-031 Textured Black 10" W., 14.37" ht. 1 medium base, 100w max.



P560049-031 Textured Black 8.62" W., 11.5" ht. 1 medium base, 100w max.



Tremont

Clear seeded glass.



Matte Black



Stainless Steel

P550093-031 Matte Black ***P550093-135** Stainless Steel 9" dia., 8" ht. 1 medium base, 60w max.

*P560263-031 Matte Black P560263-135 Stainless Steel 9" W., 11" ht.





P550094-031 Matte Black ***P550094-135** Stainless Steel 9" dia., 10" ht. 1 medium base, 60w max.



Hawthorne

Etched seeded glass.

31 Textured Black

P5665-31 Textured Black 7.5" W., 16" ht. 1 medium base, 100w max.



P5513-31 Textured Black 5" dia., 9.12" ht. 1 medium base, 100w max.



P5413-31 Textured Black 7.5" dia., 17.25" ht. 2 candelabra base, 60w max. Fits 3" post (sold separately)



P5625-31 Textured Black 6" W., 12.62" ht. 1 medium base, 100w max.



P5624-31 Textured Black 5" W., 9.62" ht. 1 medium base, 100w max.



Compel

Etched opal glass within a clear seeded glass diffuser.



Textured Black

P6520-31 Textured Black 7.87" dia., 15.37" ht. 1 medium base, 100w max.



P6039-31 Textured Black 7.87" W., 13.5" ht. 1 medium base, 100w max.



P6038-31 Textured Black 5.75" W., 9.87" ht. 1 medium base, 100w max.



Format

Etched glass.

31 Textured Black

P6064-31 Textured Black 6.12" W., 16.12" ht. 1 medium base, 100w max.



P6428-31 Textured Black 9.25" W., 17.12" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P6063-31 Textured Black 4.87" W., 11.62" ht. 1 medium base, 100w max.



P6062-31 Textured Black 3.87" W., 7.62" ht. 1 medium base, 100w max.



Diverge

Etched glass.



P560046-129 Architectural Bronze 6" W., 17.75" ht., 4" D. 2 medium base, 60w max.





P560045-129 Architectural Bronze 6" W., 10.87" ht., 4" D. 1 medium base, 60w max.





McBee

Clear glass.



031 Textured Black

Geometric

9 Architectural Bronze

Seeded and water glass panels.

P560035-031 Textured Black 4.5" W., 20.75" ht. 1 medium base, 60w max.



P560048-129 Architectural Bronze 6" W., 16" ht., 4" D. 2 medium base, 60w max.





Jack

Antique Bronze with etched umber flax glass and Textured black with etched white flax glass.



Antique Bronze



Textured Black

***P5949-20** Antique Bronze **P5949-31** Textured Black 8" W., 15.25" ht. 1 medium base, 100w max.



P5948-20 Antique Bronze ***P5948-31** Textured Black 6" W., 13.62" ht. 1 medium base, 100w max.



Botta

Clear seeded glass.



P5561-20 Antique Bronze 7.75" dia., 12" ht. 1 medium base, 100w max.



P5560-20 Antique Bronze 6.25" dia., 9.75" ht. 1 medium base, 100w max.



P6436-20 Antique Bronze 7.75" dia., 16" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P6050-20 Antique Bronze 7.75" W., 13.87" ht. 1 medium base, 100w max.



P6043-20 Antique Bronze 6.25" W., 11.62" ht. 1 medium base, 100w max.



Padgett

Clear seeded glass.



Antique Bronze



Textured Black

*P560309-020 Antique Bronze P560309-031 Textured Black 10" W., 18.87" ht. 1 medium base, 100w max.



P540093-020 Antique Bronze ***P540093-031** Textured Black 8" sq., 18.5" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P560308-020 Antique Bronze ***P560308-031** Textured Black 8" W., 15" ht. 1 medium base, 100w max.



*P560307-020 Antique Bronze P560307-031 Textured Black 6" W., 11.25" ht. 1 medium base, 100w max.



East Haven

Clear seeded glass.



Antique Bronze



Textured Black

*P6075-20 Antique Bronze P6075-31 Textured Black 9.5" W., 15.12" ht. 1 medium base, 100w max.



P6425-20 Antique Bronze ***P6425-31** Textured Black 7.5" dia., 15" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P6074-20 Antique Bronze ***P6074-31** Textured Black 7.5" W., 12.75" ht. 1 medium base, 100w max.



*P6073-20 Antique Bronze P6073-31 Textured Black 5.75" W., 10.37" ht. 1 medium base, 100w max.



*Shown in finish

East Haven LED

Clear seeded glass.



Antique Bronze



Textured Black

*P6079-2030K9 Antique Bronze P6079-3130K9 Textured Black 9.5" W., 12" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.



P6430-3130K9 Textured Black 7.5" dia., 15" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens. Fits 3" post (sold separately)



P6078-2030K9 Antique Bronze ***P6078-3130K9** Textured Black 7.5" W., 9.75" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



*P6077-2030K9 Antique Bronze P6077-3130K9 Textured Black 5.75" W., 7.87" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



*Shown in finish All fixtures:







Derby

Clear seeded glass.



P5579-84 Espresso 8.5" dia., 12.37" ht. 1 medium base, 100w max.



P5750-84 Espresso 8.5" W., 11.25" ht. 1 medium base, 100w max.



P5749-84 Espresso 6.5" W., 8.62" ht. 1 medium base, 100w max.



Derby LED

Etched umber watermark glass.



P5749-2030K9 Antique Bronze 6.5" W., 8.37" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.









Greene Ridge

Clear seeded glass.

031 Textured Black

P560100-031 Textured Black 6.75" sq., 14.25" ht. 1 medium base, 100w max.



P560099-031 Textured Black 5.25" sq., 11.62" ht. 1 medium base, 100w max.



Essential

Antique Bronze with etched umber linen glass and Textured black with etched white linen glass.



31

Textured Black

*P6060-20 Antique Bronze P6060-31 Textured Black 8" W., 11.12" ht. 1 medium base, 100w max.



P6059-20 Antique Bronze ***P6059-31** Textured Black 5.87" W., 8.68" ht. 1 medium base, 100w max.



*Shown in finish

Arts & Crafts

Honey art glass.



P5629-46 Weathered Bronze 10" W., 15.12" ht. 1 medium base, 150w max.



P5628-46 Weathered Bronze 6.75" W., 10.62" ht. 1 medium base, 100w max.



Prairie

Clear seeded glass.



Brushed Nickel



Gilded Iron



Burnished Chestnut

P5764-09 Brushed Nickel 10" W., 13.5" ht. 1 medium base, 100w max.



P5764-71 Gilded Iron 10" W., 13.5" ht. 1 medium base, 100w max.



P5764-86 Burnished Chestnut 10" W., 13.5" ht. 1 medium base, 100w max.



Merit

Etched glass.



Textured Black

P6002-31 Textured Black 10" W., 15.75" ht. 1 medium base, 100w max.



P6001-31 Textured Black 7.75" W., 12.25" ht. 1 medium base, 100w max.



P6000-31 Textured Black 5.25" W., 8" ht. 1 medium base, 60w max.



Mac

Clear water glass.

31 Textu

Textured Black

P5907-31 Textured Black 8.5" W., 12" ht. 1 medium base, 100w max.



P6023-31 Textured Black 11" sq., 6.87" ht. 2 medium base, 100w max.



Burlington

Clear glass.



P6617-20 Antique Bronze 11" W., 21.87" ht. 3 candelabra base, 60w max.



P6537-20 Antique Bronze 9" sq., 15.75" ht. 2 candelabra base, 60w max.



P6437-20 Antique Bronze 9" sq., 18.37" ht. 2 candelabra base, 60w max. Fits 3" post (sold separately)



P6616-20 Antique Bronze 9" W., 18.75" ht. 2 candelabra base, 60w max.



P6615-20 Antique Bronze 7" W., 12.87" ht. 1 medium base, 100w max.



P550035-020 Antique Bronze 7" sq., 7" ht. 1 medium base, 60w max.



New Haven

Clear glass.



Textured Black

P6612-31 Textured Black 11" W., 21.87" ht. 3 candelabra base, 60w max.



P6533-31 Textured Black 11" dia., 19.75" ht. 3 candelabra base, 60w max.



P6433-31 Textured Black 11" dia., 23" ht. 3 candelabra base, 60w max. Fits 3" post (sold separately)



P6611-31 Textured Black 9" W., 18.12" ht. 1 medium base, 100w max.



P6610-31 Textured Black 7.62" W., 14.87" ht. 1 medium base, 100w max.



Dillard

Clear glass.

020

Antique Bronze



Textured Black

P560323-020 Antique Bronze ***P560323-031** Textured Black 9.75" W., 18.12" ht. 1 medium base, 60w max.



*P550122-020 Antique Bronze P550122-031 Textured Black 7.5" W., 13.62" ht. 1 medium base, 60w max.



P540099-020 Antique Bronze *P540099-031 Textured Black 9.75" W., 18.12" ht. 1 medium base, 60w max. Fits 3" post (sold separately)



*P560322-020 Antique Bronze P560322-031 Textured Black 8.12" W., 15.5" ht. 1 medium base, 60w max.



P560321-020 Antique Bronze ***P560321-031** Textured Black 6.5" W., 11.37" ht. 1 medium base, 60w max.



*Shown in finish

Edition

Clear water glass.



Antique Bronze



Textured Black

*P6072-20 Antique Bronze P6072-31 Textured Black 9" W., 15.87" ht. 1 medium base, 100w max.



P6529-20 Antique Bronze ***P6529-31** Textured Black 7.12" dia., 13.25" ht. 1 medium base, 100w max.



*P6429-20 Antique Bronze P6429-31 Textured Black 9" dia., 21.87" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P6071-20 Antique Bronze ***P6071-31** Textured Black 7.12" W., 12.5" ht. 1 medium base, 100w max.



*P6070-20 Antique Bronze P6070-31 Textured Black 5.5" W., 9.12" ht. 1 medium base, 100w max.



District



Antique Bronze



Textured Black



Metallic Gray

P5551-20 Antique Bronze 12" dia., 8.25" ht. 1 medium base, 100w max.



P5623-20 Antique Bronze P5623-31 Textured Black ***P5623-82** Metallic Gray 12" dia., 10.5" ht. 1 medium base, 100w max.



P5622-31 Textured Black 8" W., 8.25" ht. 1 medium base, 100w max.



P5622-20 Antique Bronze 8" W., 8.25" ht. 1 medium base, 100w max.



*Shown in finish All fixtures:



District LED



Antique Bronze

P5623-2030K9 Antique Bronze 12" W., 10.5" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



P5622-2030K9 Antique Bronze 8" W., 8.25" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.







Ward

031 Textured Black

P560296-031 Textured Black 7.87" dia., 7.37" ht. 1 medium base, 100w max.





Precinct



P560301-031 Textured Black 8" dia., 9.5" ht. 1 medium base, 100w max.





Ceramic Sconce



P560044-030 White 8.25" W., 10" ht. 1 medium base, 100w max.





Westport

Clear seeded glass.

20 Antique Bronze





Textured Black

P3883-20 Antique Bronze ***P3883-31** Textured Black 9.12" dia., 10.25" ht. 1 medium base, 100w max.



*P5458-20 Antique Bronze P5458-31 Textured Black 11" dia., 19" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



*P5445-30 White P5445-20 Antique Bronze P5445-31 Textured Black 9" dia., 16.25" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P5864-20 Antique Bronze *P5864-31 Textured Black 11" W., 19.25" ht. 2 candelabra base, 60w max.



P5863-30 White ***P5863-20** Antique Bronze **P5863-31** Textured Black 9" W., 16" ht. 1 medium base, 100w max.



*P5862-30 White P5862-20 Antique Bronze P5862-31 Textured Black 6.87" W., 12.75" ht. 1 medium base, 60w max.



*Shown in finish

Westport LED

Etched seeded glass.

31 Tex

Textured Black

P5864-3130K9 Textured Black 11" W., 15.37" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.



P5445-3130K9 Textured Black 9" dia., 16.37" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens. Fits 3" post (sold separately)



P5863-3130K9 Textured Black 9" W., 12.87" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



P5862-3130K9 Textured Black 6.87" W., 10.25" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



All fixtures:







Weldon

Clear seeded glass.

Textured Black



Architectural Bronze

P540019-031 Textured Black 10" W., 15.62" ht. 1 medium base, 60w max. Fits 3" post (sold separately)



P550042-031 Textured Black *P550042-129 Architectural Bronze 10.75" dia., 4.5" ht. 2 medium base, 60w max.



P560121-031 Textured Black 10" W., 14.87" ht. 1 medium base,



P560120-031 Textured Black 8" W., 11.87" ht.

1 medium base, 60w max.



P560119-031 Textured Black 6" W., 9" ht. 1 medium base,

60w max.



*Shown in finish

Onion Lanterns

Clear glass.

Textured Black

P5878-31 Textured Black 6.5" W., 21.25" ht. 1 medium base, 100w max.



P5700-31 Textured Black 7.75" W., 23.25" ht. 3 candelabra base, 60w max.



P5401-31 Textured Black 11.12" dia., 27.75" ht. 4 candelabra base, 60w max. Fits 3" post (sold separately)



Welbourne

Clear glass.



Textured White



Textured Black

P5582-31 Textured Black 9.37" dia., 14.06" ht. 1 medium base, 100w max.



*P5482-30 Textured White P5482-31 Textured Black 9.37" dia., 21.75" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P5483-31 Textured Black 12.62" dia., 25.87" ht. 3 candelabra base, 60w max.
Fits 3" post (sold separately)



P5690-31 Textured Black 12.62" W., 22.18" ht. 3 candelabra base, 60w max.



P5683-31 Textured Black 9.37" W., 16" ht. 1 medium base, 100w max.



*P5682-30 Textured White P5682-31 Textured Black 6.25" W., 13.06" ht. 1 medium base, 100w max.



P5681-31 Textured Black 6.5" W., 16.87" ht. 1 medium base, 100w max.



P5684-31 Textured Black 9.37" W., 30.75" ht. 1 medium base, 100w max.





Carriage Classics

Clear glass.



09 Brushed Nickel



Matte Black

*P5756-09 Brushed Nickel P5756-31 Matte Black 5.37" W., 10.25" ht. 1 medium base, 100w max.



P5432-31 Matte Black 9.75" dia., 21.31" ht. 3 candelabra base, 60w max. Fits 3" post (sold separately)



P5846-31 Matte Black 5.25" W., 14.68" ht. 1 medium base, 60w max.



P5758-31 Matte Black 5.37" W., 18.75" ht. 1 medium base, 100w max.



P5831-31 Matte Black 7" W., 28.5" ht. 1 medium base, 100w max.



P5731-31 Matte Black 9.75" W., 33.25" ht. 3 candelabra base, 60w max.



Roman Coach



Antique Bronze



Textured Black

*P5762-20 Antique Bronze P5762-31 Textured Black 6" W., 9.75" ht. 1 medium base, 100w max.



P5765-20 Antique Bronze ***P5765-31** Textured Black 7" W., 15.25" ht. 1 medium base, 100w max.



P5770-20MD Antique Bronze 7" W., 15.37" ht. 1 medium base, 100w max.



P5565-20 Antique Bronze 7" dia., 13" ht. 1 medium base, 100w max.



shown as ceiling mount



P6417-20 Antique Bronze ***P6417-31** Textured Black 8.5" dia., 22.62" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



P5767-20 Antique Bronze shown without tail **P5767-31** Textured Black shown with tail
7" W., 19.25" ht.
1 medium base, 100w max.





P6019-20 Antique Bronze ***P6019-31** Textured Black 11" dia., 6.18" ht. 2 medium base, 60w max.



Roman Coach

20 Antique Bronze



Textured Black

*P5985-20MD Antique Bronze P5985-31MD Textured Black 4.62" W., 10" ht. 1 medium base, 100w max.



P5986-20MD Antique Bronze ***P5986-31MD** Textured Black 4.62" W., 6.5" ht. 1 medium base, 100w max.



P5773-20 Antique Bronze 5.75" W., 13.5" ht. 1 medium base, 100w max.



shown with tail

P5777-20 Antique Bronze 7" W., 12.75" ht. 1 medium base, 100w max.



Flat Glass



Brushed Nickel



Antique Bronze



Textured Black

P5607-09 Brushed Nickel 4.56" W., 8.62" ht. 1 medium base, 100w max.



P5607-20 Antique Bronze 4.56" W., 8.62" ht. 1 medium base, 100w max.



P5607-31 Textured Black 4.56" W., 8.62" ht. 1 medium base, 100w max.



Globe Lantern

Clear glass.



Matte Black

P560092-031 Matte Black 9.87" W., 11.62" ht. 1 medium base, 100w max.



P540007-031 Matte Black 9.87" dia., 13.25" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



Gunther

Clear glass.



Antique Bronze



Matte Black

P550021-020 Antique Bronze ***P550021-31M** Matte Black* 12.62" dia., 5.75" ht. 2 medium base, 75w max.



P540020-020 Antique Bronze P540020-31M Matte Black 8" dia., 13.5" ht. 1 medium base, 100w max. Fits 3" post (sold separately)



***P560058-020** Antique Bronze* **P560058-31M** Matte Black 8" W., 11.5" ht. 1 medium base, 100w max.



P560057-020 Antique Bronze ***P560057-31M** Matte Black* 6.5" W., 9.5" ht. 1 medium base, 100w max.



*Shown in finish

Cast Lantern

Clear acrylic panels.



Textured Black

P5826-31 Textured Black 7" W., 14.12" ht. 1 medium base, 75w max.



Non-Metallic Lanterns

Clear acrylic panels.



P5656-31 Textured Black 8" W., 20" ht. 1 medium base, 100w max. P5737-31 Textured Black 8" W., 16" ht. 1 medium base, 60w max. P5738-31 Textured Black 8" W., 21" ht. 1 medium base, 60w max. P5456-31 Textured Black 7.75" dia., 17.62" ht. 1 medium base, 100w max. Fits 3" post (sold separately)









Trafford Non-Metallic

Textured Black

P560289-031 Textured Black 6" W., 14" ht. 1 medium base, 60w max.



P560288-031 Textured Black 5" W., 11.5" ht. 1 medium base, 60w max.



Milford Non-Metallic Frosted acrylic diffuser.



P560283-031-PC Textured Black 7.43" W., 9.87" ht. 1 medium base, 40w max.



Newport Non-Metallic

Clear prismatic diffuser.



White



Textured Black

*P5645-30 White P5645-31 Textured Black 10" W., 12.87" ht. 1 medium base, 60w max.



P5444-31 Textured Black 10" dia., 9.87" ht. 1 medium base, 60w max. Fits 3" post (sold separately)



P5493-31 Textured Black 23.25" W., 12.62" ht. 2 medium base, 60w max. Fits 3" post (sold separately)



*Shown in finish

Mansard Non-Metallic

Clear beveled panes.



White



Textured Black

P5814-30 White ***P5814-31** Textured Black 8" W., 13" ht. 1 medium base, 60w max.



P5414-30 White *P5414-31 Textured Black 8" dia., 12.56" ht. 1 medium base, 60w max. Fits 3" post (sold separately)



*P5815-30 White P5815-31 Textured Black 8" W., 17" ht. 1 medium base, 60w max.



Non-Metallic Lanterns



White



Textured Black

*P5612-30 White P5612-31 Textured Black 4.75" W., 7.25" ht. 1 medium base, 60w max.



P5817-31 Textured Black 4.37" W., 7" ht. 1 medium base, 60w max.



P5813-30 White ***P5813-31** Textured Black 6" W., 7.75" ht. 1 medium base, 60w max.



*P5844-30 White P5844-31 Textured Black 6" W., 8.87" ht. 1 medium base, 60w max.



*Shown in finish

Acrylic Globes

P5626-60 Textured Black 8" W., 15" ht. 1 medium base, 100w max.



P5478-60 Textured Black 10" dia., 10.25" ht. 1 medium base, 100w max. White globe with black fitter. Fits 3" post (sold separately)



P5426-60 White 12" dia., 11.87" ht. 1 medium base, 100w max. White globe with white fitter. Fits 3" post (sold separately)



P5436-60 White 14" dia., 14" ht. 1 medium base, 150w max. White globe with white fitter. Fits 3" post (sold separately)



Ceiling Mount



31 Matte Black



Textured Black

Metal Textured glass.

P5727-31 Matte Black 7.5" dia., 5" ht. 1 medium base, 60w max.



P5729-31 Matte Black 9.25" dia., 5" ht. 2 medium base, 60w max.



Polycarbonate

White acrylic diffuser.

P5744-30 White ***P5744-31** Textured Black 8.25" dia., 4.75" ht. 1 medium base, 60w max.



***P5745-30** White **P5745-31** Textured Black 10.25" dia., 5.5" ht. 2 medium base, 60w max.



*Shown in finish

Utility

Glass shade.

30 White

te (

31 Textured Black

*P5602-30 White P5602-31 Textured Black 4.5" W., 7.25" ht. 1 medium base, 75w max.



P5603-30 White ***P5603-31** Textured Black 4.87" dia., 6.25" ht. 1 medium base, 60w max.



P5604-30 White **P5604-31** Textured Black 6" W., 8.5" ht. 1 medium base, 100w max.





Bell LED

Etched glass.





Textured Graphite

P5676-13630K9 Textured Graphite 5.5" W., 10.62" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



P5676-2030K9 Antique Bronze 5.5" W., 10.62" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



All fixtures:







Die-Cast LED

Etched glass.



P560136-031-30 Textured Black 5.62" sq., 8.87" ht. 11w integrated LED, 3000K, 80 CRI, 560 delivered lumens.







Bulkheads

Clear patterned glass.



White

Textured Black

P3706-30 White **P3706-31** Textured Black 6.37" W., 11" ht., 4.75" D. 1 medium base, 100w max.



shown ceiling mounted



P3709-30 White **P3709-31** Textured Black 7.87" dia., 4.12" ht. 1 medium base, 60w max.



shown ceiling mounted



All fixtures:



Polycarbonate Bulkheads

polycarbonate shade.



White

P5706-30 White 10.5" W., 5.87" ht. 1 medium base, 60w max.



P5703-30 White 10" dia., 10" ht. 1 medium base, 75w max.



P5704-30 White 5.87" W., 10.5" ht., 3.75 D. 1 medium base, 60w max.





P5705-30 White 5.87" W., 10.5" ht., 4" D. 1 medium base, 60w max.





Bulkheads LED

White polycarbonate shade.



White



Textured Black

P3648-3030K9 White *P3648-3130K9 Textured Black 9.5" dia., 4.5" D. 17w LED module, 3000K, 90 CRI, 623 source lumens.



*P3649-3030K9 White P3649-3130K9 Textured Black 10.5" W., 4.5" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



P3650-3030K9 White **P3650-3130K9** Textured Black 9.12" dia., 4.68" D. 9w LED module, 3000K, 90 CRI, 623 source lumens.



shown ceiling mounted



*Shown in finish All fixtures:







Hard-Nox LED

White polycarbonate shade.



Satin White



Black

P550112-028-30 Satin White ***P550112-031-30** Black 11.9" dia., 3" ht. 25w LED module, 3000K, 90 CRI, 2347 source lumens.



P550113-028-30 Satin White 10.6" sq., 4" ht. 25w LED module, 3000K, 90 CRI, 2347 source lumens.



*P550114-028-30 Satin White P550114-031-30 Black 9.9" dia., 4.8" ht. 25w LED module, 3000K, 90 CRI, 2347 source lumens.



P550115-028-30 Satin White ***P550115-031-30** Black 10" sq., 4.5" ht. 25w LED module, 3000K, 90 CRI, 2347 source lumens.



*Shown in finish All fixtures:



Z-1030 LED



Antique Bronze



Textured Black



Metallic Gray

*P560051-020-30 Antique Bronze P560051-030-30 White P560051-031-30 Textured Black **P560051-082-30** Metallic Gray 5.12" W., 12" ht. 9w LED module, 3000K, 90 CRI, 624 source lumens.



P560056-020-30 Antique Bronze P560056-030-30 White P560056-031-30 Textured Black *P560056-082-30 Metallic Gray 5.12" W., 20" ht. 9w LED module, 3000K, 90 CRI, 624 source lumens.



*Shown in finish All fixtures:









White acrylic shade.



09 Brushed Nickel



Architectural Bronze

*P5800-0930K9 Brushed Nickel P5800-12930K9 Architectural Bronze 5.62" W., 8" ht. 9w LED module, 3000K, 90 CRI, 623 source lumens.



P5801-0930K9 Brushed Nickel *P5801-12930K9 Architectural Bronze 8.62" W., 11" ht. 17w LED module, 3000K, 90 CRI, 1211 source lumens.



P5806-0930K9 Brushed Nickel *P5806-12930K9 Architectural Bronze 5.62" W., 16" ht. 9w LED modules, 3000K, 90 CRI, 623 source lumens per module.



*Shown in finish All fixtures:





Z-1070 LED

White acrylic shade.



P560208-031-30 Textured Black 6" W., 12.56" ht. 11w integrated LED, 3000K 90 CRI, 528 delivered lumens.



P560209-031-30 Textured Black 6" W., 23.12" ht. 22w integrated LED, 3000K 90 CRI, 1019 delivered lumens.



All fixtures:





Z-1080 LED

White acrylic shade.



Textured Black



Metallic Gray

*P560210-031-30 Textured Black P560210-082-30 Metallic Gray 5" W., 13" ht. 11w integrated LED, 3000K, 90 CRI, 415 delivered lumens.



P560211-031-30 Textured Black ***P560211-082-30** Metallic Gray 5" W., 23.5" ht. 22w integrated LED, 3000K, 90 CRI, 847 delivered lumens.



*Shown in finish All fixtures:







Z-1090 LED



P560137-031-30 Matte Black 4.5" W., 16" ht. 9w Module LED, 3000K, 90 CRI, 624 source lumens.



All fixtures:







Z-1010 LED

Clear seeded glass.

Textured Black



Architectural Bronze

P560029-031-30 Textured Black 7.5" W., 16" ht. 9w LED module. 3000K 90 CRI, 624 source lumens.



P560029-129-30 Architectural Bronze 7.5" W., 16" ht. 9w LED module. 3000K 90 CRI, 624 source lumens.









Z-1060 LED

White or clear seeded glass.



P560072-031-30 Textured Black 4.5" W., 4.5" ht. 9w LED module, 3000K, 90 CRI, 624 source lumens.



P560073-031-30 Textured Black 4.5" W., 4.5" ht. 9w LED module, 3000K, 90 CRI, 624 source lumens.



All fixtures:





Z-2020 LED



Satin White



Textured Black

P560260-028-30 Satin White 6.25" dia., 2.25" D. 9w LED module, 3000K, 90 CRI, 623 source lumens.



P560260-031-30 Textured Black 6.25" dia., 2.25" D. 9w LED module, 3000K, 90 CRI, 623 source lumens.



All fixtures:









Satin White




Textured Black

P560259-028-30 Satin White 6.25" sq., 2.25" D. 9w LED module, 3000K, 90 CRI, 623 source lumens.



P560259-031-30 Textured Black 6.25" sq., 2.25" D. 9w LED module, 3000K,





All fixtures:







Strata LED



Antique Bronze



hite C





Metallic Gray

P560090-030-30K White 6.5" W., 5.5" ht. 12w integrated LED, 3000K, 90 CRI, 825 delivered lumens.



P560090-082-30K Metallic Gray 6.5" W., 5.5" ht. 12w integrated LED, 3000K, 90 CRI, 825 delivered lumens.



P560090-020-30K Antique Bronze

6.5" W., 5.5" ht. 12w integrated LED, 3000K, 90 CRI, 825 delivered lumens.



P560090-031-30K Black 6.5" W., 5.5" ht. 12w integrated LED, 3000K, 90 CRI, 825 delivered lumens.



All fixtures:





Textured Black



Cornice LED

P5634-2030K9 Antique Bronze 5.25" W., 4.75" ht. 9w LED module, 3000K, 623 source lumens.



P5634-3130K9 Textured Black 5.25" W., 4.75" ht. 9w LED module, 3000K, 623 source lumens.



Antique Bronze

P5635-2030K9 Antique Bronze 6.12" W., 5" ht. 9w LED module, 3000K, 623 source lumens.



P5635-3130K9 Textured Black 6.12" W., 5" ht. 9w LED module, 3000K, 623 source lumens.









3" Round Aluminum Cylinders



Antique Bronze









Satin Nickel

P563000-020-30K Antique Bronze P563000-030-30K White P563000-143-30K Graphite P563000-147-30K Satin Nickel 5.5" W., 5.62" ht. 12w integrated LED, 3000K, 90 CRI, 900 delivered lumens.

















5" Round Aluminum Cylinders



Antique Bronze





Metallic Gray

P5674-20 Antique Bronze P5674-30 White P5674-31 Black P5674-82 Metallic Gray 5" W., 7.5" ht. PAR30 Lamp, 75w max. or BR30 Lamp, 65w max.





All fixtures:







5" Round Non-Metallic Cylinders







P5712-30 White P5712-31 Black 5" W., 7.25" ht. PAR30 Lamp, 75w max. or BR-30 Lamp, 65w max.









5" Round Aluminum Cylinders with Photocell



Antique Bronze





P550101-020-30 Antique Bronze P550101-031-30 Black 5" W., 7.25" ht. 18.6w integrated LED, 3000K, 90 CRI, 511 delivered lumens.













6" Round Aluminum Cylinders



Antique Bronze



White





Metallic Gray

P5641-20 Antique Bronze

P5641-30 White

P5641-31 Black

P5641-82 Metallic Gray

6" W., 12" ht.

PAR38 Lamp, 250w max. or BR40 Lamp, 150w max.

P5641-20/30K Antique Bronze

P5641-30/30K White

P5641-31/30K Black

P5641-82/30K Metallic Gray

6" W., 12" ht.

29w integrated LED, 3000K, 90 CRI, 1800 delivered lumens.

All fixtures:















T24 () (T)

6" Round Aluminum Cylinders with Photocell



Antique Bronze



Black

P550103-020-30 Antique Bronze P550103-031-30 Black 6" W., 12" ht. 32.5w integrated LED, 3000K, 90 CRI. 953 delivered lumens.











6" Square Aluminum Cylinders



Antique Bronze



White



Black



Metallic Gray

P5643-20 Antique Bronze

P5643-30 White

P5643-31 Matte Black

P5643-82 Metallic Gray

6" W., 12" ht.

PAR38 Lamp, 250w max. or BR40 Lamp, 150w max.

P5643-20-30K Antique Bronze P5643-30-30K White

P5643-31-30K Black

P5643-82-30K Metallic Gray

6" W., 12" ht.

29w integrated LED, 3000K,

90 CRI, 1800 delivered lumens.

All fixtures:









3" Round Aluminum Cylinders



Antique Bronze





Graphite



Satin Nickel

P563001-020-30K Antique Bronze P563001-030-30K White P563001-143-30K Graphite P563001-147-30K Satin Nickel 5.5" W., 8.25" ht. 24w integrated LED, 3000K, 90 CRI, 1800 delivered lumens..

















5" Round Aluminum Cylinders



Antique Bronze



Black

Metallic Gray

P5675-20 Antique Bronze P5675-30 White P5675-31 Black P5675-82 Metallic Gray 5" W., 14" ht. 2 PAR30 Lamps, 75w max.

P5675-20/30K Antique Bronze P5675-30/30K White **P5675-31/30K** Black **P5675-82/30K** Metallic Gray 5" W., 14" ht. 34w integrated LED, 3000K, 90 CRI, 1025 delivered lumens.









All fixtures:





Compatible Accessories



White



TOP COVER LENS

Adapts up/down fixtures for wet location use. Heat & shatter-resistant clear tempered lens with metal trim.

P860045-030 White P860045-031 Black 5" dia., 0.83" ht.





5" Round Non-Metallic Cylinders



White



Black

P5713-30 White P5713-31 Black 5" W., 14" ht. 2 PAR30 Lamps, 75w max. or 2 BR-30 Lamps, 65w max.







5" Round Aluminum Cylinders Wet Location



Antique Bronze



Black

P560290-020 Antique Bronze P560290-031 Black 5" W., 7.25" ht. 2 PAR30 Lamps, 75w max.

P560291-020-30 Antique Bronze P560291-031-30 Black 5" W., 7.25" ht. 37.2w integrated LED, 3000K, 90 CRI, 730 delivered lumens.







Wet location lens included.

All fixtures:





5" Round Aluminum Cylinders with Photocell



Antique Bronze



P550102-020 Antique Bronze P550102-031 Black 5" W., 14" ht.

36.9w integrated LED, 3000K, 90 CRI, 819 delivered lumens.











Wet location lens included.

6" Round Aluminum Cylinders



Antique Bronze





Black



Metallic Gray

P5642-20 Antique Bronze

P5642-31 Black

P5642-82 Metallic Gray

6" W., 18" ht.

2 PAR38 Lamps, 250w max or 2 BR40 Lamps, 150w max.

P5642-20/30K Antique Bronze

P5642-30/30K White

P5642-31/30K Black

P5642-82/30K Metallic Gray

6" W., 18" ht.

58w integrated LED, 3000K,

90 CRI, 2150 delivered lumens.



All fixtures:





Compatible Accessories

TOP COVER LENS

Adapts up/down fixtures for wet location use. Heat & shatter-resistant clear tempered lens with metal trim.

P860046-030 White P860046-031 Black 6" dia., 0.79" ht.







Black

6" Round Aluminum Cylinders Wet Location



Antique Bronze



P560292-020 Antique Bronze P560292-031 Black

6" W., 18" ht.

2 PAR38 Lamps, 250w max.

P560293-020-30 Antique Bronze P560293-031-30 Black

6" W., 18" ht.

64w integrated LED, 3000K, 90 CRI, 1833 delivered lumens.





Wet location lens included

All fixtures:





6" Round Aluminum Cylinders with Photocell

Antique Bronze



031 Black

P550104-020-30 Antique Bronze P550104-031-30 Black

6" W., 18" ht.

65.2w integrated LED, 3000K, 90 CRI, 1582 delivered lumens











Wet location lens included.

6" Square Aluminum Cylinders



Antique Bronze



White





Metallic Gray

P5644-20 Antique Bronze

P5644-30 White

P5644-31 Matte Black

P5644-82 Metallic Gray

6" W., 18" ht.

2 PAR38 Lamps, 250w max or

2 BR40 Lamps, 150w max.

P5644-20-30K Antique Bronze

P5644-30-30K White

P5644-31-30K Black

P5644-82-30K Metallic Gray

6" W., 18" ht.

58w integrated LED, 3000K, 90 CRI, 1800 delivered lumens.

All fixtures:





Compatible Accessories

TOP COVER LENS

Adapts up/down fixtures for wet location use. Heat & shatter-resistant clear tempered lens with metal trim.









030 White



Black

P860047-030 White P860047-031 Black 6" sq., 0.77" ht.





6" Square Aluminum Cylinders Wet Location



Antique Bronze



Black

P560294-020 Antique Bronze P560294-031 Black 6" W., 18" ht.

2 PAR38 Lamps, 250w max.

P560295-020-30 Antique Bronze P560295-031-30 Black 6" W., 18" ht. 64w integrated LED, 3000K, 90 CRI, 3641 delivered lumens.

All fixtures:











Wet location lens included.

Ceiling Mount Down Cylinders

3" Round Aluminum Cylinders



Antique Bronze



White



alternate view

P550140-020 Antique Bronze P550140-030 White P550140-031 Black 5.06" W., 7.37" ht. A19 or PAR20 Lamp, 60w max.

P550139-020-30 Antique Bronze P550139-030-30 White P550139-031-30 Black 5.06" W., 7.37" ht. 12w integrated LED, 3000K, 90 CRI, 986 delivered lumens.











5" Round Aluminum Cylinders



Antique Bronze



Black



Metallic Gray

P5774-20 Antique Bronze P5774-30 White P5774-31 Black 5" dia., 6.75" ht.

1 medium base, 75w max.

P5774-20/30K Antique Bronze P5774-30/30K White P5774-31/30K Black P5774-82/30K Metallic Gray

5" dia., 6.5" ht. 17w integrated LED, 3000K, 90 CRI, 764 delivered lumens.









All fixtures:





6" Round Aluminum Cylinders



Antique Bronze





Black



Metallic Gray

P5741-20 Antique Bronze **P5741-30** White

P5741-31 Black

6" dia., 12" ht. PAR38 Lamp, 250w max or BR40 Lamp, 150w max.

P5741-20/30K Antique Bronze P5741-30/30K White **P5741-31/30K** Black **P5741-82/30K** Metallic Gray 6" dia., 12" ht. 29w integrated LED, 3000K,

90 CRI, 1800 delivered lumens.









All fixtures:





Compatible Accessories

sections with coupling. Not compatible with P5774.

P8741-20 Antique Bronze P8741-30 White P8741-31 Black 5" dia., 18" ht.

















Pendant kit adapts P5741 ceiling fixture to 6", 12" or 18" stem mounting. Includes canopy, hang-straight swivel, 6" and 12"





Cord Suspended Down Cylinders



Compatible Accessories

ALUMINUM CYLINDER ACCESSORIES

150" cord replacement kit for P500355, P500356, P550099 and P550100.



(030)

White

Black

Non-Metallic Par Lampholders





White



Black

*P5202-20 Antique Bronze P5202-31 Black 6.25" dia., 11.31" ht. PAR38 Lamp, 150w max.



P5203-20 Antique Bronze **P5203-30** White ***P5203-31** Black 22.5" W., 11.31" ht. 2 PAR38 Lamps, 150w max.



P5207-30 White 13" W., 5.75" ht. 2 PAR20, PAR30, or PAR38 Lamps, 150w max.



P5212-30 White ***P5212-20** Antique Bronze 11" W., 4.62" ht. 2 PAR38 Lamps, 120w max.



P5214-30 White 5.78" dia., 3.90" ht. PAR lampholder shroud.



P5212-30 shown with P5214-30 shroud



*Shown in finish All fixtures:



Door Chime



White

Includes transformer, chime assembly and lighted push button.

PC001-30 White 4" dia., 7.18" ht.



Address Lights

31 Textured Black

Long lamp life (50,000 hours) and weather resistant. Housing constructed from high-grade polypropylene. Stainless steel mounting hardware and lamps included. Complies with municipal codes that require illuminated house numbers. Order 16V transformer separately.

Address Light Housing

Numbers, letters and blanks must be ordered separately from address light fixture.

P5968-31WB Textured Black 12.5" W., 6.75" ht. 2 miniature wedge 5w max.



Address Light Transformer

P5969-01 Unfinished 1.81" W., 2.56" ht.



Address Numbers

Numbers, letters and blanks must be ordered separately from address light fixture, P5968. Ten numbers per pack.

PRODUCT NO.	DESCRIPTION	SIZE						
P5970-000	0	2.25" W., 5" ht.						
P5970-001	1			_			_	
P5970-002	2		$\mathbf{\Lambda}$	1			Л	
P5970-003	3					_ 5	4	7
P5970-004	4					U	T	V
P5970-005	5							
P5970-006	6 or 9							
P5970-007	7							
P5970-008	8			7	0	7		
P5970-HLF	1/2		n		7	$\overline{}$		
P5970-FBK	Full Blank					2		
P5970-HBK	Half Blank	1.12" W., 5" ht.						

Photo Control

Remote mount photo control installs into standard, rain-tight junction box and includes faceplate and gasket. Max load 2000 watts.

PTORK3010 Stainless Steel 3" W., 5.62" ht.



Post Lantern Accessories





Textured Black

Aluminum base for installation of post lanterns on brick columns or similar structure - use in place of lantern post.

P8726-20 Antique Bronze 7" dia., 3.25" ht.



P8726-31 Textured Black 7" dia., 3.25" ht.



Cast aluminum base for surface mounting 3" dia. lantern post. Anchor bolts and Allen set screws included.

P8748-31 Textured Black 8" dia., 5" ht.



Night Saver® Shield



Antique Bronze



Textured Black

Shield fits over A-19 medium base bulb to provide Dark Sky friendly illumination.

P8709-20 Antique Bronze **P8709-31** Textured Black 2.87" dia., 5" ht.







P8400-31 Black 4" dia., 5.87" ht.





FIXTURE COMPATIBILITY LIST FOR P8400

Collection Name

ESSENTIAL (page 698)

P6059 P6060

RESORT (page 679)

P5987

P5988

P5989

Posts

20 Antique Bronze

031

Textured Black

31

Matte Black

*P5390-20 Antique Bronze P5390-31 Matte Black 3" dia., 84" ht. Aluminum; can be field cut to desired height. **P5390-31PC** Matte Black 3" dia., 84" ht. Aluminum with photocell for automatic dusk to dawn operation; can be field cut to desired height. **P540005-031** Textured Black 3" dia., 84" ht. Fluted aluminum; can be field cut to desired height.

minum; can be field ired height.

P5391-31 Matte Black 3" dia., 84" ht. Aluminum with ladder rest; can be field cut to desired height. *P5391-20PC Antique Bronze P5391-31PC Matte Black 3" dia., 84" ht. Aluminum with ladder rest and photocell for automatic dusk to dawn operation; can be field cut to desired height.



P5392-31PC Matte Black 3" dia., 84" ht. Aluminum with ladder rest, GCO and photocell for automatic dusk to dawn operation; can be field cut to desired height.



P5394-31 Matte Black 3" dia., 144" ht. Commercial grade aluminum (0.125" wall thickness); can be field cut to desired height.

*Shown in finish





Functional

DISCOVER
THE LATEST



738 CATALOG 134

Recessed Downlighting

Everlume® Recessed LED

With a slim profile and using the latest LED technology, Everlume Recessed Downlights offer long lasting, energy saving and high quality illumination to homes and commercial spaces. Its edge-lit surface delivers low glare light. Its crisp white silhouette blends quietly into its surroundings. By eliminating the need for an additional recessed housing, Everlume Recessed Downlights are easily installed into new construction and remodel ceiling applications.

P807000-028-30 Satin White 4.72" dia., 1.13" ht. 10w integrated LED, 3000K, 90 CRI, 825 lumens









P807001-028-30 Satin White 7.16" dia., 1" ht. 12w integrated LED, 3000K, 90 CRI, 950 lumens





P807002-028-CS Satin White 7.16" dia., 1" ht. 12w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 825 lumens (at 3000K)





5-CCT

SELECTABLE



3000K

3500K 4000K 5000K











2700K Warm White

3000K Soft White

3500K **Bright White**

4000K Cool White

5000K Daylight

P807003-028-30 Satin White 7.16" dia., 1.81" ht. 12w integrated LED, 3000K 90 CRI, 925 lumens







P860062-000 26" L., 8.37" W. New construction mounting accessory



4" Recessed

Housings

For complete fixture, order housing with trim.

P804N-N-MD-ICAT Unfinished 5.86" L, 10.2" W., 6.3" ht. Medium base socket



New Construction Air-Tight IC and Non-IC with E26 socket

P804N-N-MD-AT Unfinished 5.99" L, 8.51" W., 5.52" ht. Medium base socket



New Construction Air-Tight Non-IC with E26 socket

P804N-R-MD-AT Unfinished 4.81" dia.. 11.33" W.. 5.52" ht. Medium base socket



Remodel Air-Tight Non-IC with E26 socket

HOUSING SPECIFICATIONS

- Suitable for 2x6 & 2x8 ceilings
- Insulation Contact & Non-IC contact options
- Airtight per ASTM E283 requirements
- · Installs to ceiling thickness from ½" to 1 ¼"
- Compatible with A19, PAR20, & R20 lamps
- · Provided with push in wire connectors
- Hanger bar max. span 24"

IC Trims and Non-IC Trims

P804000-020 Antique Bronze P804000-028 Satin White P804000-031 Black 4.98" dia., 2.19" ht. PAR20 lamp, 50w max.









P804001-028 Satin White 5" dia., 3.45" ht. PAR20 lamp, 50w max.





P804002-028 Satin White 5" dia., 3.45" ht. PAR20 lamp, 50w max.





P804003-028 Satin White 4.98" dia., 2.8" ht. PAR20 lamp, 50w max.





P804004-028 Satin White 4.98" dia., 3" ht. PAR20 lamp, 35w max.





LED Trims

P800022-028-CS Satin White P800022-020-CS Antique Bronze P800022-031-CS Black 5.71" dia., 3.21" ht. 8w integrated LED,










2700K, 3000K, 3500K, 4000K, 5000K







P800022-031-CS shown adjusted





5" Recessed

Housings

For complete fixture, order housing with trim.

P851-ICAT Unfinished 14.75" L, 13.25" W., 7.25" ht. Medium base socket



New Construction Air-Tight IC with E26 socket

P851-ICAT HOUSING FEATURES

- Rated for direct contact with insulated ceiling.
- Meets ASTM-E283 air flow requirements.
- Adjustable housing to accommodate ceiling thickness 1/2" to 1-1/2".
- Bar hangers with integral nail, can be installed up to 24" joists.
- · Use with compatible items only.

P1851-ICAT Unfinished 12.12" L, 6" W., 7.18" ht. Medium base socket



Remodel Air-Tight IC with E26 socket

P1851-ICAT HOUSING FEATURES

- Rated for direct contact with insulated ceiling.
- Meets ASTM-E283 air flow requirements.
- Adjustable housing to accommodate ceiling thickness 1/2" to 1-1/2".

IC Trims and Non-IC Trims

6.5" outside diameter. Can also be used with P851-ICAT.

P868-28 White **P868-31** Black 6.5" dia., 4.75" ht. 50w max. PAR30/R30







P8268-21 Clear Alzak **P8268-28** Satin White 6.5" dia., 4.75" ht. 50w max. PAR30/R30







LED Trims Can be used with standard and shallow 5" recessed housings.

P800002-028-30 Satin White 7.5" dia., 2.5" ht. 8w integrated LED, 3000K 90 CRI, 759 delivered lumens.









P800021-028-30 Satin White 7.5" dia., 3.38" ht. 13w integrated LED, 3000K 90 CRI, 1356 delivered lumens.









P800018-020-CS Antique Bronze **P800018-028-CS** Satin White **P800018-031-CS** Black 7.75" dia., 4" ht.

8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K 90 CRI, 698 delivered lumens.











P800019-028-CS Satin White 7.38" dia., 3.44" ht. 8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 771 delivered lumens.














5" Shallow Recessed

Housings

For complete fixture, order housing with trim.

P841-ICAT Unfinished 13.18" L, 14.76" W., 5.35" ht. Medium base socket



New Construction Air-Tight IC with E26 socket

P841-ICAT HOUSING FEATURES

- · Rated for direct contact with insulated ceiling.
- · Meets ASTM-E283 air flow requirements.
- · Adjustable housing to accommodate ceiling thickness 1/2" to 1-1/2".
- Use with compatible items only.



P1841-ICAT Unfinished 12.12" L, 6" W., 5.37" ht. Medium base socket



Remodel Air-Tight IC with E26 Socket

P1841-ICAT HOUSING FEATURES

- · Rated for direct contact with insulated ceiling.
- Meets ASTM-E283 air flow requirements.
- · Adjustable housing to accommodate ceiling thickness 1/2" to 1-1/2".
- · Use with compatible items only.

IC Trims and Non-IC Trims

6.5" outside diameter. Can also be used with 5" standard height recessed housings.

6.5" dia., 3.75" ht. 50w max. PAR 30 Wet location listed when used with an outdoor rated PAR30* *WL trims require use with outdoor rated PAR lamps



P876-28 White 6.5" dia., 2.62" ht. 75w max. PAR30



P8475-28 Satin White 6.5" dia., 3.7" ht. 50w max. PAR30/R30 Compatible with P851-ICAT and P1841-ICAT





LED Trims Can be used with standard and shallow 5" recessed housings.

P800002-028-30 Satin White 7.5" dia., 2.5" ht. 8w integrated LED, 3000K 90 CRI, 759 delivered lumens.









P800021-028-30 Satin White 7.5" dia., 3.38" ht. 13w integrated LED, 3000K 90 CRI, 1356 delivered lumens.









P800018-020-CS Antique Bronze P800018-028-CS Satin White P800018-031-CS Black 7.75" dia., 4" ht.

8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K 90 CRI, 698 delivered lumens.











P800019-028-CS Satin White 7.38" dia., 3.44" ht. 8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI. 771 delivered lumens.
















5" Recessed LED

LED Housings

For complete fixture, order housing with trim.

P1841-LED Unfinished 12.12" L, 6" W., 5.37" ht. **LED Connector**




Remodel Air-Tight IC with LED Quick Connect

P1841-LED HOUSING FEATURES

- · Rated for direct contact with insulated ceiling.
- Adjustable housing to accommodate ceiling thickness 1/2" to 1-1/2"
- Meets ASTM-E283 air flow requirements.

5" LED Round Trim

P8061-28-30K Satin White 6.34" dia., 4" ht. 10.5w integrated LED, 3000K, 90 CRI, 700 lumens.









COMPATIBLE RECESSED HOUSINGS

P851-ICAT P1851-ICAT P1841-LED P1841-ICAT

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8061 TRIM FEATURES

- The trim is equipped with both Edison base adapter and quick link connector allowing easy installation in many standard medium based socket recessed housings and Progress LED recessed housings.
- A polycarbonate diffused lens reduces glare and pixilation from LEDs.
- Trim uses friction springs for easy installation into recessed housings.
- cCSAus Listed for Wet Locations, Energy Star.
- Flicker free dimming down to 10% with many Triac or ELV dimmers.
- Suitable for use in IC and Non IC applications.
- LEDs are 3000K, CRI 90+ and rated for 50,000 hours.

6" Recessed

Housings

For complete fixture, order housing with trim.

P806N-N-MD-ICAT Unfinished 6.61" L, 9.4" W., 7.37" ht. Medium base socket



New Construction Air-Tight IC and Non-IC with E26 socket

P806N-R-MD-ICAT Unfinished 7.2" L, 12.9" W., 7.4" ht. Medium base socket.



Remodel Air-Tight IC and Non-IC with E26 socket

HOUSING SPECIFICATIONS

- Standard height for 2x8 ceilings
- IC Rated for Insulation Contact
- Airtight per ASTM E283 requirements
- Installs to ceiling thickness from ½" to 1 ¼"
- Compatible with A19, PAR30, R30, BR30, PAR38 & BR40 lamps
- · Provided with push in wire connectors
- Hanger bar max. span 24"

IC Trims and Non-IC Trims

P806000-020 Antique Bronze P806000-028 Satin White P806000-031 Black 7.28" dia., 4.87" ht. PAR38 lamp, 90w max.







P806001-028 Satin White P806001-031 Black 7.29" dia., 4.87" ht. PAR38 lamp, 90w max.





P806002-028 Satin White 8" dia., 5.17" ht. PAR38 lamp, 90w max.



P806004-028 Satin White 8.23" dia., 1.25" ht. A19 lamp, 40w max.



P800020-028 Satin White 7.75" dia., 4" ht.





P806003-028 Satin White 7.29" dia., 4.87" ht. PAR38 lamp, 90w max.



P806005-028 Satin White 7.5" dia., 2.5" ht. A19 lamp, 40w max.





PAR30 lamp, 75w max.





P800002-028-30 Satin White 7.5" dia., 2.5" ht. 8w integrated LED, 3000K 90 CRI, 759 delivered lumens.









P800018-020-CS Antique Bronze P800018-028-CS Satin White P800018-031-CS Black

7.75" dia., 4" ht. 8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K 90 CRI, 698 delivered lumens.











P800019-028-CS Satin White 7.38" dia., 3.44" ht. 8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 771 delivered lumens.











P800021-028-30 Satin White 7.5" dia., 3.38" ht. 13w integrated LED, 3000K 90 CRI, 1356 delivered lumens.









6" Shallow Recessed

Housings

For complete fixture, order housing with trim.

P806S-N-MD-ICAT Unfinished 6.6" L, 9.4" W., 5.6" ht. Medium base socket



New Construction Air-Tight IC and Non-IC with E26 socket

P806S-R-MD-ICAT Unfinished 7.2" L, 12.9" W., 5.6" ht. Medium base socket



Remodel Air-Tight IC and Non-IC with E26 socket

HOUSING SPECIFICATIONS

- · Shallow height for 2x6 ceilings
- IC Rated for Insulation Contact
- Airtight per ASTM E283 requirements
- Installs to ceiling thickness from $\frac{1}{2}$ " to 1 $\frac{1}{4}$ "
- Compatible with A19, PAR30, & R30 lamps
- · Provided with push in wire connectors
- Hanger bar max. span 24"

IC Trims and Non-IC Trims

P806006-028 Satin White P806006-031 Black 7.31" dia., 3.75" ht. 1 medium base, 50w max. PAR30S lamp, 50w max.



P806007-028 Satin White 7.31" dia., 3.75" ht. 1 medium base, 50w max. PAR30S lamp, 50w max.







6" Shallow Recessed LED

Housings

For complete fixture, order housing with trim.

P871-LED-001 Unfinished 9.41" L, 6.61" W., 5.55" ht. LED Connector



New Construction Air-Tight IC and Non-IC with LED Quick Connect

P1871-LED-001 Unfinished 11.93" L, 7.16" W., 5.55" ht. **LED Connector**



Remodel Air-Tight IC and Non-IC with LED Quick Connect

HOUSING SPECIFICATIONS

- · Shallow height for 2x6 and 2x8 ceilings
- IC Rated for Insulation Contact
- Airtight per ASTM E283 requirements
- Installs to ceiling thickness from $\frac{1}{2}$ " to 1 $\frac{1}{4}$ "
- Compatible with LED trims
- Provided with push in wire connectors
- Hanger bar max. span 24"



LED Quick Connector

LED Trims

P800002-028-30 Satin White 7.5" dia., 2.5" ht. 8w integrated LED, 3000K 90 CRI, 759 delivered lumens.











P800018-020-CS Antique Bronze P800018-028-CS Satin White P800018-031-CS Black

7.75" dia., 4" ht. 8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K 90 CRI, 698 delivered lumens.











P800019-028-CS Satin White 7.38" dia., 3.44" ht. 8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 771 delivered lumens.











P800021-028-30 Satin White 7.5" dia., 3.38" ht. 13w integrated LED, 3000K 90 CRI, 1356 delivered lumens.









6" Sloped Recessed

Housings

For complete fixture, order housing with trim.

P806A-N-MD-ICAT Unfinished 10.3" L, 13.4" W., 7.9" ht. Medium base socket



New Construction Air-Tight IC and Non-IC with E26 socket

P806A-N-MD-AT Unfinished 10.3" L, 13.4" W., 7.5" ht. Medium base socket



New Construction Air-Tight Non-IC with E26 socket

P806A-R-MD-AT Unfinished 6.6" L, 13.1" W., 8.2" ht. Medium base socket



Remodel Air-Tight Non-IC with E26 socket

HOUSING SPECIFICATIONS

- Angled for slope ceiling installation
- Lamp socket adjusts to accommodate 2/12 to 7/12 ceiling pitches
- Insulation Contact & Non-IC contact options
- Airtight per ASTM E283 requirements
- Installs to ceiling thickness from $\frac{1}{2}$ " to
- Compatible with PAR30, & R30 lamps
- Provided with push in wire connectors
- Hanger bar max. span 24"

IC Trims and Non-IC Trims

P806008-020 Antique Bronze **P806008-028** Satin White **P806008-031** Black 8.12" dia., 3.62" ht. PAR30 lamp, 75w max.









Intrinsic Recessed LED

Elevate any room's design with the Intrinsic Recessed LED collection, offered in smooth or baffle trim design options. The simple, classic design and adjustable mounting options of these light fixtures provide easy installation in a variety of 5-inch and 6-inch recessed housings. The trims are preset to work with 6-inch recessed housings out of the box and are provided with an E26 medium base socket adaptor.

Smooth

A smooth polycarbonate trim ring houses an integrated LED light ready to emit general ambient lighting. The non-metallic construction is a dead front design that will not corrode. Torsion spring mounting provides easy installation into most 5-inch and 6-inch recessed housings.

P800002-028-30 Satin White 7.4" dia., 2.36" ht. 8w integrated LED, 3000K, 90 CRI, 759 lumens.







COMPATIBLE RECESSED HOUSINGS

 P851-ICAT
 P806N-N-MD-ICAT

 P1851-ICAT
 P806N-R-MD-ICAT

 P841-ICAT
 P806S-N-MD-ICAT

 P1841-ICAT
 P806S-R-MD-ICAT

P871-LED-001 P1871-LED-001

Baffle 5-CCT

The baffle trim reduces glare and provides a familiar and classic look. The 5-CCT selectable LED light engine offers flexibility in application, allowing the choice of 5 different color temperatures: warm, soft, bright, cool or daylight. Select the best lighting color to highlight the décor or to match the function of the space. The friction spring mounting allows for universal installation into most 5-inch and 6-inch recessed housings.

P800019-028-CS Satin White 7.4" dia., 3.44" ht. 8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 771 lumens (at 3000K).











COMPATIBLE RECESSED HOUSINGS


 P851-ICAT
 P806N-N-MD-ICAT

 P1851-ICAT
 P806N-R-MD-ICAT

 P841-ICAT
 P806S-N-MD-ICAT

 P1841-ICAT
 P806S-R-MD-ICAT

P871-LED-001 P1871-LED-001













2700K Warm White **3000K** Soft White **3500K** Bright White **4000K** Cool White **5000K** Daylight

Intrinsic Recessed LED

High Lumen

Achieve your design vision with our Intrinsic High Lumen LED. The The simple, classic design and 5 - 6 in. adjustability of this light fixture can easily be installed into a variety of style applications in both residential and light commercial settings. The baffle trim ring surrounds an integrated LED 1000 lumen light engine ready to emit bright, functional light.

P800021-028-30 Satin White 7.43" dia., 3.4" ht. 13W integrated LED, 3000K, 90 CRI, 1356 lumens









Eyeball 5-CCT

The smooth metal trim provides an elevated look. The adjustable light source can be aimed allowing the trim to be used as a standard downlight, accent light, wall wash or sloped ceiling light. This unique design allows the adjustable light source to remain hidden within the trim, allowing for the cleanest appearance. An integrated ceiling pitch indicator makes adjusting the light to match the ceiling pitch easy. The 5-CCT selectable LED light engine offers flexibility in application, allowing for the choice of 5 different color temperatures: warm, soft, bright, cool or daylight.

P800018-028-CS Satin White P800018-020-CS Antique Bronze P800018-031-CS Black 7.72" dia., 3.94" ht. 8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 750 lumens (at 3000K).







COMPATIBLE RECESSED HOUSINGS

P851-ICAT P806N-N-MD-ICAT P1851-ICAT P806N-R-MD-ICAT P841-ICAT P806S-N-MD-ICAT P1841-ICAT P806S-R-MD-ICAT

P871-LED-001 P1871-LED-001


P800022-028-CS Satin White P800022-020-CS Antique Bronze P800022-031-CS Black

5.71" dia., 3.217" ht. 8w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K 90 CRI, 800 lumens (at 3000K).



















2700K Warm White

3000K Soft White

3500K Bright White

4000K Cool White 5000K Daylight

All fixtures:









Recessed Accessories

P8587-01 Unfinished 7.5" dia., 0.12" ht. 6" ceiling gasket Ceiling gasket seals housing to drywall opening for Washington State Energy Code compliance.



P8585-01 White 8.87" dia., 0.06" ht. Goof Ring for use with any recessed trim with a 7.75" OD.



P8773-01

Four mounting clips and screws for T-Bar ceilings for any new construction recessed product using bar hangers.



Recessed Enclosure for Non-IC Housings in IC applications

P8555-01 White 24.5" W., 35" ht. Creates a barrier to prevent insulation from making contact with recessed fixtures.

Note: The P8555-01 does not make recessed housings IC-rated.

FEATURES

- Material is Coroplast™, which is made from polypropylene co-polymer resin.
- Deflection temperature F(@66psi) = 194 (90°C).
- Melting point = 162°C, 324°F.
- Normal termperature performance range = -17°F to 160°F.
- MSDS available upon request.

APPLICATION

• Requires no insulation on top.



Surface Mount Downlighting



Intrinsic Surface Mount LED

Elevate your design vision with just the flip of a switch with our Intrinsic Surface Mount LED Collection. The simple, classic design of these light fixtures can easily be installed into a variety of style applications in both residential and commercial settings. We offer two different sizes of surface mounts, both coated in a crisp white finish, to meet your unique design needs. Each smooth trim ring surrounds an integrated LED light fixture ready to emit general ambient lighting wherever it calls home in your design plan.

P810012-028-30 Satin White 5.5" dia., 1" ht. 12w integrated LED, 3000K, 90 CRI, 600 lumens.



P810013-028-30 Satin White 7.5" dia., 1.18" ht. 15.5w integrated LED, 3000K, 90 CRI, 1000 lumens.

LED FEATURES

- · Wet location listed.
- · 120v input voltage.
- 60 Lumens per watt.
- · Flicker-free dimming with many Triac and ELV dimmers. 50,000 hour life.



All fixtures:







CCT Selectable

Achieve your design vision with our 5-CCT selectable 7.5" Intrinsic Surface Mount LED. The simple, classic design of this light fixture can easily be installed into a variety of style applications in both residential and light commercial settings. The smooth trim ring surrounds an integrated 5-CCT LED light fixture ready to emit ambient lighting wherever it calls home in your design plan.

P810035-028-CS Satin White 7.5" dia., 1.34" ht. 15.5w integrated LED, 2700K, 3000K, 3500K, 4000K and 5000K 90 CRI, 1110 lumens.














Intrinsic Directional Surface Mount LED

The Intrinsic Surface Mount Eyeball LED represents the ultimate in design flexibility and ease of installation. Installation to a standard height junction box is made easy with the intuitive snap spring design. Suitable for residential and commercial needs, its clean profile elegantly accents the ceiling while the light can be adjusted to offer standard downlight, accent light, wall washer or sloped ceiling light. An integrated ceiling pitch indicator makes adjusting the light to match the ceiling pitch easy.

P810029-020-030 Antique Bronze P810029-028-30 Satin White P810029-031-30 Black 7.25" dia., 1.54" ht. 15.5w integrated LED, 3000K, 90 CRL 1000 lumens.













Emblem Surface Mount LED

Easy installation and a sleek, modern lighting aesthetic are offered by our Emblem Surface Mount LED Collection. An excellent choice for general ambient lighting, each polished design features a smooth, slightly tapered trim ring surrounding a single, integrated LED light source. Enjoy the unmatched level of glare control offered by the fixture's diffused polycarbonate lens that also hides any unwanted LED pixelation. Each light fixture is home to an integrated AC LED light engine that seamlessly installs to a variety of ceiling pan junction boxes to give you added flexibility when it comes to creating your design vision. The surface mount provides unparalleled longevity with its, 50,000hour LED life span and 80% energy savings.

LED FEATURES

- · Wet location listed.
- · 120v input voltage.
- 60 Lumens per watt.
- · Flicker-free dimmingwith many Triac and ELV dimmers. 50,000 hour life.



Shown installed into 1/2" ceiling pan J-box

P810027-020-30 Antique Bronze P810027-028-30 Satin White 5.5" dia., 1.87" ht. 12.5w integrated LED, 3000K, 90 CRI, 750 lumens.





P810014-020-30 Antique Bronze P810014-028-30 Satin White 7.25" dia., 1.37" ht. 15.5w integrated LED, 3000K, 90 CRI, 1080 lumens.





All fixtures:







Round Surface Mount LED

P8222-28-30K White 7.25" dia., 1.25" ht. 17w LED integrated, 3000K, 90 CRI, 1170 lumens.









Decorative Surface Mount LED

Get the perfect lighting for any situation or task with our Decorative Surface Mount Triac Dimming Collection. This collection offers a flicker-free dimming lighting solution that allows the fixture to dim down to 10% with many Triac or forward phase dimmers. Choose from two different sizes of round surface mounts, each in a beautiful brushed nickel finish and trimmed with etched glass for an added level of aesthetic appeal.

P8247-09-30K Brushed Nickel 5.5" dia., 1.5" ht. 10.5w integrated LED, 3000K, 90 CRI, 690 lumens, 66 lumens per watt. Triac/ELV dimming



P8147-09-30K Brushed Nickel 7.25" dia., 2.75" ht. 16.4w integrated LED, 3000K, 90 CRI 1035 lumens, 63 lumens per watt. Triac/FLV dimming



All fixtures:







Retrofit Recessed Accessories

P8595-01 Unfinished 5.18" L, 5.18" W., 3.56" ht. Recessed mounting accessory for P810014, P8147 and P8222 series. Allows for installation in 6" housings. Edison base adapter included.



Everlume® Linear Panel LED

The Everlume™ Linear Panel LED is a modern take on a classic rectangular wrap frame. Its clean low-profile design has a frosted polycarbonate diffuser lit by LEDs along the perimeter of the fixture. Light is diffused through a light guide, providing even illumination without dark spots, shadow or glare. Hardware and fasteners are not visible after installation, providing a clean appearance. The fixture can be mounted to off-centered junction boxes making aligning multiple fixtures on center easy. This product is a great addition to laundry rooms, kitchens, walk in closets, garages and basements.

P810032-028-30 Satin White 23.75" L, 11.93" W., 1.24" ht. 21w integrated LED, 3000K, 90 CRI, 1587 lumens.





LED FEATURES

- Flicker-free dimming with many Triac and ELV dimmers.
- · 120v input voltage.
- 50,000 hour life.

P810033-028-30 Satin White 47.75" L, 11.93" W., 1.24" ht. 43w integrated LED, 3000K, 90 CRI, 3181 lumens.

All fixtures:











Everlume® Square Surface Mount LED

Edgelit technology creates a large glare free and evenly illuminated surface for a variety of applications for both residential and commercial applications. Offering a low profile design, LED EverlumeTM Square Surface Mount is available in three sizes: 7'', 11'', and 14'', in a White finish. The integrated driver does not recess into junction box, allowing for easy installation into 4'' octagonal, 4'' round PVC and 4'' x 1/2'' ceiling pan junction boxes. Wet location listed and offers a 50.000-hour LED life.

LED FEATURES

- · Wet location listed.
- 120v input voltage.
- Flicker-free dimming with many Triac and ELV dimmers.
- 50,000 hour life.



P810019-030-30 White

7" sq., 1.13" ht. 15w integrated LED, 3000, 90 CRI, 1100 lumens.



P810020-030-30 White 11" sq., 1.13" ht. 17w integrated LED, 3000, 90 CRI, 1400 lumens.



P810021-030-30 White

14" sq., 1.13" ht. 20w integrated LED, 3000, 90 CRI, 1600 lumens.



All fixtures







Everlume® Square Trim Accessories

Design the perfect lighting aesthetic for any residential or commercial setting with our Everlume™ Square Trim Accessories collection. We offer a variety of finishes and square trim sizes to best fit your unique design. Each square trim is easy to install and can make an excellent addition to a variety of style settings.

Compatible with P810019-030-30 **P860053-009** Brushed Nickel **P860053-020** Antique Bronze **P860053-031** Black









Compatible with P810020-030-30 **P860054-009** Brushed Nickel **P860054-020** Antique Bronze

P860054-031 Black

11" sq., 1.12" ht.







Compatible with P810021-030-30 **P860055-009** Brushed Nickel **P860055-020** Antique Bronze **P860055-031** Black

14" sq., 1.12" ht.







Everlume® Round Surface Mount LED

Edgelit technology creates a large glare free and evenly illuminated surface for a variety of applications for both residential and commercial applications. Offering a low profile design, LED Everlume™ Round Surface Mount is available in a White finish. The integrated driver does not recess into junction box, allowing for easy installation into 4" octagonal, 4" round PVC and 4-1/2" ceiling pan junction boxes. Wet location listed and offers a 50,000-hour LED life.

LED FEATURES

- · Wet location listed.
- Flicker-free dimming with many Triac and ELV dimmers.
- 120v input voltage.
- 50,000 hour life.



P810024-030-30 White

5" dia., 1.13" ht. 12w integrated LED 3000K, 90 CRI, 800 lumens.



P810015-030-30 White

7" dia., 1.13" ht. 15w integrated LED 3000K, 90 CRI, 1000 lumens.



P810016-030-30 White

11" dia., 1.13" ht. 17w integrated LED 3000K, 90 CRI, 1300 lumens.



P810017-030-30 White

14" dia., 1.13" ht. 19.5w integrated LED 3000K, 90 CRI, 1700 lumens.



P810018-030-30 White

18" dia., 1.13" ht. 23w integrated LED 3000K, 90 CRI, 2100 lumens.







Everlume® Round Trim Accessories

You'll never have to sacrifice function for style with our Everlume™ Round Trim Accessories. This collection offers a variety of finishes and trim ring sizes to best fit your unique design needs. Each trim ring is easy to install in both residential and commercial settings.

Compatible with P810024-030-30 P860048-009 Brushed Nickel P860048-020 Antique Bronze P860048-031 Black 5" dia., 1.12" ht.







Compatible with P810015-030-30 **P860049-009** Brushed Nickel **P860049-020** Antique Bronze **P860049-031** Black 7" dia., 1.12" ht.







Compatible with P810016-030-30 **P860050-009** Brushed Nickel **P860050-020** Antique Bronze **P860050-031** Black 11" dia., 1.12" ht.







Compatible with P810017-030-30 **P860051-009** Brushed Nickel **P860051-020** Antique Bronze **P860051-031** Black 14" dia., 1.12" ht.







Compatible with P810018-030-30 **P860052-009** Brushed Nickel **P860052-020** Antique Bronze **P860052-031** Black 18" dia., 1.12" ht.







756 CATALOG 134

Directionals

Ridgecrest



009 Brushed Nickel





Infuse an abundance of sophistication, versatility, and light to any commercial or residential setting with our Ridgecrest collection. Multi-directional lamp heads provide design flexibility and illuminate typically hard-to-reach areas. Select a brushed nickel, satin white, or black finish to best fit your design aesthetic. Each lamp head features a crisp frosted glass shade for soft, general ambient light.

P900011-009 Brushed Nickel P900011-028 Satin White P900011-031 Black 5" dia., 6.4" ht. 1 medium base lamp, 60w max.







P900012-009 Brushed Nickel P900012-028 Satin White **P900012-031** Black 26.1" L, 5" W., 7.17" ht. 4 medium base lamps, 60w max.



Kitson

009 Brushed Nickel



Satin White



Black

Incorporate a hint of stylish industrial light to any commercial or residential setting with our Kitson collection. Multi-directional lamp heads provide design flexibility and illuminate typically hard-to-reach areas, such as highlighting images in a lobby or gallery. Select a brushed nickel, satin white, or black finish to best fit your design aesthetic. Each lamp head features an industrial-styled shade with an outer ribbed design. Use with GU10 lamps to create different beam shapes as desired.

P900013-009 Brushed Nickel P900013-028 Satin White **P900013-031** Black 5" dia., 5.94" ht. 1 GU10 lamp, 50w max.







P900014-009 Brushed Nickel **P900014-028** Satin White **P900014-031** Black 26.1" L, 5" W., 6.46" ht. 4 GU10 lamps, 50w max.



Round Back Directionals



09 Brushed Nickel



White



Urban Bronze

P6144-30 White **P6144-174** Urban Bronze 5" dia., 7.25" ht. 1 PAR20 medium base lamp, 75w max.





P6147-09 Brushed Nickel **P6147-30** White **P6147-174** Urban Bronze 5" dia., 6.5" ht. 1 PAR20 medium base lamp, 50w max.







P6149-09 Brushed Nickel **P6149-30** White **P6149-174** Urban Bronze 9" dia, 6.5" ht. 2 PAR20 medium base lamps, 50w max.







P6160-09 Brushed Nickel **P6160-30** White **P6160-174** Urban Bronze 27.18" L, 6.56" W., 4.25" ht. 3 PAR20 lamps, 50w max.



Round Back Directionals



Brushed Nickel



Urban Bronze

P6162-09 Brushed Nickel **P6162-174** Urban Bronze 36" L, 4.25" W., 5.12" ht. 4 PAR20 lamps, 50w max.



On-Off Switch Round Back Directionals



09 Brushed Nickel



White

P6155-09 Brushed Nickel **P6155-30** White On/off switch. 5" dia., 6.81" ht. 1 PAR20 medium base lamp, 50w max.









Heat Lamp Flat Back Directionals



White

P6397-30 White Adjustable wall or ceiling heat lamp with black baffle. 5.75" dia., 8.12" ht. 1 BR-40 medium base lamp, 250w max.



760 CATALOG 134

Undercabinet

Shining Useful Light.

Which Hide-A-Lite[™] Fits?

There are two primary types of HIDE-a-LITE™ lighting: linear undercabinet, and tape. Linear undercabinet lighting evenly illuminates under the entire cabinet length. Tape lighting is flexible and can be used where space is limited, or where longer lengths of light are needed.

Quick Tip

Most rooms will need a combination of some or both of these types of task and ambient lighting. Begin by assessing the size of the space.



Linear Undercabinet


Pick linear undercabinet lighting where even illumination and high light levels are desired. It comes complete with 120V direct wire application, eliminating the need for remote power supplies or conversion boxes, and an on-off switch for easy access task lighting.





Tape Lights

Available in various lengths, tape lights can be cut to fit a specific size. Its length, low profile, flexibility for navigating curves, and adhesive backing that sticks to many surfaces makes it ideal for use in hard-to-light areas.



Linear Undercabinet 5-CCT LED



The Hide-a-Lite Linear Undercabinet LED has an elegant design combined with energy efficient LED light, providing the ideal solution for residential and light commercial applications. The clean design of its aluminum housing features a lens that optimizes light distribution, ensuring for proper illumination of the workspace below. The 5-CCT selectable LED light engine offers flexibility in application, allowing the choice of 5 different color temperatures: Warm, Soft, Bright, Cool, Daylight, allowing for the best lighting color to fulfill the design intent of the space. An access plate and quick connect wire connectors make installation easy. Fixture is direct wired. Two armored cable fittings are also included, an onoff switch on the front allows for easy task light illumination.



P700024-028-CS Satin White 9" L, 3.28" W., 1.05" ht. 4w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 228 delivered lumens

(at 3000K).



P700025-028-CS Satin White 11.5" L, 3.28" W., 1.05" ht. 4.5w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 299 delivered lumens (at 3000K).



P700026-028-CS Satin White 17.5" L, 3.28" W., 1.05" ht. 6.5w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 457 delivered lumens (at 3000K).



P700027-028-CS Satin White 23.5" L, 3.28" W., 1.05" ht.

8.5w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 608 delivered lumens (at 3000K).



P700028-028-CS Satin White

35.5" L, 3.28" W., 1.05" ht. 11.5w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90 CRI, 859 delivered lumens (at 3000K).






switch

CCT selector Access plate



connectors











Linear Undercabinet LED





The HIDE-a-LITE™ Linear undercabinet series provides the ideal solution for residential and light commercial applications. The luminaire is constructed from an aluminum housing and features a lens designed to optimize light distribution, ensuring for proper illumination of the work space below. The HIDE-A-LITE linear undercabinet utilizes a through hole mounting method to allow for an easy installation. The luminaire can be direct wired, removing the need for separate cords. Two armored cable fittings are included with the product for applications requiring the use of armored cable. An on/off switch is located on the front of the luminaire, allowing for easy access when used as a task light. The energy efficient LEDs can be dimmed down to 10% with many forward phase (TRIAC) and electronic low voltage (ELV) dimmers.



P70000-020-30 Antique Bronze **P700000-028-30** White 9" L., 3.25" W., 1.13" ht. 4.5w integrated LED, 3000K, 90 CRI, 300 delivered lumens.





P700001-020-30 Antique Bronze **P700001-028-30** White 11.5" L., 3.25" W., 1.13" ht. 7.5w integraged LED, 3000K, 90 CRI, 500 delivered lumens.



P700002-020-30 Antique Bronze **P700002-028-30** White 17.5" L., 3.25" W., 1.13" ht. 12.5w integrated LED, 3000K, 90 CRI, 815 delivered lumens.



P700003-020-30 Antique Bronze **P700003-028-30** White 23.5" L., 3.25" W., 1.13" ht. 15.5w integrated LED, 3000K, 90 CRI, 980 delivered lumens.



P700004-020-30 Antique Bronze **P700004-028-30** White 35.5" L., 3.25" W., 1.13" ht. 20w integrated LED, 3000K, 90 CRI, 1500 delivered lumens.









HIDE a LITE™

Tape Undercabinet System LED

LED Tape provides lighting to enhance aesthetics, while also aiding in tasks around the home. Common applications for LED Tape include; undercabinet lighting in kitchens to add illumination to work surfaces, highlighting back splashes in kitchens or bathroom areas and adding toe kick lighting at the bases of cabinets for dramatic and functional lighting.

LED FEATURES

- Field cuttable at every 4" to end of run.
- · cETLus listed damp location.
- 300 lumens per foot and consumes 4.2 watts per foot (71 lumens/w).
- 90 CRI, 50,000 hr. life.
- 5 year warranty.

Follow Five Simple Steps:

1. Choose Tape Length



12", 60" and 240" lengths to meet different sized projects and features an adhesive backing for easy application to desired surfaces.





Flexible tape can be cut every 4 inches (cut ends can be reconnected, allowing for full use of LED tape).



Tape is fully enclosed in silicone to allow for use in damp location. 24 VDC tape pairs with 24 VDC power supplies.

P700008-000-30 Unfinished 12" L., 0.33" W., 0.13" ht. 3000K











2. Select Transformer

Progress Lighting offers multiple power supplies to meet various project sizes. Power supplies can be dimmed, flicker-free, on Forward Phase (TRIAC) and Reverse Phase (ELV) dimmers down to 10% output.

P700020-031 Black

Max length of tape 60" 8-.19" L., 2" W., 1.75" ht. 25w

P700021-031 Black Max length of tape 120" 8-.19" L., 2" W., 1.75" ht.

P700023-031 Black Max length of tape 240" 9.19" L., 3.33" W., 1.94" ht. 80w



PRODUCT FEATURES

- Maximum operating temperature -20° C to +40° C.
- · Enclosure provided.
- Wire nuts and additional hardware included.

All fixtures:



Tape Undercabinet System LED

3. Additional System Connectors

Various connectors allow for customized layouts. Use linking connectors to join runs of tape. Use the L Connector for 90° bends and use the Y Connector to split one run of tape into two.



Connectors feature piercing conductors for secure connection.



Y, L and multi-linking connectors allow for flexibility in design.





Connectors provided with snap-fit covers for intuitive installation.

2" CONNECTOR CORD P700011-000 Unfinished
2" L., 0.63" W., 0.25" ht.
2" Connector for tape sections:
P700008, P700009, P700010



18" CONNECTOR CORD P700013-000 Unfinished 18" L., 0.63" W., 0.25" ht. 18" Connector for tape sections: P700008, P700009, P700010

36" CONNECTOR CORD P700014-000 Unfinished
36" L., 0.63" W., 0.25" ht.
36" Connector for tape sections:
P700008, P700009, P700010









72" CONNECTOR CORD P700015-000 Unfinished 72" L., 0.63" W., 0.25" ht. 72" Connector for tape sections: P700008, P700009, P700010



Y CONNECTOR P700017-000 Unfinished 3.19" L., 3.19" W., 0.25" ht. Three-way Y connector for connecting sections of tape (P700008, P700009, P700010)

OUTPUT POWER CONNECTOR P700022-000 Unfinished 60" L., 0.63" W., 0.25" ht. Output Power Connector







4. Mounting Clips/End Clips

Select end caps or add mounting clips to finish the installation.

P700018-000 Unfinished 1.13" L., 0.25" W., 0.13" ht. Pack of 10 clips/screws for straight runs for added support (2 clips per foot recommended)



P700019-000 Unfinished 0.5" L., 0.5" W., 0.25" ht. End caps to terminate run of LED tape. For use when tape has been cut at end of run. Sold in sets of 10.



5. Additional Accessories

P7024-31 Black 1" L., 2" W., 0.63" ht. Splicer for LED Tape Undercabinet System with connection between Romex wire and low voltage cable. Includes mounting screws.



766 CATALOG 134

Steps, Corridors & Wall Lights

009 Brushed Nickel



Antique Bronze

Indoor Step Lights LED





Black

The mini-steplights are ideal for indoor residential applications. Energy efficient steplights include both vertical and horizontal louvers and are available in four finishes.

P660003-009-30K Brushed Nickel

2.75" W., 4.5" ht. 1w LED, 3000K, 90 CRI, 12 lumens.





P660003-020-30K Antique Bronze

2.75" W., 4.5" ht. 1w LED, 3000K, 90 CRI, 12 lumens.





P660003-028-30K Satin White

2.75" W., 4.5" ht. 1w LED, 3000K, 90 CRI, 12 lumens.





P660003-031-30K Black

2.75" W., 4.5" ht. 1w LED, 3000K, 90 CRI, 12 lumens.





All fixtures:



Photocell Step Lights LED



Antique Bronze



Black

Add safety and security with these LED steplights.

The integrated photocell automatically turns on and off the fixture with the sunset and sunrise. Great for accenting and lighting outdoor walk ways. These lights include both the horizontal and vertical face plates, allowing distributors to provide more options in fewer skus.

FEATURES

- Includes both horizontal and vertical faceplates
- Integral power supply module in a compact package
- Consumes less than 5w of power per fixture
- · Enclosed in a gasketed lens
- cCSAus listed for wet locations
- Warm white 3000K dimmable LEDs
- 90 CRI

P660006-020-30 Antique Bronze

***P660006-031-30** Black 3" W., 4.75" ht. 4.5w integrated LED





*P660007-020-30 Antique Bronze P660007-031-30 Black

3" W., 4.75" ht. 4.5w integrated LED











Indoor/Outdoor Step & Wall Lights LED





Antique Bronze



(028) Satin White



Black

A horizontal and a vertical exterior face plate are provided to accommodate either a horizontally or vertically oriented installation. The step light features an integrated 120V AC light engine, eliminating the need for an additional LED driver. The light engine is enclosed in a gasketed lens, allowing it to meet the rigorous demands of wet location use.

P660004-009-30 Brushed Nickel

3.12" W., 4.87" ht. 4.5w integrated LED





P660005-009-30 Brushed Nickel

3.03" W., 4.87" ht. 4.5w integrated LED





P660004-028-30 Satin White

3.12" W., 4.87" ht. 4.5w integrated LED





P660005-028-30 Satin White

3.03" W., 4.87" ht. 4.5w integrated LED





P660004-020-30 Antique Bronze

3.12" W., 4.87" ht. 4.5w integrated LED





P660005-020-30 Antique Bronze

3.03" W., 4.87" ht. 4.5w integrated LED





P660004-031-30 Black 3.12" W., 4.87" ht. 4.5w integrated LED





P660005-031-30 Black 3.03" W., 4.87" ht. 4.5w integrated LED









Egress

Combo Exit/Emergency Sign LED

The PECUE Series offers quality and value with a compact and attractive LED based combination emergency exit. The white housing and lamp-heads are made of high impact UL flame rated thermoplastic. Snap together canopy, housing, removable chevrons for quick and easy installation. Universal single or double-face. The remote capacity (-RC) units will run 2 PERHC Series single remote heads or 1 PERHC double remote head.

PECUE-UG-30 White/Green PECUE-UR-30 White/Red 18" W., 7.25" ht. Universal face. 101 lumens.







Exit Sign LED

The PETPE Series offers quality and value with a compact and attractive LED based emergency exit. The white housing is made of high impact UL flame rated thermoplastic. Snap together canopy, housing, removable chevrons for quick and easy installation. Universal single or double-face. Remote capacity (-RC) unit will run 2 PERHC Series single remote heads or 1 PERHC double remote head.

PETPE-UG-30 White/Green PETPE-UR-30 White/Red 11.5" W., 7.25" ht. Universal face. 101 lumens.

PETPE-UG-30-RC White/Green PETPE-UR-30-RC White/Red Remote capacity. 11.5" W., 7.25" ht. Universal face.





Emergency Light LED

The PE2EU Series offers quality and value with a compact and attractive LED based emergency light. The white housing and lamp-heads are fully adjustable and glare-free. Snap together design for quick and easy installation with option for Wall or Ceiling mount. Remote capacity unit will run 2 PERHC Series single remote heads or 1 PERHC double remote head.

PE2EU-30 White 9" W., 4.63" ht. Input 120V or 277V, AC Input. 101 lumens.

PE2EU-30-RC White 9" W., 4.63" ht. Input 120V or 277V, AC Input. 101 lumens.



Indoor/Outdoor Remote Heads LED

The PERHC Series offers quality and value with a compact and attractive LED based remote emergency light. Source-heads are fully adjustable and glare-free. The remote heads are driven by the Progress remote capacity Exit combo or Emergency Light. The Outdoor Remote Source-heads are fully gasketed and weatherproof to ensure operation in wet environments. Must be used with PETPE, PE2EU, and PECUE remote capacity models.

PERHC-SG-ID-30 White 4.6"W., 4.6" ht.



PERHC-DB-ID-30 White 6.7"W.. 4.7" ht.



PERHC-SG-OD-30 White 4.5"W., 4.5" ht.



PERHC-DB-OD-30 White 7.4"W., 4.5" ht.



Normally On/Off Emergency Light LED

The PEOEU Series offers LED performance in "normally on" AC and emergency lighting modes. The unit has a prismatic polycarbonate refractor with a durable die-cast aluminum housing available with durable powder coated finish in Bronze. The housing is fully sealed and gasketed. It is designed for wall mounting with a universal K/O pattern in the back-plate for installation to most standard size junction boxes. Illumination is provided by 2 high power LEDs driven at 3 watts each. LED color at 5500K.

PEOEU-EM-20 Bronze 6.13" W., 10.5" ht. Input 120V or 277V, AC Input. AC Mode-223 lumens. DC Mode-261 lumens. (Running on Emergency Battery) PEOEU-EM-20-HTR Bronze 6.13" W., 10.5" ht. Input 120V or 277V, AC Input. AC Mode-223 lumens. DC Mode-261 lumens. (Running on Emergency Battery)



Reference Guide

Lamp Selection Guide

It's important to note, not all bulbs are created equal. Choosing the right source for your light fixtures can affect the functionality and appearance of your home, as well as your energy bill. Light output, energy efficiency, durability and style greatly vary from source to source. Consider the following five categories, wattage, lumens, efficacy, temperature and style to choose a lamp that helps you meet design and efficiency goals.

Medium Base - E26











Candelabra Base - E12









PIN Base



Bulb Bases

The bulb base is determined by the type of socket in the fixture and is noted on the fixture's catalog page or spec sheet on progresslighting.com.



Medium Base E-26



Candelabra Base F-12




PIN Base

Color Temperature Information

Color temperature refers to the visible color of a white light source, or how the actual light appears to your eye. It is measured on the Kelvin (K) scale, numbered from 1,000 - 10,000.

- Warm light is understood to be up to 3000K (ranges from yellow to reddish)
- Cool light is typically 3500K 5000K and will have hues from blue to white.













2700K Warm White

3000K Soft White

3500K Bright White

4000K Cool White

5000K Daylight

Lumens

Lumens measure the amount of light produced by a bulb. Put simply, the more lumens a light bulb has, the brighter the light. For lights that are further from the area they are lighting (such as downlights in a 12- foot ceiling) – you will want a higher lumen output to ensure functional illumination. For task applications, higher lumen output is also desired to provide bright, direct light over work areas.

Equivalent Light Output

Pay careful attention to the bulb manufacturer's caution statements regarding use in enclosed fixtures or dimmer compatibility.

LEGACY WATTS (W)	TYPICAL LIGHT OUTPUT (LUMENS)	LED EQUIVALENT WATTS (W)
40	450	10
60	800	12.5
75	1,100	15
100	1,600	17.5
150	2,600	20

Foyer Sizing Guides

Foyers

The rule of thumb is to accommodate 2.5 - 3 inches of chandelier height for each foot of ceiling height.

9' - 10' Ceiling

Hang a fixture using a guideline 7-to-7.5 feet should proceed sufficient results.

11' + Ceiling


Divide the vertical space into thirds, positioning the fixture(s) two-thirds of the distance from the floor, so that the ceiling height does not overwhelm the space. If the foyer is large and has a high ceiling, it's recommended to choose a slightly larger fixture than formulas suggest.

*Note confirm that light doesn't interfere with door swing. If it does, place it further back.

Foyer Sizing Recommendations

ROOM WIDTH	Fixture Width			
(smallest rm. dimension)	Max.	Target	Min.	
5′	21"	16.8"	9"	
6'	25.2"	20.2"	10.8"	
7'	29.4"	23.5"	12.6"	
8′	33.6"	26.9"	14.4"	
9'	37.8"	30.2"	16.2"	
10'	42"	33.6"	18"	
11'	46.2"	37"	19.8"	
12'	50.4"	40.3"	21.6"	
13'	54.6"	43.7"	23.4"	
14'	58.8"	47"	25.2"	
15'	63"	50.4"	27"	
16'	63"	53.8"	28.8"	
17'	71.4"	57.1"	30.6"	
18'	75.6"	60.5"	32.4"	

	Fixture Height			
ROOM HEIGHT	Max.	Min.		
8′	12"	-		
9'	24"	-		
10′	30"	18"		
11'	33"	19.8"		
12'	36"	21.6"		
13'	39"	23.4"		
14'	42"	25.2"		
15′	45"	27"		
16′	48"	28.8"		
17′	51"	30.6"		
18'	54"	32.4"		
19'	57"	34.2"		
20′	60"	36"		
21′	63"	37.8"		
22'	66"	39.6"		
23'	69"	41.4"		
24'	72"	43.2"		




Dining Sizing Guides

Dining

The table under the fixture should serve as a guide for selecting the right fixture for your space. To calculate the correct width, start with the width of your table and subtract 12". (For example, if your table is 42" wide, your chandelier should not be more than 30" wide.)

Based on an 8' ceiling, your fixture should hang between 30"-36" above the table.



Dining Sizing Recommendations

		Width		Fixture Height
(smallest rm. dimension)	Max.	Min.	ROOM HEIGHT	Max.
10'	30"	See Notes Below	8′	24"
11'	33"		9'	27"
12'	36"		10'	30"
13'	39"		11′	33"
14'	42"		12'	36"
15'	45"		13'	39"
16'	48"	_	14'	42"
17'	51"	_	15'	45"
18'	54"	_	16′	48"
20'	57"	_	17'	51"
21′	63"	_	18'	54"

Dining Mounting Recommendations

Ceiling Height	Distance from bottom of fixture to table surface
8'	30"
9'	33"
10'	36"
11'	39"
12'	42"
Above 12'	Fixture should be mounted more in relation to the room than to the table

Minimum Width Recommendations: Add width of room + length and use this number as inches

Note: For 10'-0" ceiling heights or below, fixture should not exceed width of table less than 12".

Kitchen Sizing Guides

Kitchen Pendants


Start the row 12"-15" in from either end of the island and then space the pendants evenly within that span.

Space pendants around 24"- 30" apart from one another (depending on style & quantity).

Pendants should be at least 10" smaller in diameter than the width of the countertops. Consider the rule of odd numbers (unless using oversized fixtures).

Keep 30"-36" of space between the countertop and fixtures.

- 8' island = 96"
- 96" 24" (12" from ends of island) = 72"
- 72" 24" 24" = 24"/3 = 8" diameter max. (spaced 24" apart from each other)
- 72" 30" 30" =30"/3 = 4" diameter min. (spaced 30" apart from each other)



Bath Sizing Guides

Single Bowl Vanities


Position fixtures on both sides of the mirror to provide shadow-free lighting for your face. Ideal width is at least 28" apart and centered 66" above the floor, depending on mirror size and ceiling height.

Task Lighting

Center recessed downlights 24" to 36" between where the face and the mirror are at the vanity to eliminate shadows.

Vanities With Two Sinks

Consider mounting two separate fixtures, one above each sink. They should be approximately 75"-80" above the floor.




Outdoor Sizing Guides

Front Door - Wall Lanterns

For a front door with two lanterns, the lantern height should be approximately 1/4 the height of the door. Front doors with one lantern should be approximately 1/3 the height of the door. Mount lanterns approximately 66" above floor for accurate lighting effects.

For a door that is 96" in height, multiply the height by .25 to get 24" for the suggested height of each fixture.



Front Door - Hanging Lanterns

For a front door with a hanging lantern, the lantern height should be approximately 1/5 the height of the door.

Hanging lanterns are hung using chain or stems connections, so be sure to consider the additional length of the chain or stem. The hanging lantern should not hang below 7' from the ground, including the fixture, chain and stem.


Allow 6" minimum clearance from the bottom of the lantern to the top of the door to allow the door to open and close. If there is not enough clearance, consider using a flush mount outdoor fixture. the height of the door.



Garage - Wall Lanterns

If you are installing two or more wall lanterns on the exterior of your garage, the lantern height should be approximately 1/4 the height of the door. For installing a single wall lantern, the height of the fixture should be approximately 1/3 the height of the door.

For a garage door that is 16' in height, multiply the height by .25 to get 4'. Divide 4' by 2 to get 24", which is the suggested height of each fixture.



Icon Guide



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.



Please note dry location products should only be used indoors. Even if an outdoor area or screened-in porch is covered, the fixture can be affected when exposed to humidity. You can, however, "bring the outdoors inside" – as using outdoor products are perfectly acceptable to use in interior spaces.



Damp Location products and fixtures can be used in covered spaces outdoors or indoors.



If the product will have direct contact with water, you'll need to ensure that the product has a "wet" listing. Wet location products may also be used indoors.



This marking indicates fixtures that have an integrated LED or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.enegy.ca.gov



DC motor ceiling fans feature high torque for increased air movement, whisper quiet operation, and greater energy efficiency than AC motors.



Products with this icon can be installed with the shades facing up or down.



Products with this icon can be installed horizontally or vertically.



Products with this icon are suited for wall or ceiling installation.



Products with DURASHIELD, use a high-performance outdoor material that's built to last. Made of composite materials with UV protection for maximum durability in harsh environments – resisting rust, corrosion and fading.



Table 150.0A defines products that do not have to meet JA8 and can be used to comply with 2016 Title 24.



Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at www.appliances.energy.ca.gov.



Products with this icon are Dark-Sky Friendly: in accordance with international dark sky initiatives, these fixtures help to minimize glare while reducing light trespass and skyglow (they don't pollute the night sky.)



Products with this icon have a feature that allows for selectable CCT (correlated color temperature)



Ceiling fans with this icon have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCan.



Complies with American with Disabilities Act



Products with this icon are WiFi compatible and may be controlled with WiFi when one of the following controls is added;

- AC Motor fans can add the P2667-31 WiFi remote control
- DC Motor fans that are WiFi compatible can add the P2673-01 WiFi module.

With the addition of one of the above controls, you may easily control your ceiling fan or light with your smart phone, tablet, voice controls, or hand held remote. Use the Smart by Bond technology to control on/off function of the fan and the light kit along with full range dimming and fan speed control.

Warranty

For more details regarding product warranty coverage, please consult a qualified Progress Lighting distributor or visit:

progresslighting.com/warranty

Where to buy

To purchase Progress Lighting products from one of our authorized dealers visit:

progresslighting.com/where-to-buy

Product Index

P1000				P3000
P1841 741, 742	P250011 433	P2540 390	P2665 456	P300039 574
P1851 740	P250012	P2542	P2666 457	P300040 574
P1871 744	P250016 413	P2544 389	P2667 456	P300041 574
	P250021 382	P2546	P2668 393	P300045 587
	P250024 378	P2548 387	P2669 423	P300046 587
D0000	P250026 369	P2550	P2673 456	P300047 587
P2000	P250028 423	P2552		P300048 587
D0000 057 611	P250030	P2553	P2700 600	P300049 590
P2000 611	P250034 438 P250036 441	P2554	P2701 600 P2702 600	P300050 590 P300051 590
P2002 611	P250058 419	P2556	P2703 600	P300052 590
P2003 611	P250059	P2560	P2706 259, 613	P300066 229, 592
P2004 604	P250060	P2562 443	P2707 613	P300067 592
P2005 604	P250061	P2564 440	P2708 613	P300068 592
P2006 604	P250062 436	P2570 376	P2709 613	P300069 592
P2007 604	P250063 350	P2572 422	P2713 613	P300080 588
P2008 610	P250065 356	P2574 437	P2714 613	P300081 588
P2009 610	P250066 412	P2576 439	P2775 579	P300082 588
P2010 610	P250067 354	P2578 388	P2776 579	P300083 588
P2011 610	P250068 352	P2582 385	P2777 579	P300084 607
P2016 604	P250069 370	P2584	P2781 494, 509	P300085 607
P2018 255, 607	P250070	P2586	P2782 509	P300086 607
P2019 607	P250071	P2588 420, 421	P2794 602	P300087 607 P300093 508
P2020 607 P2021 607	P250072	P2592	P2795 602 P2796 602	P300094 508
P2041 254, 605	P250074	P2599 407	P2797 602	P300095 258, 609
P2060 579	P250075	1 2333	12/3/	P300096 609
P2078 605	P250076 394	P2600 453	P2801 583	P300097 609
P2079 605	P250077 414	P260000 356, 357	P2802 583	P300098 609
P2080 605	P250078 415	P260002 449	P2803 583	P300099 609
P2081 605	P250080 400, 401	P260004 449	P2804 582	P300116 577
	P250081 409	P2601 448	P2809 597	P300117 577
P2131 252, 608	P250082 408	P2602 451	P2851 248	P300118 577
P2143 506	P250084 411	P2603 454		P300119 577
P2144 506	P250085 410	P2604	P2913 611	P300120 169, 171, 576
P2145 506 P2146 253. 600	P250089 392 P250093 397	P2605 454 P2606	P2915 611 P2919 611	P300121 576 P300122 576
P2146 600	P250093	P2606	P2919 611 P2928 611	P300122 576 P300123 576
P2148 600	P250095	P2608 454	P2959 602	P300124 593
P2149 600	P250096	P2609 454	P2977 602	P300125 593
P2158 608	P250097 432	P2610 453	P2978 602	P300126 593
P2159 608	P250098 428	P2611 448	P2989 589	P300131 601
P2160 608	P250099 418	P2612 449	P2991 589	P300132 601
P2165 601	P2501 402, 403	P2613 456	P2992 589	P300133 601
P2166 601	P250100 391	P2618 456	P2997 589	P300134 601
P2167 601	P250101 429	P2628 452	P2998 602	P300137 578
P2168 601	P250102	P2630 456		P300138 578
50700	P250103	P2631 456		P300139 578
P2308 482 P2318 476	P250104	P2636		P300140 578
P2318 476 P2320 476	P2502	P2642 451 P2643 451		P300150 511 P300151 511
1 2020 4/0	P2521 405	P2644		P300151 511
P2500 416	P2524 425	P2645 450		P300155 531
P250000	P2525 424	P2650 450		P300156 531
P250002	P2526 444	P2654 450		P300157 531
P250003	P2530 399	P2659 452		P300158 599
P250007 381	P2531 404	P2661 456		P300159 599
P250008 417	P2533 445	P2662 456		P300160 599
P250009 361	P2539 398	P2663 456		P300161 599

P300182 514	P300291 507	P300381 584	P300456 503	P3401 475
P300183 513	P300295 555	P300382 584	P300457 549	P3405 474
P300184 513	P300296 555	P300383 584	P300458 549	P3406 474
P300185 505	P300297 555	P300384 584	P300459 549	P3408 474, 482
P300186 505	P300298 554	P300385 608	P300460 548	P3410 474
P300187 505	P300299 534	P300386 598	P300461 551	P3412 474
P300188 505	P300300 535	P300387 598	P300462 551	P3423 252
P300189 585	P300304 525	P300388 598	P300463 551	P3424 252
P300191 585	P300305 525	P300389 598	P300464 550	P3447 480
P300203 574	P300306 525	P300390 616	P300465 533	P3448 480
P300205 517	P300312 504	P300391 616	P300466 533	P3450
P300206 517	P300313 504	P300392 616	P300467 533	P3452 466
P300207 517	P300314 580	P300393 616	P300468 532	P3460 469
P300208	P300315 580	P300394 616	P3025 617	P3473
P300209	P300316 580	P300395 559	P3026 617	P3474
P300210	P300317 580	P300396 559	P3027 610	P3475
P300211 519	P300320	P300397 559	P3028 610	P3476
P300212	P300321	P300398	P3029 610	P350005 479
P300213 519	P300322	P300403 521	P3041 610	P350006 479
P300215 149, 553	P300323	P300404	P3051 616	P350007 479
P300216 575	P300327 260, 603	P300405 521	P3052 616	P350008 479
P300217 575	P300328 603	P300406 522	P3053 616	P350022 209, 211, 212, 213
P300218 575 P300222 490	P300329 603	P300407 522	P3054 616	P350037 466
	P300330 603	P300408 523	P3055 616	P350039209, 211, 212, 213
P300223 516	P300331 510	P300409	P3056 616	P350042 244
P300224 516	P300332 510	P300410 520	P3110 614	P350044
P300225 516	P300333 510	P300411 520 P300412 520	P3110 614	P350046
P300226 586	P300341 599		P3111 614 P3114 617	P350049
P300227 586 P300228 586	P300342 599 P300343 599	P300413 545 P300414 545	P3114 617	P350051 478 P350052 478
	P300344 599		P3115 617	P350052 478
P300229 586 P300230 591	P300345 553	P300415 545 P300416 544	P3116 617	P350054 478
P300230 591	P300346 553	P300410 603	P3117 617	P350055 478
P300232 591	P300347 553	P300421	P3161 606	P350056 478
P300233 612	P300348 552	P300423 567	P3162 606	P350057 258
P300234 612	P300349 561	P300424 567	P3163 606	P350059 228, 229
P300235 612	P300350 561	P300425 566	P3164 606	P350060 251
P300236 612	P300351 560	P300426 565	P3184 245	P350061 251
P300237 612	P300356 529	P300427 565	P3190 606	P350070 480
P300238 612	P300357 529	P300428 565	P3191 606	P350071 480
P300239 525	P300358 529	P300429 564	P3192 606	P350074 235
P300240 525	P300359 528	P300430 541	P3193 606	P350075 464
P300243 524	P300360 527	P300431 541		P350076 481
P300244 524	P300361 527	P300432 541	P3203 475	P350077 481
P300253 595	P300362 527	P300433 540	P3267 614	P350078 481
P300254 595	P300363 526	P300434 557	P3268 614	P350085 478
P300255 595	P300368 539	P300435 557	P3269 614	P350086 478
P300256 595	P300369 539	P300436 557	P3287 615	P350088 481
P300257 547	P300370 539	P300437 556	P3288 615	P350098 169, 171
P300258 547	P300371 538	P300438 573	P3289 615	P350100 478
P300259 546	P300372 530	P300439 573	P3290 250	P350101 478
P300272 594	P300373 581	P300440 573	P3298 617	P350107 246
P300273 594	P300374 581	P300441 572	P3299 617	P350110 467
P300274 594	P300375 581	P300442 543		P350117 223
P300275 594	P300376 581	P300443 543	P3300 617	P350129 468
P300277 598	P300377 571	P300444 543	P3311 247	P350130 468
P300278 598	P300378 571	P300445 542	P3312 247	P350132 129, 131
P300279 598	P300379 571	P300454 503	P3333 617	P350134 477
P300290 507	P300380 570	P300455 503	P3335 617	P350135 477

Product Index

			P4000	
P350136 258	P3561 264	P3852 246	P400029 244	P400295 113, 117, 121
P350137 467	P3567 264	P3854 246	P400030 244	P400296 113, 117, 121
P350144 193	P3569 264	P3855 257	P400042	P400297 113, 117, 121
P350146 470	P3573 264	P3864 257	P400043 251	P400300 111, 115, 119
P350147 470	P3575 264	P3876 473	P400044 251	P400301 198, 199, 200, 201
P350148	P3587 257	P3883 704	P400047 209, 211, 212, 213	P400302 199, 201
P350149 161, 163	P3599 475	P3889 215, 216, 217	P400048 209, 211, 212, 213	P400313 150, 151,
P350150 195, 197			P400055 229	
P350151 195, 197	P3605 475	P3912 249	P400057 235	P400314 151, 153, 155
P350153 185, 187	P3610 479	P3914 259	P400058 234, 235	P400315 151, 153, 155
P350167 468	P3611 479	P3924 472	P400062 258	P400316 172, 173, 174, 175
P350168 468	P3612 479	P3925 472	P400063 258	P400317 173, 175
P350169 221	P3620 248	P3926 472	P400064 258	P400325
P350170 471	P3631 476	P3927 472	P400095168, 169, 170, 171	145, 146, 147
P350171 165, 167	P3632 476	P3928 259	P400097	P400326 143, 145, 147
P350172 227	P3633 253	P3929 259	P400118 246	P400340 237, 238, 239
P350178 471	P3644 253	P3931 255	P400119 246	P400341 237, 238, 239
P350179 471	P3648 717	P3942 466	P400158 222, 223	P400342 237, 238, 239
P350181 181	P3649 717	P3951 257	P400159 223	P400343 237, 238, 239
P350183 231	P3650 717	P3977 248	P400177 129, 131	P400348 241, 242, 243
P350195 466	P3658 476	P3991 471	P400178 128, 129, 131	P400349 241, 242, 243
P350197 225	P3663 247	P3992 471	P400190 192, 193	P400350 241, 242, 243
P350198 462	P3683 477		P400193 262	P400351 241, 242, 243
P350199 462	P3688 470		P400194 182, 183	P4008
P350200 461	P3689 470		P400196 183	P4009 262
P350205 466	P3693 254		P400197 160, 161, 163	
P350209 271	P3694 254		P400198 161, 163	P4217 262
P350210 137	P3696 477		P400199 194, 195, 197	P4280 247
P350213 464	P3697 470		P400202 188, 189, 191	P4281 247
P350214 463			P400206 184, 185, 187	
P350217 466	P3701 333		P400207 185, 187	P4318 252
P350218 143, 145, 147	P3706 716		P400209 261	P4319 252
P350219 461	P3709 716		P400210 261	P4324 256
P350220 235	P3712 468		P400218 195, 197	P4328 256
P350224 199, 201	P3713 468		P400225 165, 167	P4329 256
P350226 463	P3720 469		P400226164, 165, 166, 167	P4365 256
P350227 463	P3739 469		P400228 189	
P350229 273	P3740 467		P400243 181	P4401 339
P350230 267	P3748 259		P400250 157	P4402 339
P350231 151, 153, 155	P3753 263		P400251156, 157, 158, 159	P4403 339
P350234 143, 145, 147	P3757 250		P400252 157, 159	P4405 245
P350235 143, 145, 147	P3786 325		P400253 225	P4406 339
P350237 460	P3787 325		P400254 225	P4416 245
P350238 460	P3792 247		P400260 266, 267	P4417 245
P350239 173, 175	P3793 247		P400261 267	P4434 250
P350253 465	P3799 255		P400263 268, 269	P4435 250
P350254 465			P400264 270, 271	P4436 250
P350255113, 117, 121, 461	P3806 256		P400270 141	P4439 250
P350256 627	P3813 614		P400274 260	P4440 259
P350258237, 238, 239, 465	P3816 473		P400275 260	P4441 259
P350259237, 238, 239, 465	P3817 473		P400276 260	P4458 248
P350260	P3818 473		P400286 176, 177, 179	P4459 259
P3509 250	P3821 249		P400287 177, 179	P4489
P3511 471	P3827 215, 216, 217		P400291 202, 203	P4490
P3518 474	P3841 214, 215, 216, 217		P400292 203	P4492
P3520 474	P3843 245		P400293	P4497 257
P3549 471	P3846 248 P3847 245			
	r JU4/ 245		P400294 123, 125, 127	

P5000

	1 3000			
P4609 475	P500018 329	P500238 185, 187	P500381 315	P5167 250
P4610 475	P500019 329	P500239 185, 187	P500382	P5170 252
P4612	P500021	P500240 185, 187	P500383	P5173
P4613 253	P500022	P500241 295	P500284 309	P5180 324
P4618 233	P500023	P500242 295	P500285 308, 309	P5182
				P5183
P4619 248	P500029	P500243 261	P500286	
P4621 249	P500030	P500274 165, 167	P500287	P5184
P4622 249	P500041 209, 211, 212, 213	P500276 283	P500390 151, 153, 155	P5188 322, 323
P4623 249	P500051	P500277 226, 227	P500391 151, 153, 155	P5190
P4625 249	P500052	P500281	P500403	P5196
P4626 248	P500053 321	P500283 143, 145, 147	P500404	P5197 323
P4627 259	P500055	P500284 143, 145, 147	P500405	
P4632 255	P500056 229	P500287 133, 135	P500406	P5202 732
P4635 255	P500061 235	P500288 263	P500409 298	P5203 732
P4638 255	P500065 329	P500302 189	P500410 173, 175	P5207 732
P4695 254	P500068 133	P500303 189	P500411 173, 175	P5212 732
P4696 254	P500069 132, 133, 135	P500307 231	P500415 136, 137, 139	P5214 732
P4697 254	P500071 258	P500308 231	P500416 137, 139	P5270 257
P4699 244	P500090 220, 221	P500309 303	P500429 293	
	P500092 219	P500310 302, 303	P500430 292, 293	P5300 249
P4700 244	P500093 219	P500311 303	P500431 237, 238, 239	P5315 328
P4720 328	P500094 218, 219	P500313 306	P500432 237, 238, 239	P5328 317
P4726 252	P500103 169	P500314 157	P500433 237, 238, 239	P5341 281
P4734 259	P500113 329	P500315 157	P5011	P5390 735
P4735 259	P500125 246	P500316 189	P5012	P5391 735
P4739 255	P500126 246	P500317 225	P5013	P5392 735
P4757 263	P500135	P500318 279	P5024	P5394 735
P4758 248	P500137	P500319 273	P5026	
P4762 263	P500147 280	P500320 273	P5038 264	P540005 735
P4770 263	P500148 280	P500321 269	P5050 323	P540007 710
	P500149	P500324 310	P5065 255	P540010 658
P4961 475	P500152 319	P500325 310	P5066 253	P540011 660
P4962 475	P500156 304	P500329	P5067	P540012 665
	P500157 223	P500333 260	P5068	P540019 705
	P500159 149	P500341 177, 179	P5070	P540020 710
	P500160 148, 149	P500342 177, 179	P5072	P540024 653
	P500176 129, 131	P500343 207	P5078 247	P540028 662
	P500177 129, 131	P500344 206, 207	P5082 244	P540029 669
	P500178 209, 211, 212, 213	P500355 731	P5087	P540030 671
	P500192 193	P500356	P5091	P540031 670
	P500206	P500358 291	P5092	P540032 688
	P500207	P500359 290. 291	P5094	P540033 635
	P500208 161, 163	P500360 113, 117, 121	P5095 256	P540039 638
				P540054 645
	P500209 161, 163	P500361 113, 117, 121	P5096 256	
	P500210 195, 197	P500363 123, 125, 127	DE100 2F0	P540062 636 P540064 632
	P500212	P500365 296	P5108	
	P500213 111, 115, 119	P500366 278	P5110	P540065 637
	P500214 . 110, 111, 115, 118,	P500367 289	P5112	P540068 664
		P500368 288, 289	P5113 259	P540090 641
	P500223 205	P500369 274, 275	P5131	P540093 695
	P500224 205	P500370 275	P5142 215, 216	P540094 659
	P500225 204, 205	P500371 111, 115, 119	P5143	P540095 661
	P500229	P500372 277	P5147 248	P540097 643
	P500230	P500373 276, 277	P5152	P540099 701
	P500231	P500377 199, 201	P5153 245	P540103 684
	P500234 625	P500378 199, 201	P5156 264	P540104 642
	P500235 625	P500379 301	P5158	P540105 652
	P500236 320	P500380 300, 301	P5161 328	P540120 644

Product Index

P540292 650	P550110 650	P560072 721	P560210 719	P5603 714
P5400 654	P550111 626	P560073 721	P560211 719	P5604 714
P5401 705	P550112 717	P560077 662	P560255 650	P5605 654
P5404 672	P550113 717	P560078 662	P560256 650	P5607 709
P5413 692	P550114 717	P560079 662	P560257 650	P5610 654
P5414 712	P550115 717	P560080 669	P560259 721	P5612 713
P5426 713	P550116 684	P560081 669	P560260 721	P5613 654
P5432 707	P550120 644	P560082 669	P560261 667	P5622 702
P5436 713	P550122 701	P560083 671	P560262 667	P5623 702
P5444 712	P550126 628	P560084 671	P560263 691	P5624 692
P5445 704	P550127 628	P560085 671	P560264 661	P5625 692
P5450 677	P550128 623	P560087 635	P560265 661	P5626 713
P5456 711	P550129 623	P560088 635	P560266 661	P5627 678
P5458 704	P550130 623	P560090 722	P560268 666	P5628 698
P5474 675	P550131 624	P560091 687	P560269 666	P5629 698
P5478 713	P550131 624	P560092 710	P560273 643	P5641 725
P5482 706	P550133 651	P560094 670	P560281 659	P5642
P5483 706	P550134 651	P560095 670	P560282 659	P5643
P5487 678	P550135 652	P560096 670	P560283 711	P5644 729
P5493 712	P550136 652	P560097 688	P560286 641	P5645 712
	P550139 730	P560098 688	P560287 641	P5649 677
P550011 665	P550140 730	P560099 698	P560288 711	P5650 677
P550012 665	P550141 649	P560100 689	P560289 711	P5651 677
P550019 691	P550292 650	P560110 658	P560290 727	P5652 677
P550021 710	P5500 654	P560111 658	P560291 727	P5656 711
P550025 668	P5504 672	P560112 658	P560292 728	P5665 692
P550028 662	P5513 692	P560113 660	P560293 728	P5670 675
P550029 669	P5550 676	P560114 660	P560294 729	P5671 675
P550030 671	P5551 702	P560115 660	P560295 729	P5672 675
P550031 670	P5560 695	P560119 705	P560296 703	P5674 723
P550032 688	P5561 695	P560120 705	P560301 703	P5675 726
P550035 700	P5562 676	P560121 705	P560307 695	P5676 715
P550038 658	P5565 708	P560129 653	P560308 695	P5681 706
P550039 658	P5579 697	P560130 653	P560309 695	P5682 706
P550040 660	P5582 706	P560131 653	P560313 644	P5683 706
P550042 705	P5587 678	P560136 715	P560314 644	P5684 706
P550047 653	P5589	P560137 720	P560315 644	P5686 675
P550050 634	1 3303 333	P560148 645	P560316 640	P5687 678
P550054 645	P560029 720	P560149 645	P560317 640	P5688 678
P550061 639	P560035 694	P560150 645	P560321 701	P5689 678
P550062 636	P560036 665	P560156 664	P560322 701	P5690 706
		P560157 664		
P550064 632 P550065 637	P560037 665 P560038 665	P560157 664 P560158 664	P560323 701 P560333 683	P5692 672 P5693 672
P550068 664	P560044 703	P560164 639	P560334 683	P5699 672
P550069 664	P560045 693	P560166 638	P560335 682	55700
P550070 685	P560046 693	P560167 638	P560336 682	P5700 705
P550083 631	P560048 694	P560168 639	P560337 642	P5703 716
P550084 630	P560049 691	P560171 636	P560338 642	P5704 716
P550089 627	P560050 691	P560172 636	P560339 642	P5705 716
P550093 691	P560051 718	P560173 636	P560340 651	P5706 716
P550094 691	P560052 689	P560174 633	P560341 652	P5712 723
P550099 731	P560053 689	P560175 633	P560342 652	P5713 727
P550100 731	P560056 718	P560176 633	P560343 652	P5721 690
P550101 723	P560057 710	P560177 637	P560356 649	P5722 690
P550102 727	P560058 710	P560178 637	P560357 649	P5723 690
P550103 725	P560065 668	P560185 637	P563000 723	P5727 714
P550104 728	P560066 668	P560208 719	P563001 726	P5729 714
P550109 659	P560067 668	P560209 719	P5602 714	P5731 707

	P6000		P7000	
P5737 711	P6000 699	P6436 695	P700000 763	P710090 497
P5738 711	P6001 699	P6437 700	P700001 763	P710093 227
P5741 730	P6002 699	P6440 674	P700002 763	P710094 486
P5744 714	P6019 708	P6452 655	P700003 763	P710095 486
P5745 714	P6023 699		P700004 763	P710097 181
P5749 697	P6030 663	P6520 692	P700008	P710102 497
P5750 697	P6031	P6529 701	P700009	P710103
P5753 673	P6032	P6531 663	P700010	P710104 488
P5754 673 P5755 673	P6038 692 P6039 692	P6533 700 P6537 700	P700011 765 P700012 765	P710105 493, 504 P710106 123, 125, 127
P5756 707	P6043 695	P0337 700	P700013 765	P710100 123, 125, 127 P710107 123, 125, 127
P5758 707	P6050 695	P660003 766	P700014 765	P710109 199, 201
P5762 708	P6052 655	P660004 767	P700015 765	P710110 521
P5764 699	P6053 655	P660005 767	P700016 765	P710111113, 117, 121, 489
P5765 708	P6054 655	P660006 766	P700017 765	P710114143, 145, 147, 536
P5767 708	P6055 655	P660007 766	P700018 765	P710115 596
P5770 708	P6056 647	P6610 700	P700019 765	P710116 596
P5773 709	P6057 647	P6611 700	P700020 764	P710118 490
P5774 730	P6058 647	P6612 700	P700021 764	P7103 491
P5777 709	P6059 698	P6615 700	P700022 765	P7112 491
P5788 473	P6060 698	P6616 700	P700023	P7149 244
P5789 473	P6062 693	P6617 700	P700024	P7153 491
P5800 718	P6063 693 P6064 693	P6630 674 P6631 674	P700025 762 P700026 762	P7156 597 P7170 264
P5801	P6067 646	P0031 6/4	P700027	P7170
P5806 718	P6068 646		P700028	P7181 245, 491
P5813	P6069 646		P7024 765	P7185 491
P5814 712	P6070 701		P7083 496	
P5815 712	P6071 701		P7085 496	P7249 480
P5817 713	P6072 701		P7088 496	P7250 480
P5826 710	P6073 696		P7092 496	P7251 480
P5831 707	P6074 696		P7093 496	P7253 480
P5844 713	P6075 696			P7278 483
P5846 707	P6077 696		P710010 496	P7279 483
P5862 704	P6078 696		P710012	5770000
P5863 704 P5864 704	P6079 696			P730000 483
P5875 677	P6084 680, 681 P6085 680, 681		P710015 193, 575 P710031 221, 593	P730001 483 P730002 482
P5878 705	P0063 060, 061		P710036 497	P730002 482
P5895 648	P6144 758		P710045 488	P730005 482
P5896 648	P6147		P710047 492, 511	P730006 482
P5899 648	P6149 758		P710049 492, 514	P730007 482
	P6155 759		P710050 493, 513	P730008 482
P5907 699	P6160 758		P710051 283, 512	P730011 483
P5948 694	P6162 759		P710052 283, 512	P730012 483
P5949 694	P6397 759		P710071 497	
P5968 733			P710072 490	
P5969	P6404 679		P710073 161, 163, 547	
P5970	P6417 708		P710074 195, 197	
P5985 709	P6424 680, 681		P710080 494	
P5986 709 P5987 679	P6425 696 P6427 646		P710081 494 P710082 261. 598	
P5988 679	P6428 645		P710082 486	
P5989 679	P6429 701		P710085 486	
	P6430 696		P710086 488	
	P6431 663		P710087 489	
	P6432 673		P710088 489	
	P6433 700		P710089 165, 167	

Product Index

P8000		P9000
P800002	P8400	P900011
	P8403 341	P900012
P800018740, 741,	P8404 341	P900013 757
		P900014 757
P800019740, 741,		
743, 744, 746	P841 741	
P800020 743	P8475 741	PC - PT
P800021 743		
P800022 739, 747	P851 740	PC001
P804000 739	P8555 748	PE2EU
P804001 739	P8585 748	PECUE
P804002 739	P8587 748	PEOEU
P804003 739	P8595 752	PERHC
P804004 739		PETPE 768
P804N 739	P860004 341	PTORK3010
P806000 743	P860042 342	
P806001 743	P860045 726	
P806002 743	P860046 728	
P806003 743	P860047 729	
P806004 743	P860048 755	
P806005 743	P860049 755	
P806006 744	P860050 755	
P806007 744	P860051 755	
P806008 745	P860052	
P8061 742	P860053	
P806A 745	P860054	
P806N	P860055	
P806S	P860058	
P807000	P860059	
P807001	P860060	
P807002	P860061	
P807003 738	P860062	
P810012 750	P8602	
P810013	P8625	
P810014	P8678 343	
P810015	P867 741	
P810016	P868 740	
P810017 754	P8685 343	
P810018		
P810019 753	P8709 734	
P810020	P871 744	
P810021 753	P8726 734	
P810024	P8741 730	
P810027 751	P8748 734	
P810029	P8755 342	
P810032	P8757 342	
P810033 752	P8758 342	
P810035 750	P876 741	
P8147 752		
	P8926 342	
P8222		
P8247		
P8268 740		

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2023 All rights reserved. International copyright secured.







A proud member of the Hubbell family.

PROGRESS LIGHTING 701 Millennium Boulevard Greenville, South Carolina 29607

