


Straight Blade Devices



60 Amp Industrial Grade Plugs and Receptacles

60A 125/250V AC, 3Ø 250V AC and 3ØY 120/208V AC Plugs and Receptacles Inches (mm)



Device Type		Plug		Receptacle
		Standard	Angle 12 Position	Flush
Cord Diameter		.425"-1.320" (10.8-33.5)	.625"-1.380" (15.9-35.1)	
Rating	Color	Thermoplastic	Nylon	Reinforced Black Thermoplastic Polyester
NEMA 14-60, 60A 125/250V 3-Pole 4-Wire	Black/White	9460NP	9462ANPB	9460FR
NEMA 15-60, 60A 3Ø 250V AC 3-Pole 4-Wire	Black/White	8460NP	8462ANPB	8460FR
NEMA 18-60, 60A 3ØY 120/208V AC 4-Pole 4-Wire	Black/White	—	8362ANPB*	8360FR*

Stainless Steel Wallplate
For Flush Receptacles

Descriptor	Catalog Number
2-gang, 1-single 2.40" (63.0) diameter hole	SS701

Note: *Device has no provision for a grounding conductor. Intended for use in applications where a separate grounding means is provided.
Receptacles fit standard boxes 4¹/₁₆ in. square and not less than 2.23 in. (54.0) deep.

Product Dimensions Inches (mm)

	Plug	Angled Plug	Receptacle
A	2.88" (73.0)	3.25" (82.6)	2.25" (57.2)
B	4.13" (104.8)	4.19" (106.4)	3.68" (93.5)
C	—	1.75" (82.6)	2.12" (54.0)
D	—	—	2.50" (63.3)
E	—	—	2.37" (60.3)
F	—	—	1.81" (46.0)

