

Straight Blade Devices



Industrial Grade Extra Heavy Duty, Specification Grade Duplex Receptacles



- Nylon construction with Circuit ID marking area
- Heavy duty nickel and brass plated steel wrap-around yoke
- Heavy duty, copper-alloy self-grounding system
- UL Listed, CSA Certified, Complies with NEMA® Standards WD-1 and WD-6, Listed to UL 498, Verified under Federal Specification WC596

The BRY5362 Design

The one-piece ground system provides a more reliable continuity to ground than riveted designs. Triple-wipe brass line contacts deliver excellent conductivity for low resistance, low heat rise. Superior spring properties provide reliable, long-life blade retention. All nylon, wrap-around, full-face design provides secure assembly, even under stress.

15A and 20A 125V and 250V Receptacles, Back and Side Wired



Rating	Color	Duplex		Color	Isolated Ground		Color	Corrosion Resistant
		Standard	Weather Resistant		Standard	Weather Resistant		Standard
NEMA 5-15, 15A 125V 	Black	BRY5262BLK	BRY5262BLKWR	Brown Gray Ivory Orange White	BRY5262IGB BRY5262IGGRY BRY5262IGI BRY5262IG BRY5262IGW	— BRY5262IGGRYWR BRY5262IGIWR BRY5262IGWR BRY5262IGWWR	Brown Yellow	BRY5262BCR BRY5262CR
	Blue	BRY5262BU	BRY5262BUWR					
	Brown	BRY5262	BRY5262WR					
	Gray	BRY5262GRY	BRY5262GRYWR					
	Ivory	BRY5262I	BRY5262IWR					
Red	BRY5262RED	BRY5262REDWR						
White	BRY5262W	BRY5262WWR						
NEMA 5-20, 20A 125V 	Black	BRY5362BLK	BRY5362BLKWR	Brown Gray Ivory Orange White	BRY5362IGB BRY5362IGGRY BRY5362IGI BRY5362IG BRY5362IGW	— BRY5362IGGRYWR BRY5362IGIWR BRY5362IGWR BRY5362IGWWR	Yellow	BRY5362CR
	Blue	BRY5362BU	BRY5362BUWR					
	Brown	BRY5362	BRY5362WR					
	Gray	BRY5362GRY	BRY5362GRYWR					
	Ivory	BRY5362I	BRY5362IWR					
Red	BRY5362RED	BRY5362REDWR						
White	BRY5362W	BRY5362WWR						
NEMA 6-15, 15A 250V 	Black	BRY5662BLK	—	Orange	BRY5662IG	—	Yellow	BRY5662CR
	Brown	BRY5662	—					
	Gray	BRY5662GRY	—					
	Ivory	BRY5662I	—					
	Red	BRY5662RED	—					
White	BRY5662W	—						
NEMA 6-20, 20A 250V 	Black	BRY5462BLK	—	Orange	BRY5462IG	—	Yellow	BRY5462CR
	Brown	BRY5462	—					
	Gray	BRY5462GRY	—					
	Ivory	BRY5462I	—					
	Red	BRY5462RED	—					
White	BRY5462W	—						

Note: See page R-6 for weather resistant description. See page A-28 for technical specifications.

See Section C for isolated ground products. See page R-6 for weather resistant description.

See Section I for corrosion-resistant products.

15A and 20A 125V Specialty Receptacles

Inches (mm)

Rating	Description	Color	Catalog Number
NEMA 5-15, 15A 125V	BRY5262 on 4.0" (101.6) round metal box cover	Brown	BRY5282
NEMA 5-20, 20A 125V	BRY5362 on 4.0" (101.6) round metal box cover	Brown	BRY5382

NEMA® is a registered trademark of the National Electrical Manufacturers Association.



Product Dimensions

Inches (mm)

A	4.06" (103.1)
B	3.28" (83.3)
C	1.54" (39.1)
D	1.16" (29.5)

