



- Weatherproof receptacle lift covers
- Available with six 20A straight blade or locking receptacles
- Features 50A locking input and output
- Over current protection for each circuit
- Individual GFCI module for each receptacle
- Nested leg design allows boxes to be easily stacked
- UL Type 3R for outdoor rainproof applications

### Temporary Power Distribution Boxes

Rating	Type	Qty	Receptacle Ratings	Protection Overload	GFCI Protected	Catalog Number
50A 120/240V AC (Max.)	Straight Blade	6	20A 125V	Yes	Yes	<b>TPDSB</b>
	Locking	1	30A 250V	Yes	No	
	Locking (inlet)	1	50A 125/250V	No	No	
	Locking (outlet)	1	50A 125/250V	No	No	
50A 120/240V AC (Max.)	Locking	6	20A 125V	Yes	Yes	<b>TPDLB</b>
	Locking	1	30A 250V	Yes	No	
	Locking (inlet)	1	50A 125/250V	No	No	
	Locking (outlet)	1	50A 125/250V	No	No	

### Cable Sets



Description	50 Ft. Cable	100 Ft. Cable
50A cord set, #6/3, #8/1 cable type, with 50A locking plug and connector, not UL Listed or CSA Certified	<b>TPC50B*</b>	<b>TPC100B*</b>

### Replacement Parts



Description	20A 125V	30A 250V	50A 125/250V
Straight blade receptacle	<b>CRS20</b>	—	—
Locking receptacle	—	<b>70530FR</b>	<b>CS6369L</b>
Plug	—	—	<b>CS6365L</b>
Connector	—	—	<b>CS6364L</b>
Inlet	—	—	<b>CS6375L</b>
Weather protective plate for receptacle	<b>RW51470</b>	<b>7420B</b>	<b>7774CR</b>
Weather protective plate for inlet	—	—	<b>7780</b>

### Product Dimensions Inches (mm)

TPD Box	
A	12.52" (317.9)
B	10.23" (259.8)
C	14.50" (368.3)
D	21.50" (546.1)

