



## Commercial Standard and Hospital Grade GFCI Receptacles





### Features


- Patented CIRCUITPRO® self-test technology includes disconnecting power to the receptacle if critical components are damaged and GFCI protection is lost
- Internal back wiring clamp and guide for quick and secure termination
- Night light option includes light sensor controls for automatic ON and OFF, custom dual lens for optimum light output
- Fed. Spec. UL Listed (Hospital Grade)





### Standard

Rating	Color	Standard	Night Light Two LED Night Lights	Alarm	Blank Face Available in 20A Only	Standard 3-Pack Three Devices per Pack
NEMA 5-15, 15A 125V 	Black	GFRST15BK	GFRST15BKNL	GFRST15BKB	—	—
	Brown	GFRST15	GFRST15NL	GFRST15B	—	—
	Gray	GFRST15GY	GFRST15GYNL	GFRST15GYB	—	—
	Ivory	GFRST15I	GFRST15INL	GFRST15IB	—	GFRST15I3
	Light Almond	GFRST15LA	GFRST15LANL	GFRST15LAB	—	GFRST15LA3
	Red	GFRST15R	GFRST15RNL	GFRST15RB	—	—
White	GFRST15W	GFRST15WNL	GFRST15WB	—	GFRST15W3	
NEMA 5-20, 20A 125V 	Black	GFRST20BK	GFRST20BKNL	GFRST20BKB	GFBFST20BK	—
	Brown	GFRST20	GFRST20NL	GFRST20B	GFBFST20	—
	Gray	GFRST20GY	GFRST20GYNL	GFRST20GYB	GFBFST20GY	—
	Ivory	GFRST20I	GFRST20INL	GFRST20IB	GFBFST20I	GFRST20I3
	Light Almond	GFRST20LA	GFRST20LANL	GFRST20LAB	GFBFST20LA	GFRST20LA3
	Red	GFRST20R	GFRST20RNL	GFRST20RB	GFBFST20R	—
White	GFRST20W	GFRST20WNL	GFRST20WB	GFBFST20W	GFRST20W3	

### Hospital Grade ●



Rating	Color	Standard0	Night Light Two LED Night Lights	Alarm
NEMA 5-15, 15A 125V 	Black	GFST82BK	GFST82BKNL	GFST82BKB
	Brown	GFST82	GFST82NL	GFST82B
	Gray	GFST82GY	GFST82GYNL	GFST82GYB
	Ivory	GFST82I	GFST82INL	GFST82IB
	Light Almond	GFST82LA	GFST82LANL	GFST82LAB
	Red	GFST82R	GFST82RNL	GFST82RB
White	GFST82W	GFST82WNL	GFST82WB	
NEMA 5-20, 20A 125V 	Black	GFST83BK	GFST83BKNL	GFST83BKB
	Brown	GFST83	GFST83NL	GFST83B
	Gray	GFST83GY	GFST83GYNL	GFST83GYB
	Ivory	GFST83I	GFST83INL	GFST83IB
	Light Almond	GFST83LA	GFST83LANL	GFST83LAB
	Red	GFST83R	GFST83RNL	GFST83RB
White	GFST83W	GFST83WNL	GFST83WB	

### Product Dimensions Inches (mm)

	GFCI Receptacle
A	3.27" (83.1)
B	2.75" (69.8)
C	1.75" (44.5)
D	1.47" (37.4)
E	1.10" (27.9)

