

Manual Set Portable GFCI Line Cords



- Easy-to-operate sealed key pad
- High-impact PVC watertight housing
- SJTW-A cord #14/3
- Sealed molded plug
- Bright fault light

Portable GFCI Line Cords

Portable GFCI Line Cords provide ground fault protection both indoors and out. They interrupt electrical power to protect personnel when leakage to ground is 4-6 milliamperes. Available in lengths of 18 inches (45.7 cm), 6 feet (182.9 cm), and 25 feet (762.0 cm). A 15 feet (457.2 cm) OEM version with stripped leads is also available. They are offered with Manual Set feature to meet your application.

IP20
SUITABILITY

Manual Set Portable GFCI Line Cords Feet (cm)



Description	18 In. (45.7)	6' (182.9)	25' (762.0)
15A 120V AC, #14-3 SJTW-A	GFPST4C15A	GFPST6C15A	GFPST25C15A

QUADPLEX® Ground Fault Cord Sets Feet (cm)



Description	6' (182.9)
15A 120V AC 12/3 SJO cord, pilot light, yellow, thermoplastic	T1254GF6

Product Dimensions Inches (mm)

GFCI Line Cord	
A	18.00" (457.2)
B	5.19" (131.8)
C	2.56" (65.0)
D	1.58" (40.1)
E	9.00" (228.6)

