

Portable GFCI Products



- Available with an automatic or manual “safe start” reset feature
- Single and triple power tap configurations
- Recessed “test and reset” buttons
- LED indicates power and fault status

GFCI In-Line – Single & Triple Tap 15A

This In-Line Ground Fault Circuit Interrupter is rated for 15 Amps at 120V AC. Product is available with an automatic or manual “safe start” reset features. Product variations include single and triple power tap configurations. Recessed “test and reset” buttons avoid accidental contact during handling and use. LED indicates power and fault status at a glance. Heavy duty construction is rated NEMA 3R.

Portable GFCI Feet (cm)



Description	Set	GFCI Line Cord			In-Line GFCI	
		Single Tap		Triple Tap	Single Tap	Triple Tap
		2' (61.0)	25' (762.0)	2' (61.0)	2' (61.0)	2' (61.0)
15A 120V AC, 12/3 SJEOW	Automatic	GFC2A	—	GFC2TRIA	GFC15125A	GFC15125TRIA
	Manual	GFC2M	GFC25M	GFC2TRIM	GFC15125M	GFC15125TRIM

OEM Equipment Integrated Cord Sets Feet (cm)



Description	Set	GFCI with Flying Leads 15 (457.2)	Field Wireable Black Plug
15A 120V AC, 14/3 SJEOW	Automatic	GFCL15A	GFP15A
	Manual	—	GFP15MA

Product Dimensions Inches (mm)

GFCI Plug	
A	5.16" (131.0)
B	4.25" (108.0)
C	1.72" (43.7)
D	1.90" (48.3)
E	1.06" (26.8)

